

H11D1X, H11D2X, H11D3X, H11D4X
H11D1, H11D2, H11D3, H11D4



ISOCOM
COMPONENTS

**HIGH VOLTAGE OPTICALLY
COUPLED ISOLATOR
PHOTOTRANSISTOR OUTPUT**



'X' SPECIFICATION APPROVALS

- VDE0884 in 3 available lead forms :-
- STD
- G form
- SMD approved to CECC 00802

DESCRIPTION


The H11D series of optically coupled isolators consist of infrared light emitting diode and NPN silicon photo transistor in a standard 6 pin dual in line plastic package.

FEATURES

- Options :-
10mm lead spread - add G after part no.
Surface mount - add SM after part no.
Tape&reel - add SMT&R after part no.
- High Isolation Voltage (5.3kV_{RMS}, 7.5kV_{PK})
- High BV_{CER} (300V - H11D1, H11D2)
(200V - H11D3, H11D4)
- All electrical parameters 100% tested
- Custom electrical selections available

APPLICATIONS

- DC motor controllers
- Industrial systems controllers
- Measuring instruments
- Signal transmission between systems of different potentials and impedances



ABSOLUTE MAXIMUM RATINGS
(25°C unless otherwise specified)

| | |
|----------------------------|---|
| Storage Temperature | -55°C to +150°C |
| Operating Temperature | -55°C to +100°C |
| Lead Soldering Temperature | (1/16 inch (1.6mm) from case for 10 secs) 260°C |

INPUT DIODE


| | |
|-------------------|-------|
| Forward Current | 60mA |
| Reverse Voltage | 6V |
| Power Dissipation | 100mW |

OUTPUT TRANSISTOR

| | |
|---|-------|
| Collector-emitter Voltage BV _{CER} (R _{BE} = 1MΩ) | |
| H11D1, H11D2 | 300V |
| H11D3, H11D4 | 200V |
| Collector-base Voltage BV _{CBO} | |
| H11D1, H11D2 | 300V |
| H11D3, H11D4 | 200V |
| Emitter-collector Voltage BV _{ECO} | 6V |
| Collector Current | 100mA |
| Power Dissipation | 150mW |

POWER DISSIPATION

| | |
|--|-------|
| Total Power Dissipation | 250mW |
| (derate linearly 2.67mW/°C above 25°C) | |



ISOCOM COMPONENTS 2004 LTD
Unit 25B, Park View Road West,
Park View Industrial Estate, Brenda Road
Hartlepool, TS25 1UD England
Tel: (01429)863609 Fax: (01429)863581 e-mail
sales@isocom.co.uk http://www.isocom.com

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ Unless otherwise noted)

| PARAMETER | | MIN | TYP | MAX | UNITS | TEST CONDITION |
|--------------------------------|---|--------------------|-----|---------------|------------------|--|
| Input | Forward Voltage (V_F) | | 1.2 | 1.5 | V | $I_F = 10\text{mA}$ |
| | Reverse Current (I_R) | | | 10 | μA | $V_R = 6\text{V}$ |
| Output | Collector-emitter Breakdown (BV_{CER}) H11D1, H11D2 | 300 | | | V | $I_C = 1\text{mA}, R_{\text{BE}} = 1\text{M}\Omega$ (note 2) |
| | H11D3, H11D4 | 200 | | | V | |
| | Collector-base Breakdown (BV_{CBO}) H11D1, H11D2 | 300 | | | V | $I_C = 100\mu\text{A}$ |
| | H11D3, H11D4 | 200 | | | V | |
| | Emitter-collector Breakdown (BV_{ECO}) | 6 | | | V | $I_E = 100\mu\text{A}$ |
| | Collector-emitter Dark Current (I_{CER}) H11D1, H11D2 | | | 100 | nA | $V_{\text{CE}} = 200\text{V}, R_{\text{BE}} = 1\text{M}\Omega$ $V_{\text{CE}} = 200\text{V}, R_{\text{BE}} = 1\text{M}\Omega,$ $T_A = 100^\circ\text{C}$ |
| H11D3, H11D4 | | | 250 | μA | | |
| Coupled | Current Transfer Ratio (CTR) | 20 | | | % | $10\text{mA } I_F, 10\text{V } V_{\text{CE}},$ $R_{\text{BE}} = 1\text{M}\Omega$ |
| | Collector-emitter Saturation Voltage $V_{\text{CE(SAT)}}$ | | | 0.4 | V | |
| | Input to Output Isolation Voltage V_{ISO} | 5300 | | | V_{RMS} | $10\text{mA } I_F, 0.5\text{mA } I_C,$ $R_{\text{BE}} = 1\text{M}\Omega$ See note 1 |
| | | 7500 | | | V_{PK} | |
| | Input-output Isolation Resistance R_{ISO} | 5×10^{10} | | | Ω | $V_{\text{IO}} = 500\text{V}$ (note 1) |
| | Turn-on Time t_{on} | | 5 | | μs | $V_{\text{CC}} = 10\text{V}, I_C = 2\text{mA},$ $R_L = 100\Omega$, fig 1 |
| Turn-off Time t_{off} | | 5 | | μs | | |

Note 1 Measured with input leads shorted together and output leads shorted together.

Note 2 Special Selections are available on request. Please consult the factory.






FIG 1


Collector Power Dissipation vs. Ambient Temperature




Relative Current Transfer Ratio vs. Forward Current (normalised to 10mA I_F)




Forward Current vs. Ambient Temperature



Relative Current Transfer Ratio vs. Ambient Temperature



Forward Voltage vs. Forward Current



Collector-base Current vs. Ambient Temperature

