# **ESD Protection Diode Array**

# **Dual Common Anode**

These dual monolithic silicon zener diodes are designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. Their dual junction common anode design protects two separate lines using only one package. These devices are ideal for situations where board space is at a premium.

## **Specification Features:**

- SOT-23 Package Allows Either Two Separate Unidirectional Configurations or a Single Bidirectional Configuration
- Working Peak Reverse Voltage Range 12 V
- Standard Zener Breakdown Voltage Range 13.3 V to 15.75 V
- Peak Power 300 Watt (8 X 20 μs)
- Low Leakage
- Flammability Rating UL 94 V–0

## **Mechanical Characteristics:**

CASE: Void-free, transfer-molded, thermosetting plastic case FINISH: Corrosion resistant finish, easily solderable MAXIMUM CASE TEMPERATURE FOR SOLDERING PURPOSES:

260°C for 10 Seconds


Package designed for optimal automated board assembly Small package size for high density applications Available in 8 mm Tape and Reel

Use the Device Number to order the 7 inch/3,000 unit reel. Replace the "T1" with "T3" in the Device Number to order the 13 inch/10,000 unit reel.



# **ON Semiconductor**<sup>™</sup>

#### www.onsemi.com



## **ORDERING INFORMATION**

Device	Package	Shipping		
SM12T1	SOT-23	3000/Tape & Reel		

## **MAXIMUM RATINGS**

Rating	Symbol	Value	Unit	
Peak Power Dissipation @ 20 $\mu s$ (Note 1) @ $T_L \leq 25^\circ C$	P <sub>pk</sub>	300	Watts	
IEC 61000–4–2 (ESD)	Air ontact	±15 ±8.0	kV	
IEC 61000–4–4 (EFT)		40	А	
IEC 61000-4-5 (Lightening)		12	А	
Total Power Dissipation on FR-5 Board (Note 2) @ T <sub>A</sub> = 25°C Derate above 25°C	PD	225 1.8	mW mW/°C	
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	556	°C/W	
Total Power Dissipation on Alumina Substrate (Note 3) @ $T_A = 25^{\circ}C$ Derate above 25°C	PD	300 2.4	mW mW/°C	
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	417	°C/W	
Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	– 55 to +150	°C	
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260	°C	


1. Non-repetitive current pulse per Figure 3 2. FR-5 =  $1.0 \times 0.75 \times 0.62$  in. 3. Alumina =  $0.4 \times 0.3 \times 0.024$  in., 99.5% alumina \*Other voltages may be available upon request

**ELECTRICAL CHARACTERISTICS** 

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$ 

UNIDIRECTIONAL (Circuit tied to Pins 1 and 3 or 2 and 3)

Symbol	Parameter			
I <sub>PP</sub>	Maximum Reverse Peak Pulse Current			
V <sub>C</sub>	Clamping Voltage @ I <sub>PP</sub>			
V <sub>RWM</sub>	Working Peak Reverse Voltage			
I <sub>R</sub>	Maximum Reverse Leakage Current @ V <sub>RWM</sub>			
V <sub>BR</sub>	Breakdown Voltage @ I <sub>T</sub>			
Ι <sub>Τ</sub>	Test Current			
$\Theta V_{BR}$	Maximum Temperature Coefficient of $V_{BR}$			
١ <sub>F</sub>	Forward Current			
V <sub>F</sub>	Forward Voltage @ I <sub>F</sub>			
Z <sub>ZT</sub>	Maximum Zener Impedance @ I <sub>ZT</sub>			
I <sub>ZK</sub>	Reverse Current			
Z <sub>ZK</sub>	Maximum Zener Impedance @ I <sub>ZK</sub>			



### **ELECTRICAL CHARACTERISTICS**

				V <sub>BR</sub> , Breakdown Voltage		V <sub>C</sub> @	Max Ipp	Typical Capacitance
	Device	V <sub>RWM</sub>	I <sub>R</sub> @ V <sub>RWM</sub>	(Volts)		I <sub>PP</sub> = 1 Amp	(Note 4)	(pF)
Device	Marking	(Volts)	(μΑ)	Min	Max	(Volts)	(Amps)	Pin 1 to 3 @ 0 Volts
SM12T1	12M	12	1.0	13.3	15.75	19	12	95

4.  $8\times 20~\mu s$  pulse waveform per Figure 3

# SM12T1






Figure 1. Non-Repetitive Peak Pulse Power versus Pulse Time

Figure 2. Steady State Power Derating Curve




Figure 4. Typical Diode Capacitance


# SM12T1

# **TYPICAL COMMON ANODE APPLICATIONS**


A quad junction common anode design in a SOT-23 package protects four separate lines using only one package. This adds flexibility and creativity to PCB design especially

when board space is at a premium. Two simplified examples of surge protection applications are illustrated below.

# **Computer Interface Protection**




### **Microprocessor Protection**



# **INFORMATION FOR USING THE SOT-23 SURFACE MOUNT PACKAGE**

### MINIMUM RECOMMENDED FOOTPRINT FOR SURFACE MOUNTED APPLICATIONS

Surface mount board layout is a critical portion of the total design. The footprint for the semiconductor packages must be the correct size to insure proper solder connection interface between the board and the package. With the correct pad geometry, the packages will self align when subjected to a solder reflow process.





### SOT-23 POWER DISSIPATION

The power dissipation of the SOT-23 is a function of the drain pad size. This can vary from the minimum pad size for soldering to a pad size given for maximum power dissipation. Power dissipation for a surface mount device is determined by  $T_{J(max)}$ , the maximum rated junction temperature of the die,  $R_{\theta JA}$ , the thermal resistance from the device junction to ambient, and the operating temperature,  $T_A$ . Using the values provided on the data sheet for the SOT-23 package,  $P_D$  can be calculated as follows:

$$P_{D} = \frac{T_{J(max)} - T_{A}}{R_{\theta JA}}$$

The values for the equation are found in the maximum ratings table on the data sheet. Substituting these values into the equation for an ambient temperature  $T_A$  of 25°C, one can calculate the power dissipation of the device which in this case is 225 milliwatts.

$$P_{D} = \frac{150^{\circ}C - 25^{\circ}C}{556^{\circ}C/W} = 225 \text{ milliwatts}$$

The 556°C/W for the SOT–23 package assumes the use of the recommended footprint on a glass epoxy printed circuit board to achieve a power dissipation of 225 milliwatts. There are other alternatives to achieving higher power dissipation from the SOT–23 package. Another alternative would be to use a ceramic substrate or an aluminum core board such as Thermal Clad<sup>®</sup>. Using a board material such as Thermal Clad, an aluminum core board, the power dissipation can be doubled using the same footprint.

### SOLDERING PRECAUTIONS

The melting temperature of solder is higher than the rated temperature of the device. When the entire device is heated to a high temperature, failure to complete soldering within a short time could result in device failure. Therefore, the following items should always be observed in order to minimize the thermal stress to which the devices are subjected.


- Always preheat the device.
- The delta temperature between the preheat and soldering should be 100°C or less.\*
- When preheating and soldering, the temperature of the leads and the case must not exceed the maximum temperature ratings as shown on the data sheet. When using infrared heating with the reflow soldering method, the difference shall be a maximum of 10°C.
- The soldering temperature and time shall not exceed 260°C for more than 10 seconds.
- When shifting from preheating to soldering, the maximum temperature gradient shall be 5°C or less.
- After soldering has been completed, the device should be allowed to cool naturally for at least three minutes. Gradual cooling should be used as the use of forced cooling will increase the temperature gradient and result in latent failure due to mechanical stress.
- Mechanical stress or shock should not be applied during cooling.

\* Soldering a device without preheating can cause excessive thermal shock and stress which can result in damage to the device.

## SM12T1

#### PACKAGE DIMENSIONS

SOT-23 (TO-236) CASE 318-08 ISSUE AR



Thermal Clad is a registered trademark of the Bergquist Company

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights or others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconducts harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: <u>SM05T1G</u> <u>SM12T1G</u>