
MI0603J680R-10

UNCONTROLLED DOCUMENT

PHYSICAL DIMENSIONS:



ELECTRICAL CHARACTERISTICS:										
Z @ 100M (Ω)	1Hz	DCR (Ω)	Rated Current							
Nominal	68									
Minimum	51									
Maximum	85	0.10	1000 mA							


NOTES: UNLESS OTHERWISE SPECIFIED

- 1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 4000 PCS/REEL.
- 2. TERMINATION FINISH IS 100% TIN.
- 3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
- 4. OPERATING TEMP. RANGE: -40°C~+125°C. (INCLUDING SELF-HEATING)


Z vs FREQUENCY
IMPEDANCE UNDER DC BIAS

FREQUENCY (MHz)


LAND PATTERNS FOR REFLOW SOLDERING



RECOMMENDED SOLDERING CONDITIONS







2002/95/EG

(For wave soldering, add 0.762 [.030] to this dimension)

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Lair									
				Tech. and is loaned in confidence subject to return upon request an with the understanding that no			1		= "				
						Laird							
				copies shall be made without the									
				written consent of Laird Tech. Al		_	—		_				
				rights to design or invention are		_							
				reserved.		l							
				PROJECT/PART NUMBER:	1	REV	PART TY	PE:	DRAWN BY:				
С	ADD OPERATING TEMPERATURE UPDATE LAIRD LOGO AND REFLOW CURVE	08/05/13	QU	MI0603J680R-10		С	co-	-FIRE	тмв				
В	UPDATE COMPANY LOGO ADD ROHS SYM	07/24/08	JRK	DATE: 03/30/04	SCAL	E:		SHEET:					
Α		03/30/04			TOOL	_		_	6 0				
REV	DESCRIPTION	DATE	INT	MI0603J680R-10-C	1002	•	-		2 of 2				

AGILENT E4991A RF Impedance/Material Analyzer HP 16194A Test Fixture. TEST REF. 3227

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird:

MI0603J680R-10