

Advanced IGBT/MOSFET driver

Features

- 1.7 A sink / 1.3 A source (typ) current capability
- Active Miller clamp feature
- Desaturation detection
- Adjustable turn-on delay
- UVLO protection
- 2k V ESD protection

Applications

- 1200 V 3-phase inverter
- Motor control systems
- UPS

Description


This device is an advanced gate driver for IGBTs and power MOSFETs. Control and protection functions are included and allow the design of high reliability systems.

The innovative active Miller clamp function eliminates the need for negative gate drive in most applications and allows the use of a simple bootstrap supply for the high side driver.

The TD352 includes an adjustable turn-on delay. This feature can be used to implement reliable deadtime between high and low sides of a half bridge. An external resistor and capacitor are used to provide accurate timing.

Table 1. Device summary

Order codes	Temperature range	Package	Packaging	
TD352ID	-40°C. +125°C	SO-8	Tube	
TD352IDT	-40 C, +125 C	30-6	Tape and reel	



Contents


1	Bloc	k diagram	3
2	Pin c	onnections	4
3	Abso	olute maximum ratings	5
4	Elect	rical characteristics	6
5	Func	tional description	8
	5.1	Input stage	8
	5.2	Voltage reference	8
	5.3	Active Miller clamp	8
	5.4	Turn-on delay	8
	5.5	Desaturation protection	9
	5.6	Output stage	9
	5.7	Undervoltage protection	9
6	Timir	ng diagrams	1
7	Туріс	cal performance curves	3
8	Appli	ication diagrams1	5
9	Pack	age mechanical data1	6
10	Revis	sion history	7



TD352 Block diagram

1 Block diagram

Figure 1. TD352 block diagram



Pin connections TD352

2 Pin connections

Figure 2. Pin connections (top view)




Table 2. Pin description

Pin n°	Name	Туре	Function
IN	1	Analog input	Input
VREF	2	Analog output	+5 V reference voltage
CD	3	Timing capacitor	Turn on delay
DESAT	4	Analog input	Desaturation protection
CLAMP	5	Analog output	Miller clamp
VL	6	Power supply	Signal ground
OUT	7	Analog output	Gate drive output
VH	8	Power supply	Positive supply

3 Absolute maximum ratings

Table 3. Absolute maximum ratings

Symbol	Parameter	Value	Unit
VHL	Maximum supply voltage (VH - VL)	28	V
V _{out}	Voltage on OUT, CLAMP, DESAT pins	VL-0.3 to VH+0.3	٧
V _{other}	Voltage on other pins (IN, CD, VREF)	-0.3 to 7	٧
P _d	Power dissipation	500	mW
T _{stg}	Storage temperature	-55 to 150	°C
Tj	Maximum junction temperature	150	°C
R _{thJA}	Thermal resistance junction-ambient	150	°C/W
ESD	Electrostatic discharge (HBM)	2	kV

Table 4. Operating conditions

Symbol	Parameter	Value	Unit
VH	Positive supply voltage vs. VL	UVLO to 26	V
T _{oper}	Operating free air temperature range	-40 to 125	°C

57

Electrical characteristics TD352

4 Electrical characteristics

 T_A = -20 to 125 °C, VH = 16 V, unless otherwise specified.

Table 5. Electrical characteristics

Symbol	Parameter	Test condition	Min	Тур	Max	Unit
Input						
V _{ton}	IN turn-on threshold voltage		0.8	1.0		V
V _{toff}	IN turn-off threshold voltage			4.0	4.2	V
I _{inp}	IN input current	IN input voltage < 4.5V			1	μA
Voltage refe	erence ⁽¹⁾	•				
V _{ref}	Voltage reference	T = 25°C	4.85	5.00	5.15	٧
I _{ref}	Maximum output current		10			mA
Clamp		•				
V _{tclamp}	CLAMP pin voltage threshold			2.0		٧
V _{CL}	Clamp low voltage	I _{csink} = 500mA			2.5	٧
Delay		•				
V _{tdel}	Voltage threshold			2.5		V
R _{del}	Discharge resistor	I=1mA			500	Ω
Desaturatio	n protection					
V _{des}	Desaturation threshold			VH-2		V
I _{des}	Source current			250		μA
Output		•	•			
I _{sink}	Output sink current	V _{out} = 6V	1000	1700		mA
I _{src}	Output source current	V _{out} = VH-6V	750	1300		mA
V _{OL1}	Output low voltage 1	I _{osink} = 20mA			0.35	٧
V _{OL2}	Output low voltage 2	I _{osink} = 500mA			2.5	٧
V _{OH1}	Output high voltage 1	I _{osource} = 20mA	VH-2.5			V
V _{OH2}	Output high voltage 2	I _{osource} = 500mA	VH-4.0			V
t _r	Rise time	C _L = 1nF, 10% to 90%			100	ns
t _f	Fall time	C _L = 1nF, 90% to 10%			100	ns
t _{don}	Turn on propagation delay	10% OUT change: $R_d = 4.7k\Omega$, no C_d $R_d = 11k\Omega$, $C_d = 220$ pF	1.8	2.0	500 2.2	ns µs
t _{doff}	Turn off propagation delay	10% OUT change			400	ns

6/18 Doc ID 11095 Rev 2

Table 5. Electrical characteristics (continued)

Symbol	Parameter	Test condition	Min	Тур	Max	Unit
Under volta	Under voltage lockout (UVLO)					
UVLOH	UVLO top threshold		10	11	12	٧
UVLOL	UVLO bottom threshold		9	10	11	٧
V _{hyst}	UVLO hysteresis	UVLOH-UVLOL	0.5	1		٧
Supply current						
I _{in}	Quiescent current	OUT = 0V; no load			2.5	mA

^{1.} Recommended capacitor range on VREF pin is 10 nF to 100 nF

5 Functional description

5.1 Input stage

The TD352 IN input is internally clamped at about 5 V to 7 V. The input is triggered by the signal edge. When using an open collector optocoupler, the resistive pull-up resistor can be connected to either VREF or VH.

Recommended pull-up resistor value with VH=16 V is from 4.7 k Ω to 22 k Ω

5.2 Voltage reference

A voltage reference is used to create accurate timing for the turn-on delay with external resistor and capacitor.

A decoupling capacitor (10 nF to 100 nF) on the VREF pin is required to ensure good noise rejection.

5.3 Active Miller clamp

The TD352 offers an alternative solution to the problem of Miller current in IGBT switching applications. Instead of driving the IGBT gate to a negative voltage to increase the safety margin, the TD352 uses a dedicated CLAMP pin to control the Miller current. When the IGBT is off, a low impedance path is established between the IGBT gate and emitter to carry the Miller current, and the voltage spike on the IGBT gate is greatly reduced.

During turn-off, the gate voltage is monitored and the clamp output is activated when the gate voltage goes below 2 V (relative to VL). The clamp voltage is VL+4V max for a Miller current up to 500 mA. The clamp is disabled when the IN input is triggered again.

The CLAMP function does not affect the turn-off characteristic, but only keeps the gate at low level throughout the off time. The main benefit is that negative voltage can be avoided in many cases, allowing a bootstrap technique for the high side driver supply.

5.4 Turn-on delay

Turn-on (T_a) delay is programmable through external resistor R_d and capacitor C_d for accurate timing. T_a is approximately given by (see *Figure 5*):

$$T_a (\mu s) = 0.7 * R_d (k\Omega) * C_d (nF)$$

The turn-on delay can be disabled by connecting the CD pin to VREF with a 4.7 k Ω resistor. Input signals with ON-time smaller than T_a are ignored.

Desaturation protection 5.5

Desaturation protection ensures the protection of the IGBT in the event of overcurrent. When the DESAT voltage goes higher than VH-2V, the TD352 OUT pin is driven low. The fault state is only exited after a power-down and power-up cycle.

A programmable blanking time is used to allow enough time for IGBT saturation. Blanking time is provided by an internal current source and external C_{des} capacitor. The T_{bdes} blanking time value is given by:

$$T_{bdes} = V_{des} * C_{des} / I_{des}$$

At VH=16V, T_{bdes} is approximately given by:


$$T_{bdes}$$
 (µs) = 0.056 * C_{des} (pF)

5.6 Output stage

The output stage is able to sink/source 1.7 A/1.3 A (typical) at 25 °C and 1.0 A/0.75 A min. over the full temperature range. This current capability is specified near the usual IGBT Miller plateau.

5.7 Undervoltage protection

Undervoltage detection protects the application in the event of a low VH supply voltage (during startup or a fault situation). During undervoltage, the OUT pin is driven low (active pull-down for VH>2V, and passive pull-down for VH<2V).



UVLO IN VRE<u>F</u> 5V Vref Control Block CLAMP DESAT VH OUT 婖 VL AM02828v1

Figure 4. Detailed internal schematic



TD352 Timing diagrams

6 Timing diagrams

Figure 5. General turn-on and turn-off sequence






Figure 6. Input and output waveform dynamic parameters




Timing diagrams TD352

Figure 7. Desaturation fault



7 Typical performance curves

Figure 8. Quiescent current vs temperature Figure 9. Rdel resistance vs temperature







Figure 10. Low level output voltage vs temp. Figure 11. High level output voltage vs temp.








Figure 12. Sink current vs temperature

Figure 13. Source current vs temperature





577

14/18 Doc ID 11095 Rev 2

8 Application diagrams

Figure 14. Single supply IGBT drive with active Miller clamp and DESAT protection




Figure 15. Use of DESAT input for direct overcurrent detection





Figure 16. Large IGBT drive with negative voltage gate drive and optional current buffers



577

Doc ID 11095 Rev 2

Package mechanical data 9

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

Table 6. SO-8 mechanical data

Dim.		mm.			inch			
Dim.	Min.	Тур	Max.	Min.	Тур.	Max.		
Α	1.35		1.75	0.053		0.069		
A1	0.10		0.25	0.04		0.010		
A2	1.10		1.65	0.043		0.065		
В	0.33		0.51	0.013		0.020		
С	0.19		0.25	0.007		0.010		
D	4.80		5.00	0.189		0.197		
E	3.80		4.00	0.150		0.157		
е		1.27			0.050			
Н	5.80		6.20	0.228		0.244		
h	0.25		0.50	0.010		0.020		
L	0.40		1.27	0.016		0.050		
k	(max.) 8							
ddd			0.1			0.04		

△ ddd C С 0016023/C

Figure 17. SO-8 mechanical drawing

Doc ID 11095 Rev 2 16/18

TD352 Revision history

10 Revision history

Table 7. Document revision history

Date	Revision	Changes
01-Nov-2004	1	Initial release
13-Jun-2011	2	Deleted order code TD352IN. Content reworked to improve readability.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2011 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

18/18 Doc ID 11095 Rev 2

