











LM4120





SNVS049F - FEBRUARY 2000 - REVISED MARCH 2016

LM4120 Precision Micropower Low Dropout Voltage Reference

Features

- Small SOT23-5 Package
- Low Dropout Voltage: 120 mV Typical at 1 mA
- High Output Voltage Accuracy: 0.2%
- Source and Sink Current Output: ±5 mA
- Supply Current: 160 µA Typical
- Low Temperature Coefficient: 50 ppm/°C
- **Enable Pin**
- Fixed Output Voltages: 1.8, 2.048, 2.5, 3, 3.3, 4.096, and 5 V
- Industrial Temperature Range: -40°C to 85°C
- (For Extended Temperature Range, -40°C to 125°C, Contact TI)

2 Applications

- Portable, Battery-Powered Equipment
- Instrumentation and Process Control
- Automotive and Industrial
- Test Equipment
- **Data Acquisition Systems**
- **Precision Regulators**
- **Battery Chargers**
- **Base Stations**
- Communications
- Medical Equipment

3 Description

The LM4120 device is a precision low-power, low dropout bandgap voltage reference with up to 5-mA output current source and sink capability.

This series reference operates with input voltages as low as 2 V and up to 12 V, consuming 160-µA (typical) supply current. In power-down mode, device current drops to less than 2 µA.

The LM4120 comes in two grades (A and Standard) and seven voltage options for greater flexibility. The best grade devices (A) have an initial accuracy of 0.2%, while the standard have an initial accuracy of 0.5%, both with a temperature coefficient of 50 ppm/°C ensured from -40°C to 125°C.

The very low dropout voltage, low supply current, and power-down capability of the LM4120 make this product an ideal choice for battery-powered and portable applications.


The device performance is ensured over the industrial temperature range (-40°C to 85°C), while certain specifications are ensured over the extended temperature range (-40°C to 125°C). Contact TI for full specifications over the extended temperature range. The LM4120 is available in a standard 5-pin SOT-23 package.

Device Information⁽¹⁾

PART NUMBER		PACKAGE	BODY SIZE (NOM)					
	LM4120	SOT-23 (5)	1.60 mm × 2.90 mm					

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Functional Block Diagram





Ta	hl	Δ	af (ᡣ	nto	ents
ıa	νı	\boldsymbol{c}	UI '	UU	חונכ	HUS

2Applications17.4 Device Functional Modes.3Description18Application and Implementation4Revision History28.1 Application Information5Pin Configuration and Functions38.2 Typical Application6Specifications39 Power Supply Recommendations6.1 Absolute Maximum Ratings310 Layout6.2 ESD Ratings310.1 Layout Guidelines6.3 Recommended Operating Conditions410.2 Layout Example6.4 Thermal Information411 Device and Documentation Support6.5 Electrical Characteristics411.1 Community Resources6.6 Typical Characteristics711.2 Trademarks7 Detailed Description1011.3 Electrostatic Discharge Caution7.1 Overview1011.4 Glossary7.2 Functional Block Diagram1012 Mechanical, Packaging, and Orderable Information	1	Features 1		7.3 Feature Description	10
3Description18Application and Implementation4Revision History28.1 Application Information5Pin Configuration and Functions38.2 Typical Application6Specifications39Power Supply Recommendations6.1 Absolute Maximum Ratings310Layout6.2 ESD Ratings310.1 Layout Guidelines6.3 Recommended Operating Conditions410.2 Layout Example6.4 Thermal Information411Device and Documentation Support6.5 Electrical Characteristics411.1 Community Resources6.6 Typical Characteristics711.2 Trademarks7Detailed Description1011.3 Electrostatic Discharge Caution7.1 Overview1011.4 Glossary7.2 Functional Block Diagram1010Mechanical, Packaging, and Orderable	2			7.4 Device Functional Modes	10
4 Revision History. 2 8.1 Application Information	3		8	Application and Implementation	11
5Pin Configuration and Functions38.2Typical Application6Specifications39Power Supply Recommendations6.1Absolute Maximum Ratings310Layout6.2ESD Ratings310.1Layout Guidelines6.3Recommended Operating Conditions410.2Layout Example6.4Thermal Information411Device and Documentation Support6.5Electrical Characteristics411.1Community Resources6.6Typical Characteristics711.2Trademarks7Detailed Description1011.3Electrostatic Discharge Caution7.1Overview1011.4Glossary7.2Functional Block Diagram10Mechanical, Packaging, and Orderable	_			8.1 Application Information	<u>1</u> 1
6 Specifications 3 9 Power Supply Recommendations 10 Layout 11.1 Community Resources 11.2 Trademarks 11.3 Electrostatic Discharge Caution 11.4 Glossary 11.4 Mechanical, Packaging, and Orderable					
6.1 Absolute Maximum Ratings 3 6.2 ESD Ratings 3 6.3 Recommended Operating Conditions 4 6.4 Thermal Information 4 6.5 Electrical Characteristics 4 6.6 Typical Characteristics 7 Detailed Description 10 7.1 Overview 10 7.2 Functional Block Diagram 10 Layout Guidelines 10.1 Layout Guidelines 11.1 Layout Example 11.2 Layout Example 11.3 Electrostation Support 11.1 Community Resources 11.1 Community Resources 11.2 Trademarks 11.3 Electrostatic Discharge Caution 11.4 Glossary	-		9	Power Supply Recommendations	15
6.2 ESD Ratings 3 10.1 Layout Guidelines 10.2 Layout Example 10.2 Layout Example 10.3 Layout Example 10.4 Layout Example 10.5 Electrical Characteristics 4 11.1 Community Resources 11.1 Community Resources 11.2 Trademarks 11.2 Trademarks 11.3 Electrostatic Discharge Caution 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.5 Electrostatic Discharge And Orderable 11.5 Electr	٠	•	10	Layout	16
6.3 Recommended Operating Conditions				10.1 Layout Guidelines	16
6.4 Thermal Information				10.2 Layout Example	16
6.5 Electrical Characteristics			11	Device and Documentation Support	17
6.6 Typical Characteristics 7 11.2 Trademarks 11.3 Electrostatic Discharge Caution 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.4 Glossary 11.5 Functional Block Diagram 10 Mechanical, Packaging, and Orderable				11.1 Community Resources	17
7 Detailed Description				11.2 Trademarks	17
7.1 Overview	7	**		11.3 Electrostatic Discharge Caution	17
7.2 Functional Block Diagram10 12 Mechanical, Packaging, and Orderable	•			11.4 Glossary	17
			12		17
		E: Page numbers for previous revisions may differ from pag ges from Revision E (February 2016) to Revision F			Pag

Changes from Revision D (July 2015) to Revision E

Changes from Revision C (April 2013) to Revision D

Page


Added ESD Ratings table, Feature Description section, Device Functional Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device and Documentation Support section, and

Changes from Revision B (April 2013) to Revision C

Page



5 Pin Configuration and Functions



Pin Functions

PIN		1/0	DESCRIPTION		
NAME	NO.	1/0	DESCRIPTION		
Enable	3	I	Pulled to input for normal operation. Forcing this pin to ground will turn off the output.		
GND	2	_	Negative supply or ground connection		
REF	1	_	REF pin. This pin must be left unconnected.		
V _{IN}	4	1	Positive supply		
V _{OUT}	5	0	Reference output		

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) (1)

		MIN	MAX	UNIT
Maximum voltage on input or enable pins		-0.3	14	V
Output short-circuit duraion			Indefinite	
Power dissipation (T _A = 25°C) ⁽²⁾			350	mW
	Soldering, (10 sec.)		260	°C
Lead temperature	Vapor Phase (60 sec.)		215	°C
	Infrared (15 sec.)		220	°C
Storage temperature, T _{stg}		-65	150	°C

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

			VALUE	UNIT
		Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 (1)	±2000	
V _(ESD)	Electrostatic discharge	Charged device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±750	V
		Machine Model	±200	

⁽¹⁾ JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

⁽²⁾ Without PCB copper enhancements. The maximum power dissipation must be derated at elevated temperatures and is limited by T_{JMAX} (maximum junction temperature), R_{BJA} (junction-to-ambient thermal resistance) and T_A (ambient temperature). The maximum power dissipation at any temperature is: PDiss_{MAX} = (T_{JMAX} – T_A) / R_{BJA} up to the value listed in the *Absolute Maximum Ratings*.

⁽²⁾ JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

	MIN	NOM MAX	UNIT
Ambient temperature	-40	85	°C
Junction temperature	-40	125	°C

6.4 Thermal Information

		LM4120	
	THERMAL METRIC ⁽¹⁾	DBV [SOT-23]	UNIT
		5 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	170.4	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	123.9	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	30.4	°C/W
ΨЈТ	Junction-to-top characterization parameter	17.2	°C/W
ΨЈВ	Junction-to-board characterization parameter	29.9	°C/W

⁽¹⁾ For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

6.5 Electrical Characteristics

unless otherwise specified, $V_{IN} = 3.3 \text{ V}$, $I_{LOAD} = 0$, $C_{OUT} = 0.01 \mu\text{F}$, $T_A = T_i = 25^{\circ}\text{C}$.

PARAMETER		TEST CONI	TEST CONDITIONS		TYP (2)	MAX ⁽¹⁾	UNIT
1.8 V, 2.048 V,	AND 2.5 V						
V _{OUT}	Output voltage initial accuracy LM4120A-1.800 LM4120A-2.048 LM4120A-2.500					±0.2%	
	LM4120-1.800 LM4120-2.048 LM4120-2.500					±0.5%	
TCV _{OUT} /°C	Temperature coefficient	-40 °C $\leq T_A \leq +125$ °C			14	50	ppm/°c
$\Delta V_{OUT}/\Delta V_{IN}$	Line regulation	3.3 V ≤ V _{IN} ≤ 12 V			0.0007	0.008	- %/V
ΔVOUT/ΔVIN			-40 °C $\leq T_A \leq 85$ °C			0.01	
		0 m \ < 1			0.03	0.08	
		0 mA ≤ I _{LOAD} ≤ 1 mA	-40 °C $\leq T_A \leq 85$ °C			0.17	
۸۱/ /۸۱	Lood regulation	1 m \ < 1			0.01	0.04	0/ /m Λ
$\Delta V_{OUT}/\Delta I_{LOAD}$	Load regulation	$1 \text{ mA} \le I_{LOAD} \le 5 \text{ mA}$	-40 °C $\leq T_A \leq 85$ °C			0.1	%/mA
		$-1 \text{ mA} \le I_{LOAD} \le 0 \text{ mA}$			0.04	0.12	
		-5 mA ≤ I_{LOAD} ≤ -1 mA			0.01		
		J 0 A			45	65	
		$I_{LOAD} = 0 \text{ mA}$	-40°C ≤ T _A ≤ 85°C			80	
\/ -\/	Dronout voltage (3)				120	150	
V_{IN} - V_{OUT}	Dropout voltage (3)	$I_{LOAD} = 1 \text{ mA}$	-40°C ≤ T _A ≤ 85°C			180	mV
					180	210	
		$I_{LOAD} = 5 \text{ mA}$	-40°C ≤ T _A ≤ 85°C			250	

⁽¹⁾ Limits are 100% production tested at 25°C. Limits over the operating temperature range are ensured through correlation using Statistical Quality Control (SQC) methods. The limits are used to calculate Tl's Averaging Outgoing Quality Level (AOQL).

⁽²⁾ Typical numbers are at 25°C and represent the most likely parametric norm.

⁽³⁾ Dropout voltage is the differential voltage between V_{OUT} and V_{IN} at which V_{OUT} changes ≤ 1% from V_{OUT} at V_{IN} = 3.3 V for 1.8 V, 2 V, 2.5 V, and V_{OUT} + 1 V for others. For 1.8-V option, dropout voltage is not ensured over temperature. A parasitic diode exists between input and output pins; it will conduct if V_{OUT} is pulled to a higher voltage than V_{IN}.



Electrical Characteristics (continued)

unless otherwise specified, $V_{IN} = 3.3 \text{ V}$, $I_{LOAD} = 0$, $C_{OUT} = 0.01 \mu\text{F}$, $T_A = T_j = 25^{\circ}\text{C}$.

	PARAMETER	TEST COND	ITIONS	MIN ⁽¹⁾	TYP (2)	MAX (1)	UNIT	
.,	0(4)	0.1 Hz to 10 Hz			20			
V_N	Output ⁽⁴⁾	10 Hz to 10 kHz			36		μV_{PP}	
	0				160	250		
I _S	Supply current		-40°C ≤ T _A ≤ 85°C			275	μA	
	Power-down supply	Enable = 0.4 V				1		
I _{SS}	current	-40 °C \leq T _J \leq 85°C Enable = 0.2 V	-40°C ≤ T _A ≤ 85°C			2	μA	
\/	Logic high input voltage				2.4		V	
V _H	Logic nigh input voltage	-40 °C $\leq T_A \leq 85$ °C		2.4			V	
V	Logic low input voltage				0.4		V	
V_L	Logic low input voltage	-40°C ≤ T _A ≤ 85°C				0.2	V	
	Landa Blak Samura anno at				7		^	
lн	Logic high input current	-40°C ≤ T _A ≤ 85°C				15	μA	
L	Logic low input current				0.1		μA	
	·	V 00VV			15			
	Short circuit current	$V_{IN} = 3.3 \text{ V}, V_{OUT} = 0$	-40°C ≤ T _A ≤ 85°C	6		30		
I _{SC}					17		mA	
		$V_{IN} = 12 \text{ V}, V_{OUT} = 0$	-40°C ≤ T _A ≤ 85°C	6		30		
Hyst	Thermal hysteresis (5)	-40°C ≤ T _A ≤ 125°C	Λ		0.5		mV/V	
ΔV _{OUT}	Long term stability (6)	1000 hrs @ 25°C			100		ppm	
3 V, 3.3 V, 4.09		1.000 10 3 20 0					ΡΡ	
V _{оит}	Output voltage initial accuracy LM4120A-3.000 LM4120A-3.300 LM4120A-4.096 LM4120A-5.000					±0.2%		
	LM4120-3.000 LM4120-3.300 LM4120-4.096 LM4120-5.000					±0.5%		
TCV _{OUT} /°C	Temperature coefficient	-40 °C $\leq T_A \leq 125$ °C			14	50	ppm/°c	
۸۱/ /۸۱/	Line regulation	(//			0.0007	0.008	%/V	
$\Delta V_{OUT}/\Delta V_{IN}$	Line regulation	$(V_{OUT} + 1 V) \le V_{IN} \le 12 V$	-40 °C $\leq T_A \leq 85$ °C			0.01	/0/ V	
		0 m/ < 1 < 1 m/			0.03	0.08		
		0 mA ≤ I _{LOAD} ≤ 1 mA	-40°C ≤ T _A ≤ 85°C			0.17		
A\/ /AI	Lood roomistiss	1 m \ < 1 \ < 5 \cdots 1			0.01	0.04	0// 4	
$\Delta V_{OUT}/\Delta I_{LOAD}$	Load regulation	1 mA \leq I _{LOAD} \leq 5 mA	-40°C ≤ T _A ≤ 85°C			0.1	%/mA	
		$-1 \text{ mA} \le I_{LOAD} \le 0 \text{ mA}$	*		0.04	0.12		
		-5 mA ≤ I _{LOAD} ≤ -1 mA			0.01			
					45	65		
		$I_{LOAD} = 0 \text{ mA}$	-40°C ≤ T _A ≤ 85°C			80		
					120	150		
V_{IN} – V_{OUT}	Dropout voltage (3)	$I_{LOAD} = 1 \text{ mA}$	–40°C ≤ T _A ≤ 85°C		120	180	mV	
			40 0 = 1A = 00 0		180	210		
							50	

 ⁽⁴⁾ Output noise voltage is proportional to V_{OUT}. V_N for other voltage option is calculated using (V_N(1.8 V) / 1.8) × V_{OUT}. V_N (2.5 V) = (36 μV_{PP} / 1.8) × 2.5 = 46 μV_{PP}.
 (5) Thermal hysteresis is defined as the change in 25°C output voltage before and after exposing the device to temperature extremes.

Long term stability is change in V_{REF} at 25°C measured continuously during 1000 hours.



Electrical Characteristics (continued)

unless otherwise specified, V $_{IN}$ = 3.3 V, I $_{LOAD}$ = 0, C $_{OUT}$ = 0.01 μF , T $_{A}$ = T $_{j}$ = 25 $^{\circ}$ C.

	PARAMETER	TEST CON	IDITIONS	MIN ⁽¹⁾	TYP (2)	MAX ⁽¹⁾	UNIT	
3 V, 3.3 V	, 4.096 V, AND 5 V (continued)							
V	Output noise voltage (4)	0.1 Hz to 10 Hz			20		\/	
V _N	Output hoise voitage	10 Hz to 10 kHz			36		μV_{PP}	
	Complex compact				160	250		
I _S	Supply current	–40°C ≤ T _A ≤ 85°C				275	μΑ	
	Power-down supply	Enable = 0.4 V				1		
I _{SS}	current	-40 °C \leq T _J \leq 85°C Enable = 0.2 V	-40°C ≤ T _A ≤ 85°C			2	μΑ	
V	Logio high input voltogo				2.4		V	
V _H	Logic high input voltage	age -40°C ≤ T _A ≤ 85°C		2.4		V		
V	Logio love input voltago				0.4		V	
V_L	Logic low input voltage	-40 °C $\leq T_A \leq 85$ °C				0.2	V	
	Logio bigh input ourrent				7			
IH	Logic high input current	-40 °C $\leq T_A \leq 85$ °C			15	μA		
IL	Logic low input current				0.1		μΑ	
			V 0			15		
	Short circuit current	$V_{OUT} = 0$	-40 °C $\leq T_A \leq 85$ °C	6		30	A	
I _{SC}	Short circuit current	V 42.V V 0			17		mA	
		$V_{IN} = 12 \text{ V}, V_{OUT} = 0$	-40°C ≤ T _A ≤ 85°C	6		30		
Hyst	Thermal hysteresis (5)	-40°C ≤ T _A ≤ 125°C			0.5		mV/V	
ΔV_{OUT}	Long term stability (6)	1000 hours @ 25°C			100		ppm	


Submit Documentation Feedback

Copyright © 2000–2016, Texas Instruments Incorporated



6.6 Typical Characteristics


unless otherwise specified, V_{IN} = 3.3 V, V_{OUT} = 2.5 V, I_{LOAD} = 0, C_{OUT} = 0.022 μ F, T_A = 25°C, and V_{EN} = V_{IN}



TEXAS INSTRUMENTS


Typical Characteristics (continued)


unless otherwise specified, $V_{IN}=3.3~V,~V_{OUT}=2.5~V,~I_{LOAD}=0,~C_{OUT}=0.022~\mu F,~T_A=25^{\circ}C,~and~V_{EN}=V_{IN}=0.025~\mu F$





Typical Characteristics (continued)








7 Detailed Description

7.1 Overview

The LM4120 device is a precision bandgap voltage reference available in seven different voltage options with up to 5-mA current source and sink capability. This series reference can operate with input voltages from 2 V to 12 V while consuming 160- μ A (typical) supply current. In power-down mode, device current drops to less than 2 μ A. The LM4120 is available in two grades, A and Standard.

The best grade devices (A) have an initial accuracy of 0.2% with a TEMPCO of 50 ppm/°C ensured from −40°C to 125°C.

7.2 Functional Block Diagram



7.3 Feature Description

7.3.1 Enable

The ENABLE analog input pin with limited hysteresis generally requires 6 μ A (typical) of current to start up the part. During normal operation, the Enable pin must be connected to the VIN pin. There is a minimum slew rate on this pin of about 0.003 V/ μ s to prevent glitches on the output. All of these conditions can easily be met with ordinary CMOS or TTL logic. The Enable pin can also be used to remotely operate the LM4120 by pulling up the Enable pin voltage to the input voltage level.

When remotely shutting down the LM4120, the Enable pin must be pulled down to the ground. Floating this pin is not recommended.

7.3.2 Reference

The REF pin must remain unconnected in all cases. The reference pin is sensitive to noise, and capacitive loading. Therefore, during the PCB layout care must be taken to keep this pin isolated as much as possible.

7.4 Device Functional Modes

Table 1 describes the functional modes of the LM4120.

Table 1. Enable Pin Mode Summary

ENABLE PIN CONNECTION	LOGIC STATE	DESCRIPTION
EN = VIN	1	Normal Operation. LM4120 starts up.
EN = GND 0		LM4120 in shutdown mode



8 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The standard application circuit for the LM4120 is shown in Figure 29. The device is designed to be stable with ceramic output capacitors in the range of 0.022 μ F to 0.047 μ F. The minimum required output capacitor is 0.022 μ F. These capacitors typically have an ESR of about 0.1 Ω to 0.5 Ω . Smaller ESR can be tolerated, but larger ESR cannot be tolerated. The output capacitor can be increased to improve load transient response, up to about 1 μ F. However, values above 0.047 μ F must be tantalum. With tantalum capacitors in the 1- μ F range, a small capacitor between the output and the reference pin is required. This capacitor will typically be in the 50-pF range. Care must be taken when using output capacitors of 1 μ F or larger. These applications must be thoroughly tested over temperature, line, and load.

An input capacitor is typically not required. However, a 0.1-µF ceramic can be used to help prevent line transients from entering the LM4120. Larger input capacitors must be tantalum or aluminum.

The reference pin is sensitive to noise, and capacitive loading. Therefore, the PCB layout must isolate this pin as much as possible.

The enable pin is an analog input with very little hysteresis. About 6 µA into this pin is required to turn the part on, and it must be taken close to GND to turn the part off (see *Electrical Characteristics* for thresholds). If the shutdown feature is not required, then this pin can safely be connected directly to the input supply.




Figure 19. Voltage Reference With Negative Output Circuit




Figure 20. Precision High-Current Low-Dropout Regulator Circuit

Submit Documentation Feedback
Product Folder Links: LM4120

Application Information (continued)




Figure 21. Precision High-Current Negative Voltage Regulator Circuit




Figure 22. Voltage Reference With Complimentary Output Circuit




Figure 23. Precision High-Current Low-Dropout Regulator Circuit

Submit Documentation Feedback



Application Information (continued)




Figure 24. Stacking Voltage References Circuit




Figure 25. Precision Voltage Reference With Force and Sense Output Circuit




Figure 26. Programmable Current Source Circuit

Copyright © 2000–2016, Texas Instruments Incorporated

Submit Documentation Feedback

Application Information (continued)




Figure 27. Precision Regulator With Current Limiting Circuit




Figure 28. Power Supply Splitter Circuit

8.2 Typical Application




Figure 29. Standard Application Circuit

8.2.1 Design Requirements

For this design example, use the parameters listed in Table 2 as the input parameters.

Table 2. Design Parameters

PARAMETER	EXAMPLE VALUE
Output Voltage VOUT	1.8 V, 2.048 V, 2.5 V, 3 V, 3.3 V, 4.096 V, 5 V
Input Voltage Range VIN	VOUT 120 mV to 12 V
Load Current	1 mA (typical)



8.2.2 Detailed Design Procedure


8.2.2.1 Input Capacitors

Although not always required, an input capacitor is recommended. A supply bypass capacitor on the input assures that the reference is working from a source with low impedance, which improves stability. A bypass capacitor can also improve transient response by providing a reservoir of stored energy that the reference can utilize in case where the load current demand suddenly increases. The value used for CIN may be used without limit

8.2.2.2 Output Capacitors

The LM4120 may require a 0.022-µF to 1-µF output capacitor for loop stability (compensation) as well as transient response. During the sudden changes in load current demand, the output capacitor must source or sink current during the time it takes the control loop of the LM4120 to respond.

8.2.3 Application Curves



9 Power Supply Recommendations

Noise on the power-supply input can effect the output noise, but can be reduced by using an optional bypass capacitor between the input pin and the ground. A ceramic input capacitor more than 0.1 μF or higher can be used for that purpose.



10 Layout

10.1 Layout Guidelines


The mechanical stress due to PC board mounting can cause the output voltage to shift from its initial value. The center of a PC board generally has the highest mechanical and thermal expansion stress. Mounting the device near the edges or the corners of the board where mechanical stress is at its minimum. References in SOT packages are generally less prone to assembly stress than devices in Small Outline (SOIC) package.


A mechanical isolation of the device by creating an island by cutting a U shape slot (U - SLOT) on the PCB while mounting the device helps in reducing the impact of the PC board stresses on the output voltage of the reference. This approach would also provide some thermal isolation from the rest of the circuit.

Figure 32 shows a recommended printed board layout for LM4120 along with an in-set diagram. The in-set diagram exhibits a slot cut on three sides of the reference IC, which provides a relief to the IC from external PCB stress.

10.2 Layout Example

PCB Top View








Figure 32. Typical Layout Example With LM4120

Submit Documentation Feedback

Copyright © 2000–2016, Texas Instruments Incorporated



11 Device and Documentation Support

11.1 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

11.2 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

11.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

11.4 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.





4-Nov-2016

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package	Pins	_	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking	Samples
	(1)		Drawing		Qty	(2)	(6)	(3)		(4/5)	
LM4120AIM5-1.8/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R21A	Samples
LM4120AIM5-2.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R14A	Samples
LM4120AIM5-2.5	NRND	SOT-23	DBV	5	1000	TBD	Call TI	Call TI	-40 to 85	R08A	
LM4120AIM5-2.5/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R08A	Samples
LM4120AIM5-3.0	NRND	SOT-23	DBV	5	1000	TBD	Call TI	Call TI	-40 to 85	R15A	
LM4120AIM5-3.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R15A	Samples
LM4120AIM5-3.3	NRND	SOT-23	DBV	5	1000	TBD	Call TI	Call TI	-40 to 85	R16A	
LM4120AIM5-3.3/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R16A	Samples
LM4120AIM5-4.1/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM -40 to 85		R17A	Samples
LM4120AIM5-5.0	NRND	SOT-23	DBV	5	1000	TBD	Call TI	Call TI	-40 to 85	R18A	
LM4120AIM5-5.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R18A	Samples
LM4120AIM5X-1.8/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R21A	Samples
LM4120AIM5X-2.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R14A	Samples
LM4120AIM5X-2.5/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R08A	Samples
LM4120AIM5X-3.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM -40 to 85		R15A	Samples
LM4120AIM5X-3.3/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R16A	Samples
LM4120AIM5X-4.1	NRND	SOT-23	DBV	5	3000	TBD	Call TI	Call TI	-40 to 85	R17A	
LM4120AIM5X-4.1/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R17A	Samples
LM4120AIM5X-5.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R18A	Samples





www.ti.com

4-Nov-2016

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Sample
LM4120IM5-1.8/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R21B	Sample
LM4120IM5-2.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R14B	Sample
LM4120IM5-2.5/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R08B	Sample
LM4120IM5-3.0	NRND	SOT-23	DBV	5	1000	TBD	Call TI	Call TI	-40 to 85	R15B	
LM4120IM5-3.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R15B	Sample
LM4120IM5-3.3	NRND	SOT-23	DBV	5	1000	TBD	Call TI	Call TI	-40 to 85	R16B	
LM4120IM5-3.3/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R16B	Sample
LM4120IM5-4.1/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R17B	Sample
LM4120IM5-5.0/NOPB	ACTIVE	SOT-23	DBV	5	1000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R18B	Sample
LM4120IM5X-1.8/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R21B	Sample
LM4120IM5X-2.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R14B	Sample
LM4120IM5X-2.5/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R08B	Sample
LM4120IM5X-3.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R15B	Sample
LM4120IM5X-3.3/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R16B	Sampl
LM4120IM5X-4.1/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R17B	Sample
LM4120IM5X-5.0/NOPB	ACTIVE	SOT-23	DBV	5	3000	Green (RoHS & no Sb/Br)	CU SN	Level-1-260C-UNLIM	-40 to 85	R18B	Sample

⁽¹⁾ The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.



PACKAGE OPTION ADDENDUM

4-Nov-2016

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Dec-2016

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM4120AIM5-1.8/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-2.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-2.5	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-2.5/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-3.0	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-3.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-3.3	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-3.3/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-4.1/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-5.0	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5-5.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-1.8/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-2.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-2.5/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-3.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-3.3/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-4.1	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120AIM5X-4.1/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Dec-2016

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LM4120AIM5X-5.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-1.8/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-2.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-2.5/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-3.0	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-3.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-3.3	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-3.3/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-4.1/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5-5.0/NOPB	SOT-23	DBV	5	1000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-1.8/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-2.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-2.5/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-3.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-3.3/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-4.1/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
LM4120IM5X-5.0/NOPB	SOT-23	DBV	5	3000	178.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3




^{*}All dimensions are nominal



PACKAGE MATERIALS INFORMATION

www.ti.com 20-Dec-2016

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LM4120AIM5-1.8/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-2.0/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-2.5	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-2.5/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-3.0	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-3.0/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-3.3	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-3.3/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-4.1/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-5.0	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5-5.0/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120AIM5X-1.8/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-2.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-2.5/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-3.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-3.3/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-4.1	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-4.1/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120AIM5X-5.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5-1.8/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-2.0/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-2.5/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-3.0	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-3.0/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-3.3	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-3.3/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-4.1/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5-5.0/NOPB	SOT-23	DBV	5	1000	210.0	185.0	35.0
LM4120IM5X-1.8/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5X-2.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5X-2.5/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5X-3.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5X-3.3/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5X-4.1/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0
LM4120IM5X-5.0/NOPB	SOT-23	DBV	5	3000	210.0	185.0	35.0



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4073253/P





SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. Reference JEDEC MO-178.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 4. Publication IPC-7351 may have alternate designs.
- 5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 7. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.