

Multilayer Antenna (Dual Band type)

For 2400-2484MHz / 5150-5850MHz

ANT016008LCD2442MA1

1.6x0.8mm [EIA 0603]*

* Dimensions Code JIS[EIA]



The products in this catalog will be or have been stopped production

| Discontinue Issue Date | Jun. 3, 2022 | | |
|--------------------------|---------------|--|--|
| Last Purchase Order Date | Mar. 31, 2023 | | |
| Last Shipment Date | Mar. 31, 2024 | | |

Please refer to our Web site about replacement information.




Multilayer Antenna


For 2400-2484MHz / 5150-5850MHz

Conformity to RoHS Directive

ANT016008LCD2442MA1

SHAPES AND DIMENSIONS






Terminal functions

- 1 Radiator electrode for 2.4GHz ISM
- 2 Feed point
- 3 Feed point
- 4 Radiator electrode for 5.5GHz
- 5 Feed point
- 6 Feed point
- * Terminal 2, 3, 5 and 6: Connected in inner structure


Dimensions in mm

RECOMMENDED LAND PATTERN



Dimensions in mm

SOLDER RESIST PATTERN



Dimensions in mm

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html Product.tdk.com/info/en/environment/rohs/index.html

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.



EVALUATION BOARD




PCB size: 120mm x 65mm x 1mm Antenna area: 8 x 5 mm



| | Component P/N |
|-----------|-------------------------|
| Ft 2.4GHz | 2.5pF |
| Ft 5.5GHz | 0.3pF |
| Mt Common | 1.5nH(MHQ1005P1N5B:TDK) |

☐ Measurement condition for Radiation Pattern



- All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



ELECTRICAL CHARACTERISTICS

| Item | Frequency Range (MHz) | Min. | Тур. | Max. |
|------------------------------|--------------------------|------|----------------------|------|
| VSWR | 2400 to 2484 | _ | 3.81 | 6.5 |
| VSWN | 5150 to 5850 | _ | 2.6 <mark>5</mark> | 4.0 |
| Polarization | | | Li <mark>near</mark> | |
| PCB size (mm) | | | 120×65 | |
| Antenna keep-out area (mm) | | | 8×5 | |
| Characteristic Impedance (Ω) | | | 50 (Nominal) | |


[·] This is typical antenna performance with the standard PCB.

TEMPERATURE RANGE


| Operating temperature | Storage temperature | |
|-----------------------|---------------------|--|
| (°C) | (°C) | |
| -40 to +85 | -40 to +85 | |

■ FREQUENCY CHARACTERISTICS





□IEEE802.11a




• Tested antenna has been soldered. Evaluation board size is 120x65x1 mm.

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

RADIATION PATTERNS

□2.4GHz ISM BAND



2.400GHz

2.442GHz

2 485GHz

2.485

<u>-17.5</u> -11.5

-40.5


225

Frequency(GHz)

Average(dBi)

Maximum(dBi)

Minimum(dBi)



Frequency(GHz)

Average(dBi)

180

Horizontal polarization

2.400

-48.2

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

135

2.485

-3.2 -0.2 -8.0

2.442

180

Vertical polarization

2.400


-0.5 -7.9


2.400GHz


2.442GHz 2.485GHz


RADIATION PATTERNS

□5.5GHz BAND













| | tal polal. | | |
|----------------|------------|-------|-------|
| Frequency(GHz) | 5.150 | 5.500 | 5.850 |
| Average(dBi) | -2.7 | -3.1 | -3.6 |
| Maximum(dBi) | 5.2 | 5.0 | 4.1 |
| Minimum(dBi) | -16.0 | -17.1 | -16.6 |







-38.4




[•] Tested antenna has been soldered. Evaluation board size is 120×65×1 mm.

Minimum(dBi)

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

■ RECOMMENDED REFLOW PROFILE



| Preheating | | Soldering | | | | |
|------------|-------|--------------------------|-------|-------------|-----------------|------------|
| | | Critical zone (T3 to T4) | | Peak | | |
| Temp. | | Time | Temp. | Time | Temp. | Time |
| T1 | T2 | t1 | Т3 | t2 | T4 | t3* |
| 150°C | 200°C | 60 to 120sec | 217°C | 60 to 120se | ec 240 to 260°C | 30sec max. |

*t3: Time within 5°C of actual peak temperature


The maximum number of reflow is 3.


- All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



■PACKAGING STYLE


□REEL DIMENSIONS





Dimensions in mm

TAPE DIMENSIONS



| | | | | | | | | | Dimen | sions in mm |
|-----------|----------|---------|----------|----------|---------|----------|---------|------------|----------|-------------|
| Α | В | C | D | E | F | G | Н | J | K | t |
| 0.97±0.05 | 1.8±0.05 | 8.0±0.2 | 3.5±0.05 | 1.75±0.1 | 4.0±0.1 | 2.0±0.05 | 4.0±0.1 | 1.5+0.1/-0 | 0.55max. | 0.25±0.05 |

PACKAGE QUANTITY

Standard package quantity
(pieces/reel)
4,000

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.