

DATE	DESCRIPTION	REV.



**Notes:**

Front Shell: Brass, Nickel Plate.  
Rear Shell: Steel, Nickel Plate.

Insulator: Matl: Thermoplastic  
UL 94V-0

Contacts: Matl: Phosphor Bronze  
Finish: Gold Plate over  
Nickel Plate on  
Contact Area.  
Tin Plate over  
Nickel Plate  
on Solder Tail.

**Electrical Specifications**  
Rated Voltage:  
30V AC (rms)  
Contact Current Rating:  
1A Max.  
Contact Resistance:  
30 milliohms Max.  
Dielectric Withstanding:  
500V AC  
Operating Temperature:  
-20°C to 85°C



**KEYSTONE ELECTRONICS CORP.**  
ASTORIA, N.Y. 11105-2017

PART NAME  
**USB B-TYPE HORIZONTAL SMT SOCKET**

MATERIAL  
**AS NOTED**

FINISH  
**AS NOTED**

TOLERANCES	INCH	[MM]	CODE	DWG NO.
DECIMAL	± .010	[± 0.25]	C/M	933
ANGULAR	± 1°			

THIS DOCUMENT IS THE PROPERTY OF  
KEYSTONE ELECTRONICS CORP. AND  
SHALL NOT BE REPRODUCED, DISTRIBUTED  
OR USED AS A BASIS FOR MANUFACTURE  
WITHOUT PRIOR WRITTEN PERMISSION  
FROM KEYSTONE ELECTRONICS CORP.

DRN BY: **BOONE** DATE: **5.30.06**  
App'd: **LN** SCALE: **3X**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[933](#)