| DR45 SERIES

AC SINGLE PHASE OUTPUT DIN RAIL MOUNT SSRS

Introduction

The DR45 is a powerful and compact solid state relay in a DIN rail 45mm wide package with an output rating up to 60 Amps @ 40°C offering mounting flexibility (on panel or DIN rail) and convenient input connection options. Its high I²t capability and optional built-in overvoltage protection make it suitable for demanding heating, motion and lighting applications.
Its contactor configuration and large cage clamp terminals allow connecting wires up to 3 AWG size on the output without the use of any additional accessories making them truly ready-to-use devices, therefore reducing installation cost and time.
UL Listed and VDE certified, the DR45 is a safe and versatile solid state relay with superior performance when compared to previous generation and competitor products in similar sized packages.

Features

- Output ratings up to 60 Amps at 600 VAC
- Built-in overvoltage protection
- Integral heat sink eliminates the need for complex thermal calculations
- Cage clamp terminal type accept up to 3 AWG wire size
- IP20 touch-safe housing
- Contactor configuration
- AC or DC control
- C-UL-US Listed and VDE approved

Applications

- Plastic injection molding equipment
- Packaging equipment
- Industrial ovens
- Lighting control
- Pump control
- Conveyor drives
- HVAC&R
- Railway vehicles

PRODUCT SELECTION

NOVA22

Control Voltage	45A	60A
90-280 VAC/VDC	DR4560A45x	DR4560A60x
4-32 VDC	DR4560D45x	DR4560D60x

ORDERING OPTIONS

DR45 – 60 – A – 45 – R – P – J

Series

DR45

Operating Voltage

60: 48-600 VAC

Control Voltage (1)

A: 90-280 VAC/VDC
D: 4-32 VDC

Rated Load Current

45: 45 Amps
60: 60 Amps

Switching Type

Blank: Zero Voltage Turn-On
R: Instantaneous Turn-On (Motor Rating Certified)

Overvoltage Protection

Blank: Not Included
P: Included

Input Connector

Blank: Screw Terminal
J: Spring Terminal

— Required for valid part number
☐ For options only and not required for valid part number

OUTPUT SPECIFICATIONS (2)

Description	45A	60A
Operating Voltage (47-440Hz) [V_{RMS}]	48-600	48-600
Transient Overvoltage [Vpk] (3)	1200	1200
Maximum Off-State Leakage Current @ Rated Voltage [mA_{RMS}]	1	1
Minimum Off-State dV/dt @ Maximum Rated Voltage [V/µsec]	500	500
Load Current, General Use UL508/LC A IEC62314 @ 40°C [A_{RMS}]	45	60
Load Current, Motor Starting UL508 FLA/LC B IEC62314 @ 40°C [A_{RMS}]	14/7.6	26/14
Minimum Load Current [mA_{RMS}]	100	150
Maximum 1 Cycle Surge Current (50/60Hz) [Apk]	716/750	1290/1350
Maximum On-State Voltage Drop @ Rated Current [V_{RMS}]	1.25	1.15
Maximum 1/2 Cycle I^2t for Fusing (50/60Hz) [A^2 sec]	2563/2343	8320/7593
Maximum Power Dissipation @ Rated Current [W]	52	69
Minimum Power Factor (at Maximum Load) (4)	0.5	0.5
Motor Rating UL 508/IEC62314 [HP (kW)]: 120 VAC	1 (0.74)	2 (1.5)
Motor Rating UL 508/IEC62314 [HP (kW)]: 240 VAC	3 (2.2)	5 (3.73)
Motor Rating UL 508/IEC62314 [HP (kW)]: 480 VAC	5 (3.7)	10 (7.4)

INPUT SPECIFICATIONS (2)

Description	DR4560Dxxx	DR4560Axxx
Control Voltage Range	4-32 VDC (5)	90-280 VAC/VDC
Maximum Reverse Voltage	-32 VDC	-
Minimum Turn-On Voltage	4 VDC	90 VAC/VDC
Must Turn-Off Voltage	1 VDC	5 VAC/VDC
Minimum Input Current (for on-state)	7 mA	3 mA
Maximum Input Current	15 mA	4 mA
Nominal Input Impedance	Current Limited	Switch Mode
Maximum Turn-On Time [msec]	1/2 Cycle (6)	20
Maximum Turn-Off Time [msec]	1/2 Cycle	30

GENERAL SPECIFICATIONS (2)

Description	Parameters
Dielectric Strength, Input to Output (50/60Hz)	4000 V_{RMS}
Dielectric Strength, Input/Output to Case (50/60Hz)	4000 V_{RMS}
Minimum Insulation Resistance (@ 500 VDC)	10^9 Ohms
Maximum Capacitance, Input/Output	8 pF
Ambient Operating Temperature Range	-40 to 80 °C
Ambient Storage Temperature Range (7)	-40 to 100 °C
Short Circuit Current Rating (8)	100kA
Weight (typical)	17.63 oz (500 g)
Housing Material	UL94 V-0
Heat Sink Material	Aluminum
DIN Rail Clip Material	Zinc Plated Steel
Hardware Finish	Nickel Plating
Input Terminal Screw Torque Range (lb-in/Nm)	5/0.5
Load Terminal Screw Torque Range (lb-in/Nm)	18-20/2-2.2
Humidity per IEC 60068-2-78	93% non-condensing
LED Input Status Indicator	Green
Overvoltage Category	III
Impulse Withstand Voltage According to IEC 60664-1	6kV

INPUT CURRENT INFORMATION



SURGE CURRENT INFORMATION



THERMAL DERATE INFORMATION (10)



EQUIVALENT CIRCUIT BLOCK DIAGRAMS/WIRING DIAGRAMS

DC Control * TVS option available in "P" version



Load can be wired in position A or B

AC/DC Control * TVS option available in "P" version



Load can be wired in position A or B

INSTALLATION INSTRUCTIONS

Mounting on DIN Rail

- Locate rail and align with non moveable end of DR45 DIN clip.
- Using reasonable force, push DR45 in the direction of the arrow (as shown in **fig.1**).
- For removal pull release tag in direction of arrow using blade of screwdriver and pull it away from DIN rail.

Mounting on Panel

- Locate the panel section on which the DR45 SSR will be mounted on (as shown in **fig.2**)
- DIN clip includes tabs for this type of mounting. Tab holes have a diameter of 4.5 mm. You will need three screws (not included) no larger than that to mount the SSR onto panel.
- Align SSR tabs with panel surface and screw both top and bottom sides. Recommended torque is 12 in-lbs (1.36 Nm).

Wiring Instructions

- Recommended wire sizes as shown in TABLE 1
- Maximum terminal screw torque input terminal 5 lb-in (0.5 Nm) (screw terminal only)
- Maximum terminal screw torque load terminal 18-20 lb-in (2.0-2.2 Nm)
- If multiple units are installed be sure to follow derating curves

TABLE 1. Wire Size & Pull Out Strenght

Terminal Configuration		Recommended Wire Size (Solid / Stranded)	Wire Pull-Out Strength (lb)[N]*
Output		1 x 18 AWG (1 mm²) [minimum]	20 [88]
		1 x 8 AWG (10 mm²) [maximum]	90 [400]
		2 x 8 AWG (10 mm²) [maximum]	80 [355]
		1 x 3 AWG (26.67 mm²) [maximum]	90 [400]
Input	**Screw**	30 AWG (0.05 mm²) [minimum]	4.5 [20]
		12 AWG (3.3 mm²) [maximum]	30 [133]
	Spring	26 AWG (0.13 mm²) [minimum]	5 [22]
		12 AWG (3.3 mm²) [maximum]	5 [22]

* Tests performed on Stranded wire

WARNING! Removing product from 35 mm rail incorrectly by not using the appropriate tool would damage the latching system.



fig. 1 SSR mounted on DIN rail



fig. 2 SSR mounted on Panel Mount

MECHANICAL SPECIFICATIONS

Tolerances: ±0.02 in / 0.5 mm
All dimensions are in: inches [millimeters]



ACCESSORIES

Recommended Accessories	
 **Connectors**	 **ID Marker**
CP201 Screw Terminal CP202 Spring Terminal	CNLB Blank Strips CNLN Numbered 1 to 10 Strips CNL2 Numbered 11 to 20 Strips

Protective Earth Connection



Protective earth (PE) screw type recommended is 10-32 UNC standard not provided with SSR. Through the use of a DIN rail ground (protective conductor) terminal block, the DIN rail itself can be used as the grounding bus bar. In this case, the zinc plated steel material used for the DIN rail clip of DR45 models, permits a secure path to ground and avoid the need of a further PE connection.

GENERAL NOTES

(1) Control voltage 18-52 VAC/VDC is available upon request.
(2) All parameters at 25°C unless otherwise specified.
(3) "P" option output will self trigger between 900-1200 Vpk, not suitable for capacitive loads.
(4) High inductive loads requires nominal control voltage; AC input models only.
(5) Increase minimum voltage by 1 V for operations from -20 to -40°C.
(6) Turn-on time for Instantaneous turn-on versions is 0.1 msec.
(7) No freezing or condensation allowed.
(8) When protected with the appropriate class and rated fuse. For detailed info please contact Crydom Technical Support.
(9) For single surge pulse Tc=25°C; Tj=125°C. For AC Output SSRs, AC RMS value of surge current equals the peak value divided by √2 (1.414).
(10) UL approved rating is the one that intersects at 40°C.
(11) Test made with a unit fixed between DIN RAIL Stoppers. Multiple devices mounted close each other, results may vary.

AGENCY APPROVALS, CONFORMANCES, ENVIRONMENTAL AND EMC

Approvals (Tested and Certified according To)	
c UL us LISTED E116949	VDE REG-Nr. 40047491
UL 508 and C22.2 No. 14	EN 62314

Conformances				Environmental	
Vibration and Shock Resistance (11)	Designed in accordance with	Resistances to heat and fire	CE	RoHS	50
IEC 61373: Category 1, Class B	IEC 60950-1	IEC 60335-1, Section 30	Directive 2006/95/EC	Directive 2011/65/EU	GBT 26572-2011

Electromagnetic Compatibility				
Generic Standard	Immunity Tests	Test Specification Level		Performance
EMC IEC 61000-6-2 Immunity for Industrial Environments	Electrostatic Discharge IEC 61000-4-2	8kV air discharge		Criterion B
		6kV contact discharge		Criterion A
	Fast transients (burst) IEC 61000-4-4	Output	2kV, 5kHz, 100kHz	Criterion B
		Input	1kV, 5kHz, 100kHz	Criterion B
	Surge IEC 61000-4-5	Output	1kV Line to Line	Criterion B
			2kV Line to Earth	Criterion B
		AC Input Option	1kV Line to Line	Criterion B
			2kV Line to Earth	Criterion B

WARNINGS

DANGER

RISK OF MATERIAL DAMAGE AND HOT ENCLOSURE
- The product's side panels may be hot, allow the product to cool before touching
- Follow proper mounting instructions including torque values
- Do not allow liquids or foreign objects to enter this product

Failure to follow these instructions can result in serious injury, or equipment damage.

HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH
- Disconnect all power before installing or working with this equipment
- Verify all connections and replace all covers before turning on power

Failure to follow these instructions will result in death or serious injury.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas
+1 (877) 502 5500 – Option 2
sales.crydom@sensata.com

Europe, Middle East & Africa
+44 (1202) 416170
ssr-info.eu@sensata.com

Asia Pacific
sales.isasia@list.sensata.com
China +86 (21) 2306 1500
Japan +81 (45) 277 7117
Korea +82 (31) 601 2004
India +91 (80) 67920890
Rest of Asia +886 (2) 27602006 ext 2808

Rev. 10/15/19 ECN 20785 FDE-07-01 Rev. B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

DR4560A45 DR4560A45J DR4560A45P DR4560A45PJ DR4560A45R DR4560D60RJ DR4560D60RP DR4560D60RPJ DR4560D45RPJ DR4560D60 DR4560D60J DR4560D60P DR4560D60PJ DR4560D60R DR4560D45J DR4560D45P DR4560D45PJ DR4560D45R DR4560D45RJ DR4560D45RP DR4560A60PJ DR4560A60R DR4560A60RJ DR4560A60RP DR4560A60RPJ DR4560D45 DR4560A45RJ DR4560A45RP DR4560A45RPJ DR4560A60 DR4560A60J DR4560A60P