


Low-noise JFET quad operational amplifier

Datasheet - production data



Related products

- See TL071 for single version
- See TL072 for dual version

Description

The TL074, TL074A, and TL074B are high-speed JFET input single operational amplifiers. Each of these JFET input operational amplifiers incorporates well matched, high-voltage JFET and bipolar transistors in a monolithic integrated circuit.

The devices feature high slew rates, low input bias and offset currents, and low offset voltage temperature coefficient.

Features

- Wide common-mode (up to V_{CC}⁺) and differential voltage range
- · Low input bias and offset current
- Low noise $e_n = 15 \text{ nV} / \sqrt{\text{Hz}}$ (typ)
- · Output short-circuit protection
- High input impedance JFET input stage
- Low harmonic distortion: 0.01% (typical)
- Internal frequency compensation
- Latch up free operation
- High slew rate: 16 V/µs (typical)

Contents TL074

Contents

1	Schematic diagram
2	Absolute maximum ratings and operating conditions 4
3	Electrical characteristics 5
4	Parameter measurement information
5	Typical applications11
6	Package information136.1SO14 package information14
7	Ordering information
8	Revision history



TL074 Schematic diagram

1 Schematic diagram

Figure 1. Circuit schematic

2 Absolute maximum ratings and operating conditions

Table 1. Absolute maximum ratings

		,		
Symbol	Parameter	TL074I, AI, BI	TL074C, AC, BC	- Unit
V _{CC}	Supply voltage ⁽¹⁾		±18	
V _i	Input voltage ⁽²⁾		±15	V
V _{id}	Differential input voltage ⁽³⁾		±30	
P _{tot}	Power dissipation		680	mW
R _{thja}	Thermal resistance junction to ambient ⁽⁴⁾⁽⁵⁾ SO14		105	- °C/W
R _{thjc}	Thermal resistance junction to case ⁽⁴⁾⁽⁵⁾ SO14		31	C/VV
	Output short-circuit duration ⁽⁶⁾	lı	nfinite	
T _{oper}	Operating free-air temperature range	-40 to +125	0 to +70	°C
T _{stg}	Storage temperature range -65 to +150		to +150	
	HBM: human body model ⁽⁷⁾		1	kV
ESD	MM: machine model ⁽⁸⁾		200	V
	CDM: charged device model ⁽⁹⁾	1.5		kV

All voltage values, except differential voltage, are with respect to the zero reference level (ground) of the supply voltages where the zero reference level is the midpoint between V_{CC}⁺ and V_{CC}⁻.

- 2. The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 volts, whichever is less.
- 3. Differential voltages are the non-inverting input terminal with respect to the inverting input terminal.
- 4. Short-circuits can cause excessive heating. Destructive dissipation can result from simultaneous short-circuits on all amplifiers.
- Rth are typical values.
- The output may be shorted to ground or to either supply. Temperature and/or supply voltages must be limited to ensure that the dissipation rating is not exceeded.
- Human body model: 100pF discharged through a 1.5kΩ resistor between two pins of the device, done for all couples of pin
 combinations with other pins floating.
- Machine model: a 200pF cap is charged to the specified voltage, then discharged directly between two pins of the device with no external series resistor (internal resistor < 5Ω), done for all couples of pin combinations with other pins floating.
- Charged device model: all pins plus package are charged together to the specified voltage and then discharged directly to the ground.

Table 2. Operating conditions

Symbol	Parameter	TL074I, AI, BI	Unit	
V _{CC}	Supply voltage	6 to	V	
T _{oper}	Operating free-air temperature range	-40 to +125	0 to +70	°C



3 Electrical characteristics

Table 3. V_{CC} = ±15 V, T_{amb} = +25 °C (unless otherwise specified)

Cumbal	Parameter	TL074I,AC,AI, BC,BI			TL074C			- Unit
Symbol	Farameter		Тур.	Max.	Min.	Тур.	Max.	Unit
V _{io}	Input offset voltage (R_s = 50 Ω) T_{amb} = +25°C TL074 TL074A TL074B $T_{min} \le T_{amb} \le T_{max}$ TL074 TL074A TL074B		3 3 1	10 6 3 13 7 5		3	10	mV
DV _{io}	Input offset voltage drift		10			10		μV/°C
l _{io}	Input offset current $T_{amb} = +25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$		5	100 4		5	100 10	pA nA
I _{ib}	Input bias current -note ⁽¹⁾ $T_{amb} = +25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$		20	200 20		30	200 20	pA nA
A _{vd}	Large signal voltage gain R _L = $2k\Omega$, V _o = $\pm 10V$ T_{amb} = $+25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$	50 25	200		25 15	200		V/mV
SVR	Supply voltage rejection ratio ($R_S = 50\Omega$) $T_{amb} = +25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$	80 80	86		70 70	86		dB
I _{CC}	Supply current, no load $T_{amb} = +25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$		1.4	2.5 2.5		1.4	2.5 2.5	mA
V _{icm}	Input common mode voltage range	±11	+15 -12		±11	+15 -12		V
CMR	Common mode rejection ratio ($R_S = 50\Omega$) $T_{amb} = +25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$	80 80	86		70 70	86		dB
I _{os}	Output short-circuit current $T_{amb} = +25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$	10 10	40	60 60	10 10	40	60 60	mA
±V _{opp}	Output voltage swing $ T_{amb} = +25^{\circ}C \ RL = 2k\Omega $ $RL = 10k\Omega $ $T_{min} \le T_{amb} \ \le T_{max} \ RL = 2k\Omega $ $RL = 10k\Omega $	10 12 10 12	12 13.5		10 12 10 12	12 13.5		V
SR	Slew rate $V_{in} = 10V$, $R_L = 2k\Omega$, $C_L = 100pF$, unity gain	8	13		8	13		V/µs



Electrical characteristics TL074

Table 3. V_{CC} = ±15 V, T_{amb} = +25 °C (unless otherwise specified) (continued)

Symbol	Parameter	TL074I,AC,AI, BC,BI			TL074C			Unit
Symbol	Farameter		Тур.	Max.	Min.	Тур.	Max.	Unit
t _r	Rise time V_{in} = 20mV, R_L = 2k Ω , C_L = 100pF, unity gain		0.1			0.1		μs
K _{ov}	Overshoot V_{in} = 20mV, R_L = 2k Ω , C_L = 100pF, unity gain		10			10		%
GBP	Gain bandwidth product V_{in} = 10mV, R_L = 2k Ω , C_L = 100pF, = 100kHz	2	3		2	3		MHz
R _i	Input resistance		10 ¹²			10 ¹²		Ω
THD	Total harmonic distortion f= 1kHz, R_L = 2k Ω C _L = 100pF, A_v = 20dB, V_o = 2 V_{pp})		0.01			0.01		%
e _n	Equivalent input noise voltage $R_S = 100\Omega$, f = 1kHz		15			15		$\frac{\text{nV}}{\sqrt{\text{Hz}}}$
Øm	Phase margin		45			45		degrees
V ₀₁ /V ₀₂	Channel separation A _v = 100		120			120		dB

The input bias currents are junction leakage currents which approximately double for every 10° C increase in the junction temperature.

47/

TL074 Electrical characteristics

Figure 2. Maximum peak-to-peak output voltage Figure 3. Maximum peak-to-peak output voltage versus frequency




Figure 4. Maximum peak-to-peak output voltage Figure 5. Maximum peak-to-peak output voltage versus frequency versus free air temperature





Figure 6. Maximum peak-to-peak output voltage Figure 7. Maximum peak-to-peak output voltage versus load resistance versus supply voltage




57/

DocID2297 Rev 5 7/18

Electrical characteristics TL074

Figure 8. Input bias current versus free air temperature

Figure 9. Large signal differential voltage amplification versus free air temperature







Figure 10. Large signal differential voltage amplification and phase shift versus frequency

Figure 11. Total power dissipation versus free air temperature








Figure 12. Supply current per amplifier versus Figure 13. Common mode rejection ratio versus free air temperature free air temperature






TL074 Electrical characteristics

Figure 14. Voltage follower large signal pulse response

Figure 15. Output voltage versus elapsed time








Figure 16. Equivalent input noise voltage versus frequency

Figure 17. Total harmonic distortion versus frequency






4 Parameter measurement information

Figure 18. Voltage follower

Figure 19. Gain-of-10 inverting amplifier



577


TL074 Typical applications

5 Typical applications

 $f_O = 100kHz$ 1/4 Output A TL074 1M Ω 1/4 1μF TL074 1/4 Input \bigcirc — Output B TL074 100k Ω 100k Ω 100k Ω ____ V_{cc}+ $100 \, \mu F$ 100k Ω 1/4 Output C TL074

Figure 20. Audio distribution amplifier






Typical applications TL074

Figure 22. Output A

SECOND ORDER BANDPASS FILTER fo = 100 kHz; Q = 30; Gain = 16

Figure 23. Output B



CASCADED BANDPASS FILTER fo = 100 kHz; Q = 69; Gain = 16

TL074 Package information

6 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.



DocID2297 Rev 5 13/18

Package information TL074

6.1 SO14 package information

SEATING PLANE 0,25 mm GAGE PLANE hx45° С С Α Н Α2 Ε Α1 മ Œ Φ \blacksquare # ppp 0016019_E

Figure 24. SO14 package mechanical drawing



TL074 Package information

Table 4. SO14 package mechanical data

	Dimensions						
Def		Millimeters			Inches		
Ref.	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	1.35		1.75	0.05		0.068	
A1	0.10		0.25	0.004		0.009	
A2	1.10		1.65	0.04		0.06	
В	0.33		0.51	0.01		0.02	
С	0.19		0.25	0.007		0.009	
D	8.55		8.75	0.33		0.34	
E	3.80		4.0	0.15		0.15	
е		1.27			0.05		
Н	5.80		6.20	0.22		0.24	
h	0.25		0.50	0.009		0.02	
L	0.40		1.27	0.015		0.05	
k	0 °		8 °	0 °		8 °	
е		0.40			0.015		
ddd			0.10			0.004	

Ordering information TL074

7 Ordering information

Table 5. Order codes

Order code	Temperature range	Package	Packing	Marking
TL074IDT TL074AIDT TL074BIDT	40°C 1435°C	SO14		074I 074AI 074BI
TL074IYDT ⁽¹⁾ TL074AIYDT ⁽¹⁾ TL074BIYDT ⁽¹⁾	-40°C, +125°C		Tape and reel	074IY 074AIY 074BIY
TL074CDT TL074ACDT TL074BCDT	0°C, +70°C			074C 074AC 074BC

Qualified and characterized according to AEC Q100 and Q003 or equivalent, advanced screening according to AEC Q001 & Q 002 or equivalent.



TL074 Revision history

8 Revision history

Table 6. Document revision history

Date	Revision	Changes
28-Mar-2001	1	Initial release.
30-Jul-2007	2	Added values for R _{thja} , R _{thjc} and ESD in <i>Table 1: Absolute maximum ratings</i> . Added <i>Table 2: Operating conditions</i> . Expanded <i>Table 5: Order codes</i> . Format update.
07-Jul-2008	3	Removed information concerning military temperature ranges (TL074Mx, TL074AMx, TL074BMx). Added automotive grade order codes in <i>Table 5: Order codes</i> .
04-Jul-2012	4	Removed commercial types TL074IYD, TL074AIYD, TL074BIYD. Updated <i>Table 5: Order codes</i> .
22-Nov-2013	5	Added Related products on first page Removed DIP package mechanical information Table 5: Order codes: - removed commercial types related to DIP package: TL074IN, TL074AIN, TL074BIN, TL074CN, TL074ACN, TL074BCN; - removed commercial types related to tube packing: TL074ID, TL074AID, TL074BID, TL074CD, TL074ACD, TL074BCD; - changed operating temperature range for TL074IDT, TL074AIDT, TL074BIDT, TL074IYDT, TL074AIYDT, TL074BIYDT from -40 °C, +105 °C to -40 °C, +125 °C; - updated footnote for automotive parts.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2013 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

