



Circuits	Dimension	
	A	B
4	8.45	2.54
6	10.99	5.08
8	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48



Specifications:

Current rating: 1.5A AC,DC
Voltage rating: 230V AC, DC
Contact resistance: 20m ohm Max
Insulation resistance: 1000M ohm Min
Withstanding voltage: AC 500V AC/minute
Operating Temperature: -40°C ~ +105°C

Materials and Finish

Insulator: PBT (UL94V-0)
Contact material: Phosphor Bronze
Finish: Tin Plated

How to Order

TMM-X-X-XX-X

Type _____


- 1-IDC Male
- 2-IDC Plug
- 3-DIP Male Straight
- 4-DIP Female Straight
- 5-DIP Female R/A
- 6-SMT Female Straight

Packaging

- 1 - Tape & Reel with vacuum cap
 - 2 - Tube
 - 3 - Bag
 - 4 - Tape & Reel without vacuum cap
- Number of Positions
04, 06, 08, 10, 12, 14,
16, 18, 20, 22, 24 or 26

Locking System

- 0-without lock
- L-with lock



PCB Layout

TOLERANCE (mm)			APPROVALS	DATE	TITLE TMM Series IDC Transition Plug	AMPHENOL	
X.	±0.3	DRAIN Stephane		2009/10/07		Amphenol European Design Center	
XX	±0.2	CHECKED Rob		2009/10/07		Scale N.A. Sheet 1 of 1	
XXX	±0.15	APPROVED Rob		2009/10/07		REV. E	
UNLESS OTHERWISE SPECIFIED			UNIT: mm	SIZE: A4	DRAWING N°: TMM-2-0-XX-X		