


Hour meters / timers, electromechanical

Timers for DIN rail mounting	Micro DIN rail housing (AC+DC)	SHK07.1
-------------------------------------	---------------------------------------	----------------



The micro timers SHK07.1 feature a very high shock resistance. These base and DIN rail mount counters can be used in many different fields of application. These non-resettable counters are extremely tamper-proof.

Characteristics

- 7-digit micro hour meter.
- DIN rail mount according to EN 50022.
- Base mount counter.
- High shock resistance.
- Low power consumption.
- Small dimensions.
- Magnified large figures.
- Display range 99999.99 h.

Benefits

- Wide voltage range 4.5 ...35 V DC, 20 ... 264 V AC.
- Data retention in case of power failure.
- Long service life.

Applications

General time measurement, integration in control cabinets.

Type series

Description	Mounting	Type
Timer	DIN rail 35 mm [1.38"] acc. to DIN EN 50022	SHK07.1

Technical data

Electrical connection	clamp terminal tightening torque max.	up to 2.5 mm ² [AWG13] 0.8 Nm
Power consumption (count pulses every 36 s with a pulse duration of 32 ms)		
	at U _B = 5 V DC	typ. 82 mW
	at U _B = 12 V DC	typ. 135 mW
	at U _B = 24 V DC	typ. 135 mW
	at U _B = 22 ... 32 V DC	typ. 170 mW
	20 ... 30 V AC	approx. 0.43 VA
	100 ... 130 V AC	approx. 0.82 VA
	187 ... 264 V AC	approx. 1.8 VA
On time		100 %
Number of digits		7 (99999.99 h)
Accuracy		22.5 ppm at 25 °C [77 °F]
EMC standards		EN 55011 class B EN 61000-6-2, EN 61000-6-3
Device safety	designed to protection class application area	EN 61010 part 1 2 pollution level 2
Height of figures		1.2 x 4 mm [0.047 x 0.016"]
Color of figures		white and red on black
Operating temperature	AC	-10 °C ... +50 °C [+14 °F ... +122 °F] (non-condensing)
	DC	-10 °C ... +60 °C [+14 °F ... +140 °F] (non-condensing)

Relative humidity at +30 °C [+86 °F]	≤ 80 % (non-condensing)
Altitude	up to 2000 m [6562']
Mounting position	horizontal, other on request
Protection	up to IP52 depends on version
Housing	plastic PC (Polycarbonate)
Weight	approx. 55 g [1.94 oz]

Options

Temperature range	-20 °C +70 °C [-4 °F ... +158 °F]
--------------------------	--


Approvals

CE compliant in accordance with		
	EMC Directive	2014/30/EU
	RoHS Directive	2011/65/EU
	Low Voltage Directive	2014/35/EU
UKCA compliant in accordance with		
	EMC Regulations	S.I. 2016/1091
	RoHS Regulations	S.I. 2012/3032
	Low Voltage Regulations	S.I. 2016/1101

Hour meters / timers, electromechanical

Timers for DIN rail mounting **Micro DIN rail housing (AC+DC)** **SHK07.1**

Timer for DIN rail mount
Type SHK07.1



1) Electrical connection

Type	Display	Voltage	Art. no.			
			4.5 ... 35 V	20 ... 30 V	100 ... 130 V	187 ... 264 V
SHK07.1	7 digits	AC (50...60 Hz)		3.102.101.310	3.102.101.312	3.102.101.313 ¹⁾
	7 digits	DC	3.102.101.383 ¹⁾			