

# PRODUCT DATASHEET

## LEDinestra 1000 mm 75 9.9 W/2700 K S14s

LEDinestra® DIM | Dimmable tubular LED lamps



---

### Areas of application

- Ideal for mirror lighting
- Hotels, restaurants
- Domestic applications
- Outdoor applications only in suitable luminaires

---

### Product benefits

- Very long lifetime of up to 25,000 h
- Low energy consumption
- Good color rendering

---

### Product features

- LED alternative to tubular incandescent lamps
- Dimmable (with many common dimmers, see also [www.ledvance.com/dim](http://www.ledvance.com/dim))
- For especially uniform illumination
- Mercury-free lamps
- Bulb made from glass




## TECHNICAL DATA

### Electrical data

Nominal wattage	9.9 W
Construction wattage	9.90 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	75 W
Nominal current	58 mA
Type of current	AC
Inrush current	0.5 mA
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	80
Max. lamp no. on circuit break. 16 A (B)	150
Total harmonic distortion	87.4 %
Power factor $\lambda$	0.74

### Photometrical data

Luminous flux	1055 lm
Nominal useful luminous flux 90°	1055 lm
Luminous efficacy	106 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Color rendering index Ra	$\geq 80$
Light color	827
Standard deviation of color matching	$\leq 6$ sdcn
Rated LLMF at 6,000 h	0.80
Flickering metric (Pst LM)	0.2
Stroboscope effect metric (SVM)	0.7



### Light technical data

Beam angle	200 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s
Rated beam angle (half peak value)	200.00 °

### Dimensions & Weight

Overall length	1000.00 mm
Diameter	29.00 mm
Maximum diameter	29 mm
Product weight	245.00 g

### Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
Maximum temperature at tc test point	50 °C

### Lifespan

Nominal lamp life time	25000 h
Number of switching cycles	100000
Lumen maintenance at end of serv	0.70
Rated lamp survival factor at 6,000	≥ 0.90

### Additional product data

Base (standard designation)	S14s
Mercury content	0.0 mg
Design / version	Frosted

### Capabilities

Dimmable	Yes
----------	-----

### Certificates & Standards

Energy efficiency class	F 1)
Energy consumption	10.00 kWh/1000h
Type of protection	IP20
Standards	CE / EAC
Photobiological safety group acc. to EN62778	RG0

1) Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

### Country-specific categorizations

Order reference	LEDINES100CM 9,
-----------------	-----------------

### LOGISTICAL DATA


Temperature range at storage	-20...+80 °C
------------------------------	--------------

### Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	NDLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	S14s
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Standby power	0.00 W
Networked standby power for CLS	0.00 W
Claim of equivalent power	Yes
Length	1000.00 mm
Height	29.00 mm
Width	29.00 mm
Chromaticity coordinate x	0,458
Chromaticity coordinate y	0,410
R9 Colour rendering index	7.9
Beam angle	SPHERE_360
Survival factor	0.90
Displacement factor	0.74

LED light source replaces a fluorescent light source	not applicable
EPREL ID	522909
Model number	AC33892

## DOWNLOAD DATA

DOWNLOAD DATA	
	Declarations of conformity LED SPECIAL

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075607095	Folding box 1	69 mm x 55 mm x 1,085 mm	308.00 g	4.11 dm <sup>3</sup>
4058075607101	Shipping box 5	1,060 mm x 270 mm x 75 mm	2170.00 g	21.47 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## References / Links

- For dimming conformity see [www.ledvance.com/dim](http://www.ledvance.com/dim)
- For Guarantee see [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.