
life.augmented

STPS15H100C

High voltage power Schottky rectifier

Datasheet - production data



Features

- · Negligible switching losses
- Low leakage current
- Good trade off between leakage current and forward voltage drop
- Low thermal resistance
- Avalanche capability specified
- ECOPACK[®]2 compliant component for DPAK on demand

Description

Dual center tab Schottky rectifier suited for switched mode power supply and high frequency DC to DC converters.

Packaged in DPAK, this device is intended for use in high frequency inverters.

Table 1. Device summary

Symbol	Value
I _{F(AV)}	2 x 7.5 A
V _{RRM}	100 V
Tj	175 °C
V _F (typ)	0.62 V

Characteristics STPS15H100C

1 Characteristics

Table 2. Absolute ratings (limiting values per diode at 25 °C unless otherwise specified)

Symbol	Paramete	Value	Unit			
V_{RRM}	Repetitive peak reverse voltage	100	V			
I _{F(RMS)}	Forward rms current	10	Α			
1	Average forward current, $\delta = 0.5$, square	$T_{c} = 135 {}^{\circ}C^{(1)}$	Per diode	7.5	Α	
^I F(AV)	wave		Per device	15		
I _{FSM}	Surge non repetitive forward current	75	Α			
P _{ARM}	Repetitive peak avalanche power	475	W			
T _{stg}	Storage temperature range	-65 to +175	°C			
T _j	Maximum operating junction temperature ⁽²⁾	175	°C			

^{1.} Value based on $R_{th(j-c)}$ max (per diode)

Table 3. Thermal resistance

Symbol	Parameter	Value	Unit	
D	Junction to case	Per diode	4	
R _{th(j-c)}	Junction to case	Total	2.4	°C/W
R _{th(c)}	Coupling		0.7	

When the diodes 1 and 2 are used simultaneously:

 $\Delta T_{j}(diode 1) = P(diode 1) \times R_{th(j-c)}(Per diode) + P(diode 2) \times R_{th(c)}$

Table 4. Static electrical characteristics (per diode)

Symbol	Parameter	Test Conditions		Min.	Тур.	Max.	Unit
ı (1)	I _R ⁽¹⁾ Reverse leakage current	T _j = 25 °C	$V_R = V_{RRM}$			3	μΑ
'R`		T _j = 125 °C			1.3	4	mA
	V _F ⁽²⁾ Forward voltage drop	T _j = 25 °C	I _F = 7.5 A			0.8	
		T _j = 125 °C	I _F = 7.5 A		0.62	0.67	
V (2)		T _j = 25 °C	I _F = 12 A			0.85	V
V _F , / I C		T _j = 125 °C	I _F = 12 A		0.68	0.73	V
		T _j = 25 °C	I _F = 15 A			0.89	
		T _j = 125 °C	I _F = 15 A		0.71	0.76	

^{1.} $t_p = 5 \text{ ms}, \delta < 2\%$


To evaluate the conduction losses use the following equation:

$$P = 0.58 \times I_{F(AV)} + 0.012 I_{F}^{2}_{(RMS)}$$

^{2.} $\frac{dPtot}{dTj} < \frac{1}{Rth(j-a)}$ condition to avoid thermal runaway for a diode on its own heatsink

^{2.} $t_p = 380 \ \mu s, \ \delta < 2\%$

STPS15H100C Characteristics








Figure 3. Normalized avalanche power derating versus pulse duration at T_j = 125 °C


PARM(tp)
PARM(10 µs)

0.01

1 10 100 1000











DocID8562 Rev 7

3/8

Characteristics STPS15H100C





577

4/8 DocID8562 Rev 7

STPS15H100C **Package Information**

Package Information 2

- Epoxy meets UL94,V0
- Cooling method: by conduction (C)

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

2.1 **DPAK** package information




Figure 9. DPAK package outline

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.




5/8 DocID8562 Rev 7

Package Information STPS15H100C

Table 5. DPAK package mechanical data

	Dimensions					
Ref.	Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	2.18		2.40	0.085		0.094
A1	0.90		1.10	0.035		0.043
A2	0.03		0.23	0.001		0.009
b	0.64		0.90	0.025		0.035
b4	4.95		5.46	0.194		0.214
С	0.46		0.61	0.018		0.024
c2	0.46		0.60	0.018		0.023
D	5.97		6.22	0.235		0.244
D1	4.95		5.60	0.194		0.220
E	6.35		6.73	0.250		0.264
E1	4.32		5.50	0.170		0.216
е		2.28			0.090	
e1	4.40		4.70	0.173		0.185
Н	9.35		10.40	0.368		0.409
L	1.00		1.78	0.039		0.070
L2			1.27			0.050
L4	0.60		1.02	0.023		0.040
V2	-8°		+8°	-8°	_	8°

Figure 10. DPAK footprint dimensions (in mm)



57

6/8 DocID8562 Rev 7

3 Ordering Information

Table 6. Ordering information

Order code	Marking	Package	Weight	Base qty	Delivery mode
STPS15H100CB	S15H100	DPAK	0.30 g	75	Tube
STPS15H100CB-TR	S15H100	DPAK	0.30 g	2500	Tape and reel

4 Revision history

Table 7. Document revision history

Date	Revision	Description of Changes	
Mar-2004	3	Last issue	
08-Jun-2006	4	Reformatted to current standard. Added IPAK.	
01-Aug-2014	5	Updated DPAK package information and reformatted to current standard. Removed IPAK.	
17-Sep-2014	6	Updated Figure 3 and Figure 11.	
18-Dec-2015	7	Updated DPAK package information and reformatted to current standard.	



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2015 STMicroelectronics - All rights reserved

577

8/8 DocID8562 Rev 7