


# JSM Series Sub-Miniature Slide Switches

## Features/Benefits

- RoHS compliant and meets all requirements of RoHS directive 2002/95EC, Halogen Free
- Positive detent
- Low profile
- IR reflow to 260° solder profile
- Surface and thru hole mounting
- Maintained and momentary functions
- SPDT, SP3T models

## Typical Applications

- Telecommunication products
- Computer peripherals
- Thermostat select switch
- Instrumentations



## Specifications

CONTACT RATING: 4 VDC @ 0.3A  
 ELECTRICAL LIFE: 10,000 make-and-break cycles at full load.  
 CONTACT RESISTANCE: 70 m Ω max.  
 INSULATION RESISTANCE: 100 M Ω min. @ 500V.  
 DIELECTRIC STRENGTH: 100 VAC min. @ sea level.  
 OPERATING TEMPERATURE: -10°C to +60°C  
 STORAGE TEMPERATURE: -30°C to +85°C


**NOTE:** Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

## Materials

HOUSING: LCP, Glass filled (Halogen free)  
 ACTUATOR: 4/6 nylon (UL94V-2), black.  
 CONTACTS: Beryllium copper, silver plated.  
 TERMINALS: Brass, silver plated.  
 COVER: Stainless steel  
 RETURN SPRING: Stainless steel



Slide






Third Angle Projection

Dimensions are shown: Inches (mm)  
 Specifications and dimensions subject to change





# JSM Series Sub-Miniature Slide Switches

Slide




**JSM08022SAQNL**  
SPDT Surface Mount  
Momentary only

**RECOMMENDED PC BOARD LAY OUT**  
SCALE 5:1





**CARRIER TAPE**



**COVER TAPE**





PACKAGING QUANTITY:  
1,800 PCS/REEL




**JSM08011SAQNR**  
SPDT Surface Mount  
Momentary only

**RECOMMENDED PC BOARD LAY OUT**



**PC BOARD MOUNTING SURFACE**


**CARRIER TAPE**



**COVER TAPE**





PACKAGING QUANTITY:  
1,800 PCS/REEL





Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change







# JSM Series Sub-Miniature Slide Switches



JSM08011SAQNL  
SPDT Surface Mount  
Momentary only





Shown in position 1





PACKAGING QUANTITY:  
1,800 PCS/REEL

Slide



JSM07011SAQNR  
SP3T Surface Mount  
Momentary one side  
& Maintained the other



Shown in position 2




# JSM Series Sub-Miniature Slide Switches


Slide



**JSM07011SAQNL**  
SP3T Surface Mount  
Momentary one side  
& Maintained the other



**Packaging for JSM07011SAQNR and JSM07011SAQNL**






Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change

[www.ckswitches.com](http://www.ckswitches.com)




# JSM Series Sub-Miniature Slide Switches



JSM05000SAQN  
SP3T Surface Mount  
Momentary both  
sides



RECOMMENDED PC BOARD LAY OUT  
SCALE 5:1



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change



Slide