

November 2018



- Pletronics' SM55 Series is a quartz crystal controlled precision square wave generator with a CMOS output.
- The package is designed for high density surface mount designs.
- This is a low cost mass produced oscillator.
- Tape and Reel or cut tape packaging is available.
- 0.8 to 160 MHz
- 3.2 x 5 mm LCC Ceramic Package
- Enable/Disable Function
- Disable function includes low standby power mode
- Fundamental or 3rd Overtone Crystals used
- Low Jitter

Pletronics Inc. certifies this device is in accordance with the RoHS 6/6 (2011/65/EC) and WEEE (2002/96/EC) directives.

Pletronics Inc. guarantees the device does not contain the following: Cadmium, Hexavalent Chromium, Lead, Mercury, PBB's, PBDE's Weight of the Device: 0.064 grams Moisture Sensitivity Level: 1 As defined in J-STD-020C Second Level Interconnect code: e4

Absolute Maximum Ratings:

Parameter	Unit
V _{cc} Supply Voltage	-0.5V to +7.0V
Vi Input Voltage	-0.5V to V _{cc} + 0.5V
Vo Output Voltage	-0.5V to V _{cc} + 0.5V
lo Output Current	+25 mA to -25 mA

Thermal Characteristics

The maximum die or junction temperature is 155°C

The thermal resistance junction to board is 30 to 50° C/Watt depending on the solder pads, ground plane and construction of the PCB.



November 2018

Part Number:

SM55	45	т	Е	V	- 75.0M	-xx	
							Packaging code or blank T250 = 250 per Tape and Reel T500 = 500 per Tape and Reel T1K = 1000 per Tape and Reel
							Frequency in MHz
							Supply Voltage V _{cc} V = 3.3V <u>+</u> 10%
							Optional Enhanced OTR Blank = Temp. range -10 to +70°C C = Temp. range -20 to +70°C E = Temp. range -40 to +85°C
							Series Model
							Frequency Stability 45 = ± 50 ppm 44 = ± 25 ppm 20 = ± 20 ppm
							Series Model

Part Marking and Legend:

P ff.fff MP ff.fff MPLE SM55• YMDxx• YYWWxx• YMDxx	P5xYWWx • <i>ff.fff</i> M	5xYWWxx <i>ff.fff</i> M • PLE <i>xx</i>	P fff.f M • YMDxx
--	------------------------------	---	----------------------

P or PLE = Pletronics ff.fff M or ff.ff M = Frequency in MHz YYWW or YWW or YMD = Date of Manufacture (year and week, or year-month-day) All other marking is internal factory codes

Specifications such as frequency stability, supply voltage and operating temperature range, etc. are not identified from the marking. External packaging labels and packing list will correctly identify the ordered Pletronics part number.

Code	odes for Date Code YMD																	
Code	6	7	8	9	0	Cod	le A	В	С	D	Е	F	G	Н	J	K	L	М
Year	2016	2017	201	8 201	9 202	0 Mon	th JA	N FEB	MAF	R APF	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
							1											
C	Code		1	2	3	4	5	6	7	8	9	Α	В	С	D	Е	F	G
	Day		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
C	Code		Η	J	К	L	М	Ν	Ρ	R	Т	U	V	W	Х	Y	Z	
	Day		17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	



November 2018

Electrical Specification for 3.30V ±10% over the specified temperature range

Item	Min	Max	Unit	Condition
Frequency Range	0.8	160	MHz	
Frequency Accuracy "45"	-50	+50	ppm	For all supply voltages, load changes, aging for 1
"44"	-25	+25		year, shock, vibration and temperatures
"20"	-20	+20		
Output Waveform		CMOS	6	
Output High Level	90	-	%	of V _{cc} (See load circuit)
Output Low Level	-	10	%	
Output Symmetry	45	55	%	at 50% point of V_{cc} (See load circuit)
Jitter	-	0.6	pS RMS	12 KHz to 20 MHz from the output frequency
	-	2.5	pS RMS	10 Hz to 1 MHz from the output frequency
Enable/Disable Internal Pull-up	50	-	Kohm	to V _{cc}
V disable	-	30	%	of V_{cc} applied to pad 1
V enable	70	-	%	
Output leakage V _{OUT} = V _{CC}	-10	+10	uA	Pad 1 low, device disabled
V _{OUT} = 0V	-10	+10	uA	
Standby Current I _{cc}	-	3	uA	
Enable time	-	100	nS	Time for output to reach a logic state
Disable time	-	100	nS	Time for output to reach a high Z state
Start up time	-	3	mS	Time for output to reach specified frequency
Operating Temperature Range	-10	+70	°C	Standard Temperature Range
	-20	+70	°C	Extended Temperature Range "C" Option
	-40	+85	°C	Extended Temperature Range "E" Option
Storage Temperature Range	-55	+125	°C	

Typical phase noise plot for 5 oscillators at different output frequencies.





November 2018

Electrical Specification for 3.30V ±10% over the specified temperature range

ltem	Тур	Мах	Unit	Condition				
Output $T_{\mbox{\tiny RISE}}$ and $T_{\mbox{\tiny FALL}}$	-	5	nS	< 35 MHz	$C_{LOAD} = 15 \text{ pF}$			
	-	3	nS	<u>></u> 35 MHz and < 70 MHz	See Load Circuit			
	-	2.5	nS <u>></u> 70 MHz and < 110 MHz					
	-	2	nS	<u>></u> 110 MHz				
	-	8	nS	< 35 MHz	C _{LOAD} =30 pF			
	-	5	nS	<u>></u> 35 MHz and < 70 MHz	See Load Circuit			
	-	3	nS	<u>></u> 70 MHz and < 110 MHz				
	-	2	nS	<u>></u> 110 MHz				
V_{cc} Supply Current (I _{cc})	-	9	mA	< 8 MHz	C _{LOAD} = 15 pF			
	-	11	mA	<u>></u> 8 MHz and < 16 MHz				
	-	17	mA	<u>></u> 16 MHz and < 35 MHz				
	-	26	mA	<u>></u> 35 MHz and <70 MHz				
	-	50	mA	<u>></u> 70 MHz and < 110 MHz				
	-	70	mA	<u>></u> 110 MHz				
	-	12	mA	< 8 MHz	C _{LOAD} = 30 pF			
	-	16	mA	<u>></u> 8 MHz and < 16 MHz				
	-	22	mA	<u>></u> 16 MHz and < 35 MHz				
	-	35	mA	<u>></u> 35 MHz and <70 MHz				
	-	57	mA	<u>></u> 70 MHz and < 110 MHz				
	-	90	mA	<u>></u> 110 MHz				

Specifications with Pad 1 E/D open circuit



November 2018



Reliability: Environmental Compliance

Parameter	Condition				
Mechanical Shock	MIL-STD-883 Method 2002, Condition B				
Vibration	MIL-STD-883 Method 2007, Condition A				
Solderability	MIL-STD-883 Method 2003				
Thermal Shock	MIL-STD-883 Method 1011, Condition A				

ESD Rating

Model	Minimum Voltage	Conditions
Human Body Model	1500	MIL-STD-883 Method 3115
Charged Device Model	1000	JESD 22-C101

Package Labeling

Label is 1" x 2.6" (25.4mm x 66.7mm) Font is Courier New Bar code is 39-Full ASCII



Label is 1" x 2.6" (25.4mm x 66.7mm) Font is Arial

> RoHS Compliant 2nd LvL Interconnect Category=e4 Max Safe Temp=260C for 10s 2X Max



November 2018

Mechanical:



Contacts :

Gold 11.8 to 32.7 µinches (0.3 to 0.83 µm) over Nickel 50 to 350 µinches (1.27 to 8.89 µm)

Pad	Function	Note
1	Output Enable/Disable	When this pad is not connected the oscillator shall operate. When this pad is logic low the output will be inhibited (high impedance state.) Recommend connecting this pad to V_{cc} if the oscillator is to be always on.
2	Ground (GND)	
3	Output	
4	Supply Voltage (V _{cc})	Recommend connecting appropriate power supply bypass capacitors as close as possible.



Layout and application information

For Optimum Jitter Performance, Pletronics recommends:

- a ground plane under the device
- no large transient signals (both current and voltage) should be routed under the device
- do not layout near a large magnetic field such as a high frequency switching power supply
- do not place near piezoelectric buzzers or mechanical fans.



November 2018

Reflow Cycle (typical for lead free processing)



Tape and Reel: available for quantities of 250 to 1000 per reel, cut tape for < 250

Constant Dimensions Table 1											
Tape Size	D0	D1 Min	E1	P0	P2	S1 Min	T Max	T1 Max			
8mm		1.0			2.0						
12mm	1.5	1.5	1.75	4.0	<u>+</u> 0.05						
16mm	+0.1 -0.0	1.5	<u>+</u> 0.1	<u>+</u> 0.1	2.0	0.6	0.6	0.1			
24mm		1.5			<u>+</u> 0.1						

	Variable Dimensions Table 2									
Tape Size	B1 Max	E2 Min	F	P1	T2 Max	W Max	Ao, Bo & Ko			
16 mm	12.1	14.25	7.5 <u>+</u> 0.1	8.0 <u>+</u> 0.1	8.0	16.3	Note 1			

Note 1: Embossed cavity to conform to EIA-481-B

Dimensions in mm

Not to scale





		REE			
А	inches	7.0	10.0	13.0	
	mm	mm 177.8 254		330.2	
в	inches	2.50	4.00	3.75	
	mm	63.5	101.6	95.3	Tape
с	mm	13	width		
D	mm	16.4 +2.0 -0.0	16.4 +2.0 -0.0	16.4 +2.0 -0.0	16.0

Reel dimensions may vary from the above



November 2018

IMPORTANT NOTICE

Pletronics Incorporated (PLE) reserves the right to make corrections, improvements, modifications and other changes to this product at anytime. PLE reserves the right to discontinue any product or service without notice. Customers are responsible for obtaining the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to PLE's terms and conditions of sale supplied at the time of order acknowledgment.

PLE warrants performance of this product to the specifications applicable at the time of sale in accordance with PLE's limited warranty. Testing and other quality control techniques are used to the extent PLE deems necessary to support this warranty. Except where mandated by specific contractual documents, testing of all parameters of each product is not necessarily performed.

PLE assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using PLE components. To minimize the risks associated with the customer products and applications, customers should provide adequate design and operating safeguards.

PLE products are not designed, intended, authorized or warranted to be suitable for use in life support applications, weapons, weapon systems or space applications, devices or systems or other critical applications that may involve potential risks of death, personal injury or severe property or environmental damage. Inclusion of PLE products in such applications is understood to be fully at the risk of the customer. Use of PLE products in such applications requires the written approval of an appropriate PLE officer. Questions concerning potential risk applications should be directed to PLE.

PLE does not warrant or represent that any license, either express or implied, is granted under any PLE patent right, copyright, artwork or other intellectual property right relating to any combination, machine or process which PLE product or services are used. Information published by PLE regarding third-party products or services does not constitute a license from PLE to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from PLE under the patents or other intellectual property of PLE.

Reproduction of information in PLE data sheets or web site is permissible only if the reproduction is without alteration and is accompanied by associated warranties, conditions, limitations and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. PLE is not responsible or liable for such altered documents.

Resale of PLE products or services with statements different from or beyond the parameters stated by PLE for that product or service voids all express and implied warranties for the associated PLE product or service and is an unfair or deceptive business practice. PLE is not responsible for any such statements.

Contacting Pletronics Inc.

Pletronics Inc. 19013 36th Ave. West Lynnwood, WA 98036-5761 USA Tel: 425-776-1880 Fax: 425-776-2760 E-mail: <u>ple-sales@pletronics.com</u> URL: www.pletronics.com

Copyright © 2018 Pletronics Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pletronics:

SM5545TEV-42.0M
SM5545TEV-44.0M
SM5545TEV-48.0M
SM5545TEV-49.0195M
SM5545TEV-5.0M

SM5545TEV-50.0M
SM5545TEV-50.505M
SM5545TEV-54.0M
SM5545TEV-6.144M
SM5545TEV-60.0M

SM5545TEV-62.5M
SM5545TEV-64.0M
SM5545TEV-66.0M
SM5545TEV-66.667M
SM5545TEV-68.40M

SM5545TEV-7.3728M
SM5545TEV-75.0M
SM5545TEV-80.0M
SM5544TEV-100.0M
SM5545TEV-125.0M

SM5545TEV-24.0M
SM5545TEV-75.0M
SM5545TEV-1.544M
SM5545TEV-12.0M
SM5545TEV-10.0M

SM5545TEV-106.25M
SM5545TEV-11.0592M
SM5545TEV-11.50M
SM5545TEV-12.0M
SM5545TEV-12.288M

SM5545TEV-125.0M
SM5545TEV-133.0M
SM5545TEV-13.333M
SM5545TEV-12.0M
SM5545TEV-12.288M

SM5545TEV-125.0M
SM5545TEV-12.0M
SM5545TEV-12.0M
SM5545TEV-12.0M
SM5545TEV-12.0M

SM5545TEV-126.0M
SM5545TEV-20.0M
SM5545TEV-20.0M
SM5545TEV-20.275M

SM5545TEV-22.70M
SM5545TEV-23.0M
SM5545TEV-27.0M
SM5545TEV-30.072M

SM5545TEV-23.0M
SM5545TEV-23.0M
SM5545TEV-23.0M
SM5545TEV-23.0M

SM5545TEV-33.33M
SM5545TEV-36.0M
<