

High Performance Schottky Rectifier, 1 A



SMA (DO-214AC)

PRODUCT SUMMARY				
Package SMA (DO-214AC)				
I _{F(AV)}	1 A			
V_{R}	60 V			
V _F at I _F	0.63			
I _{RM}	7.5 mA at 125 °C			
T _J max.	150 °C			
Diode variation	Single			
E _{AS}	2.0 mJ			

FEATURES

- · Small foot print, surface mountable
- Low forward voltage drop



- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION

The VS-10MQ060NTRPbF surface mount Schottky rectifier has been designed for applications requiring low forward drop and very small foot prints on PC boards. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	CHARACTERISTICS VALUES UNITS			
I _{F(AV)}	Rectangular waveform	1	Α		
V_{RRM}		60	V		
I _{FSM}	t _p = 5 μs sine	40	Α		
V _F	1.5 A _{pk} , T _J = 125 °C	0.63	V		
T_J	Range	-55 to +150	°C		

VOLTAGE RATINGS			
PARAMETER	SYMBOL	VS-10MQ060NTRPbF	UNITS
Maximum DC reverse voltage	V_{R}	60	V
Maximum working peak reverse voltage	V_{RWM}	80	V

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward current		50 % duty cycle at T_L = 120 °C, rectangular waveform On PC board 9 mm ² island (0.013 mm thick copper pad area)		1.5	٨
See fig. 4	I _{F(AV)}	50 % duty cycle at $T_L = 129$ °C, On PC board 9 mm ² island (0.01)		1	A
Maximum peak one cycle non-repetitive surge current	lea.	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated	40	Α
See fig. 6	I _{FSM}	10 ms sine or 6 ms rect. pulse	V _{RRM} applied	10	Α
Non-repetitive avalanche energy	E _{AS}	T _J = 25 °C, I _{AS} = 1 A, L = 4 mH		2.0	mJ
Repetitive avalanche current	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _B typical 1.0		Α	



ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum forward voltage drop See fig. 1		1 A	T 05 °C	0.63	V
	V _{FM} ⁽¹⁾	1.5 A	T _J = 25 °C	0.71	
	VFM \''	1 A	T _J = 125 °C	0.57	
		1.5 A		0.63	
Maximum reverse leakage current See fig. 2	ı (1)	T _J = 25 °C	V _R = Rated V _R	0.5	- mA
	I _{RM} ⁽¹⁾	T _J = 125 °C		7.5	
Threshold voltage	V _{F(TO)}	T _{.I} = T _{.I} maximum		0.45	V
Forward slope resistance	r _t			86.8	mΩ
Typical junction capacitance	C _T	$V_R = 10 V_{DC}, T_J = 25 ^{\circ}C$, test signal = 1 MHz 31		pF	
Typical series inductance	L _S	Measured lead to lead 5 mm from package body 2.0		nH	
Maximum voltage rate of change	dV/dt	Rated V _R 10 000		V/µs	

Note

 $^{^{(1)}\,}$ Pulse width $<300~\mu s,$ duty cycle <2~%

THERMAL - MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	T _J ⁽¹⁾ , T _{Stg}		-55 to +150	°C
Maximum thermal resistance, junction to ambient	R _{thJA}	DC operation	80	°C/W
Approximate weight			0.07	g
Approximate weight			0.002	OZ.
Marking device		Case style SMA (DO-214AC) (similar D-64)	1	H

Note

$$^{(1)} \quad \frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}} \quad \text{thermal runaway condition for a diode on its own heatsink}$$

www.vishay.com

Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Peak Reverse Current vs. Reverse Voltage





Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage



I_{F(AV)} - Average Forward Current (A)

Fig. 4 - Maximum Average Forward Current vs.
Allowable Lead Temperature




Fig. 5 - Maximum Average Forward Dissipation vs. Average Forward Current




Fig. 6 - Maximum Peak Surge Forward Current vs. Pulse Duration


Note

(1) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$; $Pd = Forward power loss = I_{F(AV)} \times V_{FM} at (I_{F(AV)}/D)$ (see fig. 6); $Pd_{REV} = Inverse power loss = V_{R1} \times I_R (1 - D)$; I_R at $V_{R1} = 80 \%$ rated V_R



ORDERING INFORMATION TABLE

Device code



1 - Vishay Semiconductors product

2 - Current rating (10 = 1 A)

3 - M = SMA

4 - Q = Schottky "Q" series

5 - Voltage rating (060 = 60 V)

6 - N = new SMA

7 - TR = tape and reel

8 - PbF = lead (Pb)-free

ORDERING INFORMATION (Example)					
PREFERRED P/N PREFERRED PACKAGE CODE MINIMUM ORDER QUANTITY PACKAGING DESCRIPTION					
VS-10MQ060NTRPbF	5AT	7500	13" diameter plastic tape and reel		

LINKS TO RELATED DOCUMENTS				
Dimensions <u>www.vishay.com/doc?95400</u>				
Part marking information	www.vishay.com/doc?95403			
Packaging information	www.vishay.com/doc?95404			



SMA

DIMENSIONS in inches (millimeters)

DO-214AC (SMA)



Mounting Pad Layout





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

VS-10MQ060NPBF 10MQ060N 10MQ060NTR VS-10MQ060NTRPBF