

# NINA-B2 series

## Stand-alone dual-mode Bluetooth modules

### Data sheet



### Abstract

This technical data sheet describes the NINA-B2 series stand-alone dual-mode Bluetooth® modules. NINA-B2 modules come with pre-flashed application software, dual-mode Bluetooth (Bluetooth BR/EDR and Bluetooth Low Energy). The module has a number of important security features embedded, including secure boot, which ensures that only authenticated software can run on the module. This makes NINA-B2 ideal for critical IoT applications where security is important.

# Document information

|                               |   |             |
|-------------------------------|---|-------------|
| <b>Title</b>                  | <b>NINA-B2 series</b>                   |             |
| <b>Subtitle</b>               | Stand-alone dual-mode Bluetooth modules |             |
| <b>Document type</b>          | Data sheet                              |             |
| <b>Document number</b>        | UBX-18006649                            |             |
| <b>Revision and date</b>      | R11                                     | 19-Dec-2022 |
| <b>Disclosure Restriction</b> | C1 - Public                             |             |

| <b>Product status</b>                | <b>Corresponding content status</b> |  |
|--------------------------------------|-------------------------------------|--|
| <b>Functional Sample</b>             | Draft                               | For functional testing. Revised and supplementary data will be published later.        |
| <b>In Development / Prototype</b>    | Objective Specification             | Target values. Revised and supplementary data will be published later.                 |
| <b>Engineering Sample</b>            | Advance Information                 | Data based on early testing. Revised and supplementary data will be published later.   |
| <b>Initial Production</b>            | Early Production Information        | Data from product verification. Revised and supplementary data may be published later. |
| <b>Mass Production / End of Life</b> | Production Information              | Document contains the final product specification.                                     |

This document applies to the following products:

| <b>Product name</b> | <b>Type number</b> | <b>u-connectXpress software version</b> | <b>Hardware version</b> | <b>PCN reference</b> | <b>Product status</b> |
|---------------------|--------------------|---|-------------------------|----------------------|-----------------------|
| NINA-B221           | NINA-B221-03B-01   | 4.0.0                                   | 08                      | UBX-21043575         | Mass production       |
| NINA-B222           | NINA-B222-03B-01   | 4.0.0                                   | 08                      | UBX-21043575         | Mass production       |

u-blox or third parties may hold intellectual property rights in the products, names, logos and designs included in this document. Copying, reproduction, or modification of this document or any part thereof is only permitted with the express written permission of u-blox. Disclosure to third parties is permitted for clearly public documents only.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit [www.u-blox.com](http://www.u-blox.com).

Copyright © u-blox AG.

# Contents

|   |           |
|---|-----------|
| <b>Document information .....</b>                             | <b>2</b>  |
| <b>Contents .....</b>   | <b>3</b>  |
| <b>1 Functional description .....</b>                         | <b>6</b>  |
| 1.1 Overview .....  | 6         |
| 1.2 Applications .....  | 6         |
| 1.3 Block diagram .....                                       | 7         |
| 1.4 Product variants .....                                    | 7         |
| 1.4.1 NINA-B221 .....   | 7         |
| 1.4.2 NINA-B222 .....   | 7         |
| 1.5 Radio performance.....                                    | 8         |
| 1.6 Software options .....                                    | 8         |
| 1.6.1 AT command support .....                                | 8         |
| 1.6.2 Software upgrade .....                                  | 8         |
| 1.7 MAC addresses .....                                       | 9         |
| <b>2 Interfaces .....</b>                                     | <b>10</b> |
| 2.1 Power supply .....  | 10        |
| 2.1.1 Module supply input (VCC) .....                         | 10        |
| 2.1.2 Digital I/O interfaces reference voltage (VCC_IO) ..... | 10        |
| 2.2 Low Power Clock .....                                     | 10        |
| 2.3 System functions .....                                    | 10        |
| 2.3.1 Module power on .....                                   | 10        |
| 2.3.2 Module power off .....                                  | 11        |
| 2.3.3 Module reset .....                                      | 11        |
| 2.3.4 Active mode.....  | 11        |
| 2.3.5 Standby mode.....                                       | 11        |
| 2.3.6 Sleep mode .....  | 11        |
| 2.3.7 Stop mode.....  | 11        |
| 2.4 Boot strap pins .....                                     | 12        |
| 2.5 RF antenna interface.....                                 | 12        |
| 2.5.1 Internal antenna.....                                   | 12        |
| 2.5.2 External RF antenna interface.....                      | 13        |
| 2.6 IO signals.....   | 13        |
| 2.6.1 Drive capability .....                                  | 13        |
| 2.6.2 System status IO signals .....                          | 13        |
| 2.6.3 System control IO signals .....                         | 13        |
| 2.6.4 UART IO signals.....                                    | 14        |
| 2.7 Data and command interfaces.....                          | 14        |
| 2.7.1 UART .....  | 15        |
| 2.7.2 SPI .....   | 15        |
| <b>3 Pin definition.....</b>                                  | <b>16</b> |

- 3.1 Pin assignment ..... 16
- 4 Electrical specifications ..... 18**
  - 4.1 Absolute maximum ratings ..... 18
    - 4.1.1 Maximum ESD ratings ..... 18
  - 4.2 Operating conditions ..... 18
    - 4.2.1 Operating temperature range ..... 19
    - 4.2.2 Supply/Power pins ..... 19
    - 4.2.3 RESET\_N pin ..... 19
    - 4.2.4 Digital pins ..... 19
    - 4.2.5 Current consumption ..... 20
    - 4.2.6 Bluetooth radio characteristics ..... 20
    - 4.2.7 Bluetooth Low Energy characteristics ..... 21
    - 4.2.8 Antenna radiation patterns ..... 21
- 5 Mechanical specifications ..... 23**
  - 5.1 NINA-B221 mechanical specification ..... 23
  - 5.2 NINA-B222 mechanical specification ..... 24
- 6 Qualification and approvals ..... 25**
  - 6.1 Country approvals ..... 25
  - 6.2 European Union regulatory compliance ..... 25
    - 6.2.1 Radio Equipment Directive (RED) 2014/53/EU ..... 25
    - 6.2.2 Compliance with the RoHS directive ..... 25
  - 6.3 FCC/IC compliance ..... 26
    - 6.3.1 FCC compliance ..... 26
    - 6.3.2 FCC statement ..... 26
    - 6.3.3 RF-exposure statement ..... 26
    - 6.3.4 End product user manual instructions ..... 27
    - 6.3.5 End product labeling requirements ..... 27
    - 6.3.6 End product compliance ..... 28
  - 6.4 Japan radio equipment compliance ..... 29
  - 6.5 NCC Taiwan compliance ..... 29
    - 6.5.1 Taiwan NCC Warning Statement ..... 29
    - 6.5.2 NINA-B221 labeling requirements for end product ..... 29
    - 6.5.3 NINA-B222 labeling requirements for end product ..... 30
  - 6.6 KCC South Korea compliance ..... 30
  - 6.7 Brazil compliance ..... 30
  - 6.8 Australia and New Zealand regulatory compliance ..... 31
  - 6.9 South Africa regulatory compliance ..... 31
  - 6.10 Safety compliance ..... 31
  - 6.11 Bluetooth qualification information ..... 32
- 7 Antennas ..... 33**
  - 7.1 Antenna accessories ..... 34
  - 7.2 Approved antennas ..... 34

|                          |  |           |
|--------------------------|--|-----------|
| 7.2.1                    | Single band antennas.....                      | 34        |
| 7.2.2                    | Dual-band antennas .....                       | 37        |
| <b>8</b>                 | <b>Product handling.....</b>                   | <b>39</b> |
| 8.1                      | Packaging .....                                | 39        |
| 8.1.1                    | Reels .....                                    | 39        |
| 8.1.2                    | Tapes.....                                     | 39        |
| 8.2                      | Moisture sensitivity levels .....              | 41        |
| 8.3                      | Reflow soldering.....                          | 41        |
| 8.4                      | ESD precautions .....                          | 41        |
| <b>9</b>                 | <b>Labeling and ordering information .....</b> | <b>42</b> |
| 9.1                      | Product labeling .....                         | 42        |
| 9.1.1                    | Product identifiers.....                       | 43        |
| 9.1.2                    | Identification codes.....                      | 43        |
| 9.2                      | Ordering information.....                      | 43        |
| <b>Appendix</b>          | <b>.....</b>                                   | <b>44</b> |
| <b>A</b>                 | <b>Glossary .....</b>                          | <b>44</b> |
| <b>Related documents</b> | <b>.....</b>                                   | <b>45</b> |
| <b>Revision history</b>  | <b>.....</b>                                   | <b>45</b> |
| <b>Contact.....</b>      | <b>.....</b>                                   | <b>46</b> |

# 1 Functional description

## 1.1 Overview

The NINA-B2 series comprises small, stand-alone, dual-mode Bluetooth modules designed for ease-of-use and integration in professional applications. The modules are delivered with u-connectXpress software that provides support for both peripheral and central roles, Serial Port Profile, GATT client and server, beacons, and the u-blox Bluetooth Low Energy Serial Port Service – all configurable from a host using AT commands.

NINA-B2 modules provide top grade security, thanks to secure boot, which ensures the module only boots up with original u-blox software. Intended applications include industrial automation, wireless-connected and configurable equipment, point-of-sales, and health devices.

NINA-B222 comes with an internal antenna while NINA-B221 has a pin for use with an external antenna.

NINA-B2 complies with RED standards and is certified in the following countries: Great Britain (UKCA), US (FCC), Canada (IC / ISED RSS), Japan (MIC), Taiwan (NCC), South Korea (KCC), Australia / New Zealand (ACMA), Brazil (Anatel), South Africa (ICASA). The modules are qualified according to ISO 16750 for professional grade operation, supporting an extended temperature range of  $-40\text{ }^{\circ}\text{C}$  to  $+85\text{ }^{\circ}\text{C}$ .

## 1.2 Applications

- Internet of Things (IoT)
- Bluetooth networks
- Telematics
- Point-of-sales
- Medical and industrial networking
- Access to laptops, mobile phones, and similar consumer devices
- Home/building automation
- Ethernet/Wireless gateway

## 1.3 Block diagram




Figure 1: Block diagram of NINA-B2 series

## 1.4 Product variants

NINA-B2 series modules come with pre-flashed application software, supporting Bluetooth BR/EDR and Bluetooth Low Energy v4.2. The host system can set up and control the module through the AT command interface. For more information about AT commands, see also the u-connectXpress AT commands manual [3].

### 1.4.1 NINA-B221

The NINA-B221 module has no internal antenna. Instead, the RF signal is available at a module pin for routing to an external antenna or antenna connector. The module outline is smaller in comparison to the module variants that include an antenna, only 10.0 x 10.6 mm. The module height is 2.2 mm.

### 1.4.2 NINA-B222

The NINA-B222 module has an internal PIFA antenna mounted on the module. The RF signal is not connected to any module pin. The module outline is 10.0 x 14.0 mm and the height 3.8 mm.

## 1.5 Radio performance

NINA-B2 modules support Bluetooth BR/EDR and Bluetooth Low Energy (LE) as described in [Table 1](#).

| Bluetooth BR/EDR  | Bluetooth Low Energy                         |
|---|--|
| Bluetooth v4.2+EDR<br>Maximum number of Peripherals: 7                              | Bluetooth LE 4.2 dual-mode                   |
| Band support<br>2.4 GHz, 79 channels  | Band support<br>2.4 GHz, 40 channels         |
| Typical conducted output power<br>- 1 Mbit/s: 5 dBm<br>- 2/3 Mbit/s: 5 dBm          | Typical conducted output power<br>5 dBm      |
| Typical radiated output power<br>- 1 Mbit: 8 dBm EIRP*<br>- 2/3 Mbit/s: 8 dBm EIRP* | Typical radiated output power<br>8 dBm EIRP* |
| Conducted sensitivity<br>-88 dBm  | Conducted sensitivity<br>-88 dBm             |
| Data rates:<br>1 / 2 / 3 Mbit/s   | Data rates:<br>1 Mbit/s                      |

\* RF power including maximum antenna gain (3 dBi).

**Table 1: NINA-B2 series Bluetooth characteristics**

## 1.6 Software options

NINA-B2 series modules come with the pre-flashed application software, supporting Bluetooth BR/EDR and Bluetooth Low Energy. The host system can set up and control the module through the AT command interface. NINA-B2 modules provide top grade security, thanks to secure boot, which ensures the module boots up only with original u-blox software. This makes NINA-B2 ideal for critical IoT applications where security is important.

### 1.6.1 AT command support

You can configure NINA-B2 modules with the u-blox s-center toolbox software using AT commands. See also the u-connectXpress AT commands manual [\[3\]](#) and u-connectXpress software user guide [\[7\]](#).

The s-center evaluation software supporting the AT commands is also available free of charge and can be downloaded from the u-blox website. See also the s-center user guide [\[8\]](#).

### 1.6.2 Software upgrade

For information on how to upgrade the software for NINA-B2 series, see [System control IO signals](#) and the NINA-B2 series system integration manual [\[1\]](#).



## 1.7 MAC addresses

NINA-B2 series modules have four unique consecutive MAC addresses that are reserved for each module. The addresses are stored in the configuration memory during production. The first Bluetooth address is available in the Data Matrix on the label. See also [Product labeling](#).


| MAC address         | Assignment | Last bits of MAC address | Example                  |
|---------------------|------------|--------------------------|--------------------------|
| Module 1, address 1 | Bluetooth  | 00                       | <i>D4:CA:6E:90:04:90</i> |
| Module 1, address 2 | Reserved   | 01                       | <i>D4:CA:6E:90:04:91</i> |
| Module 1, address 3 | Reserved   | 10                       | <i>D4:CA:6E:90:04:92</i> |
| Module 1, address 4 | Reserved   | 11                       | <i>D4:CA:6E:90:04:93</i> |
| Module 2, address 1 | Bluetooth  | 00                       | D4:CA:6E:90:04:94        |
| Module 2, address 2 | Reserved   | 01                       | D4:CA:6E:90:04:95        |
| Module 2, address 3 | Reserved   | 10                       | D4:CA:6E:90:04:96        |
| Module 2, address 4 | Reserved   | 11                       | D4:CA:6E:90:04:97        |

**Table 2: Example MAC addresses assignment for two modules**

## 2 Interfaces

### 2.1 Power supply

The power for NINA-B2 series modules is supplied through **VCC** and **VCC\_IO** pins by DC voltage.

-  The system power supply circuit must be able to support peak power (add 20% as margin over the listed current consumption), as during operation, the current drawn from **VCC** and **VCC\_IO** can vary significantly based on the use cases.

#### 2.1.1 Module supply input (VCC)

NINA-B2 series modules use an integrated Linear Voltage converter to transform the supply voltage presented at the **VCC** pin into a stable system voltage.

#### 2.1.2 Digital I/O interfaces reference voltage (VCC\_IO)

All modules in the NINA-B2 series provide an additional voltage supply input for setting the I/O voltage level. The separate **VCC\_IO** pin enables integration of the module in many applications with different voltage levels (for example, 1.8 V or 3.3 V) without any level converters. NINA-B2 modules support only 3.3 V as IO voltage level currently.

### 2.2 Low Power Clock

The internal clocks in NINA-B2 are used for the lowest power modes.

### 2.3 System functions

NINA-B2 series modules are power efficient devices capable of operating in different power saving modes and configurations. Different sections of the modules can be powered off when they are not needed, and complex wake up events can be generated from different external and internal inputs.

The next sections describe the system power modes in detail as well as power-on/off and reset behavior, and boot strapping options.

The following system power modes available:

- Automatic:
  - Active mode
  - Standby mode
- Manual:
  - Sleep mode
  - Stop mode

#### 2.3.1 Module power on

You can switch on or reboot the NINA-B2 series modules in one of the following ways:

- Rising edge on the VCC pin to a valid supply voltage
- Issuing a reset of the module. See also [Module reset](#).

If the u-connectXpress software has been configured to start in AT mode, **+STARTUP** will be sent over the UART interface when the software has booted and is ready to accept commands.


### 2.3.2 Module power off


There is no dedicated pin to power down the NINA-B2 series modules. Instead, the “Stop” power mode can be used to keep the module the module in the deepest power save mode. The stop mode is more power efficient than holding the module in reset.

### 2.3.3 Module reset

NINA-B2 series modules can be reset (rebooted) in the following way:

- Low level on the **RESET\_N** pin, which is normally set high by an internal pull-up. This results in a “hardware” reset of the module. The **RESET\_N** signal should be driven by an open drain, open collector or contact switch.

 NINA-B2 series modules can be reset using an AT command `+CPWROFF`. This causes a “software reset” of the module. See also u-connectXpress AT commands manual [3].

 Holding the module in reset does not yield the lowest power consumption. For performance that consumes the least power, put the module into stop mode. See also [Stop mode](#).

### 2.3.4 Active mode

In this mode, NINA-B2 actively receives and transmits data over one or more of its interfaces; 2.4 GHz radio, UART, etc. The module automatically switches between Active mode and Standby mode and seamlessly transitions between the two modes without user involvement. The module CPU operates at its highest clock speed in this mode.


### 2.3.5 Standby mode


In this mode, the module is “idling” and operates only as a background activity. Radio or physical connections are maintained, and no data packets received in this mode are lost. When required, NINA-B2 automatically enters Active mode without delay.

Users can further decrease the current consumption in Standby mode by:


- Enabling Automatic Frequency Adaption (AFA)
- Increasing the Bluetooth low energy connection interval

Automatic Frequency Adaption (AFA) allows the internal clocks to be automatically reduced whenever possible. AFA is configured using the `AT+UPWRMNG` command.

 Enabling AFA can put limits on certain module functions, maximum UART baud rate, etc. Check the u-connectXpress AT commands manual [3] to determine which clock speeds are acceptable for your application.

 For more information about how to configure u-connectXpress software using AT commands, see the u-connectXpress AT commands manual [3] and u-connectXpress software user guide [7].

### 2.3.6 Sleep mode

 Sleep mode is not available in NINA-B2.


### 2.3.7 Stop mode

Stop mode is the deepest power saving mode of NINA-B2 modules. During Stop mode, all functionality is stopped to ensure minimum power consumption; all existing connections are dropped, and the system RAM is not retained. The module always reboots when waking up from Stop mode.

Stop mode must be actively entered into by the user in one of the following ways:

- Using the `AT+D4` command, and the UART **DSR** pin to enter/leave Stop mode
- Using the `AT+USTOP` command, and a GPIO pin set by the user to enter/leave Stop mode. For information describing what GPIOs are capable of controlling Stop mode, see [Table 5](#).
- Using the `AT+USTOP` command and setting a timer to automatically wake up after a delay set by the user.

If the u-connectXpress software has been configured to start in AT mode, `+STARTUP` is sent over the UART interface when the software has booted and is ready to accept commands.

 See the u-connectXpress AT commands manual [\[3\]](#) and u-connectXpress software user guide [\[7\]](#) for more information on how to use AT commands to configure the u-connectXpress software.

## 2.4 Boot strap pins

There are several boot configuration pins available on the module that must have the correct settings during boot. See also [Table 3](#). The boot strap pins are configured to the default state internally on the module and must NOT be configured externally.

During boot, pin 32 controls if additional system information should be transmitted on the UART interface during startup. After the system has booted, it is reconfigured to **SPI\_CS**, the SPI chip select signal.

During boot, pin 36 controls the voltage level of the internal flash during startup. After the system has booted, it is reconfigured to **SPI\_MISO**, the SPI slave data output signal. It must NOT be pulled down by an external MCU or circuitry

| Pin | State during boot | Default       | Behavior  | Description                       |
|-----|-------------------|---------------|---|-----------------------------------|
| 27  | 0                 |               | ESP boot mode (factory boot)                          | ESP Factory boot Mode             |
|     | 1                 | Pull-up*      | Normal Boot from internal Flash                       |                                   |
| 32  | 0                 |               | Silent  | Printout on UART0 TXD during boot |
|     | 1                 | Pull-up*      | UART0 TXD Toggling                                    |                                   |
| 36  | 0                 |               | VDD_SDIO=3.3V (Not allowed)                           | Internal flash voltage            |
|     | 1                 | 10 kΩ pull-up | VDD_SDIO=1.8V<br>(VDD_SDIO should always be at 1.8 V) |                                   |

\*Nominally 45 kΩ

**Table 3: NINA-B2 series boot strapping pin**

## 2.5 RF antenna interface

The RF antenna interface of the NINA-B2 series supports Bluetooth BR/EDR and Bluetooth Low Energy on the same RF antenna signal. The module is equipped with a 2.4 GHz bandpass filter between the radio chip and RF antenna interface. See also [Block diagram](#).

The NINA-B2 series supports either an internal antenna (NINA-B222) or external antennas connected through an antenna pin (NINA-B221).


### 2.5.1 Internal antenna

NINA-B222 has internal antenna specifically designed and optimized for the NINA module, which is a 2.4 GHz PIFA antenna.

It is recommended to place the NINA-B222 module in such a way that the internal antenna is in the corner of the host PCB (the corner closest to Pin 16 should be in the corner). The antenna side (short side closest to the antenna), positioned along one side of the host PCB ground plane is the second best option.

For NINA-B222 keep a minimum clearance of 5 mm between the antenna and the casing. Keep a minimum of 10 mm free space from the metal around the antenna including the area below. If a metal enclosure is required, use NINA-B221 and an external antenna. It is beneficial to have a large solid ground plane on the host PCB and have a good grounding on the module. Minimum ground plane size is 24x30 mm but recommended is more than 50x50 mm.

See the NINA-B2 series system integration manual [1] for more antenna related design information.

 The ANT signal is not available at the solder pins of the NINA-B222 module.

## 2.5.2 External RF antenna interface

The NINA-B221 module has an antenna signal (**ANT**) pin with a characteristic impedance of 50 Ω for using an external antenna. The antenna signal supports both Tx and Rx.

The external antenna, for example, can be an SMD antenna (or PCB integrated antenna) on the host board. An antenna connector for using an external antenna via a coaxial cable could also be implemented. A cable antenna might be necessary if the module is mounted in a shielded enclosure such as a metal box or cabinet.

An external antenna connector (U.FL. connector) reference design (see NINA-B2 series system integration manual [1]) is available and must be followed to comply with the NINA-B2 FCC/IC modular approvals. See also [Approved antennas](#).

## 2.6 IO signals

NINA-B2 series modules support a versatile pin-out with up to 16 GPIO pins.

### 2.6.1 Drive capability

All GPIO pins are normally configured for medium current consumption. Using this standard drive capability, a pin configured as an output can source and an input sink a certain amount of current. See also [Digital pins](#).

### 2.6.2 System status IO signals

The **RED**, **GREEN** and **BLUE** pins are used to signal the status. The pins are active low and are intended to be routed to an RGB LED. See the u-connectXpress AT commands manual [3] for more information about connectivity software signals IOs.

| Mode                    | Status      | RGB LED color | GREEN | BLUE | RED  |
|-------------------------|-------------|---------------|-------|------|------|
| Data mode               | IDLE        | Green         | LOW   | HIGH | HIGH |
| Command mode            | IDLE        | Orange        | LOW   | HIGH | LOW  |
| Data mode, Command mode | CONNECTING* | Purple        | HIGH  | LOW  | LOW  |
| Data mode, Command mode | CONNECTED*  | Blue          | HIGH  | LOW  | HIGH |

\* = LED flashes on data activity

Table 4: System status indication

### 2.6.3 System control IO signals

The following input signals are used to control the system:

- **RESET\_N** is used to reset the system. See also [IO signals](#).
- If **SWITCH\_1** is driven low during start up, the UART serial settings are restored to their default values.
- **SWITCH\_2** can be used to open a connection to a peripheral device.
- If both **SWITCH\_1** and **SWITCH\_2** are driven low during start up, the system will enter the bootloader mode.

- If both **SWITCH\_1** and **SWITCH\_2** are driven low during start up and held low for 10 seconds, the system will exit the bootloader mode and restore all settings to their factory defaults.

For more information about connectivity software signals IOs, see also the u-connectXpress AT commands manual [3].

### 2.6.4 UART IO signals


In addition to the normal **RXD**, **TXD**, **CTS**, and **RTS** signals, NINA-B2 software adds the **DSR** and **DTR** pins to the UART interface. See also **UART**. Note that these signals are not used as originally intended but are used instead to control the state of the NINA module. Depending on the current configuration, the **DSR pin** can be used to:

- Enter command mode
- Disconnect and/or toggle connectable status

If **CTS/RTS** flow control is disabled, those pins can be used as GPIOs.

## 2.7 Data and command interfaces

There are two data interfaces available on a NINA-B2 module: UART and SPI. Both interfaces cannot be used at the same time. After the module has booted, the module will check for activity on both interfaces to determine which of the interfaces should be used. AT commands can always be used to enable or disable interfaces manually. **Figure 2** shows the startup and interface selection procedure.



**Figure 2: Interface detection flow chart**

**+STARTUP** will always be printed on the UART **TXD** line.

When the SPI detection is started, the NINA-B2 module will start toggling the **SPI\_DRDY** signal periodically. Once the SPI master has sent 8 clock signals on the **SPI\_SCLK** line, the SPI interface is considered to be active and the UART interface is disabled.

If an AT command is sent to the NINA-B2 module over the UART interface, the UART interface will be considered “detected”, and the **SPI\_DRDY** signal will stop toggling and the SPI interface will be disabled.

For more information about using these data and command interfaces, see also the u-connectXpress software user guide [7].

## 2.7.1 UART

NINA-B2 modules include a 6-wire UART for communication with an application host processor (AT commands, Data communication and software upgrades).

The following UART signals are available:

- Data lines (**RXD** as input, **TXD** as output)
- Hardware flow control lines (**CTS** as input, **RTS** as output)
- Link status (**DSR** as input, **DTR** as output). The **DSR/DTR** signals behavior is adapted to the u-connectXpress software functionality and differs from the UART standard. See also [UART IO signals](#).
- Programmable baud-rate generator allows most industry standard rates, as well as non-standard rates up to 3 Mbaud.
- Frame format configuration:
  - 8 data bits
  - Even or no-parity bit
  - 1 stop bit
- 8N1 default frame configuration with eight (8) data bits, no (N) parity bit, and one (1) stop bit.

## 2.7.2 SPI

The serial peripheral interface of NINA-B2 only runs in “SPI slave mode”, meaning a host controller running in “SPI master mode” is intended to send commands to the NINA module.

The following signals are used:

- **SPI\_SCLK** – Serial clock input signal
- **SPI\_MOSI** – Serial data input signal
- **SPI\_MISO** – Serial data output signal
- **SPI\_CS** – Chip Select input, enable control signal
- **SPI\_DRDY** – (optional) Additional “Data Ready” output signal, used to indicate to the controller when data is available. This signal is enabled by default but can be disabled.
- **SPI\_NORX** – (optional) Additional flow control output signal used to indicate when the NINA module cannot receive any more data. This signal is not enabled by default.

An SPI master must comply with the following:

- 10 MHz maximum clock speed
- SPI mode 1 or 3
- The SPI master must clock at least 8 bytes minimum and 4096 bytes maximum per transaction, and transaction lengths must be on 4 byte boundary



See the following application note for more information on how to use the SPI interface [\[6\]](#).

## 3 Pin definition

### 3.1 Pin assignment

Figure 3 describes the pin configuration used in the NINA-B2 u-connectXpress software modules.




Figure 3: NINA-B22x pin assignment (top view)

- The grey pins in the center of the modules are GND pins. The lower part below the dotted line is the antenna part of NINA-B222 and the outline of the NINA-B221 module ends at this line.
- Some of the signals are boot strap signals (see [Table 5](#)). It is important that these signals are in the correct state during startup. See also [Boot strapping pins](#).
- For more information describing IO functionality, see also [IO signals](#).

| Pin | Name   | I/O | Description                  | Alt. function | Remarks  |
|-----|--------|-----|------------------------------|---------------|--|
| 1   | RED    | O   | Logic Red LED signal         |               | For more information about IO functionality, see also <a href="#">System status IO signals</a> |
| 2   | GPI_2  | I   | General Purpose Input        | WKUP_2        | Can control Stop mode  |
| 3   | GPI_3  | I   | General Purpose Input        | WKUP_3        | Can control Stop mode  |
| 4   | GPI_4  | I   | General Purpose Input        | WKUP_4        | Can control Stop mode  |
| 5   | GPIO_5 | I/O | General Purpose Input/Output |               |  |



| Pin | Name                | I/O | Description   | Alt. function      | Remarks   |
|-----|---------------------|-----|---|--------------------|---|
| 6   | GND                 |     | Ground  |                    |   |
| 7   | GREEN/<br>SWITCH_1  | I/O | GREEN: System status signal /<br>SWITCH_1: Multiple functions |                    | Active low<br>See also <a href="#">System status IO signals</a> and <a href="#">System control IO signals</a> |
| 8   | BLUE                | O   | Logic Blue LED Signal   |                    | See also <a href="#">System status IO signals</a>   |
| 9   | VCC_IO              | I   | Module I/O level voltage input                                |                    | IO voltage supply   |
| 10  | VCC                 | I   | Module supply voltage input                                   |                    | Module voltage supply   |
| 11  | RSVD                |     | Reserved for future use                                       |                    | Do not connect  |
| 12  | GND                 |     | Ground  |                    |   |
| 13  | ANT                 | I/O | Antenna Tx/Rx interface                                       |                    | 50 Ω nominal characteristic impedance   |
| 14  | GND                 |     | Ground  |                    |   |
| 15  | RSVD                |     | Reserved for future use                                       |                    | Do not connect  |
| 16  | UART_DTR            | O   | UART Data Terminal Ready                                      |                    | The DTR signaling is not according to UART standard See also <a href="#">UART IO signals</a> .                |
| 17  | UART_DSR            | I   | UART Data Set Ready   |                    | The DSR signaling is not according to UART standard. See also <a href="#">UART IO signals</a>                 |
| 18  | SWITCH_2            | I   | Multiple functions  | WKUP_18            | Active low.<br>See also <a href="#">System control IO signals</a> .<br>Can control Stop mode.                 |
| 19  | RESET_N             | I   | External system reset input                                   |                    | Active low  |
| 20  | UART_RTS            | O   | UART request to send  | GPIO_20            | Active low<br>See also <a href="#">UART IO signals</a>  |
| 21  | UART_CTS            | I   | UART clear to send  | GPIO_21            | Active low<br>See also <a href="#">UART IO signals</a>  |
| 22  | UART_TXD            | O   | UART data output  |                    | See also <a href="#">UART</a>   |
| 23  | UART_RXD            | I   | UART data input   |                    | See also <a href="#">UART</a>   |
| 24  | GPIO_24             | I/O | General Purpose Input/Output                                  |                    |   |
| 25  | SPI_DRDY            | O   | SPI data ready output   | GPO_25             | See also <a href="#">SPI</a>  |
| 26  | GND                 |     | Ground  |                    |   |
| 27  | SYS_BOOT            | I   | Software download   | GPIO_27            | Default pulled-up. See also <a href="#">Boot strapping pins</a> .   |
| 28  | GPIO_28             | I/O | General Purpose Input/Output                                  |                    |   |
| 29  | GPIO_29             | I/O | General Purpose Input/Output                                  |                    |   |
| 30  | GND                 |     | Ground  |                    |   |
| 31  | SPI_SCLK            | I   | SPI clock input signal  | GPIO_31<br>WKUP_31 | Can control Stop mode<br>See also <a href="#">SPI</a>   |
| 32  | LOG_BOOT/<br>SPI_CS | I   | Debug printout on UART enable/<br>SPI chip select signal      | GPIO_32            | Default pulled-up<br>See also <a href="#">Boot strapping pins</a> and <a href="#">SPI</a>                     |
| 33  | RSVD                |     | Reserved for future use                                       |                    | Do not connect  |
| 34  | GPI_34              | I   | General Purpose Input   | WKUP_34            | Can control Stop mode   |
| 35  | SPI_MOSI            | I   | SPI serial data in signal                                     | GPIO_35<br>WKUP_34 | Can control Stop mode<br>See also <a href="#">SPI</a>   |
| 36  | SPI_MISO            | O   | SPI serial data out signal                                    | GPO_36             | Default pulled-up<br>See also <a href="#">Boot strapping pins</a> and <a href="#">SPI</a>                     |

**Table 5: NINA-B2 pinout**

## 4 Electrical specifications

Stressing the device above one or more of the ratings listed in [Absolute maximum ratings](#) can cause permanent damage. These are stress ratings only. Operating the module at these or at any conditions other than those specified in the [Operating conditions](#) should be avoided. Exposure to absolute maximum rating conditions for extended periods can affect device reliability.

All given application information is only advisory and does not form part of the specification.

### 4.1 Absolute maximum ratings

| Symbol                                 | Description                        | Condition                               | Min  | Max | Unit |
|--|------------------------------------|---|------|-----|------|
| VCC/ VCC_IO                            | Module supply voltage              | Input DC voltage at VCC and VCC_IO pins | -0.3 | 3.6 | V    |
| $I_{VCC\_MAX}$ +<br>$I_{VCC\_IO\_MAX}$ | Absolute maximum power consumption |   |      | 500 | mA   |
| DPV                                    | Digital pin voltage                | Input DC voltage at any digital I/O pin | -0.3 | 3.6 | V    |
| P_ANT                                  | Maximum power at receiver          | Input RF power at antenna pin           |      | 0   | dBm  |
| Tstr                                   | Storage temperature                |   | -40  | +85 | °C   |

**Table 6: Absolute maximum ratings**

The product is not protected against overvoltage or reversed voltages. If necessary, voltage spikes exceeding the power supply voltage specification, given in table above, must be limited to values within the specified boundaries by using appropriate protection devices.

#### 4.1.1 Maximum ESD ratings

| Parameter   | Min | Typ | Max | Unit | Remarks                                       |
|---|-----|-----|-----|------|---|
| ESD immunity  |     |     | ±8* | kV   | Indirect discharge according to IEC 61000-4-2 |
| ESD sensitivity, tested for all pins except RSVD and ANT pins #11, #15, #13 |     |     | 2.0 | kV   | Human body model according to JEDEC JS001     |

\*Tested on EVK-NINA-B2 evaluation board.

**Table 7: Maximum ESD ratings**

NINA-B2 series modules are Electrostatic Sensitive Devices and require special precautions while handling. See also [ESD precautions](#).

### 4.2 Operating conditions

Operation beyond the specified operating conditions is not recommended and extended exposure beyond them may affect device reliability.

Unless otherwise specified, all operating condition specifications are at an ambient temperature of 25 °C and at a supply voltage of 3.3 V.

### 4.2.1 Operating temperature range

| Parameter             | Min  | Max | Unit |
|-----------------------|------|-----|------|
| Operating temperature | -40* | +85 | °C   |

\* See the voltage supply condition for lowest temperature range in [Supply/Power pins](#).

Table 8: Temperature range

### 4.2.2 Supply/Power pins

| Symbol | Parameter             | Condition                            | Min  | Typ  | Max  | Unit |
|--------|-----------------------|--------------------------------------|------|------|------|------|
| VCC    | Input supply voltage  | Ambient temperature -20 °C to +85 °C | 3.00 | 3.30 | 3.60 | V    |
|        |                       | Ambient temperature -40 °C to +85 °C | 3.00 | 3.30 | 3.45 | V    |
| VCC_IO | I/O reference voltage | Ambient temperature -20 °C to +85 °C | 3.00 | 3.30 | 3.60 | V    |
|        |                       | Ambient temperature -40 °C to +85 °C | 3.00 | 3.30 | 3.45 | V    |

Table 9: Input characteristics of voltage supply pins

### 4.2.3 RESET\_N pin

The conditions for VCC and RESET\_N timing during start-up and reset duration, are shown in [Figure 4](#). The parameters shown in the timing diagram are described in [Table 10](#).




Figure 4: Module power-up and reset timing

| Pin name       | Parameter  | Min | Typ  | Max     | Unit |
|----------------|--|-----|------|---------|------|
| RESET_N        | Low-level input  | 0   |      | 0.3*VCC | V    |
|                | Internal pull-up resistance  |     | 100  |         | kΩ   |
|                | Internal capacitance   |     | 10   |         | nF   |
| t <sub>0</sub> | Time from VCC valid input level 3.0 V to RESET_N release reaches 0.6 V     | 50  | 1000 |         | μs   |
| t <sub>1</sub> | Duration of RESET_N pin < low level input 0.6 V, to trigger hardware reset | 50  |      |         | μs   |
| t_Startup      | Startup time after release of reset  |     | 2.6  |         | s    |

Table 10: RESET\_N pin characteristics

### 4.2.4 Digital pins

| Pin name        | Parameter                              | Min        | Typ | Max        | Unit | Remarks |
|-----------------|--|------------|-----|------------|------|---------|
| Any digital pin | Input characteristic: Low-level input  | 0          |     | 0.3*VCC_IO | V    |         |
|                 | Input characteristic: high-level input | 0.7*VCC_IO |     | VCC_IO     | V    |         |

| Pin name | Parameter                                   | Min        | Typ | Max    | Unit | Remarks     |
|----------|---|------------|-----|--------|------|-------------|
|          | Output characteristic:<br>Low-level output  | 0          |     | 0.4    | V    |             |
|          | Output characteristic:<br>High-level output | VCC_IO-0.4 |     | VCC_IO | V    |             |
|          | Drive strength                              |            |     | 12     | mA   | Source/sink |
|          | Pull-up/pull-down resistance                |            | 45  |        | kΩ   |             |

**Table 11: Digital pin characteristics**

## 4.2.5 Current consumption

Table 12 shows the typical and peak current consumption for NINA-B2 modules using u-connectXpress v4.0.0 software. Unless stated otherwise, the module is powered at 3.3 V and uses factory default configurations.

| Radio mode                               | Activity     | Power mode | Role               | Typ | Unit | Remarks                     |
|--|--------------|------------|--------------------|-----|------|-----------------------------|
| Bluetooth BR/EDR (Bluetooth LE disabled) | Transmitting | Active     | Peripheral/Central | 150 | mA   | Data throughput 1.25 Mbit/s |
|  | Receiving    | Active     | Peripheral/Central | 110 | mA   | Data throughput 1.25 Mbit/s |
|  | Connected    | Standby*   | Peripheral/Central | 100 | mA   |                             |
|  | Inquiry      | Standby*   | -                  | 100 | mA   |                             |
| Bluetooth LE                             | Transmitting | Active     | Peripheral/Central | 60  | mA   | Data throughput 30 kbit/s   |
|  |              |            |                    | 80  | mA   | Data throughput 180 kbit/s  |
|  | Receiving    | Active     | Peripheral/Central | 50  | mA   | Data throughput 30 kbit/s   |
|  |              |            |                    | 60  | mA   | Data throughput 180 kbit/s  |
|  | Connected    | Standby*   | Peripheral         | 35  | mA   |                             |
|  |              |            | Central            | 35  | mA   |                             |
|  | Advertising  | Standby*   | Peripheral         | 30  | mA   |                             |
|  | Discovery    | Standby*   | Central            | 100 | mA   |                             |
| Idle                                     | Standby*     | Central    | 60                 | mA  |      |                             |
| Disabled                                 | None         | Standby*   | -                  | 30  | mA   |                             |
|  |              | Sleep      | -                  | N/A | -    | Not available in NINA-B2    |
|  |              | Stop       | -                  | 5   | uA   |                             |
|  | Reset        | Reset      | -                  | 35  | uA   | Module held in reset        |

**Table 12: Current consumption of a NINA-B2 during typical use cases**

\*AFA enabled, minimum allowed clock speed set to 80 MHz.

## 4.2.6 Bluetooth radio characteristics

$V_{CC} = 3.3\text{ V}$ ,  $T_{amb} = 25\text{ °C}$

| Parameter          | Operation Mode | Specification        | Unit |
|--------------------|----------------|----------------------|------|
| RF Frequency Range |                | 2.400 – 2.4835       | GHz  |
| Supported Modes    |                | Bluetooth v4.2+EDR   |      |
| Number of channels |                | 79                   |      |
| Modulation         | 1 Mbps         | GFSK (BDR)           |      |
|                    | 2 Mbps         | $\pi/4$ -DQPSK (EDR) |      |
|                    | 3 Mbps         | 8-DPSK (EDR)         |      |

| Parameter                      | Operation Mode | Specification | Unit |
|--------------------------------|----------------|---------------|------|
| Conducted Transmit Power       | 1 Mbps         | $5 \pm 1$     | dBm  |
|                                | 2/3 Mbps       | $5 \pm 1$     | dBm  |
| Conducted Receiver Sensitivity | 1 Mbps         | $-88 \pm 2$   | dBm  |
|                                | 2 Mbps         | $-86 \pm 2$   | dBm  |
|                                | 3 Mbps         | $-80 \pm 2$   | dBm  |

**Table 13: Bluetooth radio characteristics**

## 4.2.7 Bluetooth Low Energy characteristics

 $V_{CC} = 3.3 \text{ V}$ ,  $T_{amb} = 25 \text{ }^{\circ}\text{C}$ 

| Parameter                      | Specification  | Unit |
|--------------------------------|----------------|------|
| RF Frequency Range             | 2.400 – 2.4835 | GHz  |
| Supported Modes                | Bluetooth v4.2 |      |
| Number of channels             | 40             |      |
| Modulation                     | GFSK           |      |
| Conducted Transmit Power       | $5 \pm 1$      | dBm  |
| Conducted Receiver Sensitivity | $-88 \pm 2$    | dBm  |

**Table 14: Bluetooth Low Energy characteristics**

## 4.2.8 Antenna radiation patterns

The energy radiated from the internal PIFA antenna supported in NINA-B222 is represented in the radiation patterns shown in [Table 15](#).

[Figure 5](#) provides an overview of the measurement procedure and shows how the NINA-B222 module is aligned with the XYZ-coordinate system. The procedure requires measurements to be taken in all positions shown as dots (left), with the subsequent measurements represented as grid points in the radiation pattern (right).



**Figure 5: Measurement procedure for determining radiation patterns**

Table 15 shows the radiation patterns of the internal PIFA antenna in NINA-B222.




Table 15: NINA-B222 antenna radiation patterns

## 5 Mechanical specifications

### 5.1 NINA-B221 mechanical specification




Figure 6: NINA-B221 mechanical outline

| Parameter | Description   | Typical          | Tolerance                    |
|-----------|---|------------------|------------------------------|
| A         | Module PCB length [mm]                                  | 10.6 (417.3 mil) | +0.20/-0.10 (+7.9/-3.9 mil)  |
| B         | Module PCB width [mm]                                   | 10.0 (393.7 mil) | +0.20/-0.10 (+7.9/-3.9 mil)  |
| C         | Module thickness [mm]                                   | 2.2 (86.6 mil)   | +0.40/-0.20 (+15.8/-7.9 mil) |
| ccc       | Seating plane coplanarity [mm]                          | 0.10 (3.9 mil)   | +0.02/-0.10 (+0.8/-3.9 mil)  |
| D         | Horizontal edge to lateral pin 1 edge [mm]              | 0.45 (17.7 mil)  | +0.10/-0.10 (+3.9/-3.9 mil)  |
| E         | Vertical and horizontal edge to lateral pin 1 edge [mm] | 0.30 (11.8 mil)  | +0.10/-0.10 (+3.9/-3.9 mil)  |
| F         | Vertical pin 1 edge to lateral pin edge [mm]            | 2.35 (92.5 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
| G         | Depanalizing residual [mm]                              | 0.10 (3.9 mil)   | +0.25/-0.10 (+9.8/-3.9 mil)  |
| H         | Lateral and antenna row pin to pin pitch [mm]           | 1.0 (39.4 mil)   | +0.05/-0.05 (+2.0/-2.0 mil)  |
| I         | Lateral and antenna row pin width [mm]                  | 0.70 (27.6 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
| J         | Lateral and antenna row pin height [mm]                 | 1.15 (45.3 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
| K         | Horizontal pin 1 edge to central pin edge [mm]          | 2.78 (109.4 mil) | +0.05/-0.05 (+2.0/-2.0 mil)  |
| L         | Vertical pin 1 edge to central pin edge [mm]            | 2.63 (103.5 mil) | +0.05/-0.05 (+2.0/-2.0 mil)  |
| M         | Horizontal pin 1 edge to inner row pin edge [mm]        | 1.45 (57.1 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
| N         | Vertical pin 1 edge to Inner row pin edge [mm]          | 1.6 (63.0 mil)   | +0.05/-0.05 (+2.0/-2.0 mil)  |
| O         | Central pin and inner row width and height [mm]         | 0.70 (27.6 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
| P         | Central pin to central pin pitch [mm]                   | 1.15 (45.3 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
| Q         | Inner row pin to pin pitch [mm]                         | 1.1 (43.3 mil)   | +0.05/-0.05 (+2.0/-2.0 mil)  |
| R         | Horizontal pin 1 edge to antenna row pin edge [mm]      | 8.7 (342.5 mil)  | +0.05/-0.05 (+2.0/-2.0 mil)  |
|           | Module Weight [g]                                       | <1.0             |                              |

Table 16: NINA-B221 mechanical outline data



## 5.2 NINA-B222 mechanical specification




Figure 7: NINA-B222 mechanical outline

| Parameter | Description   | Typical          | Tolerance                   |
|-----------|---|------------------|-----------------------------|
| A         | Module PCB length [mm]                                  | 14.0 (551.2 mil) | +0.20/-0.10 (+7.9/-3.9 mil) |
| B         | Module PCB width [mm]                                   | 10.0 (393.7 mil) | +0.20/-0.10 (+7.9/-3.9 mil) |
| C         | Module thickness [mm]                                   | 3.8 (149.6 mil)  | +0.40/-0.20 (+15.8/-7.9)    |
| ccc       | Seating plane coplanarity [mm]                          | 0.10 (3.9 mil)   | +0.02/-0.10 (+0.8/-3.9 mil) |
| D         | Horizontal edge to lateral pin 1 edge [mm]              | 0.45 (17.7 mil)  | +0.10/-0.10 (+3.9/-3.9 mil) |
| E         | Vertical and horizontal edge to lateral pin 1 edge [mm] | 0.30 (11.8 mil)  | +0.10/-0.10 (+3.9/-3.9 mil) |
| F         | Vertical pin 1 edge to lateral pin edge [mm]            | 2.35 (92.5 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| G         | Depanaling residual [mm]                                | 0.10 (3.9 mil)   | +0.25/-0.10 (+9.8/-3.9 mil) |
| H         | Lateral and antenna row pin to pin pitch [mm]           | 1.0 (39.4 mil)   | +0.05/-0.05 (+2.0/-2.0 mil) |
| I         | Lateral and antenna row pin width [mm]                  | 0.70 (27.6 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| J         | Lateral and antenna row pin height [mm]                 | 1.15 (45.3 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| K         | Horizontal pin 1 edge to central pin edge [mm]          | 2.78 (109.4 mil) | +0.05/-0.05 (+2.0/-2.0 mil) |
| L         | Vertical pin 1 edge to central pin edge [mm]            | 2.63 (103.5 mil) | +0.05/-0.05 (+2.0/-2.0 mil) |
| M         | Horizontal pin 1 edge to inner row pin edge [mm]        | 1.45 (57.1 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| N         | Vertical pin 1 edge to inner row pin edge [mm]          | 1.6 (63.0 mil)   | +0.05/-0.05 (+2.0/-2.0 mil) |
| O         | Central pin and inner row width and height [mm]         | 0.70 (27.6 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| P         | Central pin to central pin pitch [mm]                   | 1.15 (45.3 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| Q         | Inner row pin to pin pitch [mm]                         | 1.1 (43.3 mil)   | +0.05/-0.05 (+2.0/-2.0 mil) |
| R         | Horizontal pin 1 edge to antenna row pin edge [mm]      | 8.7 (342.5 mil)  | +0.05/-0.05 (+2.0/-2.0 mil) |
| S         | PCB and shield cover thickness [mm]                     | 2.2 (86.6 mil)   | +0.40/-0.20 (+15.8/-7.9)    |
| T         | Module antenna width [mm]                               | 3.8 (149.6 mil)  | +0.20/-0.20 (+7.9/-7.9 mil) |
| U         | Antenna overhang outside module outline on any side     | 0.0 (0.0 mil)    | +0.60 (+23.6 mil)           |
|           | Module weight [g]                                       | <1.0             |                             |

Table 17: NINA-B222 mechanical outline data



## 6 Qualification and approvals

### 6.1 Country approvals

The NINA-B2 module series is certified for use in the following countries/regions:

- Europe (RED)
- Great Britain (UKCA)
- Canada (IC)
- USA (FCC)
- Taiwan (NCC)
- Japan (MIC)
- South Korea (KCC)
- Brazil (ANATEL)
- Australia and New Zealand (ACMA)
- South Africa (ICASA)

See the following sections for more information.

### 6.2 European Union regulatory compliance

Information about regulatory compliance of the European Union for NINA-B2 series modules is available in the NINA-B2 EU declaration of conformity [4].

#### 6.2.1 Radio Equipment Directive (RED) 2014/53/EU

NINA-B2 series modules comply with the essential requirements and other relevant provisions of Radio Equipment Directive (RED) 2014/53/EU.


#### 6.2.2 Compliance with the RoHS directive

NINA-B2 series modules comply with the Directive 2011/65/EU (EU RoHS 2) and its amendment Directive (EU) 2015/863 (EU RoHS 3).

### 6.3 Great Britain regulatory compliance

For information about the regulatory compliance of NINA-B2 series modules against requirements and provisions in Great Britain, see also the NINA-B2 UKCA Declaration of Conformity [9].

#### 6.3.1 UK Conformity Assessed (UKCA)


 The United Kingdom is made up of the Great Britain (including England, Scotland, and Wales) and the Northern Ireland. Northern Ireland continues to accept the CE marking. The following notice is applicable to Great Britain only.

NINA-B2 series modules have been evaluated against the essential requirements of the Radio Equipment Regulations 2017 (SI 2017 No. 1206, as amended by SI 2019 No. 696).

Guidance about using the UKCA marking: <https://www.gov.uk/guidance/using-the-ukca-marking>

## 6.4 FCC/IC compliance

This device complies with Part 15 of the FCC Rules and with Industry Canada license-exempt RSS standard(s).

-  Any changes or modifications NOT explicitly APPROVED by u-blox AG may cause the module to not comply with the FCC rules part 15 thus void the user's authority to operate the equipment.

### 6.4.1 FCC compliance

NINA-B2 modules are for OEM integrations only. The end product will be professionally installed in such manner that only the authorized antennas can be used.

For NINA-B221, an external antenna connector (U.FL. connector) reference design is available and must be followed to comply with the NINA-B2 FCC/IC modular approval. See the NINA-B2 series system integration manual [1] for detailed information.

### 6.4.2 FCC statement

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

1. This device may not cause harmful interference, and
2. This device must accept any interference received, including interference that may cause undesired operation.

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that the interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna
- Increase the separation between the equipment and receiver
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

### 6.4.3 RF-exposure statement

#### 6.4.3.1 IC compliance

This equipment complies with the requirements of IC RSS-102 issue 5 radiation exposure limits set forth for an uncontrolled environment.

To ensure that the output power remains below the SAR evaluation Exemption limits defined in RSS-102 issue 5, customer applications integrating NINA-B221 and NINA-B222 must include a separation distance of at least 30 mm between the user (or bystander) and the antenna (or radiating element).


### 6.4.3.2 FCC compliance

This device complies with the FCC radiation exposure limits set forth for an uncontrolled environment.

To ensure that the output power remains below the SAR evaluation Exemption limits defined in SAR test exclusion limits in KDB 447498 D01v06, customer applications integrating NINA-B221 and NINA-B222 must include a separation distance of at least 25 mm between the user (or bystander) and the antenna (or radiating element).

## 6.4.4 End product user manual instructions


### 6.4.4.1 IC compliance

 User manuals for license-exempt radio apparatus shall contain the following text, or an equivalent notice that shall be displayed in a conspicuous location, either in the user manual or on the device, or both:

*This device complies with Industry Canada's license-exempt RSSs. Operation is subject to the following two conditions:*

1. *This device may not cause interference; and*
2. *This device must accept any interference, including interference that may cause undesired operation of the device.*

Under Industry Canada regulations, this radio transmitter can only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be chosen in such a way that the equivalent isotropically radiated power (e.i.r.p.) is not more than that is necessary for successful communication.

 Le manuel d'utilisation des appareils radio exempts de licence doit contenir l'énoncé qui suit, ou l'équivalent, à un endroit bien en vue dans le manuel d'utilisation ou sur l'appareil, ou encore aux deux endroits.

*Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:*

1. *l'appareil ne doit pas produire de brouillage;*
2. *l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.*

Conformément aux réglementations d'Industry Canada, cet émetteur radio ne peut fonctionner qu'à l'aide d'une antenne dont le type et le gain maximal (ou minimal) ont été approuvés pour cet émetteur par Industry Canada. Pour réduire le risque d'interférences avec d'autres utilisateurs, il faut choisir le type d'antenne et son gain de telle sorte que la puissance isotrope rayonnée équivalente (p.i.r.e) ne soit pas supérieure à celle requise pour obtenir une communication satisfaisante.

## 6.4.5 End product labeling requirements

### 6.4.5.1 IC compliance

The host product shall be properly labelled to identify the modules within the host product.

The Innovation, Science and Economic Development Canada certification label of a module shall be clearly visible at all times when installed in the host product; otherwise, the host product must be labelled to display the Innovation, Science and Economic Development Canada certification number for the module, preceded by the word "Contains" or similar wording expressing the same meaning, as shown in [Figure 8](#).

Le produit hôte devra être correctement étiqueté, de façon à permettre l'identification des modules qui s'y trouvent.

L'étiquette d'homologation d'un module d'Innovation, Sciences et Développement économique Canada devra être posée sur le produit hôte à un endroit bien en vue, en tout temps. En l'absence d'étiquette, le produit hôte doit porter une étiquette sur laquelle figure le numéro d'homologation du module d'Innovation, Sciences et Développement économique Canada, précédé du mot « contient », ou d'une formulation similaire allant dans le même sens et qui va comme suit:


This device contains  
 FCC ID: XPYNINAB22  
 IC: 8595A-NINAB22

Figure 8 Example of an end product label

### 6.4.5.2 FCC compliance

For an end product that uses the NINA-B221 or NINA-B222 modules, there must be a label containing, at least, the information shown in [Figure 8](#):

The label must be affixed on an exterior surface of the end product such that it will be visible upon inspection in compliance with the modular approval guidelines developed by the FCC.

 In accordance with 47 CFR § 15.19, the end product shall bear the following statement in a conspicuous location on the device:

"This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions;

1. this device may not cause harmful interference, and
2. this device must accept any interference received, including interference that may cause undesired operation."

When the device is so small or for such use that it is not practicable to place the statement above on it, the information shall be placed in a prominent location in the instruction manual or pamphlet supplied to the user or, alternatively, shall be placed on the container in which the device is marketed.

In case, where the final product will be installed in locations where the end-user is not able to see the FCC ID and/or this statement, the FCC ID and the statement shall also be included in the end product manual.

| Model     | FCC ID     | IC Certification Number |
|-----------|------------|-------------------------|
| NINA-B221 | XPYNINAB22 | 8595A-NINAB22           |
| NINA-B222 | XPYNINAB22 | 8595A-NINAB22           |

Table 18: FCC and IC IDs for NINA-B2 series modules

### 6.4.6 End product compliance

#### 6.4.6.1 General requirements

- Any changes to hardware, hosts or co-location configuration may require new radiated emission and SAR evaluation and/or testing.
- The regulatory compliance of NINA-B221 and NINA-B222 does not exempt the end product from being evaluated against applicable regulatory demands; for example, FCC Part 15B criteria for unintentional radiators.
- Only authorized antenna(s) may be used.
- Any notification to the end user about how to install or remove the integrated radio module is NOT allowed.

### 6.4.6.2 Co-location (simultaneous transmission)

If the module is to be co-located with another transmitter, additional measurements for simultaneous transmission are required.

## 6.5 Japan radio equipment compliance



Figure 9: Giteki mark, **R** and the NINA-B221/ NINA-B222 MIC certification number

For information about compliance of the NINA-B221/ NINA-B222 modules with the Giteki certification, see the NINA-B2 series system integration manual [\[1\]](#).

## 6.6 NCC Taiwan compliance

### 6.6.1 Taiwan NCC Warning Statement

- 經型式認證合格之低功率射頻電機，非經許可，公司、商號或使用者均不得擅自變更頻率、加大功率或變更原設計之特性及功能。
- 低功率射頻電機之使用不得影響飛航安全及干擾合法通信；經發現有干擾現象時，應立即停用，並改善至無干擾時方得繼續使用。前項合法通信，指依電信法規定作業之無線電通信。低功率射頻電機須忍受合法通信或工業、科學及醫療用電波輻射性電機設備之干擾。

Statement translation:

- Without permission granted by the NCC, any company, enterprise, or user is not allowed to change frequency, enhance transmitting power or alter original characteristic as well as performance to an approved low power radio-frequency devices.
- The low power radio-frequency devices shall not influence aircraft security and interfere legal communications; If found, the user shall cease operating immediately until no interference is achieved. The said legal communications means radio communications is operated in compliance with the Telecommunications Act. The low power radio-frequency devices must be susceptible with the interference from legal communications or ISM radio wave radiated devices.

### 6.6.2 NINA-B221 labeling requirements for end product

When a product integrated with a NINA-B221 module is placed on the Taiwan market, the product must be affixed with a label marking as shown below. The label can use wording such as the following:

**Contains Transmitter Module**

內含發射器模組:  CCAJ18LP0B41T0

or any similar wording that expresses the same meaning may be used. The marking must be visible for inspection.

### 6.6.3 NINA-B222 labeling requirements for end product

When a product integrated with an NINA-B222 module is placed on the Taiwan market, the product must be affixed with a label marking as shown below. The label can use wording such as the following:

#### Contains Transmitter Module

內含發射器模組:  **CCAJ18LP0B51T3**

or any similar wording that expresses the same meaning may be used. The marking must be visible for inspection.

## 6.7 KCC South Korea compliance

NINA-B2 series modules are certified by the Korea Communications Commission (KCC).

When a product containing a NINA-B2 module is placed on the South Korean market, the product must be affixed with a label or marking containing the KCC logo and certification number as shown in the following figure. NINA-B221 and NINA-B222 has the same certification number as the NINA-W151 and NINA-W152 modules. This information must also be included in the product user manuals.



The height of the KCC logo must be at least 5 mm.

## 6.8 Brazil compliance

When a product containing NINA-B221 or NINA-B222 modules is placed on the Brazilian market, the product must be affixed with a label or marking containing the Anatel logo, NINA-B221/NINA-B222 Homologation number: 06870-18-05903 and a statement claiming that the device may not cause harmful interference but must accept it (Resolution No 506).



“Este equipamento opera em caráter secundário, isto é, não tem direito a proteção contra interferência prejudicial, mesmo de estações do mesmo tipo, e não pode causar interferência a sistemas operando em caráter primário.”

Statement translation:

“This equipment operates on a secondary basis and, consequently, must accept harmful interference, including from stations of the same kind, and may not cause harmful interference to systems operating on a primary basis.”

When the device is so small or for such use that it is not practicable to place the statement above on it, the information shall be placed in a prominent location in the instruction manual or pamphlet supplied to the user or, alternatively, shall be placed on the container in which the device is marketed.

In case, where the final product will be installed in locations where the end user is unable to see the Anatel logo, NINA-B221/NINA-B222 Homologation number and/or this statement, the Anatel logo, NINA-B221/NINA-B222 Homologation number, and the statement shall also be included in the end product manual.

## 6.9 Australia and New Zealand regulatory compliance



The NINA-B221 and NINA-B222 modules are compliant with the standards made by the Australian Communications and Media Authority (ACMA).

The modules are compliant with AS/NZS 4268:2012 standard – Radio equipment and systems – Short range devices – Limits and methods of standard measurement. The test reports of NINA-B221/NINA-B222 modules can be used as part of the product certification and compliance folder. For more information on the test reports, send an email to the support team in your region. See also [Contact](#).

To meet overall Australian and/or New Zealand end product compliance, the integrator must create a compliance folder containing all the relevant compliance test reports such as RF, EMC, electrical safety and DoC (Declaration of Conformity) and so on. It is the responsibility of the integrator to know what is required in the compliance folder for ACMA compliance.

For more information on Australia compliance, refer to the Australian Communications and Media Authority web site <http://www.acma.gov.au/>.

For more information on New Zealand compliance, refer to the New Zealand Radio Spectrum Management Group web site [www.rsm.govt.nz](http://www.rsm.govt.nz).

## 6.10 South Africa regulatory compliance

The NINA-B221 and NINA-B222 modules are compliant and certified by the Independent Communications Authority of South Africa (ICASA). End products that are made available for sale or lease or is supplied in any other manner in South Africa shall have a legible label permanently affixed to its exterior surface. The label shall have the ICASA logo and the ICASA issued license number as shown in the figure below. The minimum width and height of the ICASA logo shall be 3 mm. The approval labels must be purchased by the customer’s local representative directly from the approval authority ICASA. A sample of a NINA-B221/NINA-B222 ICASA label is included below:



More information on registration as a Responsible Integrator and labeling requirements can be found at the following website:

Independent Communications Authority of South Africa (ICASA) web site - <https://www.icasa.org.za>

## 6.11 Safety compliance

In order to fulfill the safety standard EN 60950-1, NINA-B2 series modules must be supplied with a Class-2 Limited Power Source.

## 6.12 Bluetooth qualification information



® End products are required to be qualified and listed for the Bluetooth Special Interest Group (SIG).

Product declarations are submitted through the SIG [Bluetooth Launch Studio website](#).

NINA-B221 and NINA-B222 modules are qualified as a Controller Subsystem in accordance with the Bluetooth 4.2 specification and are registered with the SIG Qualified Design IDs (QDID) shown in [Table 19](#).

To list your product that integrates NINA-B221 and NINA-B222 as an End product (with no additional testing required), combine the pre-qualified Controller Subsystem QDID (107058) with the QDID of the Host Subsystem implemented in the u-connectXpress version used by your application, as shown in [Table 19](#).



| Model                | Product type         | QD ID  | Listing date | u-connectXpress version |
|----------------------|----------------------|--------|--------------|-------------------------|
| NINA-B221, NINA-B222 | Controller Subsystem | 107058 | 14-Mar-2018  | All versions            |
| NINA-B221, NINA-B222 | Host Subsystem       | 110883 | 30-Apr-2018  | 1.0.0 to 4.0.0          |
| NINA-B221, NINA-B222 | Host Subsystem       | 166433 | 25-May-2021  | 5.0.0 or later          |

**Table 19: NINA-B221/NINA-B222 Bluetooth QDID**



## 7 Antennas

This chapter gives an overview of the different external antennas that can be used together with the module.

-  This radio transmitter IC: 8595A-NINAB22 has been approved by Industry Canada to operate with the antenna types listed below with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.
-  Cet émetteur radio IC: 8595A-NINAB22 été approuvé par Industry Canada pour fonctionner avec les types d'antenne énumérés ci-dessous avec le gain maximum autorisé et l'impédance nécessaire pour chaque type d'antenne indiqué. Les types d'antenne ne figurant pas dans cette liste et ayant un gain supérieur au gain maximum indiqué pour ce type-là sont strictement interdits d'utilisation avec cet appareil.

For each antenna, the "Approvals" field defines in which test reports the antenna is included. Definitions of the «Approvals» field are:

- FCC - The antenna is included in the FCC test reports and thus approved for use in countries that accept the FCC radio approvals, primarily US.
- IC - The antenna is included in the IC (Industrie Canada) test reports and thus approved for use in countries that accept the IC radio approvals, primarily Canada.
- RED - The antenna is included in the ETSI test reports and thus approved for use in countries that accept the Radio Equipment Directive, primarily the European countries.
- UKCA – The antenna is included in the UKCA test reports and thus approved for use in Great Britain.
- MIC - The antenna is included in the Japanese government affiliated MIC test reports and thus approved for use in the Japanese market.
- NCC - The antenna is included in the Taiwan NCC test reports and thus approved for use in Taiwan.
- KCC - The antenna is included in the Korea KCC test reports and thus approved for use in Korea.
- ANATEL – The antenna is included in the Brazil ANATEL test reports and thus approved for use in Brazil.
- ACMA – The antenna is included in the Australia and New Zealand test reports and thus approved for use in Australia and New Zealand.
- ICASA – The antenna is included in the South Africa ICASA test reports and thus approved for use in South Africa.

In general, antennas with SMD connection, Reverse Polarity SMA connector or U.FL connector are included in FCC, IC, RED, MIC, NCC, KCC, ANATEL, ACMA and ICASA radio tests. The antennas with SMA connector are included in RED, MIC, NCC, KCC, ANATEL, ACMA and ICASA radio tests but not in the FCC or IC due to FCC/IC regulations.

The external antennas are connected to the board through U.FL connectors. Some antennas are connected directly to the U.FL connector of the board while some are connected using an SMA or reversed polarity SMA connector through a short U.FL to SMA or reversed polarity SMA adapter cable.

## 7.1 Antenna accessories

| Name               | U.FL to SMA adapter cable  |
|--------------------|--|
| Connector          | U.FL and SMA jack (outer thread and pin receptacle)  |
| Impedance          | 50 $\Omega$  |
| Minimum cable loss | 0.5 dB, The cable loss must be above the minimum cable loss to meet the regulatory requirements. Minimum cable length 100 mm.                      |
| Comment            | The SMA connector can be mounted in a panel. See NINA-B2 series system integration manual [1] for information how to integrate the U.FL connector. |
| Approval           | RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA   |



| Name               | U.FL to Reverse Polarity SMA adapter cable  |
|--------------------|---|
| Connector          | U.FL and Reverse Polarity SMA jack (outer thread and pin)   |
| Impedance          | 50 $\Omega$   |
| Minimum cable loss | 0.5 dB, The cable loss must be above the minimum cable loss to meet the regulatory requirements. Minimum cable length 100 mm.   |
| Comment            | The Reverse Polarity SMA connector can be mounted in a panel. See NINA-B2 series system integration manual [1] for information how to integrate the U.FL connector. It is required to followed this reference design to comply with the NINA-B2 FCC/IC modular approvals. |
| Approval           | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA   |



## 7.2 Approved antennas

### 7.2.1 Single band antennas

| NINA-B222    |  |
|--------------|--|
| Manufacturer | Abracon  |
| Gain         | +3 dBi   |
| Impedance    | 50 $\Omega$  |
| Size (HxWxL) | 3.0 x 3.8 x 9.9 mm   |
| Type         | PIFA   |
| Comment      | SMD PIFA antenna on NINA-B222. Should not be mounted inside a metal enclosure. See also <a href="#">Internal antenna</a> . |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA  |



---

**GW.26.0111**


---

|              |   |
|--------------|---|
| Manufacturer | Taoglas   |
| Polarization | Vertical  |
| Gain         | +2.0 dBi  |
| Impedance    | 50 Ω  |
| Size         | Ø 7.9 x 30.0 mm                                   |
| Type         | Monopole  |
| Connector    | SMA (M) .   |
| Comment      | To be mounted with the U.FL to SMA adapter cable. |
| Approval     | RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA  |




---

**ANT-2.4-CW-RH-RPS**


---

|              |   |
|--------------|---|
| Manufacturer | Linx  |
| Polarization | Vertical  |
| Gain         | -1.0 dBi  |
| Impedance    | 50 Ω  |
| Size         | Ø 7.4 x 27.0 mm   |
| Type         | Monopole  |
| Connector    | Reverse Polarity SMA plug (inner thread and pin receptacle).  |
| Comment      | To be mounted with the U.FL to Reverse Polarity SMA adapter cable.<br>An SMA version antenna is also available but not recommended for use (ANT-2.4-CW-RH-SMA). |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA   |




---

**Wi-Fi external antenna, PN PRO-EX-348**


---

|              |  |
|--------------|--|
| Manufacturer | Abracon  |
| Polarization | Vertical   |
| Gain         | +3.0 dBi   |
| Impedance    | 50 Ω   |
| Size         | Ø 12.0 x 28.0 mm   |
| Type         | Monopole   |
| Connector    | Reverse Polarity SMA plug (inner thread and pin receptacle).   |
| Comment      | The antenna needs to be surrounded by a metal ground plane for best performance. It is mounted with the U.FL to a Reverse Polarity SMA adapter cable.<br>An SMA antenna version is also available, but is not recommended for use (Ex-IT 2400 SMA 28-001). |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA<br>(certified unde PN Ex-IT 2400 RP-SMA 28-001)  |



**Wi-Fi / Bluetooth external antenna, PN PRO-EX-296**

|              |   |
|--------------|---|
| Manufacturer | Abracon   |
| Polarization | Vertical  |
| Gain         | +2.0 dBi  |
| Impedance    | 50 $\Omega$   |
| Size         | $\varnothing$ 12.0 x 28.0 mm  |
| Type         | Monopole  |
| Cable length | 100 mm  |
| Connector    | U.FL. connector   |
| Comment      | <p>The antenna needs a metal ground plane surrounding for best performance. It is mounted with the U.FL to Reverse Polarity SMA adapter cable.</p> <p>For information on how to integrate the U.FL connector, see the NINA-B2 series system integration manual [1]. This reference design must be followed to comply with NINA-B2 FCC/IC modular approvals.</p> |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA, ICASA (certified under the PN Ex-IT 2400 MHF 28)   |


**Wi-Fi / Bluetooth / Bluetooth LE external whip antenna, PN PRO-EX-333**

|              |  |
|--------------|--|
| Manufacturer | Abracon  |
| Polarization | Vertical   |
| Gain         | +3.0 dBi   |
| Impedance    | 50 $\Omega$  |
| Size         | $\varnothing$ 10 x 83 mm   |
| Type         | Monopole   |
| Connector    | Reverse Polarity SMA plug (inner thread and pin receptacle)  |
| Comment      | To be mounted with the U.FL to Reverse Polarity SMA adapter cable. An SMA version antenna is also available but not recommended for use (PN PRO-EX-332). |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA (certified under the PN Ex-IT 2400 RP-SMA 70-002)  |


**Wi-Fi / Bluetooth external whip antenna, PN PRO-EX-327**

|              |  |
|--------------|--|
| Manufacturer | Abracon  |
| Polarization | Vertical   |
| Gain         | +3.0 dBi   |
| Impedance    | 50 $\Omega$  |
| Size         | $\varnothing$ 9.4 x 70.5 mm  |
| Type         | Monopole   |
| Cable length | 100 mm   |
| Connector    | U.FL. connector  |
| Comment      | <p>To be mounted with a U.FL connector.</p> <p>For information on how to integrate the U.FL connector, see the NINA-B2 series system integration manual [1]. This reference design must be followed to comply with NINA-B2 FCC/IC modular approvals.</p> |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA (certified under the PN Ex-IT 2400 MHF 70-001)   |



**Wi-Fi / Bluetooth / Bluetooth LE board antenna, PN PRO-IS-237**

|              |   |
|--------------|---|
| Manufacturer | Abracon   |
| Gain         | +3.0 dBi  |
| Impedance    | 50 $\Omega$   |
| Size         | 27 x 12 mm (triangular)   |
| Type         | Patch   |
| Cable length | 100 mm  |
| Connector    | U.FL. connector   |
| Comment      | <p>Should be attached to a plastic enclosure or part for best performance.</p> <p>To be mounted with a U.FL connector.</p> <p>See NINA-B2 series system integration manual [1] for information how to integrate the U.FL connector. This reference design must be followed to comply with NINA-B2 FCC/IC modular approvals.</p> |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA   |




## 7.2.2 Dual-band antennas

**Wi-Fi / Bluetooth / Bluetooth LE board antenna, PN PRO-IS-299**

|              |  |
|--------------|--|
| Manufacturer | Abracon  |
| Gain         | +3.0 dBi   |
| Impedance    | 50 $\Omega$  |
| Size         | 27 x 12 mm (triangular)  |
| Type         | Patch  |
| Cable length | 100 mm   |
| Connector    | U.FL. connector  |
| Comment      | <p>Should be attached to a plastic enclosure or part for best performance. Dual-band (2.4 GHz / 5 GHz) antenna to be mounted with a U.FL connector.</p> <p>For information on how to integrate the U.FL connector, see the NINA-B2 series system integration manual [1]. This reference design must be followed to comply with NINA-B2 FCC/IC modular approvals.</p> |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA, and ICASA   |


**Wi-Fi / Bluetooth / Bluetooth LE board antenna, PN PRO-IS-432**

|              |  |
|--------------|--|
| Manufacturer | Abracon  |
| Gain         | +3.0 dBi   |
| Impedance    | 50 $\Omega$  |
| Size         | 24 x 22 x 1 mm with mounting hole  |
| Type         | Patch  |
| Cable length | 100 mm   |
| Connector    | U.FL. connector  |
| Comment      | <p>Should be attached to a plastic enclosure or part for best performance. Dual-band (2.4 GHz / 5 GHz) antenna to be mounted with a U.FL connector.</p> <p>For information on how to integrate the U.FL connector, see the NINA-B2 series system integration manual [1]. This reference design must be followed to comply with NINA-B2 FCC/IC modular approvals.</p> |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA and ICASA  |



---

**Wi-Fi / Bluetooth external whip antenna, PN PRO-EX-286**


---

|              |   |
|--------------|---|
| Manufacturer | Abracon   |
| Type         | ½ wave dipole dual-band antenna   |
| Polarization | Vertical  |
| Gain         | +3 dBi  |
| Impedance    | 50 Ω  |
| Size         | 107 mm (Straight)   |
| Type         | Monopole  |
| Connector    | Reverse Polarity SMA plug (inner thread and pin receptacle)   |
| Comment      | To be mounted with the U.FL to Reverse Polarity SMA adapter cable.                                  |
| Approval     | FCC, IC, RED, UKCA, MIC, NCC, KCC, ANATEL, ACMA, ICASA<br>(certified under the PN Ex-IT WLAN RPSMA) |

---



# 8 Product handling

## 8.1 Packaging

**⚠** NINA-B2 series modules are currently in development status. See also [Applicability](#). Consequently, the information in this section is only applicable after the module has been fully tested and approved in the Initial Production stage.

### 8.1.1 Reels

NINA-B2 series modules are delivered as hermetically sealed, reeled tapes to enable efficient production, production lot set-up and tear-down. For more information about packaging, see also the Packaging information reference [\[2\]](#).


NINA-B2 modules are deliverable in quantities of 500 pieces on a reel. The reel types for NINA-B2 modules are shown in [Table 20](#). For more information about the reel different reel types, see also the Packaging information reference [\[2\]](#).

| Model     | Reel type |
|-----------|-----------|
| NINA-B221 | B         |
| NINA-B222 | A         |

**Table 20: Reel types for the different NINA-B2 series models**

### 8.1.2 Tapes


[Figure 10](#) and [Figure 11](#) shows the position and orientation of NINA-B2 modules as they are delivered on tape. The dimensions of the tapes are specified in [Figure 12](#) and [Figure 13](#).



**Figure 10: Orientation of NINA-B221 module on tape**




**Figure 11: Orientation of NINA-B222 module on tape**



- NOTES:
1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE  $\pm 0.2$
  2. POCKET POSITION RELATIVE TO SPROCKET HOLE MEASURED AS TRUE POSITION OF POCKET, NOT POCKET HOLE.
  3. Ao AND Bo ARE MEASURED ON A PLANE AT A DISTANCE "R" ABOVE THE BOTTOM OF THE POCKET.

Figure 12: NINA-B221 tape dimension




- NOTES:
1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE  $\pm 0.2$
  2. POCKET POSITION RELATIVE TO SPROCKET HOLE MEASURED AS TRUE POSITION OF POCKET, NOT POCKET HOLE.
  3. Ao AND Bo ARE CALCULATED ON A PLANE AT A DISTANCE "R" ABOVE THE BOTTOM OF THE POCKET.

Figure 13: NINA-B222 tape dimension



## 8.2 Moisture sensitivity levels


-  NINA-B2 series modules are rated as MSL Level 4 devices in accordance with the IPC/JEDEC J-STD-020 standard. For detailed information, see the moisture sensitive warning label on the MBB (Moisture Barrier Bag).

After opening the dry pack, the modules must be mounted within 72 hours in factory conditions of maximum 30 °C/60%RH or must be stored at less than 10%RH. The modules require baking if the humidity indicator card shows more than 10% when read at 23±5 °C or if the conditions mentioned above are not met. For information about the bake procedure, see also the J-STD-033B standard.


For more information regarding MSL (Moisture Sensitivity Level), labeling, and storage, see also the Packaging information guide [\[2\]](#).

## 8.3 Reflow soldering

NINA-B2 series modules are approved for two-time reflow processes.

-  Reflow soldering profiles must be selected in accordance with u-blox soldering recommendations described in the NINA-B2 series system integration manual [\[1\]](#). Failure to observe these recommendations can result in severe damage to the product.

## 8.4 ESD precautions

-  NINA-B2 series modules are Electrostatic Sensitive Devices that demand the observance of special handling precautions against static damage. Failure to observe these precautions can result in severe damage to the product. See also [Maximum ESD ratings](#).

Proper ESD handling and packaging procedures must be applied throughout the processing, handling, and operation of any application that incorporates the NINA-B2 series module. ESD precautions are particularly relevant when handling the application board on which the module is mounted.

For further information about the handling of NINA-B2 series modules, see also the NINA-B2 system integration manual [\[1\]](#).

## 9 Labeling and ordering information

### 9.1 Product labeling

The (7.5 x 7.5 mm) labels on the NINA-B2 series modules include important product information.

Figure 14 shows the label applied to NINA-B40 series modules. Each of the given label references are described in Table 21.



Figure 14: Location of product type number on the NINA-B2 series module label

| Reference | Description   |
|-----------|---|
| 1         | Date of unit production encoded YY/WW (year, week)  |
| 2         | Major and minor product version information   |
| 3         | Product model name (NINA-B221 or NINA-B222)   |
| 4         | Data Matrix with unique serial number comprising 19 alphanumeric symbols: <ul style="list-style-type: none"> <li>- The first 3 symbols are used for production tracking and are an abbreviated representation of the Type number that is unique to each module variant.</li> <li>- The following 12 symbols represent the unique hexadecimal Bluetooth address of the module AABBCDDEEFF, and</li> </ul> The last 4 symbols represent the hardware and firmware version encoded HFFF.<br>See also <a href="#">MAC addresses</a> . |
| 5         | u-blox logo. The red dot also indicates pin 1.  |

Table 21: NINA-B2 series label description

### 9.1.1 Product identifiers

Table 22 describes the three product identifiers, namely the Type number, Model name and Ordering code.

| Format        | Description  | Nomenclature     |
|---------------|--|------------------|
| Model name    | Describes the form factor, platform technology and platform variant. Used mostly in product documentation like this data sheet, the model name represents the most common identity for all u-blox products | PPPP-TGVV        |
| Ordering code | Comprises the model name – with additional identifiers to describe the major product version and quality grade   | PPPP-TGVV-TTQ    |
| Type number   | Comprises the model name and ordering code – with additional identifiers to describe minor product versions.   | PPPP-TGVV-TTQ-XX |

Table 22: Product code formats

### 9.1.2 Identification codes

Table 23 describes the individual identification codes represented in each product identifier.

| Code | Meaning  | Example   |
|------|--|---|
| PPPP | Form factor  | NINA  |
| TG   | Platform (Technology and Generation)<br>T – Dominant technology, For example, W: Wi-Fi, B: Bluetooth<br>G – Generation | B2: Bluetooth Generation 2                            |
| VV   | Variant based on the same platform; range [00...99]  | 21: u-connectXpress software product with antenna pin |
| TT   | Major Product Version  | 00: first revision                                    |
| Q    | Quality grade<br>A: Automotive<br>B: Professional<br>C: Standard   | B: professional grade                                 |
| XX   | Minor product version (not relevant for certification)   | Default value is 00                                   |

Table 23: Part identification code

## 9.2 Ordering information

| Ordering code | Product   |
|---------------|---|
| NINA-B221-00B | Bluetooth dual-mode module with antenna pin. With u-connectXpress software including secure boot. Using ESP32-D0WDQ6.                 |
| NINA-B221-02B | Bluetooth dual-mode module with antenna pin. With u-connectXpress software including secure boot. Using ESP32-D0WDQ6-V3.              |
| NINA-B221-03B | Bluetooth dual-mode module with antenna pin. With u-connectXpress software including secure boot. Using ESP32-D0WDQ6-V3.              |
| NINA-B222-00B | Bluetooth dual-mode module with internal onboard antenna. With u-connectXpress software including secure boot. Using ESP32-D0WDQ6.    |
| NINA-B222-02B | Bluetooth dual-mode module with internal onboard antenna. With u-connectXpress software including secure boot. Using ESP32-D0WDQ6-V3. |
| NINA-B222-03B | Bluetooth dual-mode module with internal onboard antenna. With u-connectXpress software including secure boot. Using ESP32-D0WDQ6-V3. |

Table 24: Product ordering codes

# Appendix


## A Glossary

| Abbreviation | Definition  |
|--------------|---|
| ADC          | Analog to Digital Converter                       |
| AFA          | Automatic Frequency Adaption                      |
| BR           | Basic Rate  |
| BDR          | Basic Data Rate                                   |
| BPF          | Band Pass Filter                                  |
| BT           | Bluetooth   |
| CTS          | Clear To Send                                     |
| DAC          | Digital to Analog Converter                       |
| DC           | Direct Current                                    |
| DSR          | Data Set Ready                                    |
| DTR          | Data Terminal Ready                               |
| EDR          | Enhanced Data Rate                                |
| ESD          | Electro Static Discharge                          |
| FCC          | Federal Communications Commission                 |
| GND          | Ground  |
| GPIO         | General Purpose Input/Output                      |
| IC           | Industry Canada                                   |
| IEEE         | Institute of Electrical and Electronics Engineers |
| IoT          | Internet of Things                                |
| LPO          | Low Power Oscillator                              |
| MCU          | Micro Controller Unit                             |
| MDIO         | Management Data Input / Output                    |
| MII          | Media-Independent Interface                       |
| MISO         | Master In Slave Out (data output from slave)      |
| MOSI         | Master Out Slave In (data output from master)     |
| MRD          | Market Requirement Document                       |
| MSD          | Moisture Sensitive Device                         |
| N/A          | Not Applicable                                    |
| PCN          | Product Change Notification                       |
| PIFA         | Planar Inverted F Antenna                         |
| PD           | Pull-Down   |
| PU           | Pull-Up   |
| QSPI         | Quad Serial Peripheral Interface                  |
| RTS          | Request To Send                                   |
| RXD          | Receive Data                                      |
| SDIO         | Secure Digital Input Output                       |
| SDK          | Software Development Kit                          |
| SPI          | Serial Peripheral Interface                       |
| TXD          | Transmit Data                                     |
| UART         | Universal Asynchronous Receiver/Transmitter       |

**Table 25: Explanation of the abbreviations and terms used**

## Related documents

- [1] NINA-B2 series system integration manual, [UBX-18011096](#)
- [2] Product packaging guide, [UBX-14001652](#)
- [3] u-connectXpress AT commands manual, [UBX-14044127](#)
- [4] NINA-B2 EU declaration of conformity, [UBX-18007187](#)
- [5] NINA-B2 series product summary, [UBX-17062096](#)
- [6] u-connectXpress SPI peripheral protocol specification, [UBX-20028725](#)
- [7] u-connectXpress software user guide, [UBX-16024251](#)
- [8] s-center user guide, [UBX-16012261](#)
- [9] NINA-B2 UKCA declaration of conformity, [UBX-22035015](#)

 For product change notifications and regular updates of u-blox documentation, register on our website, [www.u-blox.com](http://www.u-blox.com).

## Revision history

| Revision | Date        | Name       | Comments  |
|----------|-------------|------------|---|
| R01      | 16-Mar-2018 | mwej, kgom | Initial release.  |
| R02      | 6-Jul-2018  | mwej, kgom | Updated the software version to version 1.0.0 and modified the corresponding content status to Advance Information. Modified the values for Bluetooth output power (chapter 4). Removed "pending" status for the following country approvals in section 6 - USA (FCC), Canada (IC) and Japan (MIC).   |
| R03      | 14-Dec-2018 | mwej       | Updated label description (Table 21). Removed LPO functionality. Updated RF characteristics and current consumption in chapter 4.   |
| R04      | 28-Jan-2019 | mwej       | Modified the product status to Initial Production. Updated description of usage of the DSR signal in section 2.6.4.   |
| R05      | 13-Aug-2019 | fbro, mwej | Updated pinout due to typo regarding switch 1 and 2. Added certification information for Brazil, Australia, New Zealand and South Africa (sections 6.8-6.10). Updated information about approved antennas (chapter 7). Updated with RoHS 3 compliance (section 6.2.2). Updated voltage supply range (section 4.2.2) and absolute maximum module supply voltage and maximum RF input ratings (section 4.1).<br>Updated maximum ESD ratings (section 4.1.1). Corrected information about restoring UART setting to default settings (section 2.6.3). Updated Bluetooth output power and sensitivity (sections 1.5, 4.2.6 and 4.2.7). Corrected information about blue LED signal in connected mode (Table 4). |
| R06      | 27-Jan-2020 | mlju       | Updated type numbers in the second table on page 2 with NINA-B22x-00B-01.   |
| R07      | 18-Sep-2020 | hekf, ajoh | Added antenna radiation patterns in section 4.2.8 and GPIO drive strength in section 4.2.4. Changed boot strap information in section 2.3 and ESD ratings in section 4.1.1. Added new NINA-B221 and B222 product variants. Updated Figure 3 and Table 5 to reflect the revised number of available GPIOs. Changed software name to u-connectXpress, and added SPI support in sections 2.7.2, 2.4 and 3.1. Added descriptions of the new power modes in section 2.2. Updated current consumption data in electrical specifications, section 4.2.5. Added GPI and SPI functionality to pins in chapter 3.1.   |
| R08      | 18-May-2021 | mape, hekf | Updated Bluetooth terminology. Updated the <a href="#">Pin assignment</a> . Removed current peak values in <a href="#">Current consumption</a> . Added version NINA-B22x-03B in <a href="#">Applicability</a> and <a href="#">Ordering information</a> . Added information in <a href="#">Module reset</a> and <a href="#">Low Power Clock</a> . Added drive capability information in <a href="#">Drive capability</a> . Revised <a href="#">Labeling and ordering information</a> .   |

| Revision | Date        | Name       | Comments   |
|----------|-------------|------------|--|
| R09      | 15-Nov-2021 | hekf       | Updated names for ProAnt Ex-It series antennas and FlatWhip EOL in <a href="#">Approved antennas</a> . Added new products NINA-B221/B222-03B-01 and removed the NINA-B221/B222-00B-01, NINA-B221/B222-02B-00 and NINA-B221/B222-03B-00 in <a href="#">Document information</a> .<br>Removed ambiguous description of operating condition ranges in <a href="#">Electrical specifications</a> . Updated information describing <a href="#">Moisture sensitivity levels</a> , <a href="#">Reflow soldering</a> , and <a href="#">ESD precautions</a> . Revised <a href="#">Maximum ESD ratings</a> . |
| R10      | 16-Aug-2022 | fkru       | Updated listing details in <a href="#">Bluetooth qualification information</a> . Corrected appropriate bake mount time to 72 hours in <a href="#">Moisture sensitivity levels</a> .<br>Updated contact information. Revised <a href="#">Bluetooth qualification information</a> .<br>Revised former Proant antenna references with updated part numbers from Abracon and removed obsolete antennas (EOL) from the list of <a href="#">approved antennas</a> .  |
| R11      | 19-Dec-2022 | ecar, hekf | Updated product status in <a href="#">Document information</a> . Added data for the RESET_N pin characteristics in <a href="#">Table 10</a> . Added <a href="#">Great Britain regulatory compliance</a> statement.   |

## Contact

For further support and contact information, visit us at [www.u-blox.com/support](http://www.u-blox.com/support).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[u-blox:](#)

[NINA-B221-03B](#) [NINA-B221-04B](#) [NINA-B222-04B](#)