

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [22-04-1051](#)
Status: **Active**
Overview: Mini-Latch™ Wire-to-Board System
Description: Mini-Latch™ Wire-to-Board Header, Vertical, with Friction Ramp, 5 Circuits, Tin (Sn) Plating

Documents:

3D Model	Product Specification PS-5102-001 (PDF)
Drawing (PDF)	Product Specification PS-5102-002 (PDF)
Product Specification PS-5045-001 (PDF)	Product Specification PS-51191-002 (PDF)
Product Specification PS-5045-002 (PDF)	Packaging Specification SPK-5045-001 (PDF)
Product Specification PS-5051-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5051-005 (PDF)	

Agency Certification


UL E29179

General

Product Family	PCB Headers
Series	5045
Application	Signal, Wire-to-Board
Overview	<u>Mini-Latch™ Wire-to-Board System</u>
Product Name	KK®
UPC	800753740754

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	517.600/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5045Series

Mates With

KK® 2.50mm Housings 51191 , 5051

Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3A
Voltage - Maximum	250V

Material Info

Old Part Number	5045-05A
-----------------	----------

Reference - Drawing Numbers

Packaging Specification	SPK-5045-001
Product Specification	PS-5045-001, PS-5045-002, PS-5051-001, PS-5051-005, PS-5102-001, PS-5102-002, PS-51191-002, RPS-5045-001, RPS-51191-007
Sales Drawing	SD-5045-NA

This document was generated on 10/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION