

Specification Sheet

Part Number: T40R0HSM4



Heat stabilized cable ties provide excellent resistance to high heat exposures.
Inside serrations allow for strong grip on cables and wire bundles.
Head design provides high tensile strength with very low insertion force.
Bent tail ensures a quick and simple installation.

High-Temp Cable Tie, 8" Long, UL Rated, 40lb Tensile Strength, PA66HS, Black, 1000/pkg

Article Number 111-04140

Type T40R(U)

Color Black (BK)

Quantity Per bag

Product Description T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description High-Temp Cable Tie, 8" Long, UL Rated, 40lb Tensile Strength, PA66HS, Black, 1000/pkg

Global Part Name T40R(U)-PA66HS-BK

Minimum Tensile Strength (Imperial) 40.0

Minimum Tensile Strength (Metric) 180.0

Length L (Imperial) 8.0

Length L (Metric) 210.82

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.16

Width W (Metric) 4.0

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 2.17

Bundle Diameter Max (Metric) 55.0

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T40R0HSM4](#)