# **General Purpose Transistors**

## **NPN Silicon**

These transistors are designed for general purpose amplifier applications. They are housed in the SC-70/SOT-323 which is designed for low power surface mount applications.

#### **Features**

- S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **MAXIMUM RATINGS**

Rating	Symbol	Value	Unit
Collector-Emitter Voltage  BC846 BC847 BC848	V <sub>CEO</sub>	65 45 30	٧
Collector-Base Voltage  BC846 BC847 BC848	V <sub>CBO</sub>	80 50 30	V
Emitter-Base Voltage  BC846 BC847 BC848	V <sub>EBO</sub>	6.0 6.0 5.0	V
Collector Current – Continuous	Ic	100	mAdc

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Total Device Dissipation FR-5 Board, (Note 1) T <sub>A</sub> = 25°C	P <sub>D</sub>	200	mW
Thermal Resistance, Junction-to-Ambient	$R_{ heta JA}$	620	°C/W
Junction and Storage Temperature	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

1.  $FR-5 = 1.0 \times 0.75 \times 0.062$  in.



#### ON Semiconductor®

www.onsemi.com





SC-70/SOT-323 CASE 419 STYLE 3

#### **MARKING DIAGRAM**



XX = Specific Device Code

M = Month Code

= Pb-Free Package

(Note: Microdot may be in either location)


#### **ORDERING INFORMATION**

See detailed ordering, marking and shipping information in the package dimensions section on page 12 of this data sheet.

## **ELECTRICAL CHARACTERISTICS** ( $T_A = 25$ °C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS						
Collector – Emitter Breakdown Voltage (I <sub>C</sub> = 10 mA)	BC846 Series BC847 Series BC848 Series	V <sub>(BR)CEO</sub>	65 45 30	- - -	- - -	V
Collector – Emitter Breakdown Voltage ( $I_C = 10 \mu A, V_{EB} = 0$ )	BC846 Series BC847 Series BC848 Series	V <sub>(BR)CES</sub>	80 50 30	- - -	- - -	٧
Collector – Base Breakdown Voltage ( $I_C = 10 \mu A$ )	BC846 Series BC847 Series BC848 Series	V <sub>(BR)CBO</sub>	80 50 30	- - -	- - -	٧
Emitter-Base Breakdown Voltage (I <sub>E</sub> = 1.0 μA)	BC846 Series BC847 Series BC848 Series	V <sub>(BR)EBO</sub>	6.0 6.0 5.0	- - -	- - -	V
Collector Cutoff Current (V <sub>CB</sub> = 30 V)	(V <sub>CB</sub> = 30 V, T <sub>A</sub> = 150°C)	I <sub>CBO</sub>	_ _	- -	15 5.0	nA μA
ON CHARACTERISTICS						
DC Current Gain (I <sub>C</sub> = 10 $\mu$ A, V <sub>CE</sub> = 5.0 V)	BC846A, BC847A, BC848A BC846B, BC847B, BC848B BC847C, BC848C	h <sub>FE</sub>	- - -	90 150 270	- - -	_
$(I_C = 2.0 \text{ mA}, V_{CE} = 5.0 \text{ V})$	BC846A, BC847A, BC848A BC846B, BC847B, BC848B BC847C, BC848C		110 200 420	180 290 520	220 450 800	
Collector – Emitter Saturation Voltage ( $I_C = 10 \text{ mA}$ , $I_B = 0.00$ ) ( $I_C = 100 \text{ mA}$ , $I_B = 0.00$ )		V <sub>CE(sat)</sub>	- -	- -	0.25 0.6	V
Base – Emitter Saturation Voltage ( $I_C$ = 10 mA, $I_B$ = 0.5 ( $I_C$ = 100 mA, $I_B$ = 5.		V <sub>BE(sat)</sub>	_ _	0.7 0.9	- -	V
Base – Emitter Voltage ( $I_C$ = 2.0 mA, $V_{CE}$ = 5.0 V) ( $I_C$ = 10 mA, $V_{CE}$ = 5.0 V)		V <sub>BE(on)</sub>	580 -	660 -	700 770	mV
SMALL-SIGNAL CHARACTERISTICS						
Current – Gain – Bandwidth Product (I <sub>C</sub> = 10 mA, V <sub>CE</sub> = 5.0 Vdc, f = 100 MHz)		f <sub>T</sub>	100	_	_	MHz
Output Capacitance (V <sub>CB</sub> = 10 V, f = 1.0 MHz)		C <sub>obo</sub>	-	_	4.5	pF
Noise Figure ( $I_C = 0.2$ mA, $V_{CE} = 5.0$ Vdc, $R_S = 2.0$ k $\Omega$ , $f = 1.0$ kHz, BW = 200 Hz)			-	-	10	dB

#### BC846A, BC847A, BC848A



300 150°C VCE = 5 V VCE = 5 V 25°C 25°C 0 0.001 0.01 0.1 I<sub>C</sub>, COLLECTOR CURRENT (A)

Figure 1. DC Current Gain vs. Collector Current

Figure 2. DC Current Gain vs. Collector Current






Figure 3. Collector Emitter Saturation Voltage vs. Collector Current








Figure 5. Base Emitter Voltage vs. Collector Current

#### BC846A, BC847A, BC848A




Figure 6. Collector Saturation Region

Figure 7. Base-Emitter Temperature Coefficient




Figure 8. Capacitances




Figure 9. Current-Gain - Bandwidth Product

#### **BC846B**




Figure 10. DC Current Gain vs. Collector Current

Figure 11. DC Current Gain vs. Collector Current





Figure 12. Collector Emitter Saturation Voltage vs. Collector Current



0.1 × vs.





Figure 13. Base Emitter Saturation Voltage vs. Collector Current

Figure 14. Base Emitter Voltage vs. Collector Current

#### BC846B



 $\theta_{\mbox{\scriptsize VB}}$  TEMPERATURE COEFFICIENT (mV/  $^{\circ}\mbox{\scriptsize C}$ 1.8  $\theta_{\text{VB}}$  for  $\text{V}_{\text{BE}}$ -55°C to 125°C 2.2 2.6 0.2 2.0 10 50 100 200 0.5 1.0 5.0 I<sub>C</sub>, COLLECTOR CURRENT (mA)

Figure 15. Collector Saturation Region

Figure 16. Base-Emitter Temperature Coefficient




Figure 17. Capacitance





Figure 18. Current-Gain - Bandwidth Product

#### BC847B, BC848B



600 150°C 150°C 400 25°C 25°C 100 0 0.001 0.01 0.1

Figure 19. DC Current Gain vs. Collector Current

Figure 20. DC Current Gain vs. Collector Current





Figure 21. Collector Emitter Saturation Voltage vs. Collector Current









Figure 23. Base Emitter Voltage vs. Collector Current

## BC847B, BC848B

1.2

400 300




θ√B, TEMPERATURE COEFFICIENT (mV/°C) 1.6 2.0 2.4 2.8 0.2 1.0 10 I<sub>C</sub>, COLLECTOR CURRENT (mA)

55°C to +125°C

Figure 24. Collector Saturation Region

Figure 25. Base-Emitter Temperature Coefficient

100







Figure 26. Capacitances

I<sub>C</sub>, COLLECTOR CURRENT (mAdc) Figure 27. Current-Gain - Bandwidth Product

#### BC847C, BC848C



1000 900 150°C 800 hFE, DC CURRENT GAIN 700 600 25°C 500 400 –55°C 300 200 100 0.001 0.01 0.1 I<sub>C</sub>, COLLECTOR CURRENT (A)

Figure 28. DC Current Gain vs. Collector Current

Figure 29. DC Current Gain vs. Collector Current





Figure 30. Collector Emitter Saturation Voltage vs. Collector Current

1.2






Figure 31. Base Emitter Saturation Voltage vs. **Collector Current** 

Figure 32. Base Emitter Voltage vs. Collector Current

## BC847C, BC848C





Figure 33. Collector Saturation Region

Figure 34. Base–Emitter Temperature Coefficient








Figure 36. Current-Gain - Bandwidth Product





Figure 37. Safe Operating Area for BC846A, BC846B

Figure 38. Safe Operating Area for BC847A, BC847B, BC847C



 $V_{CE}$ , COLLECTOR EMITTER VOLTAGE (V)

Figure 39. Safe Operating Area for BC848A, BC848B, BC848C

#### **DEVICE ORDERING AND SPECIFIC MARKING INFORMATION**

Device	Specific Marking Code	Package	Shipping <sup>†</sup>	
BC846BWT1G	1B	SC-70 (SOT-323) (Pb-Free)	3,000 / Tape & Reel	
SBC846BWT1G*	ID			
BC847AWT1G	1E		2 000 / Tone & Book	
SBC847AWT1G*	15		3,000 / Tape & Reel	
BC847BWT1G	1F		3,000 / Tape & Reel	
SBC847BWT1G*	IF			
BC847CWT1G	1G		2 000 / Topo & Book	
SBC847CWT1G*	10		3,000 / Tape & Reel	
BC847CWT3G	1G		10,000 / Tape & Reel	
SBC847CWT3G*	10			
BC848BWT1G	1K			
NSVBC848BWT1G*	I I K		3,000 / Tape & Reel	
BC848CWT1G	1L			

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.
\*S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable.






SC-70 (SOT-323) CASE 419 ISSUE P

**DATE 07 OCT 2021** 

#### NOTES:


- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1982.
- 2. CONTROLLING DIMENSION: INCH

	MILLIMETERS				INCHES	
DIM	MIN.	N□M.	MAX.	MIN.	N□M.	MAX.
Α	0.80	0.90	1.00	0.032	0.035	0.040
A1	0.00	0.05	0.10	0.000	0.002	0.004
A2	0.70 REF				0.028 BS	C
b	0.30	0.35	0.40	0.012	0.014	0.016
С	0.10	0.18	0.25	0.004	0.007	0.010
D	1.80	2.10	2.20	0.071	0.083	0.087
Ε	1.15	1.24	1.35	0.045	0.049	0.053
e	1.20	1.30	1.40	0.047	0.051	0.055
e1	0.65 BSC				0.026 BS	C
L	0.20	0.38	0.56	0.008	0.015	0.022
HE	2.00	2.10	2.40	0.079	0.083	0.095
				`		



For additional information on our Pb-Free strategy and soldering details, please download the IIN Semiconductor Soldering and Mounting Techniques Reference Manual, SILDERRM/D.

SOLDERING FOOTPRINT



# GENERIC MARKING DIAGRAM



XX = Specific Device Code

M = Date Code

■ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

STYLE 1: CANCELLED	STYLE 2: PIN 1. ANODE 2. N.C. 3. CATHODE	STYLE 3: PIN 1. BASE 2. EMITTER 3. COLLECTOR	STYLE 4: PIN 1. CATHODE 2. CATHODE 3. ANODE	STYLE 5: PIN 1. ANODE 2. ANODE 3. CATHODE	
STYLE 6: PIN 1. EMITTER	STYLE 7: PIN 1. BASE	STYLE 8: PIN 1. GATE	STYLE 9: PIN 1. ANODE	STYLE 10: PIN 1. CATHODE	STYLE 11: PIN 1. CATHODE
2. BASE	2. EMITTER	2. SOURCE	2. CATHODE	2. ANODE	2. CATHODE
<ol><li>COLLECTOR</li></ol>	<ol><li>COLLECTOR</li></ol>	3. DRAIN	<ol><li>CATHODE-ANODE</li></ol>	3. ANODE-CATHODE	<ol><li>CATHODE</li></ol>

DOCUMENT NUMBER:	98ASB42819B	Electronic versions are uncontrolled except when accessed directly from the Document Reposit Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	SC-70 (SOT-323)		PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer p

#### PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

onsemi Website: www.onsemi.com