
STM8S105xx



Access line, 16 MHz STM8S 8-bit MCU, up to 32 Kbytes Flash, integrated EEPROM,10-bit ADC, timers, UART, SPI, I²C

Datasheet - production data



Features

Core

- 16 MHz advanced STM8 core with Harvard architecture and 3-stage pipeline
- Extended instruction set

Memories

- Medium-density Flash/EEPROM:
 - Program memory up to 32 Kbytes; data retention 20 years at 55°C after 10 kcycles
 - Data memory up to 1 Kbytes true data EEPROM; endurance 300 kcycles
- RAM: Up to 2 Kbytes

Clock, reset and supply management

- 2.95 V to 5.5 V operating voltage
- Flexible clock control, 4 master clock sources:
 - Low power crystal resonator oscillator
 - External clock input
 - Internal, user-trimmable 16 MHz RC
 - Internal low power 128 kHz RC
- Clock security system with clock monitor
- Power management:
 - Low power modes (wait, active-halt, halt)
 - Switch-off peripheral clocks individually
- Permanently active, low consumption power-on and power-down reset

Interrupt management

- Nested interrupt controller with 32 interrupts
- Up to 37 external interrupts on 6 vectors

Timers

- 2x 16-bit general purpose timers, with 2+3 CAPCOM channels (IC, OC or PWM)
- Advanced control timer: 16-bit, 4 CAPCOM channels, 3 complementary outputs, dead-time insertion and flexible synchronization
- 8-bit basic timer with 8-bit prescaler
- Auto wake-up timer
- Window and independent watchdog timers

Communications interfaces

- UART with clock output for synchronous operation, Smartcard, IrDA, LIN
- SPI interface up to 8 Mbit/s
- I²C interface up to 400 Kbit/s

Analog-to-digital converter (ADC)

 10-bit, ±1 LSB ADC with up to 10 multiplexed channels, scan mode and analog watchdog

I/Os

- Up to 38 I/Os on a 48-pin package including 16 high sink outputs
- Highly robust I/O design, immune against current injection

Development support

 Embedded single wire interface module (SWIM) for fast on-chip programming and non-intrusive debugging

Unique ID

• 96-bit unique key for each device

Table 1: Device summary

Reference	Part number
STM8S105xx	STM8S105K4, STM8S105K6, STM8S105S4, STM8S105S6, STM8S105C4, STM8S105C6

Contents STM8S105xx

Contents

1	Introduc	tion		8
2	Descript	tion		9
3	Block di	agram		10
4	Product	overview		11
	4.1	Single wir	e interface module (SWIM) and debug module (DM)	11
	4.2	Interrupt of	controller	12
	4.3	Flash prog	gram and data EEPROM memory	12
	4.4	Clock con	troller	13
	4.5	Power ma	anagement	14
	4.6		timers	
	4.7	Auto wake	eup counter	15
	4.8	Beeper		15
	4.9	TIM1 - 16	-bit advanced control timer	15
	4.10	TIM2, TIM	13 - 16-bit general purpose timers	15
	4.11	TIM4 - 8-k	oit basic timer	16
	4.12	Analog-to	-digital converter (ADC1)	16
	4.13	Communi	cation interfaces	17
		4.13.1	UART2	17
		4.13.2	SPI	
		4.13.3	I ² C	
5	Pinout a	=	scription	
	5.1	STM8S10	5 pinouts and pin description	
		5.1.1	Alternate function remapping	24
6	Memory	and regis	ster map	25
	6.1	Memory n	nap	25
	6.2	Register r	map	26
		6.2.1	I/O port hardware register map	
		6.2.2	General hardware register map	
	_	6.2.3	CPU/SWIM/debug module/interrupt controller registers	
7	-		napping	
8	Option k	ytes		37
9	Unique l	D		41
2/00			DocID14771 Ray 13	

10	Electrica	al characte	eristics	42
	10.1	Paramete	r conditions	42
		10.1.1	Minimum and maximum values	42
		10.1.2	Typical values	42
		10.1.3	Typical curves	42
		10.1.4	Typical current consumption	42
		10.1.5	Loading capacitor	43
		10.1.6	Pin input voltage	43
	10.2	Absolute r	maximum ratings	43
	10.3	Operating	conditions	45
		10.3.1	VCAP external capacitor	46
		10.3.2	Supply current characteristics	47
		10.3.3	External clock sources and timing characteristics	56
		10.3.4	Internal clock sources and timing characteristics	58
		10.3.5	Memory characteristics	60
		10.3.6	I/O port pin characteristics	61
		10.3.7	Typical output level curves	64
		10.3.8	Reset pin characteristics	68
		10.3.9	SPI serial peripheral interface	70
		10.3.10	I2C interface characteristics	
		10.3.11	10-bit ADC characteristics	
		10.3.12	EMC characteristics	77
11	Package	e informati	ion	80
	11.1	48-pin LQ	FP package mechanical data	80
	11.2	44-pin LQ	FP package mechanical data	81
	11.3	32-pin LQ	FP package mechanical data	82
	11.4	32-lead U	FQFPN package mechanical data	84
	11.5		ackage mechanical data	
12			ristics	
	12.1		document	
	12.2		the product temperature range	
13			ion	
14			OM microcontroller option list	
15	STM8 de	-	nt tools	
	15.1	Emulation	and in-circuit debugging tools	94
	•			

Conte	nts			STM8S105xx
	15.2	Software	tools	94
		15.2.1	STM8 toolset	94
		15.2.2	C and assembly toolchains	95
	15.3	Programr	ning tools	95
16	Revision	n history		96
17	Disclaim	ner		99

STM8S105xx List of tables

List of tables

Table 1: Device summary	1
Table 2: STM8S105xx access line features	9
Table 3: Peripheral clock gating bit assignments in CLK_PCKENR1/2 registers	14
Table 4: TIM timer features	16
Table 5: Legend/abbreviations for pinout tables	19
Table 6: Pin description for STM8S105 microcontrollers	
Table 7: Flash, Data EEPROM and RAM boundary addresses	26
Table 8: I/O port hardware register map	
Table 9: General hardware register map	
Table 10: CPU/SWIM/debug module/interrupt controller registers	34
Table 11: Interrupt mapping	
Table 12: Option bytes	
Table 13: Option byte description	38
Table 14: Description of alternate function remapping bits [7:0] of OPT2	39
Table 15: Unique ID registers (96 bits)	
Table 16: Voltage characteristics	
Table 17: Current characteristics	
Table 18: Thermal characteristics	
Table 19: General operating conditions	
Table 20: Operating conditions at power-up/power-down	
Table 21: Total current consumption with code execution in run mode at VDD = 5 V	47
Table 22: Total current consumption with code execution in run mode at VDD = 3.3 V	
Table 23: Total current consumption in wait mode at VDD = 5 V	
Table 24: Total current consumption in wait mode at VDD = 3.3 V	
Table 25: Total current consumption in active halt mode at VDD = 5 V	
Table 26: Total current consumption in active halt mode at VDD = 3.3 V	
Table 27: Total current consumption in halt mode at VDD = 5 V	
Table 28: Total current consumption in halt mode at VDD = 3.3 V	
Table 29: Wakeup times	
Table 30: Total current consumption and timing in forced reset state	
Table 31: Peripheral current consumption	
Table 32: HSE user external clock characteristics	
Table 33: HSE oscillator characteristics	
Table 34: HSI oscillator characteristics	
Table 35: LSI oscillator characteristics	
Table 36: RAM and hardware registers	
Table 37: Flash program memory/data EEPROM memory	
Table 38: I/O static characteristics	
Table 39: Output driving current (standard ports)	63
Table 40: Output driving current (standard ports)	
Table 41: Output driving current (high sink ports)	
Table 42: NRST pin characteristics	
Table 43: SPI characteristics	
Table 44: I2C characteristics	
Table 45: ADC characteristics	
Table 46: ADC characteristics	
Table 47: ADC accuracy with RAIN < 10 kΩ , VDDA= 3 V	
Table 48: EMS data	
Table 49: EMI data	
Table 50: ESD absolute maximum ratings	
Table 51: Electrical sensitivities	
Table 52: 48-pin low profile quad flat package mechanical data	
Table 53: 44-pin low profile quad flat package mechanical data	81



List of tables STM8S105xx

Table 54: 32-pin low profile quad flat package mechanical data	82
Table 55: 32-lead ultra thin fine pitch quad flat no-lead package mechanical data	
Table 56: 32-lead shrink plastic DIP (400 ml) package mechanical data	
Table 57: Thermal characteristics (1)	
Table 58: Document revision history	

STM8S105xx List of figures

List of figures

Figure 1: STM8S105xx access line block diagram	10
Figure 2: Flash memory organization	
Figure 3: LQFP 48-pin pinout	
Figure 4: LQFP 44-pin pinout	
Figure 5: LQFP/UFQFPN 32-pin pinout	
Figure 6: SDIP 32-pin pinout	
Figure 7: Memory map	
Figure 8: Supply current measurement conditions	42
Figure 9: Pin loading conditions	43
Figure 10: Pin input voltage	43
Figure 11: fCPUmax versus VDD	46
Figure 12: External capacitor CEXT	47
Figure 13: Typ. IDD(RUN) vs. VDD, HSE user external clock, fCPU = 16 MHz	54
Figure 14: Typ. IDD(RUN) vs. fCPU, HSE user external clock, VDD= 5 V	54
Figure 15: Typ. IDD(RUN) vs. VDD, HSI RC osc, fCPU = 16 MHz	
Figure 16: Typ. IDD(WFI) vs. VDD, HSE user external clock, fCPU = 16 MHz	55
Figure 17: Typ. IDD(WFI) vs. fCPU, HSE user external clock VDD = 5 V	
Figure 18: Typ. IDD(WFI) vs. VDD, HSI RC osc, fCPU = 16 MHz	55
Figure 19: HSE external clocksource	56
Figure 20: HSE oscillator circuit diagram	
Figure 21: Typical HSI accuracy at VDD = 5 V vs 5 temperatures	
Figure 22: Typical HSI accuracy vs VDD @ 4 temperatures	
Figure 23: Typical LSI accuracy vs VDD @ 4 temperatures	
Figure 24: Typical VIL and VIH vs VDD @ 4 temperatures	
Figure 25: Typical pull-up resistance vs VDD @ 4 temperatures	
Figure 26: Typical pull-up current vs VDD @ 4 temperatures	
Figure 27: Typ. VOL @ VDD = 5 V (standard ports)	
Figure 28: Typ. VOL @ VDD = 3.3 V (standard ports)	
Figure 29: Typ. VOL @ VDD = 5 V (true open drain ports)	
Figure 30: Typ. VOL @ VDD = 3.3 V (true open drain ports)	
Figure 31: Typ. VOL @ VDD = 5 V (high sink ports)	
Figure 32: Typ. VOL @ VDD = 3.3 V (high sink ports)	
Figure 33: Typ. VDD - VOH @ VDD = 5 V (standard ports)	
Figure 34: Typ. VDD - VOH @ VDD = 3.3 V (standard ports)	
Figure 35: Typ. VDD - VOH @ VDD = 5 V (high sink ports)	
Figure 36: Typ. VDD - VOH @ VDD = 3.3 V (high sink ports)	
Figure 37: Typical NRST VIL and VIH vs VDD @ 4 temperatures	
Figure 38: Typical NRST pull-up resistance vs VDD @ 4 temperatures	
Figure 39: Typical NRST pull-up current vs VDD @ 4 temperatures	70
Figure 40: Recommended reset pin protection	
Figure 41: SPI timing diagram - slave mode and CPHA = 0	
Figure 42: SPI timing diagram - slave mode and CPHA = 1(1)	
Figure 43: SPI timing diagram - master mode(1)	
Figure 44: Typical application with I2C bus and timing diagram (1)	
Figure 45: ADC accuracy characteristics	
Figure 46: Typical application with ADC	
Figure 47: 48-pin low profile quad flat package (7 x 7)	
Figure 48: 44-pin low profile quad flat package	
Figure 49: 32-pin low profile quad flat package (7 x 7)	
Figure 50: 32-lead, ultra thin, fine pitch quad flat no-lead package (5 x 5)	
Figure 51: 32-lead shrink plastic DIP (400 ml) package	
Figure 52. STIVIOSTUSXX access line ordening information scheme	09



Introduction STM8S105xx

1 Introduction

This datasheet contains the description of the device features, pinout, electrical characteristics, mechanical data and ordering information.

 For complete information on the STM8S microcontroller memory, registers and peripherals, please refer to the STM8S microcontroller family reference manual (RM0016).

- For information on programming, erasing and protection of the internal Flash memory please refer to the STM8S Flash programming manual (PM0051).
- For information on the debug and SWIM (single wire interface module) refer to the STM8 SWIM communication protocol and debug module user manual (UM0470).
- For information on the STM8 core, please refer to the STM8 CPU programming manual (PM0044).

STM8S105xx Description

2 Description

The STM8S105xx access line 8-bit microcontrollers offer from 16 to 32 Kbytes Flash program memory, plus integrated true data EEPROM. They are referred to as medium-density devices in the STM8S microcontroller family reference manual (RM0016).

All devices of the STM8S105xx access line provide the following benefits: reduced system cost, performance and robustness, short development cycles, and product longevity.

The system cost is reduced thanks to an integrated true data EEPROM for up to 300k write/erase cycles and a high system integration level with internal clock oscillators, watchdog, and brown-out reset.

Device performance is ensured by a 16 MHz CPU clock frequency and enhanced characteristics which include robust I/O, independent watchdogs (with a separate clock source), and a clock security system.

Short development cycles are guaranteed due to application scalability across common family product architecture with compatible pinout, memory map and modular peripherals. Full documentation is offered with a wide choice of development tools.

Product longevity is ensured in the STM8S family thanks to their advanced core which is made in a state-of-the art technology for applications with 2.95 V to 5.5 V operating supply.


Device	STM8S105C6	STM8S105C4	STM8S105S6	STM8S105S4	STM8S105K6	STM8S105K4			
Pin count	48	48	44	44	32	32			
Maximum number of GPIOs	38	38	34	34	25	25			
Ext. Interrupt pins	35	35	31	31	23	23			
Timer CAPCOM channels	9	9	8	8	8	8			
Timer complementary outputs	3	3	3	3	3	3			
A/D Converter channels			9	9	7	7			
High sink I/Os	16	16	15	15	12	12			
Medium density Flash Program memory (bytes)	32K	16K	32K	16K	32K	16K			
Data EEPROM (bytes)	1024	1024	1024	1024	1024	1024			
RAM (bytes)	2K	2K	2K	2K	2K	2K			
Peripheral set	Advanced control timer (TIM1), General-purpose timers (TIM2 and TIM3), Basic timer (TIM4) SPI, I ² C, UART, Window WDG, Independent WDG, ADC								

Table 2: STM8S105xx access line features

Block diagram STM8S105xx

3 Block diagram

Figure 1: STM8S105xx access line block diagram



STM8S105xx Product overview

4 Product overview

The following section intends to give an overview of the basic features of the device functional modules and peripherals.

For more detailed information please refer to the corresponding family reference manual (RM0016).

Central processing unit STM8

The 8-bit STM8 core is designed for code efficiency and performance.

It contains 6 internal registers which are directly addressable in each execution context, 20 addressing modes including indexed indirect and relative addressing and 80 instructions.

Architecture and registers

- Harvard architecture
- 3-stage pipeline
- 32-bit wide program memory bus single cycle fetching for most instructions
- X and Y 16-bit index registers enabling indexed addressing modes with or without offset and read-modify-write type data manipulations
- 8-bit accumulator
- 24-bit program counter 16-Mbyte linear memory space
- 16-bit stack pointer access to a 64 K-level stack
- 8-bit condition code register 7 condition flags for the result of the last instruction

Addressing

- 20 addressing modes
- Indexed indirect addressing mode for look-up tables located anywhere in the address space
- Stack pointer relative addressing mode for local variables and parameter passing

Instruction set

- 80 instructions with 2-byte average instruction size
- Standard data movement and logic/arithmetic functions
- 8-bit by 8-bit multiplication
- 16-bit by 8-bit and 16-bit by 16-bit division
- Bit manipulation
- Data transfer between stack and accumulator (push/pop) with direct stack access
- Data transfer using the X and Y registers or direct memory-to-memory transfers

4.1 Single wire interface module (SWIM) and debug module (DM)

The single wire interface module and debug module permits non-intrusive, real-time incircuit debugging and fast memory programming.

SWIM

Single wire interface module for direct access to the debug module and memory programming. The interface can be activated in all device operation modes. The maximum data transmission speed is 145 bytes/ms.

Product overview STM8S105xx

Debug module

The non-intrusive debugging module features a performance close to a full-featured emulator. Beside memory and peripherals, also CPU operation can be monitored in real-time by means of shadow registers.

- R/W to RAM and peripheral registers in real-time
- R/W access to all resources by stalling the CPU
- Breakpoints on all program-memory instructions (software breakpoints)
- Two advanced breakpoints, 23 predefined configurations

4.2 Interrupt controller

- Nested interrupts with three software priority levels
- 32 interrupt vectors with hardware priority
- Up to 37 external interrupts on 6 vectors including TLI
- Trap and reset interrupts

4.3 Flash program and data EEPROM memory

- Up to 32 Kbytes of Flash program single voltage Flash memory
- Up to 1 Kbytes true data EEPROM
- Read while write: Writing in data memory possible while executing code in program memory
- User option byte area

Write protection (WP)

Write protection of Flash program memory and data EEPROM is provided to avoid unintentional overwriting of memory that could result from a user software malfunction.

There are two levels of write protection. The first level is known as MASS (memory access security system). MASS is always enabled and protects the main Flash program memory, data EEPROM and option bytes.

To perform in-application programming (IAP), this write protection can be removed by writing a MASS key sequence in a control register. This allows the application to write to data EEPROM, modify the contents of main program memory or the device option bytes.

A second level of write protection, can be enabled to further protect a specific area of memory known as UBC (user boot code). Refer to the figure below.

The size of the UBC is programmable through the UBC option byte, in increments of 1 page (512 bytes) by programming the UBC option byte in ICP mode.

This divides the program memory into two areas:

- Main program memory: Up to 32 Kbytes minus UBC
- User-specific boot code (UBC): Configurable up to 32 Kbytes

The UBC area remains write-protected during in-application programming. This means that the MASS keys do not unlock the UBC area. It protects the memory used to store the boot program, specific code libraries, reset and interrupt vectors, the reset routine and usually the IAP and communication routines.

STM8S105xx Product overview

Data memory area (1 Kbyte) Data EEPROM memory Option bytes Programmable area UBC area from 1 Kbyte Remains write protected during IAP (2 first pages) up to 32 Kbytes (1 page steps) Medium density Flash program memory (up to 32 Kbytes) Program memory area Write access possible for IAP

Figure 2: Flash memory organization

Read-out protection (ROP)

The read-out protection blocks reading and writing the Flash program memory and data EEPROM memory in ICP mode (and debug mode). Once the read-out protection is activated, any attempt to toggle its status triggers a global erase of the program and data memory. Even if no protection can be considered as totally unbreakable, the feature provides a very high level of protection for a general purpose microcontroller.

4.4 Clock controller

The clock controller distributes the system clock (f_{MASTER}) coming from different oscillators to the core and the peripherals. It also manages clock gating for low power modes and ensures clock robustness.

Features

- **Clock prescaler:** To get the best compromise between speed and current consumption the clock frequency to the CPU and peripherals can be adjusted by a programmable prescaler.
- **Safe clock switching:** Clock sources can be changed safely on the fly in run mode through a configuration register. The clock signal is not switched until the new clock source is ready. The design guarantees glitch-free switching.
- **Clock management:** To reduce power consumption, the clock controller can stop the clock to the core, individual peripherals or memory.
- Master clock sources: Four different clock sources can be used to drive the master clock:
 - 1-16 MHz high-speed external crystal (HSE)
 - Up to 16 MHz high-speed user-external clock (HSE user-ext)
 - 16 MHz high-speed internal RC oscillator (HSI)
 - 128 kHz low-speed internal RC (LSI)

Product overview STM8S105xx

• **Startup clock:** After reset, the microcontroller restarts by default with an internal 2 MHz clock (HSI/8). The prescaler ratio and clock source can be changed by the application program as soon as the code execution starts.

- Clock security system (CSS): This feature can be enabled by software. If an HSE clock failure occurs, the internal RC (16 MHz/8) is automatically selected by the CSS and an interrupt can optionally be generated.
- **Configurable main clock output (CCO):** This outputs an external clock for use by the application.

Bit	Peripheral clock						
PCKEN17	TIM1	PCKEN13	UART2	PCKEN27	Reserved	PCKEN23	ADC
PCKEN16	TIM3	PCKEN12	Reserved	PCKEN26	Reserved	PCKEN22	AWU
PCKEN15	TIM2	PCKEN11	SPI	PCKEN25	Reserved	PCKEN21	Reserved
PCKEN14	TIM4	PCKEN10	I ² C	PCKEN24	Reserved	PCKEN20	Reserved

Table 3: Peripheral clock gating bit assignments in CLK_PCKENR1/2 registers

4.5 Power management

For efficient power management, the application can be put in one of four different low-power modes. You can configure each mode to obtain the best compromise between lowest power consumption, fastest start-up time and available wakeup sources.

- Wait mode: In this mode, the CPU is stopped, but peripherals are kept running. The wakeup is performed by an internal or external interrupt or reset.
- Active halt mode with regulator on: In this mode, the CPU and peripheral clocks are stopped. An internal wakeup is generated at programmable intervals by the auto wake up unit (AWU). The main voltage regulator is kept powered on, so current consumption is higher than in active halt mode with regulator off, but the wakeup time is faster. Wakeup is triggered by the internal AWU interrupt, external interrupt or reset.
- Active halt mode with regulator off: This mode is the same as active halt with regulator on, except that the main voltage regulator is powered off, so the wake up time is slower.
- Halt mode: In this mode the microcontroller uses the least power. The CPU and
 peripheral clocks are stopped, the main voltage regulator is powered off. Wakeup is
 triggered by external event or reset.

4.6 Watchdog timers

The watchdog system is based on two independent timers providing maximum security to the applications.

Activation of the watchdog timers is controlled by option bytes or by software. Once activated, the watchdogs cannot be disabled by the user program without performing a reset.

Window watchdog timer

The window watchdog is used to detect the occurrence of a software fault, usually generated by external interferences or by unexpected logical conditions, which cause the application program to abandon its normal sequence.

The window function can be used to trim the watchdog behavior to match the application perfectly.

STM8S105xx Product overview

The application software must refresh the counter before time-out and during a limited time window.

A reset is generated in two situations:

- 1. Timeout: At 16 MHz CPU clock the time-out period can be adjusted between 75 μ s up to 64 ms.
- 2. Refresh out of window: The downcounter is refreshed before its value is lower than the one stored in the window register.

Independent watchdog timer

The independent watchdog peripheral can be used to resolve processor malfunctions due to hardware or software failures.

It is clocked by the 128 kHz LSI internal RC clock source, and thus stays active even in case of a CPU clock failure

The IWDG time base spans from 60 µs to 1 s.

4.7 Auto wakeup counter

- Used for auto wakeup from active halt mode
- Clock source: Internal 128 kHz internal low frequency RC oscillator or external clock
- LSI clock can be internally connected to TIM3 input capture channel 1 for calibration

4.8 Beeper

The beeper function outputs a signal on the BEEP pin for sound generation. The signal is in the range of 1, 2 or 4 kHz.

The beeper output port is only available through the alternate function remap option bit AFR7.

4.9 TIM1 - 16-bit advanced control timer

This is a high-end timer designed for a wide range of control applications. With its complementary outputs, dead-time control and center-aligned PWM capability, the field of applications is extended to motor control, lighting and half-bridge driver

- 16-bit up, down and up/down autoreload counter with 16-bit prescaler
- Four independent capture/compare channels (CAPCOM) configurable as input capture, output compare, PWM generation (edge and center aligned mode) and single pulse mode output
- Synchronization module to control the timer with external signals
- Break input to force the timer outputs into a defined state
- Three complementary outputs with adjustable dead time
- Encoder mode
- Interrupt sources: 3 x input capture/output compare, 1 x overflow/update, 1 x break

4.10 TIM2, TIM3 - 16-bit general purpose timers

- 16-bit autoreload (AR) up-counter
- 15-bit prescaler adjustable to fixed power of 2 ratios 1...32768
- Timers with 3 or 2 individually configurable capture/compare channels
- PWM mode
- Interrupt sources: 2 or 3 x input capture/output compare, 1 x overflow/update

Product overview STM8S105xx

4.11 TIM4 - 8-bit basic timer

• 8-bit autoreload, adjustable prescaler ratio to any power of 2 from 1 to 128

Clock source: CPU clock

• Interrupt source: 1 x overflow/update

Table 4: TIM timer features

Timer	Counter size (bits)	Prescaler	Counting mode	CAPCOM channels	Complem. outputs	Ext. trigger	Timer synchronization/ chaining
TIM1	16	Any integer from 1 to 65536	Up/Down	4	3	Yes	No
TIM2	16	Any power of 2 from 1 to 32768	Up	3	0	No	
TIM3	16	Any power of 2 from 1 to 32768	Up	2	0	No	
TIM4	8	Any power of 2 from 1 to 128	Up	0	0	No	

4.12 Analog-to-digital converter (ADC1)

The STM8S105xx products contain a 10-bit successive approximation A/D converter (ADC1) with up to 10 multiplexed input channels and the following main features:

Input voltage range: 0 to V_{DD}
 Input voltage range: 0 to V_{DDA}
 Conversion time: 14 clock cycles

- Single and continuous and buffered continuous conversion modes
- Buffer size (n x 10 bits) where n = number of input channels
- Scan mode for single and continuous conversion of a sequence of channels
- Analog watchdog capability with programmable upper and lower thresholds
- Analog watchdog interrupt
- External trigger input
- Trigger from TIM1 TRGO
- End of conversion (EOC) interrupt



Additional AIN12 analog input is not selectable in ADC scan mode or with analog watchdog. Values converted from AIN12 are stored only into the ADC_DRH/ADC_DRL registers.

STM8S105xx Product overview

4.13 Communication interfaces

The following communication interfaces are implemented:

 UART2: Full feature UART, synchronous mode, SPI master mode, Smartcard mode, IrDA mode, LIN2.1 master/slave capability

- SPI: Full and half-duplex, 8 Mbit/s
- I2C: Up to 400 Kbit/s

4.13.1 UART2

Main features

- One Mbit/s full duplex SCI
- SPI emulation
- High precision baud rate generator
- Smartcard emulation
- IrDA SIR encoder decoder
- LIN master mode
- LIN slave mode

Asynchronous communication (UART mode)

- Full duplex communication NRZ standard format (mark/space)
- Programmable transmit and receive baud rates up to 1 Mbit/s (f_{CPU}/16) and capable of following any standard baud rate regardless of the input frequency
- Separate enable bits for transmitter and receiver
- Two receiver wakeup modes:
 - Address bit (MSB)
 - Idle line (interrupt)
- Transmission error detection with interrupt generation
- Parity control

Synchronous communication

- Full duplex synchronous transfers
- SPI master operation
- 8-bit data communication
- Maximum speed: 1 Mbit/s at 16 MHz (f_{CPU}/16)

LIN master mode

- Emission: Generates 13-bit synch break frame
- Reception: Detects 11-bit break frame

LIN slave mode

- Autonomous header handling one single interrupt per valid message header
- Automatic baud rate synchronization maximum tolerated initial clock deviation ±15 %
- Synch delimiter checking
- 11-bit LIN synch break detection break detection always active
- Parity check on the LIN identifier field
- LIN error management
- Hot plugging support

4.13.2 SPI

- Maximum speed: 8 Mbit/s (f_{MASTER}/2) both for master and slave
- Full duplex synchronous transfers

Product overview STM8S105xx

• Simplex synchronous transfers on two lines with a possible bidirectional data line

- Master or slave operation selectable by hardware or software
- CRC calculation
- 1 byte Tx and Rx buffer
- Slave/master selection input pin

4.13.3 I²C

- I2C master features:
 - Clock generation
 - Start and stop generation
- I²C slave features:
 - Programmable I2C address detection
 - Stop bit detection
- Generation and detection of 7-bit/10-bit addressing and general call
- Supports different communication speeds:
 - Standard speed (up to 100 kHz)
 - Fast speed (up to 400 kHz)


5 Pinout and pin description

Table 5: Legend/abbreviations for pinout tables

Туре	I= Input, O = Output, S = Power supply							
Level	Input	CM = CMOS						
	Output	HS = High sink						
Output speed	O1 = Slow (up to 2 MHz)							
	O2 = Fast (up to 10 MHz)							
	O3 = Fast/slow programmability with slow as default state after reset							
	O4 = Fas	t/slow programmability with fast as default state after reset						
Port and control	Input	float = floating, wpu = weak pull-up						
configuration	Output T = True open drain, OD = Open drain, PP = Push p							
Reset state	Bold X (pin state after internal reset release).							
	Unless otherwise specified, the pin state is the same during the reset phase and after the internal reset release.							

5.1 STM8S105 pinouts and pin description

Figure 3: LQFP 48-pin pinout



- 1. (HS) high sink capability.
- 2. (T) True open drain (P-buffer and protection diode to V_{DD} not implemented).
- 3. [] alternate function remapping option (If the same alternate function is shown twice, it indicates an exclusive choice not a duplication of the function).







Figure 4: LQFP 44-pin pinout


- 1. (HS) high sink capability.
- 2. (T) True open drain (P-buffer and protection diode to V_{DD} not implemented).
- 3. [] alternate function remapping option (If the same alternate function is shown twice, it indicates an exclusive choice not a duplication of the function).

Figure 5: LQFP/UFQFPN 32-pin pinout



- 1. (HS) high sink capability.
- 2. [] alternate function remapping option (If the same alternate function is shown twice, it indicates an exclusive choice not a duplication of the function).

Figure 6: SDIP 32-pin pinout



- 1. (HS) high sink capability.
- 2. (T) True open drain (P-buffer and protection diode to V_{DD} not implemented).
- 3. [] alternate function remapping option (If the same alternate function is shown twice, it indicates an exclusive choice not a duplication of the function).



Table 6: Pin description for STM8S105 microcontrollers

	Pin	number					Input			Out	Output Main			Alternate function	
LQFP48	LQFP44	LQFP32/ UFQFPN32	SDIP32	Pin name	Type	floating	ndw	Ext. interrupt	High sink	peedS	Q0	æ	function (after reset)	Default alternate function	after remap [option bit]
1	1	1	6	NRST	1/0		<u>X</u>							Reset	
2	2	2	7	PA1/ OSC IN	I/O	<u>X</u>	Х			01	Х	Х	Port A1	Resonator crystal in	
3	3	3	8	PA2/ OSC OUT	1/0	<u>X</u>	Χ	Χ		01	Χ	Χ	Port A2	Resonator crystal out	
4	4	-	-	V _{SSIO_1}	S									I/O ground	
5	5	4	9	V _{SS}	S									Digital ground	
6	6	5	10	VCAP	S								1.8 V	regulator capacitor	
7	7	6	11	V_{DD}	S								Diç	gital power supply	
8	8	7	12	V_{DDIO_1}	S								1/	O power supply	
9	•	-	-	PA3/ TIM2 _CH3 [TIM3 _CH1]	I/O	<u>X</u>	Х	Χ		01	Χ	Х	Port A3	Timer 2 - channel 3	TIM3_CH1 [AFR1]
10	9	-	-	PA4	1/0	<u>X</u>	Χ	Χ	HS	03	Χ	Χ	Port A4		
11	10	-	-	PA5	1/0	<u>X</u>	χ	Χ	HS	03	Χ	Χ	Port A5		
12	11	-	-	PA6	1/0	<u>X</u>	Χ	Χ	HS	03	Χ	Χ	Port A6		
-	-	8	13	PF4/ AIN12 ⁽¹⁾	1/0	<u>X</u>	χ			01	Χ	Χ	Port F4	Analog input 12 (2)	
13	12	9	14	V_{DDA}	S								Ana	alog power supply	
14	13	10	15	V_{SSA}	S									Analog ground	
15	14	-	-	PB7/ AIN7	1/0	<u>X</u>	Χ	Χ		01	Χ	Χ	Port B7	Analog input 7	
16	15	-	-	PB6/ AIN6	1/0	<u>X</u>	Χ	Χ		01	Χ	Χ	Port B6	Analog input 6	
17	16	11	16	PB5/ AIN5 [I ² C_ SDA]	I/O	<u>X</u>	Х	Х		01	Х	Х	Port B5	Analog input 5	I ² C_SDA [AFR6]
18	17	12	17	PB4/ AIN4 [I ² C_ SCL]	I/O	<u>X</u>	Х	Х		01	Χ	Х	Port B4	Analog input 4	I ² C_SCL [AFR6]
19	18	13	18	PB3/ AIN3 [TIM1_ ETR]	I/O	<u>X</u>	Х	Х		01	Х	Х	Port B3	Analog input 3	TIM1_ETR [AFR5]
20	19	14	19	PB2/ AIN2 [TIM1_CH3N]	I/O	<u>X</u>	Х	Х		01	Х	Х	Port B2	Analog input 2	TIM1_CH3N [AFR5]
21	20	15	20	PB1/ AIN1 [TIM1_CH2N]	I/O	<u>X</u>	Х	Х		01	Х	Х	Port B1	Analog input 1	TIM1_ CH2N [AFR5]
22	21	16	21	PB0/ AIN0 [TIM1_CH1N]	I/O	<u>X</u>	Х	Х		01	Х	Х	Port B0	Analog input 0	TIM1_CH1N [AFR5]
23		-		PE7/ AIN8	I/O	<u>X</u>	Χ	Χ		01	Χ	Χ	Port E7	Analog input 8	
24	22	-	-	PE6/ AIN9	1/0	<u>X</u>	χ	Χ		01	Χ	Χ	Port E6	Analog input 9 (3)	
25	23	17	22	PE5/SPI_NSS	I/O	<u>X</u>	Χ	Χ		01	Χ	Χ	Port E5	SPI master/slave select	
26	24	18	23	PC1/TIM1_CH1 UART2_CK	I/O	<u>X</u>	Х	Х	HS	03	Х	Х	Port C1	Timer 1 – channel 1/ UART2 synchronous clock	

STM8S105xx

Pinout and pin description

	Pin	number					Input			Out	out		Main		Alternate function
LQFP48	LQFP44	LQFP32/ UFQFPN32	SDIP32	Pin name	Туре	floating	ndw	Ext. interrupt	High sink	peeds	QO	В	function (after reset)	Default alternate function	after remap [option bit]
27	25	19	24	PC2/ TIM1_CH2	1/0	<u>X</u>	χ	Χ	HS	03	Х	Χ	Port C2	Timer 1- channel 2	
28	26	20	25	PC3/ TIM1_CH3	1/0	<u>X</u>	Χ	Χ	HS	03	Χ	Χ	Port C3	Timer 1 - channel 3	
29	-	21	26	PC4/ TIM1_CH4	1/0	<u>X</u>	χ	Χ	HS	03	Χ		Port C4	Timer 1 - channel 4	
30	27	22	27	PC5/ SPI_SCK	1/0	<u>X</u>	χ	Χ	HS	03	Χ	Χ	Port C5	SPI clock	
31	28	-	-	V _{SSIO_2}	S									I/O ground	
32	29	-	-	V _{DDIO_2}	S								1/	O power supply	
33	30	23	28	PC6/ SPI_MOSI	1/0	<u>X</u>	χ	Χ	HS	03	Χ	Χ	Port C6	SPI master out/slave in	
34	31	24	29	PC7/ SPI_MISO	1/0	<u>X</u>	χ	Χ	HS	03	Χ	Χ	Port C7	SPI master in/ slave out	
35	32	-		PG0	1/0	<u>X</u>	Χ			01	Χ	Χ	Port G0		
36	33	-		PG1	1/0	<u>X</u>	Χ			01	Χ	Χ	Port G1		
37	-	-		PE3/ TIM1_BKIN	1/0	<u>X</u>	Χ	Χ		01	Χ	Χ	Port E3	Timer 1 - break input	
38	34	-	-	PE2/ I ² C_SDA	1/0	<u>X</u>		Χ		01	T ⁽⁴⁾		Port E2	I ² C data	
39	35	-	-	PE1/ I ² C_ SCL	1/0	<u>X</u>		Χ		01	T ⁽⁴⁾		Port E1	I ² C clock	
40	36	-		PE0/ CLK_ CCO	I/O	<u>X</u>	Х	Х	HS	03	Х	Х	Port E0	Configurable clock output	
41	37	25	30	PD0/ TIM3_CH2 [TIM1_BKIN] [CLK_CCO]	I/O	<u>X</u>	Х	Х	HS	03	Х	Χ	Port D0	Timer 3 - channel 2	TIM1_BKIN [AFR3]/ CLK_CCO [AFR2]
42	38	26	31	PD1/ SWIM ⁽⁵⁾	1/0	<u>X</u>	χ	Χ	HS	04	Χ	Χ	Port D1	SWIM data interface	
43	39	27	32	PD2/ TIM3_CH1 [TIM2_CH3]	I/O	<u>X</u>	Х	Х	HS	03	Χ	Χ	Port D2	Timer 3 - channel 1	TIM2_CH3 [AFR1]
44	40	28	1	PD3/ TIM2_CH2 [ADC_ETR]	I/O	<u>X</u>	Х	Х	HS	03	Х	Х	Port D3	Timer 2 - channel 2	ADC_ETR [AFR0]
45	41	29	2	PD4/ TIM2_CH1 [BEEP]	I/O	<u>X</u>	Х	Х	HS	03	Х	Х	Port D4	Timer 2 - channel 1	BEEP output [AFR7]
46	42	30	3	PD5/ UART2_TX	I/O	<u>X</u>	Х	Х		01	Х	Х	Port D5	UART2 data transmit	
47	43	31	4	PD6/ UART2_RX	I/O	<u>X</u>	Х	Х		01	Х	Χ	Port D6	UART2 data receive	
48	44	32	5	PD7/ TLI [TIM1_CH4]	I/O	<u>X</u>	Х	Х		01	Х	Х	Port D7	Top level interrupt	TIM1_CH4 [AFR4]

Notes:

 $[\]begin{picture}(5){c} The PD1 pin is in input pull-up during the reset phase and after internal reset release. \end{picture}$



 $^{^{(1)}}$ A pull-up is applied to PF4 during the reset phase. This pin is input floating after reset release.

⁽²⁾ AIN12 is not selectable in ADC scan mode or with analog watchdog.

⁽³⁾ In 44-pin package, AIN9 cannot be used by ADC scan mode.

⁽⁴⁾ In the open-drain output column, 'T' defines a true open-drain I/O (P-buffer, weak pull-up and protection diode to V_{DD} are not implemented).

24/99

5.1.1 Alternate function remapping

As shown in the rightmost column of the pin description table, some alternate functions can be remapped at different I/O ports by programming one of eight AFR (alternate function remap) option bits. When the remapping option is active, the default alternate function is no longer available.


To use an alternate function, the corresponding peripheral must be enabled in the peripheral registers.

Alternate function remapping does not affect GPIO capabilities of the I/O ports (see the GPIO section of the family reference manual, RM0016).

6 Memory and register map

6.1 Memory map

Figure 7: Memory map



The following table lists the boundary addresses for each memory size. The top of the stack is at the RAM end address in each case.

Table 7: Flash, Data EEPROM and RAM boundary addresses

Memory area	Size (bytes)	Start address	End address
Flash program memory	32K	0x00 8000	0x00 FFFF
	16K	0x00 8000	0x00 BFFF
RAM	2K	0x00 0000	0x00 07FF
Data EEPROM	1024	0x00 4000	0x00 43FF

6.2 Register map

6.2.1 I/O port hardware register map

Table 8: I/O port hardware register map

Address	Block	Register label	Register name	Reset status
0x00 5000	Port A	PA_ODR	Port A data output latch register	0x00
0x00 5001		PA_IDR	Port A input pin value register	0xXX
0x00 5002		PA_DDR	Port A data direction register	0x00
0x00 5003		PA_CR1	Port A control register 1	0x00
0x00 5004		PA_CR2	Port A control register 2	0x00
0x00 5005	Port B	PB_ODR	Port B data output latch register	0x00
0x00 5006		PB_IDR	Port B input pin value register	0xXX
0x00 5007		PB_DDR	Port B data direction register	0x00
0x00 5008		PB_CR1	Port B control register 1	0x00
0x00 5009		PB_CR2	Port B control register 2	0x00
0x00 500A	Port C	PC_ODR	Port C data output latch register	0x00
0x00 500B		PC_IDR	Port C input pin value register	0xXX
0x00 500C		PC_DDR	Port C data direction register	0x00
0x00 500D		PC_CR1	Port C control register 1	0x00
0x00 500E		PC_CR2	Port C control register 2	0x00
0x00 500F	Port D	PD_ODR	Port D data output latch register	0x00
0x00 5010		PD_IDR	Port D input pin value register	0xXX
0x00 5011		PD_DDR	Port D data direction register	0x00
0x00 5012		PD_CR1	Port D control register 1	0x02
0x00 5013		PD_CR2	Port D control register 2	0x00
0x00 5014	Port E	PE_ODR	Port E data output latch register	0x00
0x00 5015		PE_IDR	Port E input pin value register	0xXX
0x00 5016		PE_DDR	Port E data direction register	0x00
0x00 5017		PE_CR1	Port E control register 1	0x00
0x00 5018		PE_CR2	Port E control register 2	0x00
0x00 5019	Port F	PF_ODR	Port F data output latch register	0x00

Address	Block	Register label	Register name	Reset status
0x00 501A		PF_IDR	Port F input pin value register	0xXX
0x00 501B		PF_DDR	Port F data direction register	0x00
0x00 501C		PF_CR1	Port F control register 1	0x00
0x00 501D		PF_CR2	Port F control register 2	0x00
0x00 501E	Port G	PG_ODR	Port G data output latch register	0x00
0x00 501F		PG_IDR	Port G input pin value register	0xXX
0x00 5020		PG_DDR	Port G data direction register	0x00
0x00 5021		PG_CR1	Port G control register 1	0x00
0x00 5022		PG_CR2	Port G control register 2	0x00
0x00 5023	Port H	PH_ODR	Port H data output latch register	0x00
0x00 5024		PH_IDR	Port H input pin value register	0xXX
0x00 5025		PH_DDR	Port H data direction register	0x00
0x00 5026		PH_CR1	Port H control register 1	0x00
0x00 5027		PH_CR2	Port H control register 2	0x00
0x00 5028	Port I	PI_ODR	Port I data output latch register	0x00
0x00 5029		PI_IDR	Port I input pin value register	0xXX
0x00 502A		PI_DDR	Port I data direction register	0x00
0x00 502B		PI_CR1	Port I control register 1	0x00
0x00 502C		PI_CR2	Port I control register 2	0x00

6.2.2 General hardware register map

Table 9: General hardware register map

Address	Block	Register label	Register name	Reset status			
0x00 5050 to 0x00 5059		Reserved area (10 bytes)					
0x00 505A	Flash	FLASH_CR1	Flash control register 1	0x00			
0x00 505B		FLASH_CR2	Flash control register 2	0x00			
0x00 505C		FLASH_NCR2	Flash complementary control register 2	0xFF			
0x00 505D		FLASH _FPR	Flash protection register	0x00			
0x00 505E		FLASH _NFPR	Flash complementary protection register	0xFF			
0x00 505F		FLASH_IAPSR	Flash in-application programming status register	0x00			
0x00 5060 to 0x00 5061		Reserved area (2 bytes)					
0x00 5062	Flash	FLASH_PUKR	Flash program memory unprotection register	0x00			

Address	Block	Register label	Register name	Reset status		
0x00 5063			Reserved area (1 byte)			
0x00 5064	Flash	FLASH _DUKR	Data EEPROM unprotection register	0x00		
0x00 5065 to 0x00 509F		Reserved area (59 bytes)				
0x00 50A0	ITC	EXTI_CR1	External interrupt control register 1	0x00		
0x00 50A1		EXTI_CR2	External interrupt control register 2	0x00		
0x00 50A2 to 0x00 50B2		F	Reserved area (17 bytes)			
0x00 50B3	RST	RST_SR	Reset status register	0xXX ⁽¹⁾		
0x00 50B4 to 0x00 50BF		F	Reserved area (12 bytes)			
0x00 50C0	CLK	CLK_ICKR	Internal clock control register	0x01		
0x00 50C1		CLK_ECKR	External clock control register	0x00		
0x00 50C2			Reserved area (1 byte)			
0x00 50C3	CLK	CLK_CMSR	Clock master status register	0xE1		
0x00 50C4		CLK_SWR	Clock master switch register	0xE1		
0x00 50C5		CLK_SWCR	Clock switch control register	0xXX		
0x00 50C6		CLK_CKDIVR	Clock divider register	0x18		
0x00 50C7		CLK_PCKENR1	Peripheral clock gating register 1	0xFF		
0x00 50C8		CLK_CSSR	Clock security system register	0x00		
0x00 50C9		CLK_CCOR	Configurable clock control register	0x00		
0x00 50CA		CLK_PCKENR2	Peripheral clock gating register 2	0xFF		
0x00 50CB		CLK_CANCCR	CAN clock control register	0x00		
0x00 50CC		CLK_HSITRIMR	HSI clock calibration trimming register	0x00		
0x00 50CD		CLK_SWIMCCR	SWIM clock control register	0bXXXX XXX0		
0x00 50CE to 0x00 50D0		1	Reserved area (3 bytes)			
0x00 50D1	WWDG	WWDG_CR	WWDG control register	0x7F		
0x00 50D2		WWDG_WR	WWDR window register	0x7F		
0x00 50D3 to 0x00 50DF		F	Reserved area (13 bytes)			
0x00 50E0	IWDG	IWDG_KR	IWDG key register	0xXX ⁽²⁾		
0x00 50E1	1	IWDG_PR	IWDG prescaler register	0x00		
0x00 50E2	1	IWDG_RLR	IWDG reload register	0xFF		
0x00 50E3 to 0x00 50EF		F	Reserved area (13 bytes)			
0x00 50F0	AWU	AWU_CSR1	AWU control/ status register 1	0x00		

				- i		
Address	Block	Register label	Register name	Reset status		
0x00 50F1		AWU_APR	AWU asynchronous prescaler buffer register	0x3F		
0x00 50F2		AWU_TBR	AWU timebase selection register	0x00		
0x00 50F3	BEEP	BEEP_CSR	BEEP control/ status register	0x1F		
0x00 50F4 to 0x00 50FF		F	Reserved area (12 bytes)			
0x00 5200	SPI	SPI_CR1	SPI control register 1	0x00		
0x00 5201		SPI_CR2	SPI control register 2	0x00		
0x00 5202		SPI_ICR	SPI interrupt control register	0x00		
0x00 5203		SPI_SR	SPI status register	0x02		
0x00 5204		SPI_DR	SPI data register	0x00		
0x00 5205		SPI_CRCPR	SPI CRC polynomial register	0x07		
0x00 5206		SPI_RXCRCR	SPI Rx CRC register	0xFF		
0x00 5207		SPI_TXCRCR	SPI Tx CRC register	0xFF		
0x00 5208 to 0x00 520F		Reserved area (8 bytes)				
0x00 5210	I ² C	I2C_CR1	I ² C control register 1	0x00		
0x00 5211		I2C_CR2	I ² C control register 2	0x00		
0x00 5212		I2C_FREQR	I ² C frequency register	0x00		
0x00 5213		I2C_OARL	I ² C Own address register low	0x00		
0x00 5214		I2C_OARH	I ² C own address register high	0x00		
0x00 5215			Reserved			
0x00 5216		I2C_DR	I ² C data register	0x00		
0x00 5217		I2C_SR1	I ² C status register 1	0x00		
0x00 5218		I2C_SR2	I ² C status register 2	0x00		
0x00 5219		I2C_SR3	I ² C status register 3	0x00		
0x00 521A		I2C_ITR	I ² C interrupt control register	0x00		
0x00 521B		I2C_CCRL	I ² C clock control register low	0x00		
0x00 521C		I2C_CCRH	I ² C clock control register high	0x00		
0x00 521D		I2C_TRISER	I ² C TRISE register	0x02		
0x00 521E		I2C_PECR	I ² C packet error checking register	0x00		
0x00 521F to 0x00 522F		Reserved area (17 bytes)				
0x00 5230 to 0x00 523F			Reserved area (6 bytes)			
0x00 5240	UART2	UART2_SR	UART2 status register	0xC0		
0x00 5241		UART2_DR	UART2 data register	0xXX		
0x00 5242		UART2_BRR1	UART2 baud rate register 1	0x00		

ina rogiotor map				
Address	Block	Register label	Register name	Reset status
0x00 5243		UART2_BRR2	UART2 baud rate register 2	0x00
0x00 5244		UART2_CR1	UART2 control register 1	0x00
0x00 5245		UART2_CR2	UART2 control register 2	0x00
0x00 5246		UART2_CR3	UART2 control register 3	0x00
0x00 5247		UART2_CR4	UART2 control register 4	0x00
0x00 5248		UART2_CR5	UART2 control register 5	0x00
0x00 5249		UART2_CR6	UART2 control register 6	0x00
0x00 524A	1	UART2_GTR	UART2 guard time register	0x00
0x00 524B		UART2_PSCR	UART2 prescaler register	0x00
0x00 524C to 0x00 524F			Reserved area (4 bytes)	
0x00 5250	TIM1	TIM1_CR1	TIM1 control register 1	0x00
0x00 5251		TIM1_CR2	TIM1 control register 2	0x00
0x00 5252		TIM1_SMCR	TIM1 slave mode control register	0x00
0x00 5253		TIM1_ETR	TIM1 external trigger register	0x00
0x00 5254		TIM1_IER	TIM1 interrupt enable register	0x00
0x00 5255		TIM1_SR1	TIM1 status register 1	0x00
0x00 5256		TIM1_SR2	TIM1 status register 2	0x00
0x00 5257		TIM1_EGR	TIM1 event generation register	0x00
0x00 5258		TIM1_CCMR1	TIM1 capture/ compare mode register 1	0x00
0x00 5259		TIM1_CCMR2	TIM1 capture/compare mode register 2	0x00
0x00 525A		TIM1_CCMR3	TIM1 capture/ compare mode register 3	0x00
0x00 525B		TIM1_CCMR4	TIM1 capture/compare mode register 4	0x00
0x00 525C		TIM1_CCER1	TIM1 capture/ compare enable register 1	0x00
0x00 525D		TIM1_CCER2	TIM1 capture/compare enable register 2	0x00
0x00 525E		TIM1_CNTRH	TIM1 counter high	0x00
0x00 525F		TIM1_CNTRL	TIM1 counter low	0x00
0x00 5260		TIM1_PSCRH	TIM1 prescaler register high	0x00
0x00 5261		TIM1_PSCRL	TIM1 prescaler register low	0x00
0x00 5262		TIM1_ARRH	TIM1 auto-reload register high	0xFF
0x00 5263		TIM1_ARRL	TIM1 auto-reload register low	0xFF
0x00 5264		TIM1_RCR	TIM1 repetition counter register	0x00

UKK				giotoi map
Address	Block	Register label	Register name	Reset status
0x00 5265		TIM1_CCR1H	TIM1 capture/ compare register 1 high	0x00
0x00 5266		TIM1_CCR1L	TIM1 capture/ compare register 1 low	0x00
0x00 5267		TIM1_CCR2H	TIM1 capture/ compare register 2 high	0x00
0x00 5268		TIM1_CCR2L	TIM1 capture/ compare register 2 low	0x00
0x00 5269		TIM1_CCR3H	TIM1 capture/ compare register 3 high	0x00
0x00 526A		TIM1_CCR3L	TIM1 capture/ compare register 3 low	0x00
0x00 526B		TIM1_CCR4H	TIM1 capture/ compare register 4 high	0x00
0x00 526C		TIM1_CCR4L	TIM1 capture/ compare register 4 low	0x00
0x00 526D		TIM1_BKR	TIM1 break register	0x00
0x00 526E		TIM1_DTR	TIM1 dead-time register	0x00
0x00 526F		TIM1_OISR	TIM1 output idle state register	0x00
0x00 5270 to 0x00 52FF		R	eserved area (147 bytes)	
0x00 5300	TIM2	TIM2_CR1	TIM2 control register 1	0x00
0x00 5301		TIM2_IER	TIM2 interrupt enable register	0x00
0x00 5302		TIM2_SR1	TIM2 status register 1	0x00
0x00 5303		TIM2_SR2	TIM2 status register 2	0x00
0x00 5304		TIM2_EGR	TIM2 event generation register	0x00
0x00 5305		TIM2_CCMR1	TIM2 capture/ compare mode register 1	0x00
0x00 5306		TIM2_CCMR2	TIM2 capture/ compare mode register 2	0x00
0x00 5307		TIM2_CCMR3	TIM2 capture/ compare mode register 3	0x00
0x00 5308		TIM2_CCER1	TIM2 capture/ compare enable register 1	0x00
0x00 5309		TIM2_CCER2	TIM2 capture/ compare enable register 2	0x00
0x00 530A		TIM2_CNTRH	TIM2 counter high	0x00
0x00 530B		TIM2_CNTRL	TIM2 counter low	0x00
0x00 530C		TIM2_PSCR	TIM2 prescaler register	0x00
0x00 530D		TIM2_ARRH	TIM2 auto-reload register high	0xFF
0x00 530E		TIM2_ARRL	TIM2 auto-reload register low	0xFF

Address	Block	Register label	Register name	Reset status
0x00 530F		TIM2_CCR1H	TIM2 capture/ compare register 1 high	0x00
0x00 5310		TIM2_CCR1L	TIM2 capture/ compare register 1 low	0x00
0x00 5311		TIM2_CCR2H	TIM2 capture/ compare reg. 2 high	0x00
0x00 5312		TIM2_CCR2L	TIM2 capture/ compare register 2 low	0x00
0x00 5313		TIM2_CCR3H	TIM2 capture/ compare register 3 high	0x00
0x00 5314		TIM2_CCR3L	TIM2 capture/ compare register 3 low	0x00
0x00 5315 to 0x00 531F		F	Reserved area (11 bytes)	
0x00 5320	TIM3	TIM3_CR1	TIM3 control register 1	0x00
0x00 5321		TIM3_IER	TIM3 interrupt enable register	0x00
0x00 5322		TIM3_SR1	TIM3 status register 1	0x00
0x00 5323		TIM3_SR2	TIM3 status register 2	0x00
0x00 5324		TIM3_EGR	TIM3 event generation register	0x00
0x00 5325		TIM3_CCMR1	TIM3 capture/ compare mode register 1	0x00
0x00 5326		TIM3_CCMR2	TIM3 capture/ compare mode register 2	0x00
0x00 5327		TIM3_CCER1	TIM3 capture/ compare enable register 1	0x00
0x00 5328		TIM3_CNTRH	TIM3 counter high	0x00
0x00 5329		TIM3_CNTRL	TIM3 counter low	0x00
0x00 532A		TIM3_PSCR	TIM3 prescaler register	0x00
0x00 532B		TIM3_ARRH	TIM3 auto-reload register high	0xFF
0x00 532C		TIM3_ARRL	TIM3 auto-reload register low	0xFF
0x00 532D		TIM3_CCR1H	TIM3 capture/ compare register 1 high	0x00
0x00 532E		TIM3_CCR1L	TIM3 capture/ compare register 1 low	0x00
0x00 532F		TIM3_CCR2H	TIM3 capture/ compare register 2 high	0x00
0x00 5330		TIM3_CCR2L	TIM3 capture/ compare register 2 low	0x00
0x00 5331 to 0x00 533F		F	Reserved area (15 bytes)	
0x00 5340	TIM4	TIM4_CR1	TIM4 control register 1	0x00
0x00 5341	1	TIM4_IER	TIM4 interrupt enable register	0x00

Address	Block	Register label	Register name	Reset status
0x00 5342		TIM4_SR	TIM4 status register	0x00
0x00 5343		TIM4_EGR	TIM4 event generation register	0x00
0x00 5344		TIM4_CNTR	TIM4 counter	0x00
0x00 5345		TIM4_PSCR	TIM4 prescaler register	0x00
0x00 5346		TIM4_ARR	TIM4 auto-reload register	0xFF
0x00 5347 to 0x00 53DF		R	eserved area (153 bytes)	
0x00 53E0 to 0x00 53F3	ADC1	ADC _DBxR	ADC data buffer registers	0x00
0x00 53F4 to 0x00 53FF		F	Reserved area (12 bytes)	
0x00 5400	ADC1	ADC _CSR	ADC control/ status register	0x00
0x00 5401		ADC_CR1	ADC configuration register 1	0x00
0x00 5402		ADC_CR2	ADC configuration register 2	0x00
0x00 5403		ADC_CR3	ADC configuration register 3	0x00
0x00 5404		ADC_DRH	ADC data register high	0xXX
0x00 5405		ADC_DRL	ADC data register low	0xXX
0x00 5406		ADC_TDRH	ADC Schmitt trigger disable register high	0x00
0x00 5407		ADC_TDRL	ADC Schmitt trigger disable register low	0x00
0x00 5408		ADC_HTRH	ADC high threshold register high	0x03
0x00 5409		ADC_HTRL	ADC high threshold register low	0xFF
0x00 540A		ADC_LTRH	ADC low threshold register high	0x00
0x00 540B		ADC_LTRL	ADC low threshold register low	0x00
0x00 540C		ADC_AWSRH	ADC analog watchdog status register high	0x00
0x00 540D		ADC_AWSRL	ADC analog watchdog status register low	0x00
0x00 540E		ADC _AWCRH	ADC analog watchdog control register high	0x00
0x00 540F		ADC_AWCRL	ADC analog watchdog control register low	0x00
0x00 5410 to 0x00 57FF		Re	eserved area (1008 bytes)	

Notes:

⁽²⁾ Write only register.




⁽¹⁾ Depends on the previous reset source.

6.2.3 CPU/SWIM/debug module/interrupt controller registers

Table 10: CPU/SWIM/debug module/interrupt controller registers

Address	Block	Register label	Register name	Reset status
0x00 7F00	CPU	Α	Accumulator	0x00
0x00 7F01	(1)	PCE	Program counter extended	0x00
0x00 7F02		PCH	Program counter high	0x00
0x00 7F03		PCL	Program counter low	0x00
0x00 7F04		XH	X index register high	0x00
0x00 7F05		XL	X index register low	0x00
0x00 7F06		YH	Y index register high	0x00
0x00 7F07		YL	Y index register low	0x00
0x00 7F08		SPH	Stack pointer high	0x07
0x00 7F09		SPL	Stack pointer low	0xFF
0x00 7F0A		CCR	Condition code register	0x28
0x00 7F0B to 0x00 7F5F			Reserved area (85 bytes)	
0x00 7F60	CPU	CFG_GCR	Global configuration register	0x00
0x00 7F70	ITC	ITC_SPR1	Interrupt software priority register 1	0xFF
0x00 7F71		ITC_SPR2	Interrupt software priority register 2	0xFF
0x00 7F72		ITC_SPR3	Interrupt software priority register 3	0xFF
0x00 7F73		ITC_SPR4	Interrupt software priority register 4	0xFF
0x00 7F74		ITC_SPR5	Interrupt software priority register 5	0xFF
0x00 7F75		ITC_SPR6	Interrupt software priority register 6	0xFF
0x00 7F76		ITC_SPR7	Interrupt software priority register 7	0xFF
0x00 7F77		ITC_SPR8	Interrupt software priority register 8	0xFF
0x00 7F78 to 0x00 7F79			Reserved area (2 bytes)	
0x00 7F80	SWIM	SWIM_CSR	SWIM control status register	0x00
0x00 7F81 to 0x00 7F8F			Reserved area (15 bytes)	
0x00 7F90	DM	DM_BK1RE	DM breakpoint 1 register extended byte	0xFF
0x00 7F91		DM_BK1RH	DM breakpoint 1 register high byte	0xFF
0x00 7F92		DM_BK1RL	DM breakpoint 1 register low byte	0xFF
0x00 7F93		DM_BK2RE	DM breakpoint 2 register extended byte	0xFF
0x00 7F94		DM_BK2RH	DM breakpoint 2 register high byte	0xFF
0x00 7F95		DM_BK2RL	DM breakpoint 2 register low byte	0xFF
0x00 7F96]	DM_CR1	DM debug module control	0x00



Address	Block	Register label	Register name	Reset status		
			register 1			
0x00 7F97		DM_CR2	DM debug module control register 2	0x00		
0x00 7F98		DM_CSR1	DM debug module control/status register 1	0x10		
0x00 7F99		DM_CSR2	DM debug module control/status register 2	0x00		
0x00 7F9A		DM_ENFCTR	DM enable function register	0xFF		
0x00 7F9B to 0x00 7F9F		Reserved area (5 bytes)				

Notes:

⁽¹⁾ Accessible by debug module only

Interrupt vector mapping 7

Table 11: Interrupt mapping

IRQ no.	Source block	Description	Wakeup from halt mode	Wakeup from active-halt mode	Vector address
	RESET	Reset	Yes	Yes	0x00 8000
	TRAP	Software interrupt	-	-	0x00 8004
0	TLI	External top level interrupt	-	-	0x00 8008
1	AWU	Auto wake up from halt	-	Yes	0x00 800C
2	CLK	Clock controller	-	-	0x00 8010
3	EXTI0	Port A external interrupts	Yes ⁽¹⁾	Yes ⁽¹⁾	0x00 8014
4	EXTI1	Port B external interrupts	Yes	Yes	0x00 8018
5	EXTI2	Port C external interrupts	Yes	Yes	0x00 801C
6	EXTI3	Port D external interrupts	Yes	Yes	0x00 8020
7	EXTI4	Port E external interrupts	Yes	Yes	0x00 8024
8					0x00 8028
9		Reserved	-	-	0x00 802C
10	SPI	End of transfer	Yes	Yes	0x00 8030
11	TIM1	TIM1 update/ overflow/ underflow/ trigger/ break	-	-	0x00 8034
12	TIM1	TIM1 capture/ compare	-	-	0x00 8038
13	TIM2	TIM update/ overflow	-	-	0x00 803C
14	TIM2	TIM capture/ compare	-	-	0x00 8040
15	TIM3	Update/ overflow	-	-	0x00 8044
16	TIM3	Capture/ compare	-	-	0x00 8048
17		Reserved	-	-	0x00 804C
18		Reserved	-	-	0x00 8050
19	I ² C	I ² C interrupt	Yes	Yes	0x00 8054
20	UART2	Tx complete	-	-	0x00 8058
21	UART2	Receive register DATA FULL	-	-	0x00 805C
22	ADC1	ADC1 end of conversion/ analog watchdog interrupt	-	-	0x00 8060
23	TIM4	TIM update/ overflow	-	-	0x00 8064
24	Flash	EOP/ WR_PG_DIS	-	-	0x00 8068
		Reserved			0x00 806C to 0x00807C

Notes: (1) Except PA1

36/99 DocID14771 Rev 13



STM8S105xx Option bytes

8 Option bytes

Option bytes contain configurations for device hardware features as well as the memory protection of the device. They are stored in a dedicated block of the memory. Except for the ROP (read-out protection) byte, each option byte has to be stored twice, in a regular form (OPTx) and a complemented one (NOPTx) for redundancy.

Option bytes can be modified in ICP mode (via SWIM) by accessing the EEPROM address shown in the table below.

Option bytes can also be modified 'on the fly' by the application in IAP mode, except the ROP option that can only be modified in ICP mode (via SWIM).

Refer to the STM8S Flash programming manual (PM0051) and STM8 SWIM communication protocol and debug module user manual (UM0470) for information on SWIM programming procedures.

Table 12: Option bytes

Addr.	Option	Option				Ор	tion bits				Factory
	name	byte no.	7	6	5	4	3	2	1	0	default setting
0x4800	Read-out protection (ROP)	OPT0				R	OP [7:0]				00h
0x4801	User boot	OPT1		UBC [7:0]						00h	
0x4802	code(UBC)	NOPT1				NU	IBC [7:0]				FFh
0x4803	Alternate	OPT2	AFR7	AFR6	AFR5	AFR4	AFR3	AFR2	AFR1	AFR0	00h
0x4804	function remapping (AFR)	NOPT2	NAFR7	NAFR6	NAFR5	NAFR4	NAFR3	NAFR2	NAFR1	NAFR0	FFh
0x4805h	Miscell. option	OPT3		Reserved			LSI_ EN	IWDG _HW	WWDG _HW	WWDG _HALT	00h
0x4806		NOPT3		Reserved			NLSI_ EN	NIWDG _HW	NWWDG _HW	NWW G_HALT	FFh
0x4807	Clock option	OPT4		Reserved			EXT CLK	CKAWU SEL	PRS C1	PRS C0	00h
0x4808		NOPT4		Rese	erved		NEXT CLK	NCKA WUSEL	NPRSC1	NPR SC0	FFh
0x4809	HSE clock	OPT5				HSE	CNT [7:0]				00h
0x480A	startup	NOPT5				NHSI	ECNT [7:0]				FFh
0x480B	Reserved	OPT6				Re	eserved				00h
0x480C		NOPT6				Re	eserved				FFh
0x480D	Reserved	OPT7				Re	eserved				00h
0x480E		NOPT7				Re	eserved				FFh
0x480F- 0x48FD	Reserved										
0x487E	Bootloader	OPTBL				Е	BL[7:0]				00h

Option bytes STM8S105xx

Addr. Option Option Option Option bits												
	name	byte no.	7	6	5	4	3	2	1	0	default setting	
C)x487F		NOPTBL				N	BL[7:0]				

Table 13: Option byte description

OPT0 ROP[7:0] Memory readout protection (ROP) AAh: Enable readout protection (write access via SWIM protocol) Note: Refer to the family reference manual (RM0016) section on Flash/EEPROM memory readout protection for details. OPT1 UBC[7:0] User boot code area 0x00: no UBC, no write-protection 0x01: Page 0 to 1 defined as UBC, memory write-protected 0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection for more details.
AAh: Enable readout protection (write access via SWIM protocol) Note: Refer to the family reference manual (RM0016) section on Flash/EEPROM memory readout protection for details. OPT1 UBC[7:0] User boot code area 0x00: no UBC, no write-protection 0x01: Page 0 to 1 defined as UBC, memory write-protected 0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
Note: Refer to the family reference manual (RM0016) section on Flash/EEPROM memory readout protection for details. OPT1 UBC[7:0] User boot code area 0x00: no UBC, no write-protection 0x01: Page 0 to 1 defined as UBC, memory write-protected 0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
OPT1 UBC[7:0] User boot code area 0x00: no UBC, no write-protection 0x01: Page 0 to 1 defined as UBC, memory write-protected 0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
0x00: no UBC, no write-protection 0x01: Page 0 to 1 defined as UBC, memory write-protected 0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
0x01: Page 0 to 1 defined as UBC, memory write-protected 0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
0x02: Page 0 to 3 defined as UBC, memory write-protected 0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
0x03: Page 0 to 4 defined as UBC, memory write-protected 0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
0x3E: Pages 0 to 63 defined as UBC, memory write-protected Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
Other values: Reserved Note: Refer to the family reference manual (RM0016) section on Flash write protection
Note: Refer to the family reference manual (RM0016) section on Flash write protection
ioi more details.
OPT2 AFR[7:0]
Refer to following table for the alternate function remapping decriptions of bits [7:2].
OPT3 HSITRIM:High speed internal clock trimming register size
0: 3-bit trimming supported in CLK_HSITRIMR register
1: 4-bit trimming supported in CLK_HSITRIMR register
LSI_EN:Low speed internal clock enable
0: LSI clock is not available as CPU clock source
1: LSI clock is available as CPU clock source
IWDG_HW: Independent watchdog
0: IWDG Independent watchdog activated by software
1: IWDG Independent watchdog activated by hardware
WWDG_HW: Window watchdog activation
0: WWDG window watchdog activated by software
1: WWDG window watchdog activated by hardware
WWDG_HALT: Window watchdog reset on halt
0: No reset generated on halt if WWDG active
1: Reset generated on halt if WWDG active
OPT4 EXTCLK: External clock selection
0: External crystal connected to OSCIN/OSCOUT
1: External clock signal on OSCIN
CKAWUSEL:Auto wake-up unit/clock
0: LSI clock source selected for AWU
1: HSE clock with prescaler selected as clock source for for AWU

STM8S105xx Option bytes

Option byte no.	Description
	PRSC[1:0] AWU clock prescaler
	0x: 16 MHz to 128 kHz prescaler
	10: 8 MHz to 128 kHz prescaler
	11: 4 MHz to 128 kHz prescaler
OPT5	HSECNT[7:0]:HSE crystal oscillator stabilization time
	0x00: 2048 HSE cycles
	0xB4: 128 HSE cycles
	0xD2: 8 HSE cycles
	0xE1: 0.5 HSE cycles
OPT6	Reserved
OPT7	Reserved
OPTBL	BL[7:0] Bootloader option byte
	For STM8S products, this option is checked by the boot ROM code after reset. Depending on the content of addresses 0x487E, 0x487F, and 0x8000 (reset vector), the CPU jumps to the bootloader or to the reset vector. Refer to the UM0560 (STM8L/S bootloader manual) for more details.
	For STM8L products, the bootloader option bytes are on addresses 0xXXXX and 0xXXXX+1 (2 bytes). These option bytes control whether the bootloader is active or not. For more details, refer to the UM0560 (STM8L/S bootloader manual) for more details.

Table 14: Description of alternate function remapping bits [7:0] of OPT2

Option byte no.	Description ⁽¹⁾
OPT2	AFR7 Alternate function remapping option 7
	0: AFR7 remapping option inactive: Default alternate function (2).
	1: Port D4 alternate function = BEEP.
	AFR6 Alternate function remapping option 6
	0: AFR6 remapping option inactive: Default alternate functions ⁽²⁾ .
	1: Port B5 alternate function = I^2C_SDA ; port B4 alternate function = I^2C_SCL .
	AFR5 Alternate function remapping option 5
	0: AFR5 remapping option inactive: Default alternate functions ⁽²⁾ .
	1: Port B3 alternate function = TIM1_ETR; port B2 alternate function = TIM1_NCC3; port B1 alternate function = TIM1_CH2N; port B0 alternate function = TIM1_CH1N.
	AFR4 Alternate function remapping option 4
	0: AFR4 remapping option inactive: Default alternate function (2).
	1: Port D7 alternate function = TIM1_CH4.
	AFR3 Alternate function remapping option 3
	0: AFR3 remapping option inactive: Default alternate function (2).
	1: Port D0 alternate function = TIM1_BKIN.
	AFR2 Alternate function remapping option 2
	0: AFR2 remapping option inactive: Default alternate function (2).
	1: Port D0 alternate function = CLK_CCO. Note: AFR2 option has priority over AFR3 if both are activated.
	AFR1 Alternate function remapping option 1
	0: AFR1 remapping option inactive: Default alternate functions (2).

Option bytes STM8S105xx

Option byte no.	Description ⁽¹⁾
	1: Port A3 alternate function = TIM3_CH1; port D2 alternate function TIM2_CH3.
	AFR0 Alternate function remapping option 0
	0: AFR0 remapping option inactive: Default alternate function (2).
	1: Port D3 alternate function = ADC_ETR.

 $^{^{\}left(1\right)}$ Do not use more than one remapping option in the same port.

⁽²⁾ Refer to pinout description.

STM8S105xx Unique ID

9 Unique ID

The devices feature a 96-bit unique device identifier which provides a reference number that is unique for any device and in any context. The 96 bits of the identifier can never be altered by the user.

The unique device identifier can be read in single bytes and may then be concatenated using a custom algorithm.

The unique device identifier is ideally suited:

- For use as serial numbers
- For use as security keys to increase the code security in the program memory while using and combining this unique ID with software cryptographic primitives and protocols before programming the internal memory.
- To activate secure boot processes

Table 15: Unique ID registers (96 bits)

Address	Content description			ι	Jnique	ID bi	ts			
		7	6	5	4	3	2	1	0	
0x48CD	X co-ordinate on the wafer				U_IE	0[7:0]				
0x48CE					U_ID	[15:8]				
0x48CF	Y co-ordinate on the wafer	U_ID[23:16]								
0x48D0					U_ID[31:24				
0x48D1	Wafer number	U_ID[39:32]								
0x48D2	Lot number				U_ID[47:40				
0x48D3					U_ID[55:48				
0x48D4					U_ID[63:56				
0x48D5					U_ID[71:64				
0x48D6		U_ID[79:72]								
0x48D7					U_ID[87:80				
0x48D8					U_ID[95:88	:8] 16] 24] 32] 40] 48] 56] 64] 72]			

10 Electrical characteristics

10.1 Parameter conditions

Unless otherwise specified, all voltages are referred to V_{SS}.

10.1.1 Minimum and maximum values

Unless otherwise specified the minimum and maximum values are guaranteed in the worst conditions of ambient temperature, supply voltage and frequencies by tests in production on 100 % of the devices with an ambient temperature at $T_A = 25$ °C and $T_A = T_{Amax}$ (given by the selected temperature range).

Data based on characterization results, design simulation and/or technology characteristics are indicated in the table footnotes and are not tested in production. Based on characterization, the minimum and maximum values refer to sample tests and represent the mean value plus or minus three times the standard deviation (mean \pm 3 Σ).

10.1.2 Typical values

Unless otherwise specified, typical data are based on $T_A = 25$ °C, $V_{DD} = 5$ V. They are given only as design guidelines and are not tested.

Typical ADC accuracy values are determined by characterization of a batch of samples from a standard diffusion lot over the full temperature range, where 95% of the devices have an error less than or equal to the value indicated (mean \pm 2 Σ).

10.1.3 Typical curves

Unless otherwise specified, all typical curves are given only as design guidelines and are not tested.

10.1.4 Typical current consumption

For typical current consumption measurements, V_{DD} , V_{DDIO} and V_{DDA} are connected together in the configuration shown in the following figure.




Figure 8: Supply current measurement conditions

10.1.5 Loading capacitor

The loading conditions used for pin parameter measurement are shown in the following figure.

50 pF

Figure 9: Pin loading conditions

10.1.6 Pin input voltage

The input voltage measurement on a pin of the device is described in the following figure.




Figure 10: Pin input voltage

10.2 Absolute maximum ratings

Stresses above those listed as 'absolute maximum ratings' may cause permanent damage to the device. This is a stress rating only and functional operation of the device under these conditions is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

Symbol	Ratings	Min	Max	Unit
V _{DDx} - V _{SS}	Supply voltage (including $V_{DDA\ and}$ V_{DDIO}) $^{(1)}$	-0.3	6.5	٧
V _{IN}	Input voltage on true open drain pins (PE1, PE2) (2)	V _{SS} - 0.3	6.5	
	Input voltage on any other pin (2)	V _{SS} - 0.3	V _{DD} + 0.3	
V _{DDx} -	Variations between different power		50	mV

Table 16: Voltage characteristics

Symbol	Ratings	Min	Max	Unit
V_{DD}	pins			
V _{SSx} - V _{SS}	Variations between all the different ground pins		50	
V _{ESD}	Electrostatic discharge voltage	see Section 13.3.12.4: "Absolute maximum rating (electrical sensitivity)"		mum ratings

Table 17: Current characteristics

Symbol	Ratings	Max.	Unit
I_{VDD}	Total current into V _{DD} power lines (source) (2)	60	mA
I _{VSS}	Total current out of V _{SS} ground lines (sink) (2)	60	
I _{IO}	Output current sunk by any I/O and control pin	20	
	Output current source by any I/Os and control pin	20	
ΣI _{IO}	Total output current sourced (sum of all I/O and control pins) for devices with two V_{DDIO} pins $^{(3)}$	200	
	Total output current sourced (sum of all I/O and control pins) for devices with one V_{DDIO} pin $^{(3)}$	100	
	Total output current sunk (sum of all I/O and control pins) for devices with two $\rm V_{SSIO}$ pins $^{(3)}$	160	
	Total output current sunk (sum of all I/O and control pins) for devices with one V_{SSIO} pin $^{(3)}$	80	
I _{INJ(PIN)} (4)(5)	Injected current on NRST pin	±4	
	Injected current on OSCIN pin	±4	
	Injected current on any other pin (6)	±4	
ΣI _{INJ(PIN)} ⁽⁴⁾	Total injected current (sum of all I/O and control pins) (6)	±20	

 $^{^{(1)}}$ All power (V_{DD}, V_{DDIO}, V_{DDA}) and ground (V_{SS}, V_{SSIO}, V_{SSA}) pins must always be connected to the external power supply

 $I_{INJ(PIN)}$ must never be exceeded. This is implicitly insured if V_{IN} maximum is respected. If V_{IN} maximum cannot be respected, the injection current must be limited externally to the $I_{INJ(PIN)}$ value. A positive injection is induced by $V_{IN} > V_{DD}$ while a negative injection is induced by $V_{IN} < V_{SS}$. For true open-drain pads, there is no positive injection current, and the corresponding V_{IN} maximum must always be respected

⁽¹⁾ Data based on characterization results, not tested in production.

 $^{^{(2)}}$ All power (V_{DD}, V_{DDIO}, V_{DDA}) and ground (V_{SS}, V_{SSIO}, V_{SSA}) pins must always be connected to the external supply.

 $^{^{(3)}}$ I/O pins used simultaneously for high current source/sink must be uniformly spaced around the package between the V_{DDIO}/V_{SSIO} pins.

 $^{^{(4)}}$ $I_{INJ(PIN)}$ must never be exceeded. This is implicitly insured if V_{IN} maximum is respected. If V_{IN} maximum cannot be respected, the injection current must be limited externally to the $I_{INJ(PIN)}$ value. A positive injection is induced by $V_{IN} > V_{DD}$ while a negative injection is induced by $V_{IN} < V_{SS}$. For true open-drain pads, there is no positive injection current, and the corresponding V_{IN} maximum must always be respected

⁽⁵⁾ Negative injection disturbs the analog performance of the device. See note in Section 7.11: "TIM2, TIM3 - 16-bit general purpose timers".

 $^{^{(6)}}$ When several inputs are submitted to a current injection, the maximum $\Sigma I_{INJ(PIN)}$ is the absolute sum of the

positive and negative injected currents (instantaneous values). These results are based on characterization with $\Sigma I_{INJ(PIN)}$ maximum current injection on four I/O port pins of the device.

Table 18: Thermal characteristics

Symbol	Ratings	Value	Unit
T _{STG}	Storage temperature range	-65 to 150	°C
TJ	Maximum junction temperature	150	

10.3 Operating conditions

The device must be used in operating conditions that respect the parameters in the table below. In addition, full account must be taken of all physical capacitor characteristics and tolerances.

Table 19: General operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
f _{CPU}	Internal CPU clock frequency		0	16	MHz
V_{DD}/V_{DD_IO}	Standard operating voltage		2.95	5.5	V
VCAP	C _{EXT} : capacitance of external capacitor		470	3300	nF
	ESR of external capacitor	at 1 MHz	-	0.3	Ohm
	ESL of external capacitor		-	15	nΗ
P _D ⁽³⁾	Power dissipation at TA = 85 °C for suffix 6or TA= 125° C for suffix 3	44 and 48-pin devices, with output on eight standard ports, two high sink ports and two open drain ports simultaneously (4)	-	443	mW
		32-pin package, with output on eight standard ports and two high sink ports simultaneously (4)	-	360	
T _A	Ambient temperature for 6 suffix version	Maximum power dissipation	-40	85	°C
	Ambient temperature for 3 suffix version	Maximum power dissipation	-40	125	
TJ	Junction temperature	6 suffix version	-40	105	
	range	3 suffix version	-40	130	

⁽⁴⁾ Refer to Section 7.7: "Watchdog timers"



⁽¹⁾ Care should be taken when selecting the capacitor, due to its tolerance, as well as the parameter dependency on temperature, DC bias and frequency in addition to other factors. The parameter maximum value must be respected for the full application range.

⁽²⁾ This frequency of 1 MHz as a condition for VCAP parameters is given by design of internal regulator.

 $^{^{(3)}}$ To calculate $P_{Dmax}(T_A)$, use the formula $P_{Dmax} = (T_{Jmax} - T_A)/\Theta_{JA}$ (see Section 7.7: "Watchdog timers") with the value for T_{Jmax} given in the current table and the value for Θ_{JA} given in Section 7.7: "Watchdog timers".

Electrical characteristics STM8S105xx




Figure 11: fCPUmax versus VDD

Table 20: Operating conditions at power-up/power-down

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t _{VDD}	V _{DD} rise time rate		2.0 (1)		∞	μs/V
	V _{DD} fall time rate		2.0 (1)		∞	
t _{TEMP}	Reset releasedelay	V _{DD} rising			1.7 ⁽¹⁾	ms
V _{IT+}	Power-on reset threshold		2.65	2.8	2.95	V
V _{IT} -	Brown-out reset threshold		2.58	2.7	2.88	
V _{HYS(BOR)}	Brown-out reset hysteresis			70		mV

Notes:


10.3.1 VCAP external capacitor

Stabilization for the main regulator is achieved connecting an external capacitor C_{EXT} to the V_{CAP} pin. C_{EXT} is specified in the Operating conditions section. Care should be taken to limit the series inductance to less than 15 nH.

⁽¹⁾ Guaranteed by design, not tested in production.

STM8S105xx Electrical characteristics

Figure 12: External capacitor CEXT



1. ESR is the equivalent series resistance and ESL is the equivalent inductance.

10.3.2 Supply current characteristics

The current consumption is measured as described in Section 7.3: "Interrupt controller".

10.3.2.1 Total current consumption in run mode

Table 21: Total current consumption with code execution in run mode at VDD = 5 V

Symbol	Parameter	Conditio	ns	Тур	Max	Unit
I _{DD(RUN)}	Supply current in run mode, code executed from RAM	f _{CPU} = f _{MASTER} = 16 MHz	HSE crystal osc. (16 MHz)	3.2		mA
			HSE user ext. clock (16 MHz)	2.6	3.2	
		HSI R (16 N fcpu = fmaster/128 = HSE		2.5	3.2	
		$f_{CPU} = f_{MASTER}/128 = 125 \text{ kHz}$			2.2	
			HSI RC osc. (16 MHz)	1.3	2.0	
		f _{CPU} = f _{MASTER} /128 = 15.625 kHz	HSI RC osc. (16 MH3z/8)	0.75		
		f _{CPU} = f _{MASTER} = 128 kHz	LSI RC osc. (128 kHz)	0.55		
I _{DD(RUN)}	Supply current in run mode, code executed from Flash	f _{CPU} = f _{MASTER} = 16 MHz	HSE crystal osc. (16 MHz)	7.7		
			HSE user ext. clock (16 MHz)	7.0	8.0	
			HSI RC osc. (16 MHz)	7.0	8.0	
		$f_{CPU} = f_{MASTER}$	HSI RC osc.	1.5		

Symbol	Parameter	Conditio	ns	Тур	Max	Unit
		= 2 MHz	(16 MHz/8)			
		f _{CPU} = f _{MASTER} /128 = 125 kHz	HSI RC osc. (16 MHz)	1.35	2.0	
		f _{CPU} = f _{MASTER} /128 = 15.625 kHz	HSI RC osc. (16 MHz/8)	0.75		
		f _{CPU} = f _{MASTER} = 128 kHz	LSI RC osc. (128 kHz)	0.6		

Table 22: Total current consumption with code execution in run mode at VDD = 3.3 V

Symbol	Parameter	Condition	ons	Тур	Max	Unit
I _{DD(RUN)}	Supply current in run mode, code executed from RAM	f _{CPU} = f _{MASTER} = 16 MHz	HSE crystal osc. (16 MHz)	2.8		mA
			HSE user ext. clock (16 MHz)	2.6	3.2	
			HSI RC osc. (16 MHz)	2.5	3.2	
		$f_{CPU} = f_{MASTER}/128$ = 125 kHz	HSE user ext. clock (16 MHz)	1.6	2.2	
			HSI RC osc. (16 MHz)	1.3	2.0	
		f _{CPU} = f _{MASTER} /128 = 15.625 kHz	HSI RC osc. (16 MHz/8)	0.75		
		f _{CPU} = f _{MASTER} = 128 kHz	LSI RC osc. (128 kHz)	0.55		
	Supply current in run mode, code executed from Flash	f _{CPU} = f _{MASTER} = 16 MHz	HSE crystal osc. (16 MHz)	7.3		
			HSE user ext. clock (16 MHz)	7.0	8.0	
			HSI RC osc. (16 MHz)	7.0	8.0	
		f _{CPU} = f _{MASTER} = 2 MHz	HSI RC osc. (16 MHz/8) (2)	1.5		

 $^{^{\}left(1\right)}$ Data based on characterization results, not tested in production.

 $[\]ensuremath{^{(2)}}$ Default clock configuration measured with all peripherals off.

STM8S105xx Electrical characteristics

Symbol	Parameter	Condition	Тур	Max (1)	Unit	
		$f_{CPU} = f_{MASTER}/128$ $= 125 \text{ kHz}$	HSI RC osc. (16 MHz)	1.35	2.0	
		f _{CPU} = f _{MASTER} /128 = 15.625 kHz	HSI RC osc. (16 MHz/8)	0.75		
		f _{CPU} = f _{MASTER} = 128 kHz	LSI RC osc. (128 kHz)	0.6		

Notes:

10.3.2.2 Total current consumption in wait mode

Table 23: Total current consumption in wait mode at VDD = 5 V

Symbol	Parameter	Condition	s	Тур	Max	Unit
I _{DD(WFI)}	Supply current in wait mode	$f_{CPU} = f_{MASTER} = 16 \text{ MHz}$	HSE crystal osc. (16 MHz)	2.15		mA
			HSE user ext. clock (16 MHz)	1.55	2.0	
			1.9			
		$f_{CPU} = f_{MASTER}/128 = 125$ kHz	HSI RC osc. (16 MHz)			
		f _{CPU} = f _{MASTER} /128 = 15.625 kHz				
		$f_{CPU} = f_{MASTER} = 128 \text{ kHz}$	LSI RC osc. (128 kHz)	0.5		

Table 24: Total current consumption in wait mode at VDD = 3.3 V

Symbol	Parameter	Condition	Тур	Max (1)	Unit	
I _{DD(WFI)}	Supply current in wait mode	f _{CPU} = f _{MASTER} = 16 MHz	HSE crystal osc. (16 MHz)	1.75		mA
			HSE user ext. clock	1.55	2.0	



 $^{^{\}left(1\right)}$ Data based on characterization results, not tested in production.

 $^{^{\}left(2\right)}$ Default clock configuration measured with all peripherals off.

⁽¹⁾ Data based on characterization results, not tested in production.

 $^{^{\}left(2\right)}$ Default clock configuration measured with all peripherals off.

Symbol	Parameter	Condition	S	Тур	Max	Unit
			(16 MHz)			
			HSI RC osc. (16 MHz)	1.5	1.9	
		f _{CPU} = f _{MASTER} /128 = 125 kHz	HSI RC osc. (16 MHz)	1.3		
		f _{CPU} = f _{MASTER} /128 = 15.625 kHz	HSI RC osc. (16 MHz/8) (2)	0.7		
		f _{CPU} = f _{MASTER} = 128 kHz	LSI RC osc. (128 kHz)	0.5		

10.3.2.3 Total current consumption in active halt mode

Table 25: Total current consumption in active halt mode at VDD = 5 V

Symbol	Parameter	C	Conditions		Тур	Max	Max	Unit
		Main voltage regulator (MVR) (2)	Flash mode ⁽³⁾	Clock source		at 85 °C ⁽¹⁾	at 125 °C ⁽¹⁾	
I _{DD(AH)}	Supply current in active halt mode	On	Operating mode	HSE crystal osc. (16 MHz)	1080			μА
				LSI RC osc. (128 kHz)	200	320	400	
			Power- down mode	HSE crystal osc. (16 MHz)	1030			
			LSI RC osc. (128 kHz)	140	270	350		
		Off	Operating mode	LSI RC osc.	68	120	220	
			Power- down mode	(128 kHz)	12	60	150	

 $^{^{\}left(1\right)}$ Data based on characterization results, not tested in production.

⁽²⁾ Default clock configuration measured with all peripherals off.

Table 26: Total current consumption in active halt mode at VDD = 3.3 V

Symbol	Parameter	(Conditions		Тур	Max	Max	Unit		
		Main voltage regulator (MVR) (2)	Flash mode ⁽³⁾	Clock source		at 85 °C ⁽¹⁾	at 125 °C ⁽¹⁾			
I _{DD(AH)}	Supply current in active halt mode	On	Operating mode	HSE crystal osc. (16 MHz)	680			μА		
				LSI RC osc. (128 kHz)	200	320	400			
					Power- down mode	HSE crystal osc. (16 MHz)	630			
			LSI RC osc. (128 kHz)	140	270	350				
		Off	Operating mode	LSI RC osc. (128	66	120	220			
		Power- down mode	down	kHz)	10	60	150			

Notes:

10.3.2.4 Total current consumption in halt mode

Table 27: Total current consumption in halt mode at VDD = 5 V

Symbol	Parameter	Conditions	Тур	Max at 85 °C (1)	Max at 125 °C (1)	Unit
I _{DD(H)}	Supply current in halt mode	Flash in operating mode, HSI clock after wakeup	62	90	150	μΑ
		Flash in powerdown mode, HSI clock after wakeup	6.5	25	80	

⁽¹⁾ Data based on characterization results, not tested in production.



 $^{^{\}left(1\right) }$ Data based on characterization results, not tested in production

 $^{^{(2)}}$ Configured by the REGAH bit in the CLK_ICKR register.

⁽³⁾ Configured by the AHALT bit in the FLASH_CR1 register.

⁽¹⁾ Data based on characterization results, not tested in production.

 $^{^{(2)}}$ Configured by the REGAH bit in the CLK_ICKR register.

 $^{^{(3)}}$ Configured by the AHALT bit in the FLASH_CR1 register.

Table 28: Total current consumption in halt mode at VDD = 3.3 V

Symbol	Parameter	Conditions	Тур	Max at 85 °C (1)	Max at 125 °C (1)	Unit
I _{DD(H)}	Supply current in halt mode	Flash in operating mode, HSI clock after wakeup	60	90	150	μΑ
		Flash in powerdown mode, HSI clock after wakeup	4.5	20	80	

10.3.2.5 Low power mode wakeup times

Table 29: Wakeup times

Symbol	Parameter		Conditions		Тур	Max ⁽¹⁾	Unit
t _{WU(WFI)}	Wakeup time from		0 to 16 MHz				μs
	wait mode to run mode ⁽²⁾	f _{CPU}	= f _{MASTER} = 16 MH	Z	0.56		
t _{WU(AH)}	Wakeup time active halt mode to run mode ⁽²⁾	MVR voltage regulator on ⁽⁴⁾	Flash in operating mode ⁽⁵⁾	HSI (after wakeup)	1 (6)	2 (6)	
	Wakeup time active halt mode to run mode (2)	MVR voltage regulator on ⁽⁴⁾	Flash in power-down mode ⁽⁵⁾	HSI (after wakeup)	3 (6)		
	Wakeup time active halt mode to run mode ⁽²⁾	MVR voltage regulator off ⁽⁴⁾	Flash in operating mode ⁽⁵⁾	HSI (after wakeup)	48 (6)		
	Wakeup time active halt mode to run mode ⁽²⁾	MVR voltage regulator off ⁽⁴⁾	Flash in power-down mode ⁽⁵⁾	HSI (after wakeup)	50 (6)		
t _{WU(H)}	Wakeup time	Flash	in operating mode	e ⁽⁵⁾	52		
	from halt mode to run mode (2)	Flash i	n power-down mod	de ⁽⁵⁾	54		

 $^{^{\}left(1\right) }$ Data based on characterization results, not tested in production.

 $^{^{\}left(1\right) }$ Data guaranteed by design, not tested in production.

⁽²⁾ Measured from interrupt event to interrupt vector fetch.

 $^{^{(3)}}$ twu(WFI) = 2 x 1/f_{master} + 67 x 1/f_{CPU}.

 $^{^{(4)}}$ Configured by the REGAH bit in the CLK_ICKR register.

 $^{^{(5)}}$ Configured by the AHALT bit in the FLASH_CR1 register.

10.3.2.6 Total current consumption and timing in forced reset state

Table 30: Total current consumption and timing in forced reset state

Symbol	Parameter	Conditions	Тур	Max ⁽¹⁾	Unit
I _{DD(R)}	Supply current in reset state (2)	$V_{DD} = 5 \text{ V}$	500		μΑ
		$V_{DD} = 3.3 \text{ V}$	400		
t _{RESETBL}	Reset pin release to vector fetch			150	μs

Notes:

10.3.2.7 Current consumption of on-chip peripherals

Subject to general operating conditions for V_{DD} and T_A .

HSI internal RC/ $f_{CPU} = f_{MASTER} = 16 \text{ MHz}.$

Table 31: Peripheral current consumption

Symbol	Parameter	Тур.	Unit
I _{DD(TIM1)}	TIM1 supply current (1)	230	μA
I _{DD(TIM2)}	TIM2 supply current (1)	115	
I _{DD(TIM3)}	TIM3 timer supply current (1)	90	
I _{DD(TIM4)}	TIM4 timer supply current (1)	30	
I _{DD(UART2)}	UART2 supply current (2)	110	
I _{DD(SPI)}	I _{DD(SPI)} SPI supply current ⁽²⁾		
I _{DD(I} C)	² C) I ² C supply current ⁽²⁾		
I _{DD(ADC1)}	ADC1 supply current when converting (3)	955	

Notes:

10.3.2.8 Current consumption curves

The following figures show typical current consumption measured with code executing in RAM.

⁽⁶⁾ Plus 1 LSI clock depending on synchronization.

⁽¹⁾ Data guaranteed by design, not tested in production.

⁽²⁾ Characterized with all I/Os tied to V_{SS}.

⁽¹⁾ Data based on a differential I_{DD} measurement between reset configuration and timer counter running at 16 MHz. No IC/OC programmed (no I/O pads toggling). Not tested in production.

⁽²⁾ Data based on a differential I_{DD} measurement between the on-chip peripheral when kept under reset and not clocked and the on-chip peripheral when clocked and not kept under reset. No I/O pads toggling. Not tested in production.

 $^{^{(3)}}$ Data based on a differential I_{DD} measurement between reset configuration and continuous A/D conversions. Not tested in production.

Figure 13: Typ. IDD(RUN) vs. VDD, HSE user external clock, fCPU = 16 MHz




Figure 14: Typ. IDD(RUN) vs. fCPU, HSE user external clock, VDD= 5 V




Figure 15: Typ. IDD(RUN) vs. VDD, HSI RC osc, fCPU = 16 MHz




Figure 16: Typ. IDD(WFI) vs. VDD, HSE user external clock, fCPU = 16 MHz




Figure 17: Typ. IDD(WFI) vs. fCPU, HSE user external clock VDD = 5 V





Figure 18: Typ. IDD(WFI) vs. VDD, HSI RC osc, fCPU = 16 MHz



10.3.3 External clock sources and timing characteristics

HSE user external clock

Subject to general operating conditions for V_{DD} and T_A .

Table 32: HSE user external clock characteristics

Symbol	Parameter	Conditions	Min	Max	Unit
f _{HSE_ext}	User external clock source frequency		0	16	MHz
V _{HSEH} ⁽¹⁾	OSCIN input pin high level voltage		0.7 x V _{DD}	V _{DD} + 0.3 V	V
V _{HSEL} ⁽¹⁾	OSCIN input pin low level voltage		V _{SS}	0.3 x V _{DD}	
I _{LEAK_HSE}	OSCIN input leakage current	$V_{SS} < V_{IN} < V_{DD}$	-1	+1	μA

Notes:

V_{HSEL}
V_{HSEL}
V_{HSEL}
STM8

Figure 19: HSE external clocksource

HSE crystal/ceramic resonator oscillator

The HSE clock can be supplied with a 1 to 16 MHz crystal/ceramic resonator oscillator. All the information given in this paragraph is based on characterization results with specified typical external components. In the application, the resonator and the load capacitors have to be placed as close as possible to the oscillator pins in order to minimize output distortion and start-up stabilization time. Refer to the crystal resonator manufacturer for more details (frequency, package, accuracy...).

Table 33: HSE oscillator characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f _{HSE}	External high speed oscillator frequency		1		16	MHz
R_{F}	Feedback resistor			220		kΩ

 $^{^{\}left(1\right)}$ Data based on characterization results, not tested in production.

STM8S105xx Electrical characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
C ⁽¹⁾	Recommended load capacitance (2)				20	pF
I _{DD(HSE)}	HSE oscillator power consumption	C = 20 pF, f _{OSC} = 16 MHz			6 (startup) 1.6 (stabilized) (3)	mA
		C = 10 pF, f _{OSC} =16 MHz			6 (startup) 1.2 (stabilized) (3)	
g _m	Oscillator transconductance		5			mA/V
t _{SU(HSE)} (4)	Startup time	V _{DD} is stabilized		1		ms

Notes:

Resonator

CL1

OSCIN

Resonator

Consumption control

STM8

Figure 20: HSE oscillator circuit diagram

HSE oscillator critical g_m equation

$$g_{mcrit} = (2 \times \Pi \times f_{HSE})^2 \times R_m (2Co + C)^2$$

R_m: Notional resistance (see crystal specification)

L_m: Notional inductance (see crystal specification)

C_m: Notional capacitance (see crystal specification)

Co: Shunt capacitance (see crystal specification)

C_{L1}= C_{L2} = C: Grounded external capacitance

 $g_m >> g_{mcrit}$



 $^{^{(1)}}$ C is approximately equivalent to 2 x crystal Cload.

 $^{^{(2)}}$ The oscillator selection can be optimized in terms of supply current using a high quality resonator with small R_m value. Refer to crystal manufacturer for more details

⁽³⁾ Data based on characterization results, not tested in production.

⁽⁴⁾ t_{SU(HSE)} is the start-up time measured from the moment it is enabled (by software) to a stabilized 16 MHz oscillation is reached. This value is measured for a standard crystal resonator and it can vary significantly with the crystal manufacturer.

10.3.4 Internal clock sources and timing characteristics

Subject to general operating conditions for V_{DD} and T_A .

High speed internal RC oscillator (HSI)

Table 34: HSI oscillator characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit	
f _{HSI}	Frequency			16		MHz	
ACC _{HSI}	Accuracy of HSI oscillator	User-trimmed with CLK_HSITRIMR register for given V_{DD} and T_A conditions $^{(1)}$			1.0	%	
	Accuracy of HSI	$V_{DD} = 5 \text{ V}, T_A = 25^{\circ}\text{C}^{(3)}$	-1.0		1.0		
	oscillator (factory calibrated)	oscillator (factory calibrated)	$V_{DD} = 5 \text{ V}, 25 \text{ °C} \leq T_A \leq 85 \text{ °C}$	-2.0		2.0	
	,	2.95 ≤ V _{DD} ≤ 5.5 V,-40 °C ≤ T _A ≤ 125 °C	-3.0 (3)		3.0		
t _{su(HSI)}	HSI oscillator wake-up time including calibration				1.0	μs	
I _{DD(HSI)}	HSI oscillator power consumption			170	250 (3)	μΑ	

 $[\]ensuremath{^{(3)}}$ Data based on characterization results, not tested in production.




Figure 21: Typical HSI accuracy at VDD = 5 V vs 5 temperatures

⁽¹⁾ Refer to application note.

 $^{^{\}left(2\right) }$ Guaranteed by design, not tested in production.

25°C 85°C 1.00% -125°C -45°C 0.50% 0.00% % accuracy -0.50% -1.00% -1.50% -2.00% 3.5 2.5 4.5 5.5 VDD (V)

Figure 22: Typical HSI accuracy vs VDD @ 4 temperatures


Low speed internal RC oscillator (LSI)

Subject to general operating conditions for V_{DD} and T_A .

Table 35: LSI oscillator characteristics

Symbol	Parameter		Тур	Max	Unit
f _{LSI}	Frequency	110	128	146	kHz
t _{su(LSI)}	LSI oscillator wakeup time			7 (1)	μs
I _{DD(LSI)}	LSI oscillator power consumption		5		μΑ

Figure 23: Typical LSI accuracy vs VDD @ 4 temperatures



⁽¹⁾ Guaranteed by design, not tested in production.

10.3.5 Memory characteristics

RAM and hardware registers

Table 36: RAM and hardware registers

Symbol	Parameter	Conditions	Min	Unit
V_{RM}	Data retention mode (1)	Halt mode (or reset)	V _{IT-max} ⁽²⁾	V

Notes:

Flash program memory/data EEPROM memory

General conditions: $T_A = -40$ to 125°C.

Table 37: Flash program memory/data EEPROM memory

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V_{DD}	Operating voltage (all modes, execution/write/erase)	f _{CPU} ≤ 16 MHz	2.95		5.5	V
t _{prog}	Standard programming time (including erase) for byte/word/block (1 byte/4 bytes/128 bytes)			6.0	6.6	ms
	Fast programming time for 1 block (128 bytes)			3.0	3.3	ms
t _{erase}	Erase time for 1 block (128 bytes)			3.0	3.3	ms
N _{RW}	Erase/write cycles (2)(program memory)	T _A = +85 °C	10 k			cycles
	Erase/write cycles(data memory) (2)	T _A = +125 ° C	300 k	1.0M		
t _{RET}	Data retention (program memory) after 10k erase/write cycles at T _A = +85 °C	T _{RET} = 55° C	20			years
	Data retention (data memory) after 10k erase/write cycles at T _A = +85 °C	T _{RET} = 55° C	20			
	Data retention (data memory) after 300 k erase/write cycles at T _A = +125 °C	T _{RET} = 85° C	1.0			
I _{DD}	Supply current (Flash programming or erasing for 1 to 128 bytes)			2.0		mA

Notes:

60/99

⁽¹⁾ Minimum supply voltage without losing data stored in RAM (in halt mode or under reset) or in hardware registers (only in halt mode). Guaranteed by design, not tested in production. refer to Section 7.10: "TIM1 - 16-bit advanced control timer" for the value of V_{IT-max}

 $^{^{(2)}}$ Refer to the Operating conditions section for the value of V_{IT-max}

⁽¹⁾ Data based on characterization results, not tested in production.

⁽²⁾ The physical granularity of the memory is 4 bytes, so cycling is performed on 4 bytes even when a write/erase operation addresses a single byte.

10.3.6 I/O port pin characteristics

General characteristics

Subject to general operating conditions for V_{DD} and T_A unless otherwise specified. All unused pins must be kept at a fixed voltage: using the output mode of the I/O for example or an external pull-up or pull-down resistor.

Table 38: I/O static characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _{IL}	Input low level voltage	V _{DD} = 5 V	-0.3		0.3 x V _{DD}	V
V _{IH}	Input high level voltage		0.7 x V _{DD}		V _{DD} + 0.3 V	V
V_{hys}	Hysteresis (1)			700		mV
R _{pu}	Pull-up resistor	$V_{DD} = 5 V$, $V_{IN} = V_{SS}$	30	55	80	kΩ
t _R , t _F	Rise and fall time(10 % -	Fast I/Os load = 50 pF			35 ⁽²⁾	
	90 %)	Standard and high sink I/Os load = 50 pF			125 ⁽²⁾	ns
		Fast I/Os load = 20 pF			20 ⁽²⁾	
		Standard and high sink I/Os load = 20 pF			50 ⁽²⁾	
I _{lkg}	Input leakage current, analog and digital	$V_{SS} \le V_{IN} \le V_{DD}$			±1.0 ⁽³⁾	μΑ
I _{lkg ana}	Analog input leakage current	$V_{SS} \le V_{IN} \le V_{DD}$			±250 ⁽³⁾	nA
I _{lkg(inj)}	Leakage current in adjacent I/O ⁽³⁾	Injection current ±4 mA			±1.0 ⁽³⁾	μΑ

 $^{^{(1)}}$ Hysteresis voltage between Schmitt trigger switching levels. Based on characterization results, not tested in production.

⁽²⁾ Data guaranteed by design.

⁽³⁾ Data based on characterization results, not tested in production.

Figure 24: Typical VIL and VIH vs VDD @ 4 temperatures





Figure 25: Typical pull-up resistance vs VDD @ 4 temperatures



STM8S105xx Electrical characteristics

140 120 100 80 40 20 0 1 2 3 4 5 6 Voo [V]

Figure 26: Typical pull-up current vs VDD @ 4 temperatures

1. The pull-up is a pure resistor (slope goes through 0).

Table 39: Output driving current (standard ports)

Symbol	Parameter	Conditions	Min	Max	Unit
V _{OL}	Output low level with four pins sunk	$I_{IO} = 4 \text{ mA},$ $V_{DD} = 3.3 \text{ V}$		1.0 (1)	V
	Output low level with eight pins sunk	I_{IO} = 10 mA, V_{DD} = 5 V		2.0	
V _{OH}	Output high level with four pins sourced	$I_{IO} = 4 \text{ mA},$ $V_{DD} = 3.3 \text{ V}$	2.0 ⁽¹⁾		V
	Output high level with eight pins sourced	$I_{IO} = 10 \text{ mA},$ $V_{DD} = 5 \text{ V}$	2.4		

Notes:

Table 40: Output driving current (true open drain ports)

Symbol	Parameter	Conditions	Max	Unit
V_{OL}	Output low level with two pins sunk	$I_{IO} = 10 \text{ mA}, V_{DD} = 3.3 \text{ V}$	1.5 ⁽¹⁾	V
		$I_{IO} = 10 \text{ mA}, V_{DD} = 5 \text{ V}$	1.0	
		$I_{IO} = 20 \text{ mA}, V_{DD} = 5 \text{ V}$	2.0 (1)	

Table 41: Output driving current (high sink ports)

Symbol	Parameter	Conditions	Min	Max	Unit
V_{OL}	Output low level with four pins sunk	$I_{IO} = 10 \text{ mA},$		1.1 ⁽¹⁾	٧



 $[\]ensuremath{^{(1)}}$ Data based on characterization results, not tested in production

 $[\]ensuremath{^{(1)}}$ Data based on characterization results, not tested in production

Symbol	Parameter	Conditions	Min	Max	Unit
		$V_{DD} = 3.3 \text{ V}$			
	Output low level with eight pins sunk	$I_{IO} = 10 \text{ mA},$ $V_{DD} = 5 \text{ V}$		0.9	
	Output low level with four pins sunk	$I_{IO} = 20 \text{ mA},$ $V_{DD} = 5 \text{ V}$		1.6 (1)	
V _{OH}	Output high level with four pins sourced	$I_{IO} = 10 \text{ mA},$ $V_{DD} = 3.3 \text{ V}$	1.9 ⁽¹⁾		
	Output high level with eight pins sourced	$I_{IO} = 10 \text{ mA},$ $V_{DD} = 5 \text{ V}$	3.8		
	Output high level with four pins sourced	$I_{IO} = 20 \text{ mA},$ $V_{DD} = 5 \text{ V}$	2.9 ⁽¹⁾		

10.3.7 Typical output level curves

The following figures show typical output level curves measured with output on a single pin.




Figure 27: Typ. VOL @ VDD = 5 V (standard ports)

 $^{^{\}left(1\right) }$ Data based on characterization results, not tested in production

Figure 28: Typ. VOL @ VDD = 3.3 V (standard ports)




Figure 29: Typ. VOL @ VDD = 5 V (true open drain ports)




Figure 30: Typ. VOL @ VDD = 3.3 V (true open drain ports)




Figure 31: Typ. VOL @ VDD = 5 V (high sink ports)




Figure 32: Typ. VOL @ VDD = 3.3 V (high sink ports)




Figure 33: Typ. VDD - VOH @ VDD = 5 V (standard ports)





Figure 34: Typ. VDD - VOH @ VDD = 3.3 V (standard ports)




Electrical characteristics STM8S105xx

2 -40°C -25°C 1.75 -85°C 1.5 -125°C 1.5 -125

Figure 35: Typ. VDD - VOH @ VDD = 5 V (high sink ports)



Іон [mA]



10.3.8 Reset pin characteristics

Subject to general operating conditions for V_{DD} and T_{A} unless otherwise specified.

Table 42: NRST pin characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
$V_{IL(NRST)}$	NRST input low level voltage (1)		-0.3	-	0.3 x V _{DD}	V
V _{IH(NRST)}	NRST input high level voltage (1)	I _{OL} =2 mA	0.7 x V _{DD}	-	V _{DD} + 0.3	
$V_{OL(NRST)}$	NRST output low level voltage (1)		-	-	0.5	
R _{PU(NRST)}	NRST pull-up resistor (2)		30	55	80	kΩ
t _{IFP(NRST)}	NRST input filtered pulse (3)		-	1	75	ns

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t _{INFP(NRST)}	NRST input not filtered pulse (3)		500	-	-	
t _{OP(NRST)}	NRST output pulse (3)		20 15	-	-	μs

- $^{\left(1\right)}$ Data based on characterization results, not tested in production.
- $^{\left(2\right)}$ The R_{PU} pull-up equivalent resistor is based on a resistive transistor
- $\ensuremath{^{(3)}}$ Data guaranteed by design, not tested in production.

Figure 37: Typical NRST VIL and VIH vs VDD @ 4 temperatures




Figure 38: Typical NRST pull-up resistance vs VDD @ 4 temperatures




Figure 39: Typical NRST pull-up current vs VDD @ 4 temperatures

The reset network shown in the following figure protects the device against parasitic resets. The user must ensure that the level on the NRST pin can go below $V_{\text{IL}(NRST)}$ max. (see *Table 38: "I/O static characteristics"*), otherwise the reset is not taken into account internally.

For power consumption sensitive applications, the external reset capacitor value can be reduced to limit the charge/discharge current. If NRST signal is used to reset external circuitry, attention must be taken to the charge/discharge time of the external capacitor to fulfill the external devices reset timing conditions. Minimum recommended capacity is 100 nF.




Figure 40: Recommended reset pin protection

10.3.9 SPI serial peripheral interface

Unless otherwise specified, the parameters given in the following table are derived from tests performed under ambient temperature, f_{MASTER} frequency and V_{DD} supply voltage conditions. $t_{MASTER} = 1/f_{MASTER}$.

Refer to I/O port characteristics for more details on the input/output alternate function characteristics (NSS, SCK, MOSI, MISO).

Table 43: SPI characteristics

Symbol	Parameter	Conditions	Min	Max	Unit
f _{SCK} 1	SPI clock frequency	Master mode	0	8	MHz
$t_{c(SCK)}$		Slave mode	0	6	
$t_{r(SCK)} \\ t_{f(SCK)}$	SPI clock rise and fall time	Capacitive load: C = 30 pF		25	ns
t _{su(NSS)} ⁽¹⁾	NSS setup time	Slave mode	4 x t _{MASTER}		ns
t _{h(NSS)} ⁽¹⁾	NSS hold time	Slave mode	70		ns
$t_{\text{w(SCKH)}}^{(1)}$ $t_{\text{w(SCKL)}}^{(1)}$	SCK high and low time	Master mode	t _{SCK} /2 - 15	t _{SCK} /2 + 15	ns
t _{su(MI)} (1)	Data input setup time	Master mode	5		ns
t _{su(SI)} ⁽¹⁾	Data input setup time	Slave mode	5		ns
t _{h(MI)} (1)	Data input hold time	Master mode	7		ns
t _{h(SI)} ⁽¹⁾	Data input hold time	Slave mode	10		ns
t _{a(SO)} (1)(2)	Data output access time	Slave mode		3 x t _{MASTER}	ns
t _{dis(SO)} (1)(3)	Data output disable time	Slave mode	25		ns
t _{v(SO)} (1)	Data output valid time	Slave mode (after enable edge)		73	ns
t _{v(MO)} ⁽¹⁾	Data output valid time	Master mode (after enable edge)		36	ns
t _{h(SO)} ⁽¹⁾	Data output hold time	Slave mode (after enable edge)	28		ns
t _{h(MO)} ⁽¹⁾		Master mode (after enable edge)	12		ns

⁽¹⁾ Values based on design simulation and/or characterization results, and not tested in production.

⁽²⁾ Min time is for the minimum time to drive the output and the max time is for the maximum time to validate the data.

 $^{^{(3)}}$ Min time is for the minimum time to invalidate the output and the max time is for the maximum time to put the data in Hi-Z.

Electrical characteristics STM8S105xx






Figure 41: SPI timing diagram - slave mode and CPHA = 0





1. Measurement points are made at CMOS levels: $0.3 V_{DD}$ and $0.7 V_{DD}$.




Figure 43: SPI timing diagram - master mode(1)

1. Measurement points are made at CMOS levels: $0.3 V_{DD}$ and $0.7 V_{DD}$.

10.3.10 I2C interface characteristics

Table 44: I2C characteristics

Symbol	Parameter	Standard	mode I ² C	Fast mo	ode I ² C (1)	Unit
		Min ⁽²⁾	Max ⁽²⁾	Min ⁽²⁾	Max ⁽²⁾	
t _{w(SCLL)}	SCL clock low time	4.7		1.3		μs
t _{w(SCLH)}	SCL clock high time	4.0		0.6		μs
t _{su(SDA)}	SDA setup time	250		100		ns
t _{h(SDA)}	SDA data hold time	0 (3)		0 (4)	900 ⁽³⁾	ns
$t_{r(SDA)}$ $t_{r(SCL)}$	SDA and SCL rise time		1000		300	ns
t _{f(SDA)}	SDA and SCL fall time		300		300	ns
t _{h(STA)}	START condition hold time	4.0		0.6		μs
t _{su(STA)}	Repeated START condition setup time	4.7		0.6		μs
t _{su(STO)}	STOP condition setup time	4.0		0.6		μs
tw(STO:STA)	STOP to START condition time (bus free)	4.7		1.3		μs

Symbol	Parameter	Standard mode I ² C		Fast mo	de l ² C (1)	Unit
		Min (2) Max (2)		Min ⁽²⁾	Max ⁽²⁾	
C _b	Capacitive load for each bus line		400		400	pF

- (1) f_{MASTER}, must be at least 8 MHz to achieve max fast I²C speed (400kHz).
- $^{(2)}$ Data based on standard $\mathrm{I}^2\mathrm{C}$ protocol requirement, not tested in production.
- (3) The maximum hold time of the start condition has only to be met if the interface does not stretch the low time.
- ⁽⁴⁾ The device must internally provide a hold time of at least 300 ns for the SDA signal in order to bridge the undefined region of the falling edge of SCL.

 V_{DD} V_{DD} STM8S105xx $4.7 k\Omega$ 4.7kΩ 100 Ω -WWW SDA SCL 100 Ω START REPEATED START START ^tsu(STA) tf(SDA) ∤ tsu(SDA) tsu(STA:STO) STOP th(SDA) th(STA) ^tw(SCĻL) SCL ⊢^tsu(STO) tr(SCL) → tw(SCLH) + + t_{f(SCL)} ai15385b

Figure 44: Typical application with I2C bus and timing diagram (1)

Measurement points are made at CMOS levels: 0.3 x V_{DD} and 0.7 x V_{DD}

10.3.11 10-bit ADC characteristics

Subject to general operating conditions for V_{DDA}, f_{MASTER}, and T_A unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f _{ADC}	ADC clock frequency	V _{DDA} =2.95 to 5.5 V	1.0		4.0	MHz
		V _{DDA} =4.5 to 5.5 V	1.0		6.0	
V_{DDA}	Analog supply		3.0		5.5	V
V_{REF+}	Positive reference voltage		2.75 (1)		V_{DDA}	V
V_{REF}	Negative reference voltage		VSSA		0.5	V

Table 45: ADC characteristics

Symbol	Parameter	Conditions	Min	Min Typ N		Unit
					(1)	
V_{AIN}	Conversion voltage range (2)		VSSA		VDDA	V
		Devices with external V _{REF+} /V _{REF-} pins	V_{REF}		V_{REF+}	V
C _{ADC}	Internal sample and hold capacitor			3.0		pF
ts ⁽²⁾	Sampling time	f _{ADC} = 4 MHz		0.75		μs
		f _{ADC} = 6 MHz		0.5		
t _{STAB}	Wakeup time from standby			7.0		μs
t _{CONV}	Total conversion time (including	f _{ADC} = 4 MHz		3.5		μs
	sampling time, 10-bit resolution)	f _{ADC} = 6 MHz		2.33		μs
				14		1/f _{ADC}

Table 46: ADC accuracy with RAIN < 10 k Ω , VDDA= 5 V

Symbol	Parameter	Conditions	Тур	Max ⁽¹⁾	Unit
E _T	Total unadjusted error ⁽²⁾	$f_{ADC} = 2 MHz$	1.0	2.5	LSB
		f _{ADC} = 4 MHz	1.4	3.0	
		$f_{ADC} = 6 \text{ MHz}$	1.6	3.5	
E ₀	Offset error (2)	$f_{ADC} = 2 \text{ MHz}$	0.6	2.0	
		f _{ADC} = 4 MHz	1.1	2.5	
		$f_{ADC} = 6 \text{ MHz}$	1.2	2.5	
E _G	Gain error ⁽²⁾	$f_{ADC} = 2 MHz$	0.2	2.0	
		f _{ADC} = 4 MHz	0.6	2.5	
		$f_{ADC} = 6 \text{ MHz}$	0.8	2.5	
E _D	Differential linearity error (2)	$f_{ADC} = 2 MHz$	0.7	1.5	
		f _{ADC} = 4 MHz	0.7	1.5	
		f _{ADC} = 6 MHz	0.8	1.5	
E _L	Integral linearity error (2)	$f_{ADC} = 2 MHz$	0.6	1.5	
		f _{ADC} = 4 MHz	0.6	1.5	
		f _{ADC} = 6 MHz	0.6	1.5	

Notes:

⁽²⁾ ADC accuracy vs. negative injection current: Injecting negative current on any of the analog input pins should be avoided as this significantly reduces the accuracy of the conversion being performed on another analog input.



 $^{^{\}left(1\right) }$ Data guaranteed by design, not tested in production..

⁽²⁾ During the sample time the input capacitance C_{AIN} (3 pF max) can be charged/discharged by the external source. The internal resistance of the analog source must allow the capacitance to reach its final voltage level within $t_{\rm S}$. After the end of the sample time $t_{\rm S}$, changes of the analog input voltage have no effect on the conversion result. Values for the sample clock $t_{\rm S}$ depend on programming.

 $^{^{\}left(1\right)}$ Data based on characterization results, not tested in production.

It is recommended to add a Schottky diode (pin to ground) to standard analog pins which may potentially inject negative current. Any positive injection current within the limits specified for $I_{INJ(PIN)}$ and $\Sigma I_{INJ(PIN)}$ in the I/O port pin characteristics section does not affect the ADC accuracy.

Symbol	Parameter	Conditions	Тур	Max ⁽¹⁾	Unit
E _T	Total unadjusted error (2)	f _{ADC} = 2 MHz	1.1	2.0	LSB
		$f_{ADC} = 4 \text{ MHz}$	1.6	2.5	
E ₀	Offset error (2)	f _{ADC} = 2 MHz	0.7	1.5	
		$f_{ADC} = 4 \text{ MHz}$	1.3	2.0	
E _G	Gain error ⁽²⁾	f _{ADC} = 2 MHz	0.2	1.5	
		$f_{ADC} = 4 \text{ MHz}$	0.5	2.0	
E _D	Differential linearity error (2)	f _{ADC} = 2 MHz	0.7	1.0	
		$f_{ADC} = 4 \text{ MHz}$	0.7	1.0	
E _L	Integral linearity error (2)	f _{ADC} = 2 MHz	0.6	1.5	
		f _{ADC} = 4 MHz	0.6	1.5	

Table 47: ADC accuracy with RAIN < 10 k Ω RAIN, VDDA = 3.3 V

Notes:

⁽²⁾ ADC accuracy vs. negative injection current: Injecting negative current on any of the analog input pins should be avoided as this significantly reduces the accuracy of the conversion being performed on another analog input. It is recommended to add a Schottky diode (pin to ground) to standard analog pins which may potentially inject negative current. Any positive injection current within the limits specified for I_{INJ(PIN)} and ΣI_{INJ(PIN)} in Section 13.3.6: "I/O port pin characteristics" does not affect the ADC accuracy.




Figure 45: ADC accuracy characteristics

- 1. Example of an actual transfer curve.
- 2. The ideal transfer curve

 $^{^{\}left(1\right)}$ Data based on characterization results, not tested in production.

STM8S105xx Electrical characteristics

3. End point correlation line

 E_T = Total unadjusted error: maximum deviation between the actual and the ideal transfer curves.


 E_O = Offset error: deviation between the first actual transition and the first ideal one.

E_G = Gain error: deviation between the last ideal transition and the last actual one.

 $\mathsf{E}_\mathsf{D} = \mathsf{Differential}$ linearity error: maximum deviation between actual steps and the ideal one.

 E_L = Integral linearity error: maximum deviation between any actual transition and the end point correlation line.

Figure 46: Typical application with ADC



10.3.12 EMC characteristics

Susceptibility tests are performed on a sample basis during product characterization.

10.3.12.1 Functional EMS (electromagnetic susceptibility)

While executing a simple application (toggling 2 LEDs through I/O ports), the product is stressed by two electromagnetic events until a failure occurs (indicated by the LEDs).

- FESD: Functional electrostatic discharge (positive and negative) is applied on all pins
 of the device until a functional disturbance occurs. This test conforms with the IEC
 61000-4-2 standard.
- FTB: A burst of fast transient voltage (positive and negative) is applied to V_{DD} and V_{SS} through a 100 pF capacitor, until a functional disturbance occurs. This test conforms to IEC 61000-4-4 standard.

A device reset allows normal operations to be resumed. Test results are given in table below based on the EMS levels and classes defined in application note AN1709 (EMC design guide for ST Microcontrollers).

10.3.12.2 Designing hardened software to avoid noise problems

EMC characterization and optimization are performed at component level with a typical application environment and simplified MCU software. It should be noted that good EMC performance is highly dependent on the user application and the software in particular.

Therefore it is recommended that the user applies EMC software optimization and prequalification tests in relation with the EMC level requested for his application.

Software recommendations

The software flowchart must include the management of runaway conditions such as:

- Corrupted program counter
- Unexpected reset
- Critical data corruption (control registers...)



Prequalification trials

Most of the common failures (unexpected reset and program counter corruption) can be recovered by applying a low state on the NRST pin or the oscillator pins for 1 second.

To complete these trials, ESD stress can be applied directly on the device, over the range of specification values. When unexpected behavior is detected, the software can be hardened to prevent unrecoverable errors occurring. See application note AN1015 (Software techniques for improving microcontroller EMC performance).

Table 48: EMS data

Symbol	Parameter	Conditions	Level/ class
V_{FESD}	Voltage limits to be applied on any I/O pin to induce a functional disturbance	V _{DD} = 3.3 V, T _A = 25 °C, f _{MASTER} = 16 MHz (HSI clock), conforming to IEC 61000-4-2	2/B ⁽¹⁾
		V_{DD} = 5 V, T_A = 25 °C, f_{MASTER} = 16 MHz, conforming to IEC 1000-4-2	
V _{EFTB}	Fast transient voltage burst limits to be applied through 100 pF on V _{DD} and V _{SS} pins to induce a functional disturbance	V _{DD} = 3.3 V, T _A = 25 °C ,f _{MASTER} = 16 MHz (HSI clock),conforming to IEC 61000-4-4	4/A ⁽¹⁾
		V_{DD} = 5 V, T_A = 25 °C , f_{MASTER} = 16 MHz,conforming to IEC 1000-4-4	

Notes:

10.3.12.3 Electromagnetic interference (EMI)

Emission tests conform to the IEC61967-2 standard for test software, board layout and pin loading.

Table 49: EMI data

Symbol	Parameter	Conditions				
		General conditions	Monitored	Max f _{Hs}	SE/f _{CPU} ⁽¹⁾	
			frequency band	8 MHz/ 8 MHz	8 MHz/ 16 MHz	
S _{EMI}	Peak level	$V_{DD} = 5 \text{ V},$ $T_A = +25 \text{ °C},$	0.1 MHz to 30 MHz	13	14	dΒμV
		LQFP48 package conforming to	30 MHz to 130 MHz	23	19	
		IEC61967-2	130 MHz to 1 GHz	-4.0	-4.0	
	SAE EMI level			2.0	1.5	_

Notes:

⁽¹⁾ Data obtained with HSI clock configuration, after applying HW recommendations described in AN2860 (EMC guidelines for STM8S microcontrollers).

⁽¹⁾ Data based on characterization results, not tested in production.

10.3.12.4 Absolute maximum ratings (electrical sensitivity)

Based on two different tests (ESD and LU) using specific measurement methods, the product is stressed in order to determine its performance in terms of electrical sensitivity. For more details, refer to the application note AN1181.

10.3.12.5 Electrostatic discharge (ESD)

Electrostatic discharges (3 positive then 3 negative pulses separated by 1 second) are applied to the pins of each sample according to each pin combination. The sample size depends on the number of supply pins in the device (3 parts*(n+1) supply pin). This test conforms to the JESD22-A114A/A115A standard. For more details, refer to the application note AN1181.

Table 50: ESD absolute maximum ratings

Symbol	Ratings	Conditions	Class	Maximum value ⁽¹⁾	Unit
V _{ESD(HBM)}	Electrostatic discharge voltage (Human body model)	T _A = +25°C, conforming to JESD22-A114	Α	2000	V
V _{ESD(CDM)}	Electrostatic discharge voltage (Charge device model)	arge T _A =+25°C, conforming		1000	V

Notes:

10.3.12.6 Static latch-up

Two complementary static tests are required on 10 parts to assess the latch-up performance:

- A supply overvoltage (applied to each power supply pin)
- A current injection (applied to each input, output and configurable I/O pin) is performed on each sample.

This test conforms to the EIA/JESD 78 IC latch-up standard. For more details, refer to the application note AN1181.

Table 51: Electrical sensitivities

Symbol	Parameter	Conditions	Class ⁽¹⁾
LU	Static latch-up class	T _A = +25 °C	Α
		T _A = +85 °C	Α
		T _A = +125 °C	А

Notes:



⁽¹⁾ Data based on characterization results, not tested in production

⁽¹⁾ Class description: A Class is a STMicroelectronics internal specification. All limits are higher than JEDEC specifications, that means when a device belongs to class A it exceeds JEDEC standard. B class strictly covers all the JEDEC criteria (international standard).

11 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

11.1 48-pin LQFP package mechanical data

Figure 47: 48-pin low profile quad flat package (7 x 7)




Table 52: 48-pin low profile quad flat package mechanical data

Dim.		mm		inches ⁽¹⁾		
	Min	Тур	Max	Min	Тур	Max
Α			1.600			0.0630
A1	0.050		0.150	0.0020		0.0059
A2	1.350	1.400	1.450	0.0531	0.0551	0.0571
b	0.170	0.220	0.270	0.0067	0.0087	0.0106
С	0.090		0.200	0.0035		0.0079
D	8.800	9.000	9.200	0.3465	0.3543	0.3622
D1	6.800	7.000	7.200	0.2677	0.2756	0.2835
D3		5.500			0.2165	
Е	8.800	9.000	9.200	0.3465	0.3543	0.3622
E1	6.800	7.000	7.200	0.2677	0.2756	0.2835
E3		5.500			0.2165	
е		0.500			0.0197	

STM8S105xx Package information

Dim.	mm			Dim. mm inches ⁽¹⁾			
	Min	Тур	Max	Min	Тур	Max	
L	0.450	0.600	0.750	0.0177	0.0236	0.0295	
L1		1.000			0.0394		
k	0°	3.5°	7.0°	0°	3.5°	7.0°	
ccc			0.080			0.0031	

Notes:

11.2 44-pin LQFP package mechanical data

Figure 48: 44-pin low profile quad flat package




Table 53: 44-pin low profile quad flat package mechanical data

Dim.	mm				inches (1)	
	Min	Тур	Max	Min	Тур	Max
Α			1.600			0.0630
A1	0.050		0.150	0.0020		0.0059
A2	1.350	1.400	1.450	0.0531	0.0551	0.0571
b	0.300	0.370	0.450	0.0118	0.0146	0.0177
С	0.090		0.200	0.0035		0.0079
D	11.800	12.000	12.200	0.4646	0.4724	0.4803
D1	9.800	10.000	10.200	0.3858	0.3937	0.4016
D3		8.000			0.3150	
Е	11.800	12.000	12.200	0.4646	0.4724	0.4803
E1	9.800	10.000	10.200	0.3858	0.3937	0.4016

 $^{^{(1)}}$ Values in inches are converted from mm and rounded to 4 decimal digits

Dim.	mm			inches ⁽¹⁾		
	Min	Тур	Max	Min	Тур	Max
E3		8.000			0.3150	
е		0.800			0.0315	
L	0.450	0.600	0.750	0.0177	0.0236	0.0295
L1		1.000			0.0394	
k	0.0°	3.5°	7.0°	0.0°	3.5°	7.0°
ccc			0.100			0.0039

11.3 32-pin LQFP package mechanical data

Figure 49: 32-pin low profile quad flat package (7 x 7)




Table 54: 32-pin low profile quad flat package mechanical data

Dim.	mm			inches (1)		
	Min	Тур	Max	Min	Тур	Max
А			1.600			0.0630
A1	0.050		0.150	0.0020		0.0059
A2	1.350	1.400	1.450	0.0531	0.0551	0.0571
b	0.300	0.370	0.450	0.0118	0.0146	0.0177
С	0.090		0.200	0.0035		0.0079
D	8.800	9.000	9.200	0.3465	0.3543	0.3622
D1	6.800	7.000	7.200	0.2677	0.2756	0.2835
D3		5.600			0.2205	


 $^{^{(1)}}$ Values in inches are converted from mm and rounded to 4 decimal digits

Dim.	mm		Dim. m			inches (1)	
	Min	Тур	Max	Min	Тур	Max	
Е	8.800	9.000	9.200	0.3465	0.3543	0.3622	
E1	6.800	7.000	7.200	0.2677	0.2756	0.2835	
E3		5.600			0.2205		
е		0.800			0.0315		
L	0.450	0.600	0.750	0.0177	0.0236	0.0295	
L1		1.000			0.0394		
k	0°	3.5°	7.0°	0°	3.5°	7.0°	
ccc			0.100			0.0039	

(1) Values in inches are converted from mm and rounded to 4 decimal digits

11.4 32-lead UFQFPN package mechanical data

Figure 50: 32-lead, ultra-thin, fine pitch quad flat no-lead package (5 x 5)



- 1. Drawing is not to scale.
- 2. All leads/pads should be soldered to the PCB to improve the lead/pad solder joint life.
- 3. There is an exposed die pad on the underside of the UFQFPN package. It is recommended to connect and solder this backside pad to PCB ground.
- 4. Dimensions are in millimeters.


Table 55: 32-lead ultra-thin fine pitch quad flat no-lead package mechanical data

Dim.	mm			inches ⁽¹⁾		
	Min	Тур	Max	Min	Тур	Max
Α	0.500	0.550	0.600	0.0197	0.0217	0.0236
A1	0	0.020	0.050		0.0008	0.0020
А3		0.200			0.0079	
b	0.180	0.250	0.300	0.0071	0.0098	0.0118
D	4.900	5.000	5.100	0.1909	0.1969	0.2028
D2	3.200	3.450	3.700	0.1260		0.1457
Е	4.900	5.000	5.100	0.1909	0.1969	0.2028

Dim.	mm		im. mm inches		inches ⁽¹⁾	
	Min	Тур	Max	Min	Тур	Max
E2	3.200	3.450	3.700	0.1260	0.1358	0.1457
е		0.500			0.0197	
L	0.300	0.400	0.500	0.0118	0.0157	0.0197
ddd			0.080			0.0031

11.5 SDIP32 package mechanical data

Figure 51: 32-lead shrink plastic DIP (400 ml) package



 $^{^{\}mbox{\scriptsize (1)}}$ Values in inches are converted from mm and rounded to 4 decimal digits.

Table 56: 32-lead shrink plastic DIP (400 ml) package mechanical data

Dim.		mm		inches ⁽¹⁾		
	Min	Тур	Max	Min	Тур	Max
Α	3.556	3.759	5.080	0.1400	0.1480	0.2000
A1	0.508			0.0200		
A2	3.048	3.556	4.572	0.1200	0.1400	0.1800
В	0.356	0.457	0.584	0.0140	0.0180	0.0230
B1	0.762	1.016	1.397	0.0300	0.0400	0.0550
С	0.203	0.254	0.356	0.0079	0.0100	0.0140
D	27.430	27.940	28.450	1.0799	1.1000	1.1201
Е	9.906	10.410	11.050	0.3900	0.4098	0.4350
E1	7.620	8.890	9.398	0.3000	0.3500	0.3700
е		1.778			0.0700	
eA		10.160			0.4000	
eB			12.700			0.5000
L	2.540	3.048	3.810	0.1000	0.1200	0.1500

 $^{^{(1)}}$ Values in inches are converted from mm and rounded to 4 decimal digits

12 Thermal characteristics

The maximum chip junction temperature (T_{Jmax}) must never exceed the values given in Section 7.10: "TIM1 - 16-bit advanced control timer"

The maximum chip-junction temperature, T_{Jmax} , in degrees Celsius, may be calculated using the following equation:

$$T_{Jmax} = T_{Amax} + (P_{Dmax} \times \Theta_{JA})$$

Where:

- T_{Amax} is the maximum ambient temperature in °C
- Θ_{JA} is the package junction-to-ambient thermal resistance in ° C/W
- P_{Dmax} is the sum of P_{INTmax} and $P_{I/Omax}$ ($P_{Dmax} = P_{INTmax} + P_{I/Omax}$)
- P_{INTmax} is the product of I_{DD} andV_{DD}, expressed in Watts. This is the maximum chip internal power.
- $P_{I/Omax}$ represents the maximum power dissipation on output pinsWhere: $P_{I/Omax} = \Sigma$ $(V_{OL}*I_{OL}) + \Sigma((V_{DD}-V_{OH})*I_{OH})$, taking into account the actual V_{OL}/I_{OL} and V_{OH}/I_{OH} of the I/Os at low and high level in the application.

Symbol	Parameter	Value	Unit
Θ_{JA}	Thermal resistance junction-ambient LQFP 48 - 7 x 7 mm	57	°C/W
Θ_{JA}	Thermal resistance junction-ambient LQFP 44 - 10 x 10 mm	54	°C/W
ΘЈΑ	Thermal resistance junction-ambient LQFP 32 - 7 x 7 mm	60	°C/W
Θ_{JA}	Thermal resistance junction-ambient UFQFPN 32 - 5 x 5 mm	38	°C/W
ΘЈΑ	Thermal resistance junction-ambient SDIP 32 - 400 mils	60	°C/W

Table 57: Thermal characteristics (1)

1. Thermal resistances are based on JEDEC JESD51-2 with 4-layer PCB in a natural convection environment.

12.1 Reference document

JESD51-2 integrated circuits thermal test method environment conditions - natural convection (still air). Available from www.jedec.org.

12.2 Selecting the product temperature range

When ordering the microcontroller, the temperature range is specified in the order code.

The following example shows how to calculate the temperature range needed for a given application.

Assuming the following application conditions:

- Maximum ambient temperature T_{Amax} = 82 °C (measured according to JESD51-2)
- $I_{DDmax} = 15 \text{ mA}, V_{DD} = 5.5 \text{ V}$

Maximum 8 standard I/Os used at the same time in output at low level with $I_{OL} = 10$ mA, $V_{OL} = 2$ V

- Maximum 4 high sink I/Os used at the same time in output at low level with I_{OL} = 20 mA, V_{OL}= 1.5 V
- Maximum 2 true open drain I/Os used at the same time in output at low level with $I_{OL} = 20$ mA, $V_{OL} = 2$ V

 $P_{INTmax} = 15 \text{ mA } x 5.5 \text{ V} = 82.5 \text{ mW}$

 $P_{IOmax} = (10 \text{ mA x } 2 \text{ V x 8}) + (20 \text{ mA x } 2 \text{ V x 2}) + (20 \text{ mA x } 1.5 \text{ V x 4}) = 360 \text{ mW}$

This gives: $P_{INTmax} = 82.5 \text{ mW}$ and $P_{IOmax} 360 \text{ mW}$:

 $P_{Dmax} = 82.5 \text{ mW} + 360 \text{ mW}$

Thus: $P_{Dmax} = 443 \text{ mW}$


 T_{Jmax} for LQFP32 can be calculated as follows, using the thermal resistance Θ_{JA} :

$$T_{Jmax} = 82^{\circ} C + (60^{\circ} C/W \times 443 \text{ mW}) = 82^{\circ} C + 27^{\circ} C = 109^{\circ} C$$

This is within the range of the suffix 3 version parts (-40 < T_J < 131° C). In this case, parts must be ordered at least with the temperature range suffix 3.

13 Ordering information

Figure 52: STM8S105xx access line ordering information scheme



 For a list of available options (e.g. memory size, package) and orderable part numbers or for further information on any aspect of this device, please go to www.st.com or contact the ST sales office nearest to you.

14 STM8S105 FASTROM microcontroller option list

(last update: September 2010)

Customer	
Address	
Contact	
Phone no.	
Reference FASTROM code ⁽¹⁾	

Notes:

Preferable format for programing code is .Hex (.s19 is accepted)

If data EEPROM programing is required, a separate file must be sent with the requested data.



See the option byte section in the datasheet for authorized option byte combinations and a detailed explanation.

Device type/memory size/package (check only one option)

FASTROM device	16 Kbyte	32 Kbyte
LQFP32	[] STM8S105K4	[] STM8S105K6
LQFP44	[] STM8S105S4	[]STM8S105S6
LQFP48	[]STM8S105C4	[] STM8S105C6

Conditioning (check only one option)

[] Tape & reel or [] Tray

Special marking (check only one option)

[] No [] Yes

Authorized characters are letters, digits, '.', '-', '/' and spaces only. Maximum character counts are:

LQFP32: 2 lines of 7 characters max: "_____" and "_____"

LQFP44: 2 lines of 7 characters max: "_____" and "_____"

LQFP48: 2 lines of 8 characters max: "_____" and "_____"

Temperature range

[]-40°C to +85°C or []-40°C to +125°C

⁽¹⁾FASTROM code name is assigned by STMicroelectronics.

Padding value for unused program memory (check only one option)

[] 0xFF	Fixed value
[] 0x83	TRAP instruction opcode
[] 0x75	Illegal opcode (causes a reset when executed)

OPT0 memory readout protection (check only one option)

[] Disable or [] Enable

OPT1 user boot code area (UBC)

0x(_ _) fill in the hexadecimal value, referring to the datasheet and the binary format below.

UBC, bit0	[] 0: Reset [] 1: Set
UBC bit1	[] 0: Reset [] 1: Set
UBC bit2	[] 0: Reset [] 1: Set
UBC bit3	[] 0: Reset [] 1: Set
UBC bit4	[] 0: Reset [] 1: Set
UBC bit5	[] 0: Reset [] 1: Set

OPT2 alternate function remapping

AFR0 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port D3 alternate function = ADC_ETR	
AFR1 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port A3 alternate function = TIM3_CH1, port D2 alternate function = TIM2_CH3.	
AFR2 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port D0 alternate function = CLK_CCO. If both AFR2 and AFR3 are activated, AFR2 option has priority over AFR3.	
AFR3 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port D0 alternate function = TIM1_BKIN.	

AFR4 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port D7 alternate function = TIM1_CH4.
AFR5 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port B3 alternate function = TIM1_ETR, port B2 alternate function = TIM1_NCC3, port B1 alternate function = TIM1_CH2N, port B0 alternate function = TIM1_CH1N.
AFR6 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description [] 1: Port B5 alternate function = I2C_SDA, port B4 alternate function = I2C_SCL.
AFR7 (check only one option)	[] 0: Remapping option inactive. Default alternate functions used. Refer to pinout description. [] 1: Port D4 alternate function = BEEP.

OPT3 watchdog

WWDG_HALT (check only one option)	[] 0: No reset generated on halt if WWDG active. [] 1: Reset generated on halt if WWDG active.
WWDG_HW (check only one option)	[] 0: WWDG activated by software. [] 1: WWDG activated by hardware.
IWDG_HW (check only one option)	[] 0: IWDG activated by software. [] 1: IWDG activated by hardware.
LSI_EN (check only one option)	[] 0: LSI clock is not available as CPU clock source. [] 1: LSI clock is available as CPU clock source.
HSITRIM (check only one option)	[] 0: 3-bit trimming supported in CLK_HSITRIMR register. [] 1: 4-bit trimming supported in CLK_HSITRIMR register.

OPT4 wakeup

PRSC	[] for 16 MHz to 128 kHz prescaler.
(check only one option)	[] for 8 MHz to 128 kHz prescaler.
	[] for 4 MHz to 128 kHz prescaler.
CKAWUSEL	[] 0: LSI clock source selected for AWU.
(check only one option)	[] 1: HSE clock with prescaler selected as clock source for AWU.
EXTCLK	[] 0: External crystal connected to OSCIN/OSCOUT.
(check only one option)	[] 1: External clock signal on OSCIN.

OPT5 crystal oscillator stabilization HSECNT (check only one option)

[] 2048 HSE cycles

[] 128 HSE cycles

[] 8 HSE cycles

[] 0.5 HSE cycles

OPT6 is reserved

OPT7 is reserved

OPTBL bootloader option byte (check only one option)

Refer to the UM0560 (STM8L/S bootloader manual) for more details.

- [] Disable (00h)
- [] Enable (55h)

Comments:	
Supply operating range in the application	
Notes:	
Date:	
Signature:	

15 STM8 development tools

Development tools for the STM8 microcontrollers include the full-featured STice emulation system supported by a complete software tool package including C compiler, assembler and integrated development environment with high-level language debugger. In addition, the STM8 is to be supported by a complete range of tools including starter kits, evaluation boards and a low-cost in-circuit debugger/programmer.

15.1 Emulation and in-circuit debugging tools

The STice emulation system offers a complete range of emulation and in-circuit debugging features on a platform that is designed for versatility and cost-effectiveness. In addition, STM8 application development is supported by a low-cost in-circuit debugger/programmer.

The STice is the fourth generation of full featured emulators from STMicroelectronics. It offers new advanced debugging capabilities including profiling and coverage to help detect and eliminate bottlenecks in application execution and dead code when fine tuning an application.

In addition, STice offers in-circuit debugging and programming of STM8 microcontrollers via the STM8 single wire interface module (SWIM), which allows non-intrusive debugging of an application while it runs on the target microcontroller.

For improved cost effectiveness, STice is based on a modular design that allows you to order exactly what you need to meet your development requirements and to adapt your emulation system to support existing and future ST microcontrollers.

STice key features

- Occurrence and time profiling and code coverage (new features)
- Advanced breakpoints with up to 4 levels of conditions
- Data breakpoints
- Program and data trace recording up to 128 KB records
- Read/write on the fly of memory during emulation
- In-circuit debugging/programming via SWIM protocol
- 8-bit probe analyzer
- 1 input and 2 output triggers
- Power supply follower managing application voltages between 1.62 to 5.5 V
- Modularity that allows you to specify the components you need to meet your development requirements and adapt to future requirements
- Supported by free software tools that include integrated development environment (IDE), programming software interface and assembler for STM8.

15.2 Software tools

STM8 development tools are supported by a complete, free software package from STMicroelectronics that includes ST Visual Develop (STVD) IDE and the ST Visual Programmer (STVP) software interface. STVD provides seamless integration of the Cosmic and Raisonance C compilers for STM8, which are available in a free version that outputs up to 16 Kbytes of code.

15.2.1 STM8 toolset

STM8 toolset with STVD integrated development environment and STVP programming software is available for free download at www.st.com/mcu. This package includes:

ST Visual Develop - Full-featured integrated development environment from ST, featuring

- Seamless integration of C and ASM toolsets
- Full-featured debugger
- Project management
- Syntax highlighting editor
- Integrated programming interface
- Support of advanced emulation features for STice such as code profiling and coverage

ST Visual Programmer (STVP) – Easy-to-use, unlimited graphical interface allowing read, write and verify of your STM8 microcontroller's Flash program memory, data EEPROM and option bytes. STVP also offers project mode for saving programming configurations and automating programming sequences.

15.2.2 C and assembly toolchains

Control of C and assembly toolchains is seamlessly integrated into the STVD integrated development environment, making it possible to configure and control the building of your application directly from an easy-to-use graphical interface.

Available toolchains include:

- **Cosmic C compiler for STM8** Available in a free version that outputs up to 16 Kbytes of code. For more information, see www.cosmic-software.com.
- **Raisonance C compiler for STM8** Available in a free version that outputs up to 16 Kbytes of code. For more information, see www.raisonance.com.
- **STM8 assembler linker** Free assembly toolchain included in the STVD toolset, which allows you to assemble and link your application source code.

15.3 Programming tools

During the development cycle, STice provides in-circuit programming of the STM8 Flash microcontroller on your application board via the SWIM protocol. Additional tools are to include a low-cost in-circuit programmer as well as ST socket boards, which provide dedicated programming platforms with sockets for programming your STM8.

For production environments, programmers will include a complete range of gang and automated programming solutions from third-party tool developers already supplying programmers for the STM8 family.



Revision history STM8S105xx

16 Revision history

Table 58: Document revision history

Date	Revision	Changes
05-Jun- 2008	1	Initial release.
23-Jun- 2008	2	Corrected number of high sink outputs to 9 in I/Os on Section 3: "Features". Updated part numbers in Table 2: "STM8S105xx access line features".
12-Aug- 2008	3	Updated part numbers in <i>Table 2: "STM8S105xx access line features"</i> . USART renamed UART1, LINUART renamed UART2. Added Table 7: Pin-to-pin comparison of pin 7 to 12 in 32-pin access line devices.
17-Sep- 2008	4	Removed STM8S102xx and STM8S104xx root part numbers corresponding to devices without data EEPROM. Updated STM8S103 pinout in Section 5.2 on page 29. Added low and medium density Flash memory categories. Added Note 1 in Table 17: "Current characteristics". Updated Table 12: "Option bytes".
05-Feb- 2009	5	Updated STM8S103 pinout in Section 5.2 on page 29 Updated number of High Sink I/Os in pinout. TSSOP20 pinout modified (PD4 moved to pin 1 etc.) Added WFQFN20 package Updated Section 11: "Option bytes". Added Section 4: "Introduction".
27-Feb- 2009	6	Removed STM8S103x products (separate STM8S103 datasheet created) Updated Section 4: "Introduction".
12-May- 2009	7	Added SDIP32 silhouette and package to Section 3: "Features" and Section 14.5: "SDIP32 package mechanical data"; updated Section 8: "Pinout and pin description". Updated V _{DD} range (2.95 V to 5.5 V) on Section 3: "Features". Amended name of package VQFPN32 Added Table 5 on page 22. Updated Section 7.8: "Auto wakeup counter". Updated pins 25, 30, and 31 in Section 8: "Pinout and pin description". Removed Table 7: Pin-to-pin comparison of pin 7 to 12 in 32-pin access line devices. Added Table 14: "Description of alternate function remapping bits [7:0] of OPT2". Section 4: "Introduction": Updated VCAP specifications; updated Table 15, Table 18, Table 20, Table 21, Table 22, Table 23, Table 24, Table 25, Table 26, Table 27, Table 29, Table 35, and Table 42; added current consumption curves; removed Figure 20: typical HSE frequency vs fcpu @ 4 temperatures; updated Figure 13, Figure 14, Figure 15, Figure 16 and Figure 17; modified HSI accuracy in Table 33; added Figure 44; modified fSCK, tV(SO) and tV(MO) in Table 42; updated figures and tables of High speed internal RC oscillator (HSI); replaced Figure 23, Figure 24, Figure 26, and Figure 39. Section 14: "Package information": Updated Table 57: "Thermal

STM8S105xx Revision history

Date	Revision	Changes
Date	Kevision	characteristics(1)" and removed Table 57: Junction temperature range.
		Updated Figure 52: "STM8S105xx access line ordering information scheme".
10-Jun- 2009	8	Document status changed from "preliminary data" to "datasheet".
		Standardized name of the VFQFPN package.
		Removed 'wpu' from I2C pins in Section 8: "Pinout and pin description"
21-Apr-	9	Added UFQFPN32 package silhouette to the title page.
2010		Section 3: "Features": added unique ID.
		Section 7.4: "Flash program and data EEPROM memory": updated bit positions for TIM2 and TIM3.
		Section 7.9: "Beeper": added information about availability of the beeper output port through option bit AFR7.
		Section 7.13: "Analog-to-digital converter (ADC1)": added a note concerning additional AIN12 analog input.
		Section 8.1: "STM8S105 pinouts and pin description": added UFQFPN32 package details; updated default alternate function of PB2/AIN2[TIM1_CH3N] pin in the "Pin description for STM8S105 microcontrollers" table.
		Section 11: "Option bytes": added description of STM8L bootloader option bytes to the option byte description table.
		Added Section 4: "Introduction"
		Section 7.10: "TIM1 - 16-bit advanced control timer": added introductory text; removed low power dissipation condition for T_A , replaced " C_{EXT} " by "VCAP", and added ESR and ESL data in table "general operating conditions".
		Section 13.3.2.4: "Total current consumption in halt mode": replaced max value of $I_{DD(H)}$ at 85 °C from 20 μ A to 25 μ A for the condition "Flash in powerdown mode, HSI clock after wakeup in the table "total current consumption in halt mode at $V_{DD} = 5$ V.
		Section 13.3.2.5: "Low power mode wakeup times": added first condition (0 to 16 MHz) for the twu(WFI) parameter in the table "wakeup times".
		Section 13.3.4: "Internal clock sources and timing characteristics": In the table "HSI oscillator characteristics", replaced min and max values of "ACC _{HSI} factory calibrated parameter" and removed footnote 4 concerning further characterization of results.
		Section 13.3.12.1: "Functional EMS (electromagnetic susceptibility)": IEC 1000 replaced with IEC 61000.
		Section 13.3.12.2: "Designing hardened software to avoid noise problems": IEC 1000 replaced with IEC 61000.
		Section 13.3.12.3: "Electromagnetic interference (EMI)": SAE J 1752/3 replaced with IEC61967-2.
		Section 7.7: "Watchdog timers": Replaced the thermal resistance junction ambient temperature of LQFP32 7X7 mm from 59 °C to 60 °C in the thermal characteristics table.
		Added Section 6: "Block diagram".
		Added Section 17: "STM8S105 FASTROM microcontroller option list".
21-Sep- 2010	10	Table 5: "Legend/abbreviations for pinout tables ": updated "reset state"; removed "HS", (T), and "[]".
		Table 6: "Pin description for STM8S105 microcontrollers": added footnotes to the PF4 and PD1 pins.
		Table 8: "I/O port hardware register map": changed reset status of Px_IDR from 0x00 to 0xXX.
		Table 9: "General hardware register map": Standardized all address and reset state values; updated the reset state values of the RST_SR, CLK_SWCR, CLK_HSITRIMR, CLK_SWIMCCR, IWDG_KR, UART2_DR, and ADC_DRx



Revision history STM8S105xx

Date	Revision	Changes
		registers; replaced reserved address "0x00 5248" with the UART2_CR5.
		Figure 40: "Recommended reset pin protection": replaced 0.01 μF with 0.1 μF
		Updated Figure 44: "Typical application with I2C bus and timing diagram (1)".
		Updated footnote 1 in Table 46: ADC accuracy with RAIN < 10 k Ω , VDDA= 5V and Table 47: ADC accuracy with RAIN < 10 k Ω RAIN, VDDA=3.3V.
		Section 17: "STM8S105 FASTROM microcontroller option list": removed bits 6 and 7 from OPT1 user boot code area (UBC); added "disable" to 00h and "enable" to 55h of OPTBL bootloader option byte.
		VFQFPN Package Mechanical datas : replaced note 1 and added note 2.
04-Apr-	11	Removed VFQFPN32 package.
2012		Modified Section 5: "Description".
		Remove weak pull-up input for PE1 and PE2 in <i>Table 6: "Pin description for STM8S105 microcontrollers"</i>
		Updated Table 11: "Interrupt mapping" for TIM2 and TIM4.
		Updated notes related to V _{CAP} in <i>Table 19: "General operating conditions"</i> .
		Added values of t_R/t_F for 50 pF load capacitance, and updated note in <i>Table 38: "I/O static characteristics"</i> .
		Updated typical and maximum values of R _{PU} in <i>Table 38: "I/O static characteristics"</i> and <i>Table 42: "NRST pin characteristics"</i> .
		Changed SCK input to SCK output in Section 13.3.9: "SPI serial peripheral interface"
		Added Θ_{JA} for UFQFPN32 and SDIP32 in <i>Table 57: "Thermal characteristics(1)"</i> , and updated <i>Section 7.9: "Beeper"</i>
28-Jun- 2012	12	Added UFQFPN package thickness in Figure 52: "STM8S105xx access line ordering information scheme".
7-Feb-	13	UART2_CK mapped to correct pin (pin 24) in Figure 4: "LQFP 44-pin pinout".
2014		Reserved area updated in <i>Table 12: "Option bytes "</i> .
		Package Information updated in <i>Table 55: "32-lead ultra-thin fine pitch quad flat no-lead package mechanical data"</i> .

STM8S105xx Disclaimer

17 Disclaimer

Please Read Carefully

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2014 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain -Sweden - Switzerland - United Kingdom - United States of America

www.st.com

