



FOR JO2 TO 214 WIRE INSULATION DIA.
TONGUE MATERIAL THK = .039 ± .002

TABLE II

50845-2	.197	.10	50845-3	
50845-1	.171	.8	50845-4	OBSELETE
50845	.145	.6	50845-3	
PART NO.	"A"	"B"	PART NO. ON TAPE	

AMP 1470-1 REV (5/68) 4

REVISIONS

ZONE	LTN	DESCRIPTION	DATE	APPROVED
B	REDRAWN & REV	P-6077	7-20-69	REV
C	REVISED	PC-5579	10-8-70	REV
D	REVISED	PC-5578	12-6-71	REV
E	REVISED	PC-5578	2-23-72	L.D.
F	INACTIVATED	P-9257	2-1-82	DOM
G	REV 6-0465 & 6-2436	DAP	4-87	REV
H	REV -3-41-5	REV G2582	8-28-87	REV
S	REV 10120-0197-97	REV	8-20-91	REV
31	REV 8212-05-013140	REV	12/20/05	REV

TABLE I

QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH	
			NAME	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
1	WIRE TERMINAL	SEE TABLE II	BODY: COPPER (ASTM B152) NICKEL PLATE (QQ-N-290) .0003 AVG. EXT. THK.	SLEEVE: COPPER (ASTM B152) NICKEL PL (QQ-N-290). 000003 AVG. EXT. THK.
UNLESS OTHERWISE SPECIFIED DIMENSIONS TO BE IN INCHES. DECIMALS ± .008 ANGLES ± 5°			INSULATION: TEFLON (ASTM D3295) COLOR: BLACK	
MATERIAL			MATERIAL & FINISH	
SEE TABLE I			AMP	
CONTRACT NO. 7-20-69			AMP INCORPORATED	
DA 7-20-69			HARRISBURG, PENNSYLVANIA	
CHK 7-20-69				
APRD 8-6-69			WIRE TERMINAL	
REL PM 5-6-69			PIDG - STRATO-THERM - RING TONGUE	
DSGN APPD			WIRE SIZE: 12-10	
OTHER APPD			SIZE CODE IDENT NO. NUMBER	
			B 00779 50845	
			SCALE NTS	
			SHEET 1 OF 1	

CUSTOMER DRAWING

3

2

A

B

C

3

2

1