

MOSFET – P-Channel, 1.8 V Specified, POWERTRENCH® FDN306P

This P-Channel 1.8 V specified MOSFET uses **onsemi**'s advanced low voltage POWERTRENCH process. It has been optimized for

SOT-23 CASE 527AG

Features

- -2.6 A, -12 V $R_{DS(on)} = 40 \text{ m}\Omega @ V_{GS} = -4.5 \text{ V}$ $R_{DS(on)} = 50 \text{ m}\Omega @ V_{GS} = -2.5 \text{ V}$ $R_{DS(on)} = 80 \text{ m}\Omega @ V_{GS} = -1.8 \text{ V}$
- Fast Switching Speed

General Description

- High Performance Trench Technology for Extremely Low R_{DS(on)}
- SUPERSOT[™] –3 Provides Low R_{DS(on)} and 30% Higher Power Handling Capability than SOT–23 in the Same Footprint
- This is a Pb-Free and Halide Free Device

battery power management applications.

Applications

- Battery Management
- Load Switch
- Battery Protection

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted.)

Symbol	Parameter	Value	Unit
V _{DSS}	Drain-Source Voltage	-12	V
V _{GSS}	Gate-Source Voltage	±8	٧
I _D	Drain Current - Continuous (Note 1a) - Pulsed	-2.6 -10	Α
P _D	Maximum Power Dissipation (Note 1a) (Note 1b)	0.5 0.46	W
T _J , T _{STG}	Operating and Storage Junction Temperature Range	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS (T_A = 25°C unless otherwise noted.)

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient (Note 1a)	250	°C/W
$R_{ heta JC}$	Thermal Resistance, Junction-to-Case (Note 1)	75	°C/W

MARKING DIAGRAM



306 = Specific Device Code M = Month Code ■ Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]
FDN306P	SOT-23 (Pb-Free/	3000 / Tape & Reel
	Halide Free)	·

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

FDN306P

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted.)

OFF CHAR BV _{DSS} ΔBV _{DSS} / ΔT _J	Drain-Source Breakdown Voltage	LV 0VI 050 A	-							
ΔBV _{DSS} /	<u> </u>	V 0V/1 050 A		OFF CHARACTERISTICS						
	Decelele AVallere Terrerel er	$V_{GS} = 0 \text{ V}, I_D = -250 \mu\text{A}$	-12	-	-	V				
	Breakdown Voltage Temperature Coefficient	I_D = -250 μA, Referenced to 25 °C	-	-3	_	mV/°C				
I_{DSS}	Zero Gate Voltage Drain Current	V _{DS} = -10 V, V _{GS} = 0 V	-	_	-1	μΑ				
I _{GSSF}	Gate-Body Leakage, Forward	V _{GS} = 8 V, V _{DS} = 0 V	-	_	100	nA				
I _{GSSR}	Gate-Body Leakage, Reverse	$V_{GS} = -8 \text{ V}, V_{DS} = 0 \text{ V}$	-	-	-100	nA				
ON CHARA	CTERISTICS									
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = -250 \mu A$	-0.4	-0.6	-1.5	V				
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	I_D = -250 μA, Referenced to 25 °C	-	2.5	_	mV/°C				
R _{DS(on)}	Static Drain–Source On–Resistance	$\begin{array}{l} V_{GS} = -4.5 \text{ V, } I_D = -2.6 \text{ A} \\ V_{GS} = -2.5 \text{ V, } I_D = -2.3 \text{ A} \\ V_{GS} = -1.8 \text{ V, } I_D = -1.8 \text{ A} \\ V_{GS} = -4.5 \text{ V, } I_D = -2.6 \text{ A, } T_J = 125^{\circ}\text{C} \end{array}$	- - - -	30 39 54 40	40 50 80 54	mΩ				
I _{D(on)}	On-State Drain Current	$V_{GS} = -4.5 \text{ V}, V_{DS} = -5 \text{ V}$	-10	-	-	Α				
9FS	Forward Transconductance	$V_{DS} = -5 \text{ V}, I_D = -2.6 \text{ A}$	-	10	-	S				
DYNAMIC (CHARACTERISTICS									
C _{iss}	Input Capacitance	V _{DS} = -6 V, V _{GS} = 0 V, f = 1.0 MHz	-	1138	-	pF				
C _{oss}	Output Capacitance		-	454	-	pF				
C _{rss}	Reverse Transfer Capacitance		-	302	-	pF				
SWITCHING	G CHARACTERISTICS (Note 2)									
t _{d(on)}	Turn-On Delay Time	$V_{DD} = -6 \text{ V}, I_D = -1 \text{ A},$	-	11	20	ns				
t _r	Turn-On Rise Time	$V_{GS} = -4.5 \text{ V}, R_{GEN} = 6 \Omega$	_	10	20	ns				
t _{d(off)}	Turn-Off Delay Time		-	38	61	ns				
t _f	Turn-Off Fall Time		-	35	56	ns				
Qg	Total Gate Charge	$V_{DS} = -6 \text{ V}, I_D = -2.6 \text{ A}, V_{GS} = -4.5 \text{ V}$	-	12	17	nC				
Q _{gs}	Gate-Source Charge		-	2	-	nC				
Q_{gd}	Gate-Drain Charge		_	3	_	nC				
DRAIN-SO	URCE DIODE CHARACTERISTICS	AND MAXIMUM RATINGS								
I _S	Maximum Continuous Drain-Sourc	e Diode Forward Current	_	_	-0.42	Α				
V_{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_S = -0.42 \text{ (Note 2)}$	-	-0.6	-1.2	V				

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES

1. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a) 250°C/W when mounted on a 0.02 in 2 pad of 2 oz. copper.



b) 270°C/W when mounted on a minimum pad.

Scale 1:1 on letter size paper.

2. Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2.0%.

FDN306P

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage




Figure 3. On–Resistance Variation with Temperature




Figure 4. On–Resistance Variation with Gate–to–Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature

FDN306P

TYPICAL CHARACTERISTICS (Continued)




Figure 11. Transient Thermal Response Curve


Thermal characterization performed using the conditions described in Note 1b. Transient thermal response will change depending on the circuit board design.

SUPERSOT is a trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.



SOT-23/SUPERSOT™-23, 3 LEAD, 1.4x2.9 CASE 527AG ISSUE A

DATE 09 DEC 2019





NOTES: UNLESS OTHERWISE SPECIFIED


- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
 ALL DIMENSIONS ARE IN MILLIMETERS.
- ALL DIMENSIONS ARE IN MILLIMETERS.
 DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR EXTRUSIONS.

DIM	MIN.	NOM.	MAX.
Α	0.85	0.95	1.12
A1	0.00	0.05	0.10
b	0.370	0.435	0.508
С	0.085	0.150	0.180
D	2.80	2.92	3.04
Е	2.31	2.51	2.71
E1	1.20	1.40	1.52

e 0.95 BSC
e1 1.90 BSC
L 0.33 0.38 0.43







LAND PATTERN RECOMMENDATION*

*FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRMID.

GENERIC MARKING DIAGRAM*

XXXM•

XXX = Specific Device Code
M = Month Code

■ = Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON34319E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SOT-23/SUPERSOT-23, 3 LEAD, 1.4X2.9		PAGE 1 OF 1	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi: FDN306P