


KEMET Part Number: ALC80A102DF250
(A547EH102M250A)

ALC80, Aluminum Electrolytic, 1,000 uF, 20%, 250 VDC, -40/+105°C



General Information

Supplier:	KEMET
Series:	ALC80
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No
Shelf Life:	156 Weeks

Dimensions

D	35mm +1mm
L	50mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Weight:	80 g
Packaging:	Bulk, Bag

Specifications

Capacitance:	1,000 uF
Capacitance Tolerance:	20%
Voltage DC:	250 VDC, 288 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	8000 Hrs (Rated Voltage And Ripple Current At 105C), 13000 Hrs (Rated Voltage At 105C)
Resistance:	178 mOhms (100Hz 20C), 106 mOhms (10kHz 20C)
Ripple Current:	3.46 Amps (100Hz 105C), 7.52 Amps (10kHz 105C)
Leakage Current:	750 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.