


- Ultra-wide 4:1 input range
- Compact SIP-8 package
- Temperature range  $-40$  to  $+90^{\circ}\text{C}$  (up to  $+75^{\circ}\text{C}$  at full load)
- High efficiency of 82%
- Excellent load and line regulation
- Continuous short-circuit protection
- Overload protection
- I/O isolation 1500 VDC
- Remote On/Off control
- 3-year product warranty



The TMR 2WIN series is a family of isolated 2 W DC/DC converter modules with accurately regulated output voltages and ultra-wide 4:1 input voltage ranges. They require no minimum load and are protected against overload and short circuit.

An excellent efficiency along with the use of high grade components allows a compact construction in SIP-8 package; even the converters can reliably operate in an ambient temperature of  $-40^{\circ}\text{C}$  to  $+75^{\circ}\text{C}$  at full load and up to  $90^{\circ}\text{C}$  with 50% power derating. Typical applications for these converters are distributed power architectures in communication, instrumentation and industrial electronics, everywhere where space on the PCB is critical.

### Models

| Order Code    | Input Voltage Range           | Output 1 |                  | Output 2 |                  | Efficiency typ. |
|---------------|-------------------------------|----------|------------------|----------|------------------|-----------------|
|               |                               | Vnom     | I <sub>max</sub> | Vnom     | I <sub>max</sub> |                 |
| TMR 2-1210WIN | 4.5 - 18 VDC<br>(12 VDC nom.) | 3.3 VDC  | 500 mA           |          |                  | 75 %            |
| TMR 2-1211WIN |                               | 5 VDC    | 400 mA           |          |                  | 80 %            |
| TMR 2-1212WIN |                               | 12 VDC   | 167 mA           |          |                  | 82 %            |
| TMR 2-1213WIN |                               | 15 VDC   | 134 mA           |          |                  | 82 %            |
| TMR 2-1221WIN |                               | +5 VDC   | 200 mA           | -5 VDC   | 200 mA           | 80 %            |
| TMR 2-1222WIN |                               | +12 VDC  | 83 mA            | -12 VDC  | 83 mA            | 82 %            |
| TMR 2-1223WIN |                               | +15 VDC  | 67 mA            | -15 VDC  | 67 mA            | 82 %            |
| TMR 2-2410WIN | 9 - 36 VDC<br>(24 VDC nom.)   | 3.3 VDC  | 500 mA           |          |                  | 75 %            |
| TMR 2-2411WIN |                               | 5 VDC    | 400 mA           |          |                  | 80 %            |
| TMR 2-2412WIN |                               | 12 VDC   | 167 mA           |          |                  | 82 %            |
| TMR 2-2413WIN |                               | 15 VDC   | 134 mA           |          |                  | 82 %            |
| TMR 2-2421WIN |                               | +5 VDC   | 200 mA           | -5 VDC   | 200 mA           | 80 %            |
| TMR 2-2422WIN |                               | +12 VDC  | 83 mA            | -12 VDC  | 83 mA            | 82 %            |
| TMR 2-2423WIN |                               | +15 VDC  | 67 mA            | -15 VDC  | 67 mA            | 82 %            |
| TMR 2-4810WIN | 18 - 75 VDC<br>(48 VDC nom.)  | 3.3 VDC  | 500 mA           |          |                  | 74 %            |
| TMR 2-4811WIN |                               | 5 VDC    | 400 mA           |          |                  | 80 %            |
| TMR 2-4812WIN |                               | 12 VDC   | 167 mA           |          |                  | 82 %            |
| TMR 2-4813WIN |                               | 15 VDC   | 134 mA           |          |                  | 82 %            |
| TMR 2-4821WIN |                               | +5 VDC   | 200 mA           | -5 VDC   | 200 mA           | 80 %            |
| TMR 2-4822WIN |                               | +12 VDC  | 83 mA            | -12 VDC  | 83 mA            | 82 %            |
| TMR 2-4823WIN |                               | +15 VDC  | 67 mA            | -15 VDC  | 67 mA            | 82 %            |

### Input Specifications

|                           |                |   |
|---------------------------|----------------|---|
| Input Current             | - At no load   | 12 Vin models: <b>60 mA typ.</b><br>24 Vin models: <b>30 mA typ.</b><br>48 Vin models: <b>20 mA typ.</b>  |
|                           | - At full load | 12 Vin models: <b>200 mA typ.</b><br>24 Vin models: <b>100 mA typ.</b><br>48 Vin models: <b>50 mA typ.</b>  |
| Surge Voltage             |                | 12 Vin models: <b>25 VDC max.</b> (1 s max.)<br>24 Vin models: <b>50 VDC max.</b> (1 s max.)<br>48 Vin models: <b>100 VDC max.</b> (1 s max.)   |
| Start-up Voltage          |                | 12 Vin models: <b>4 VDC typ.</b><br>24 Vin models: <b>6 VDC typ.</b><br>48 Vin models: <b>12 VDC typ.</b>   |
| Under Voltage Lockout     |                | 12 Vin models: <b>4 VDC max.</b><br>24 Vin models: <b>8 VDC max.</b><br>48 Vin models: <b>16 VDC max.</b>   |
| Recommended Input Fuse    |                | 12 Vin models: <b>1'000 mA</b> (slow blow)<br>24 Vin models: <b>500 mA</b> (slow blow)<br>48 Vin models: <b>250 mA</b> (slow blow)<br>(The need of an external fuse has to be assessed in the final application.) |
| Input Filter              |                | <b>Internal Capacitor</b>   |
| Short Circuit Input Power |                | <b>1.5 W max.</b>   |

### Output Specifications

|                           |                                      |  |
|---------------------------|--------------------------------------|--|
| Voltage Set Accuracy      |                                      | <b>±2% max.</b>  |
| Regulation                | - Input Variation (Vmin - Vmax)      | single output models: <b>0.5% max.</b><br>dual output models: <b>0.5% max.</b>   |
|                           | - Load Variation (0 - 100%)          | single output models: <b>1% max.</b><br>dual output models: <b>1% max.</b> (Output 1)<br><b>1% max.</b> (Output 2)                                       |
|                           | - Voltage Balance (symmetrical load) | dual output models: <b>2% max.</b>   |
| Ripple and Noise          | - 20 MHz Bandwidth                   | <b>100 mVp-p max.</b>  |
| Capacitive Load           | - single output                      | 3.3 Vout models: <b>1'000 µF max.</b><br>5 Vout models: <b>1'000 µF max.</b><br>12 Vout models: <b>170 µF max.</b><br>15 Vout models: <b>110 µF max.</b> |
|                           | - dual output                        | 5 / -5 Vout models: <b>470 / 470 µF max.</b><br>12 / -12 Vout models: <b>100 / 100 µF max.</b><br>15 / -15 Vout models: <b>47 / 47 µF max.</b>           |
| Minimum Load              |                                      | <b>Not required</b>  |
| Temperature Coefficient   |                                      | <b>±0.02 %/K max.</b>  |
| Short Circuit Protection  |                                      | <b>Automatic recovery</b>  |
| Overload Protection       |                                      | <b>Foldback Mode</b>   |
| Output Current Limitation |                                      | <b>110% min. of Iout max.</b>  |
|                           |                                      | <b>140% typ. of Iout max.</b>  |
| Transient Response        | - Response Deviation                 | <b>5% max.</b> (75% to 100% Load Step)   |
|                           | - Response Time                      | <b>300 µs typ. / 500 µs max.</b> (75% to 100% Load Step)   |

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

## Safety Specifications

|                  |                             |   |
|------------------|-----------------------------|---|
| Safety Standards | - IT / Multimedia Equipment | CSA-C22.2, No 60950-1<br>EN 60950-1<br>EN 62368-1<br>IEC 60950-1<br>IEC 62368-1<br>UL 60950-1<br>UL 62368-1 |
|                  | - Certification Documents   | <a href="http://www.tracopower.com/overview/tmr2win">www.tracopower.com/overview/tmr2win</a>                |
| Pollution Degree |                             | PD 2  |

## General Specifications


|                           |  |   |
|---------------------------|--|---|
| Relative Humidity         |  | 95% max. (non condensing)   |
| Temperature Ranges        | - Operating Temperature<br>- Case Temperature<br>- Storage Temperature                         | -40°C to +90°C<br>+105°C max.<br>-55°C to +125°C  |
| Power Derating            | - High Temperature   | 3.33 %/K above 75°C   |
| Cooling System            |  | Natural convection (20 LFM)   |
| Remote Control            | - Voltage Controlled Remote<br><br>- Current Controlled Remote<br><br>- Off Idle Input Current | On: open circuit<br>Off: 6 to 9 VDC (via 1 kOhm resistor)<br>Refers to 'Remote' and '-Vin' Pin<br><br>On: open circuit<br>Off: 2 to 4 mA current<br>3 mA max.   |
| Altitude During Operation |  | 6'000 m max.  |
| Switching Frequency       |  | 300 kHz typ. (PFM)  |
| Insulation System         |  | Functional Insulation   |
| Isolation Test Voltage    | - Input to Output, 60 s<br>- Input to Output, 1 s  | 1'500 VDC<br>1'800 VDC  |
| Isolation Resistance      | - Input to Output, 500 VDC   | 1'000 MΩ min.   |
| Isolation Capacitance     | - Input to Output, 100 kHz, 1 V  | 250 pF typ.<br>500 pF max.  |
| Reliability               | - Calculated MTBF  | 3'430'000 h (MIL-HDBK-217F, ground benign)  |
| Housing Material          |  | Non-conductive Plastic (UL94 V-0 rated)   |
| Potting Material          |  | Silicone (UL 94 V-0 rated)  |
| Pin Material              |  | Nickel-Iron (Alloy 42)  |
| Pin Foundation Plating    |  | Nickel (1 μm min.)  |
| Pin Surface Plating       |  | Tin (3 - 5 μm), matte   |
| Soldering Profile         |  | Wave Soldering<br>260°C / 10 s max.   |
| Connection Type           |  | THD (Through-Hole Device)   |
| Weight                    |  | 4.66 g  |
| Environmental Compliance  | - REACH Declaration<br><br>- RoHS Declaration  | <a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a><br>REACH SVHC list compliant<br>REACH Annex XVII compliant<br><a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a><br>Exemptions: 7a |

## Supporting Documents

|  |  |
|--|--|
| Overview Link (for additional Documents) | <a href="http://www.tracopower.com/overview/tmr2win">www.tracopower.com/overview/tmr2win</a> |
|--|--|

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

**Outline Dimensions**



| Pinout |               |             |
|--------|---------------|-------------|
| Pin    | Single Output | Dual Output |
| 1      | -Vin (GND)    | -Vin (GND)  |
| 2      | +Vin (Vcc)    | +Vin (Vcc)  |
| 3      | Remote        | Remote      |
| 5      | NC            | NC          |
| 6      | +Vout         | +Vout       |
| 7      | -Vout         | Common      |
| 8      | NC            | -Vout       |

NC: No Connection

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TRACO Power:

[TMR 2-1210WIN](#) [TMR 2-1212WIN](#) [TMR 2-2411WIN](#) [TMR 2-1223WIN](#) [TMR 2-2410WIN](#) [TMR 2-4812WIN](#) [TMR 2-4810WIN](#) [TMR 2-4813WIN](#) [TMR 2-2422WIN](#) [TMR 2-2423WIN](#) [TMR 2-4811WIN](#) [TMR 2-4823WIN](#) [TMR 2-2421WIN](#) [TMR 2-1222WIN](#) [TMR 2-2412WIN](#) [TMR 2-1221WIN](#) [TMR 2-4822WIN](#) [TMR 2-2413WIN](#) [TMR 2-4821WIN](#) [TMR 2-1211WIN](#) [TMR 2-1213WIN](#)