


STM1001

Reset circuit

Features

- Precision monitoring of 3 V, 3.3 V, and 5 V supply voltages
- Open drain RST output
- 30 ms or 140 ms reset pulse width (min)
- Low supply current 6 µA (typ)
- Guaranteed RST assertion down to V_{CC}= 1.0 V
- Operating temperature:
 - 40 °C to 85 °C (industrial grade)
- Lead-free, small SOT23 package



Contents STM1001

Contents

1	Description
2	Operation
	2.1 Reset output
	2.2 Negative-going V _{CC} transients
3	Typical operating characteristics
4	Maximum ratings
5	DC and AC parameters
6	Package mechanical data14
7	Part numbering15
R	Revision history



STM1001 List of tables

List of tables

Table 1.	Signal names	. 5
Table 2.	Absolute maximum ratings	11
Table 3.	Operating and AC measurement conditions	12
Table 4.	DC and AC characteristics	13
Table 5.	SOT23-3 – 3-lead small outline transistor package mechanical data	14
Table 6.	Ordering information scheme	15
Table 7.	Marking description	16
Table 8.	Document revision history	



List of figures STM1001

List of figures

Figure 1.	Logic diagram	5
Figure 2.	Connections	5
Figure 3.	Block diagram	6
Figure 4.	Hardware hookup	
Figure 5.	Supply current vs. temperature, L/M/R/S/T (no load)	
Figure 6.	Power-down reset delay vs. temperature - $V_{OD} = V_{TH} - V_{CC} (L/M) \dots$	
Figure 7.	Power-down reset delay vs. temperature - $V_{OD} = V_{TH} - V_{CC} (R/S/T) \dots$	
Figure 8.	Power-up t _{rec} vs. temperature	
Figure 9.	Normalized reset threshold vs. temperature	
Figure 10.	Max transient duration not causing reset pulse vs. reset comparator overdrive	
Figure 11.	AC testing input/output waveforms	
•	SOT23-3 – 3-lead small outline transistor package outline	

STM1001 Description

1 Description

The STM1001 microprocessor reset circuit is a low-power supervisory device used to monitor power supplies. It performs a single function: asserting a reset signal whenever the V_{CC} supply voltage drops below a preset value and keeping it asserted until V_{CC} has risen above the preset threshold for a minimum period of time (t_{rec}) .

Figure 1. Logic diagram





Table 1. Signal names


V _{SS}	Ground
RST	Active-low reset output (open drain)
V _{CC}	Supply voltage

Figure 2. Connections




Description STM1001

Figure 3. Block diagram



1. Open drain

Figure 4. Hardware hookup



1. $\overline{\mbox{RST}}$ output requires pull-up resistor.

5

STM1001 Operation

2 Operation

2.1 Reset output

The STM1001 microprocessor reset circuit asserts a reset signal to the MCU whenever V_{CC} goes below the reset threshold (V_{RST}). \overline{RST} is guaranteed valid down to V_{CC} = 1 V (0° to 70 °C).

During power-up, once V_{CC} exceeds the reset threshold an internal timer keeps \overline{RST} low for the reset time-out period, t_{rec} . After this interval, \overline{RST} returns high.

If V_{CC} drops below the reset threshold, \overline{RST} goes low. Each time \overline{RST} is asserted, it stays low for at least the reset time-out period. Any time V_{CC} goes below the reset threshold, the internal timer clears. The reset timer starts when V_{CC} returns above the reset threshold. The active-low reset (\overline{RST}) is an open drain output.

2.2 Negative-going V_{CC} transients


The STM1001 is relatively immune to negative-going V_{CC} transients (glitches). Figure 10 on page 10 shows typical transient duration versus reset comparator overdrive (for which the STM1001 will NOT generate a reset pulse). The graph was generated using a negative pulse applied to V_{CC} , starting at 0.5 V above the actual reset threshold and ending below it by the magnitude indicated (comparator overdrive). The graph indicates the maximum pulse width a negative V_{CC} transient can have without causing a reset pulse. As the magnitude of the transient increases (further below the threshold), the maximum allowable pulse width decreases. Any combination of duration and overdrive which lies under the curve will NOT generate a reset signal. Typically, a V_{CC} transient that goes 100 mV below the reset threshold and lasts 20 µs or less will not cause a reset pulse. A 0.1 µF bypass capacitor mounted as close as possible to the V_{CC} pin provides additional transient immunity.

3 Typical operating characteristics


Note:

Typical values are at T_A = 25 °C, V_{CC} = 5 V for L/M versions, V_{CC} = 3.3 V for T/S versions, and V_{CC} = 3.0 V for R versions.

Figure 5. Supply current vs. temperature, L/M/R/S/T (no load)











Figure 7. Power-down reset delay vs. temperature - $V_{OD} = V_{TH} - V_{CC}$ (R/S/T)

Figure 8. Power-up t_{rec} vs. temperature



Note: Valid for $t_{rec} = 210 \text{ ms (typ)}$.

577





Figure 9. Normalized reset threshold vs. temperature

Figure 10. Max transient duration not causing reset pulse vs. reset comparator overdrive



STM1001 Maximum ratings

4 Maximum ratings

Stressing the device above the rating listed in the absolute maximum ratings table may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in the operating sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Refer also to the STMicroelectronics SURE Program and other relevant quality documents.

Table 2. Absolute maximum ratings

Symbol	Parameter	Value	Unit
T _{STG}	Storage temperature (V _{CC} off)	-55 to 150	°C
T _{SLD} ⁽¹⁾	Lead solder temperature for 10 seconds	260	°C
V _{IO}	Input or output voltage	-0.3 to V_{CC} +0.3	V
V _{CC}	Supply voltage	-0.3 to 7.0	V
I _O	Output current	20	mA
P _D	Power dissipation	320	mW

^{1.} Reflow at peak temperature of 260 °C. The time above 255 °C must not exceed 30 seconds.

5 DC and AC parameters

This section summarizes the operating measurement conditions, and the DC and AC characteristics of the device. The parameters in the DC and AC characteristics tables that follow, are derived from tests performed under the measurement conditions summarized in *Table 3: Operating and AC measurement conditions*. Designers should check that the operating conditions in their circuit match the operating conditions when relying on the quoted parameters.

Table 3. Operating and AC measurement conditions

Parameter	STM1001	Unit
V _{CC} supply voltage	1.0 to 5.5	V
Ambient operating temperature (T _A)	-40 to 85	°C
Input rise and fall times	≤ 5	ns
Input pulse voltages	0.2 to 0.8 V _{CC}	V
Input and output timing ref. voltages	0.3 to 0.7 V _{CC}	V

Figure 11. AC testing input/output waveforms




Table 4. DC and AC characteristics

Sym	Description	Test cor	Min	Тур	Max	Unit	
V	Operating voltage	$T_A = -40 \text{ to } +85 ^{\circ}\text{C}$		1.2		5.5	V
V _{CC}	Operating voltage	$T_A = 0 \text{ to}$	+70 °C	1.0		5.5	V
,	V gunnly gurrent	V _{CC} <	3.6 V		5.5	10	μA
I _{CC}	V _{CC} supply current	V _{CC} <	5.5 V		7	15	μA
I _{LO}	Open drain reset output leakage current	V _{CC} > Reset not		-1		+1	μА
V	DCT output low voltage	STM1001R/S/T over $V_{CC} = V_F$				0.3	V
V _{OL}	RST output low voltage	STM1001L/M or $V_{CC} = V_F$	· •			0.4	V
V _{OL}	RST output low voltage	$I_{OL} = 50 \mu A;$	V _{CC} > 1.0 V			0.3	V
RESE1	T thresholds						
	Reset threshold	STM1001L	25 °C	4.56	4.63	4.70	V
			–40 to 85 °C	4.50		4.75	V
		STM1001M	25 °C	4.31	4.38	4.45	V
			−40 to 85 °C	4.25		4.50	V
V		STM1001T	25 °C	3.04	3.08	3.11	V
V _{RST}			−40 to 85 °C	3.00		3.15	V
		STM1001S	25 °C	2.89	2.93	2.96	V
		3111110013	−40 to 85 °C	2.85		3.00	V
		QTM1001D	25 °C	2.59	2.63	2.66	V
		STM1001R -40	−40 to 85 °C	2.55		2.70	V
	V _{RST} temperature coefficient	V _{CC} = 3.3 V			45		ppm/°C
	V _{CC} to RST delay	$V_{CC} = V_{RST}$ to	STM1001L/M		40		μs
	VCC 10 HOT UBIAY	(V _{RST} – 100 mV) STM1001R/S/T			20		μs
t _{rec}	RST pulse width	Option B (refer to <i>Table 6</i>)		20	30	40	ms
rec	Tio i paide width	Option "Blank" (refer to <i>Table 6</i>)		140	210	280	1110

^{1.} Valid for ambient operating temperature: $T_A = -40$ to 85 °C; $V_{CC} = 1.2$ V to 5.5 V (except where noted).

6 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.




Figure 12. SOT23-3 – 3-lead small outline transistor package outline


Note: Drawing is not to scale.

Table 5. SOT23-3 – 3-lead small outline transistor package mechanical data

Symbol		mm			inches	
Symbol	Тур	Min	Max	Тур	Min	Max
Α		0.89	1.12		0.035	0.044
A1		0.01	0.10		0.001	0.004
A2		0.88	1.02		0.035	0.042
b		0.30	0.50		0.012	0.020
С		0.08	0.20		0.003	0.008
D		2.80	3.04		0.110	0.120
Е		2.10	2.64		0.083	0.104
E1		1.20	1.40		0.047	0.055
е		0.89	1.03		0.035	0.041
e1		1.78	2.05		0.070	0.081
L	0.54			0.021		
L1		0.40	0.60		0.016	0.024
Q		0°	8°		0°	8°
N		3	•		3	

STM1001 Part numbering

7 Part numbering



For other options, or for more information on any aspect of this device, please contact the ST sales office nearest you.

Part numbering STM1001

Table 7. Marking description

Part number	Reset threshold	Output	Topside marking ⁽¹⁾
STM1001LWX6F	4.63 V	Open drain RST	8BAx
STM1001MWX6F	4.38 V	Open drain RST	8BBx
STM1001TWX6F	3.08 V	Open drain RST	8BCx
STM1001SWX6F	2.93 V	Open drain RST	8BDx
STM1001RWX6F	2.63 V	Open drain RST	8BEx
STM1001SBWX6F	2.93 V	Open drain RST	8BMx

^{1.} Lowercase "x" indicates date code.

STM1001 Revision history

8 Revision history

Table 8. Document revision history

Date	Revision	Changes
09-Dec-2003	1	First edition
19-Feb-2004	2	Part number changed from STM6301
22-Mar-2004	2.1	Update DC characteristics (Table 4)
09-Apr-2004	3	Device promoted; reformatted; marking updated (Table 7)
19-Nov-2004 4		Update dimensions (<i>Table 5</i>).
19-Sep-2005 5 Remove "Valid RST Output Down to V _{CC} " text		Remove "Valid RST Output Down to V _{CC} " text
17-Feb-2010 6		Updated <i>Features</i> ; footnote in <i>Table 2</i> ; <i>Table 4</i> ; <i>Table 6</i> ; <i>Table 7</i> ; text in <i>Section 6</i> ; added note to <i>Figure 8</i> ; reformatted document.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2010 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

