CONSTANT VOLTAGE LED DRIVER 24VDC 600WATT



POWERPAX: LED-DR-24V-600W-A

Features:

- Input Voltage 108-305V AC
- IP67 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 1 Year Warranty

Description:

The Range of 600 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP67 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-24V-600W-A
Output Voltage Rating	20.4-25.2VDC
Output Current	25 A Max
Rated Power	600 Watt
Dimensions	290 x 124 x 45.5 mm
Input Voltage Range	108-305V AC
Input Voltage Frequency	47-63Hz
Inrush Current	55A/230V (25°C)
input power	3.0A/230V 50Hz 6.0A/115V 60Hz
Efficiency	95%
Power Consumption Without Load	PF>0.95 (230V 50Hz) PF>0.98(115V 50Hz) 1
Overload Protection	1.1~1.6 times rated load (auto-recovery)
Short Circuit Protection	Hiccup mode auto-recovery
Automatically Restart	Yes
Working Temperature	-40°C to +70°C
Relative Humidity	15% - 95%
MTBF	155Khrs MIL-HDBK-217F (25团)
EMC emission	EN55015,FCC PART15 ClassB
EMC Immunity	EN61000-4-2,3,4,5,6,8,11; EN55024; EN61547
Safety Standards	EN61347-1, EN61347-2-13

POWERPAX

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT Electronics plc

General Note

TT Electronics IoT Solutions Ltd Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK t: +44 (0) 1429 852 500




CONSTANT VOLTAGE LED DRIVER 24VDC 600WATT



POWERPAX: LED-DR-24V-600W-A

Diagrams



General Note TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT Electronics plc

TT Electronics IoT Solutions Ltd Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK t: +44 (0) 1429 852 500

ISS.3 17/07/2020 Page: 2

POWERPAX