


PRODUCT NUMBER: 0921-1-15-20-75-14-11-0

0921-X-XX-20-7X-14-11-0

Solder mount in .070 min. mounting hole



Basic Part Number	Length (A)	MID. Stroke (B)	Length (C)
* 0921-0	.171	.0195	.069
* 0921-1	.205	.0275	.085

* Available packaged on Tape & Reel

Standard Tolerances:
 Lengths: $\pm .006$
 Diameters: $\pm .002$
 Angles: $\pm 2^\circ$

DESCRIPTION

Surface Mount Spring-Loaded Pin

Durability:

Up to 1,000,000 Cycles @ Mid-Stroke

Current Rating:

See Spring Derating Curve

Contact Resistance:

20 mΩ Max

Operating Temperature Range:

-55/+125° C

Vibration:

No Elect. Discontinuity > 1μs @ 10-2000HZ, 20 G

Shock:

No Elect. Discontinuity > 1μs @ 50g

Mounting Feature:

Through-Hole Solder Mount


Mounting Hole: .070" (1,778mm)

Packaging: 15 - Packaged in Bulk

0921-0-15-20-76-14-11-0

Ultra low profile, Short stroke. Solder mount in .070 min. mounting hole
 24mm wide X 8mm pitch carrier tape: 1,700 parts per 13" reel

Order as: 0921-0-57-20-76-14-11-0




Standard Tolerances:
 Lengths: $\pm .006$
 Diameters: $\pm .002$
 Angles: $\pm 2^\circ$

0921-1-15-20-7X-14-11-0

Low profile, Standard stroke. Solder mount in .070 min. mounting hole
 24mm wide X 8mm pitch carrier tape: 1,500 parts per 13" reel

Order as: 0921-1-57-20-7X-14-11-0




Standard Tolerances:
 Lengths: $\pm .006$
 Diameters: $\pm .002$
 Angles: $\pm 2^\circ$

20 μ" Gold over Nickel

10 μ" Gold over Nickel

RoHS-2
2011/65/EU**SPRING:**

#75 SPRING STANDARD FORCE SPRING	Full Stroke Capability : $.055'' \pm .005''$ [1,4 ± 0,127]
Spring Material : Beryllium Copper Alloy 172	Force @ Mid. Stroke : 60 g ± 20 g
Mid. Stroke : $.0275''$ [0,7]	Initial Force (Pre-Load) : 10 g



The stroke, force and current rating values are measured using spring pins with an internal construction per the design specification. Individual spring pin performance may vary from these values based on design differences.

Material	Beryllium Copper	Grams Force	60
Max Stroke	0.06		

CONTACT MATERIAL:**BERYLLIUM COPPER ALLOY 172 (UNS C17200) per ASTM B 194**

Properties of BERYLLIUM COPPER:

- Chemical composition: Cu 98.1%, Be 1.9%
- Hardness: 36-43 Rockwell C
- Density: .298 lbs/in³
- Electrical Conductivity: 22% IACS*
- Resistance: 10 mΩ Max
- Operating Temperature: -55°C/+125°C
- Melting point: 980°C/865°C (liquidus/solidus)
- Stress Relaxation†: 96% of stress remains after 1,000 hours @ 100 °C; 70% of stress remains after 1,000 hours @ 200 °C

*International Annealed Copper Standard, i.e. as a % of pure copper.

†Since BeCu loses its spring properties over time at high temperatures; it is rated for continuous use up to 150°C. For applications up to 300°C, Mill-Max offers other materials. [Contact Tech Support](#) for more info.

STANDARD TOLERANCES ON PCB TERMINAL PINS & RECEPTACLES

Diameters +/- .002"

Lengths +/- .005"

Angles +/- 2°

STANDARD TOLERANCES ON SPRING-LOADED PINS

Diameters +/- .002"
Lengths +/- .006"
Angles +/- 2°

ADDITIONAL NOTES & SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

 © 2021 Mill-Max Mfg. Corp.
190 Pine Hollow Rd, Oyster Bay, NY 11771, USA
Phone: 516.922.6000