

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 1 of 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Cramolin Contact Cleaner

1.2. Relevant identified uses of the substance or mixture and uses advised against**Use of the substance/mixture**

Washing and cleaning products (including solvent based products)

1.3. Details of the supplier of the safety data sheet

Company name: ITW LLC & Co. KG
Street: Mühlackerstrasse 149
Place: D-75417 Mühlacker
Telephone: ++49(0)7041-96340 Telefax: ++49(0)7041-963429
e-mail: info@itwcp.de
Internet: www.itwcp.de
Responsible Department: Produktsicherheit Mo. - Do. 8.00 - 16.30 Fr. 8.00 - 14.00
Swiss Toxicological Information Centre - Téléphone : +41 44 251 51 51 (in Switzerland dial 145)
United Kingdom : National Poisons Information Service - Phone number : 8448920111
Österreich : Vergiftungsinformationszentrale Vienna - Telefon-Nummer : +43 1 406 43 43
Schweiz : Tox Info Suisse - Telefon-Nummer : +41 44 251 51 51
Italia : Centro Antiveleni, Roma - Numero di telefono : +39 06 305 4343
España : Instituto Nacional de Toxicología - Teléfono : +34 91 562 04 20
Deutschland: ++49(0)7041-96340

1.4. Emergency telephone number:**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Regulation (EC) No. 1272/2008**

Hazard categories:

Aerosol: Aerosol 1

Skin corrosion/irritation: Skin Irrit. 2

Specific target organ toxicity - single exposure: STOT SE 3

Hazardous to the aquatic environment: Aquatic Chronic 2

Hazard Statements:

Extremely flammable aerosol.

Pressurised container: May burst if heated.

Causes skin irritation.

May cause drowsiness or dizziness.

Toxic to aquatic life with long lasting effects.

2.2. Label elements**Regulation (EC) No. 1272/2008****Hazard components for labelling**

Hydrocarbons, C6, isoalkanes, <5% n-hexane

Signal word: Danger**Pictograms:**

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 2 of 8

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements

P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P271	Use only outdoors or in a well-ventilated area.
P273	Avoid release to the environment.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

CAS No	Chemical name	Quantity
	EC No	
	Index No	
	REACH No	
	GHS Classification	
	Hydrocarbons, C6, isoalkanes, <5% n-hexane	60-100 %
	931-254-9	
	01-2119484651-34	
	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H315 H336 H304 H411	
64-17-5	ethanol; ethyl alcohol	<20 %
	200-578-6	
	603-002-00-5	
	Flam. Liq. 2; H225	
124-38-9	Carbondioxide	5-10%
	204-696-9	
	Compressed gas; H280	

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

No special measures are necessary.

After inhalation

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water.

After ingestion

If swallowed, immediately drink: Water.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 3 of 8

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**Carbon dioxide (CO₂). Foam. Extinguishing powder.**Unsuitable extinguishing media**

Water. Water with tenside additive.

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking.

Hints on joint storage

Do not store together with: Material, rich in oxygen, oxidizing.

Further information on storage conditions

none

SECTION 8: Exposure controls/personal protection**8.1. Control parameters**

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 4 of 8

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
64-17-5	Ethanol	1000	1920		TWA (8 h)	WEL

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	colourless
Odour:	characteristic

Changes in the physical state

Initial boiling point and boiling range:	60 °C
Flash point:	< -20 °C
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	7 vol. %
Ignition temperature:	300 °C
Vapour pressure: (at 20 °C)	227 hPa
Vapour pressure: (at 50 °C)	719 hPa
Density (at 20 °C):	0,68 g/cm ³

SECTION 10: Stability and reactivity

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 5 of 8

10.1. Reactivity

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

CAS No	Chemical name					
	Exposure route	Dose	Species	Source	Method	
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	oral	LD50 >1000 mg/kg	Fisch 1			
64-17-5	ethanol; ethyl alcohol					
	oral	LD50 6200 mg/kg	Rat	IUCLID		
	inhalation (4 h) vapour	LC50 95,6 mg/l	Rat	RTECS		

Irritation and corrosivity

Vapours may cause drowsiness and dizziness. After skin contact: irritant.

SECTION 12: Ecological information

12.1. Toxicity

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h] [d]	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	Acute algae toxicity	ErC50 >1000 mg/l	72 h	Alge		
	Acute crustacea toxicity	EC50 >1000 mg/l	48 h	Daphnia pulex (water flea)		
64-17-5	ethanol; ethyl alcohol					
	Acute crustacea toxicity	EC50 9268 - 14221 mg/l	48 h	Daphnia magna	IUCLID	

12.3. Bioaccumulative potential

Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
64-17-5	ethanol; ethyl alcohol	-0,31

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 6 of 8

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Advice on disposal**

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information**Land transport (ADR/RID)**

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 7 of 8

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 203
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 203
IATA-max. quantity - Cargo: 150 kg

Other applicable information (air transport)

E0

: Forbidden
: Y203

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: yes



Danger releasing substance: Hydrocarbons

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 3: ethanol; ethyl alcohol

Entry 28: Hydrocarbons, C6, isoalkanes, <5% n-hexane

2004/42/EC (VOC): 266g/400ml Dose

National regulatory information

Water contaminating class (D): 2 - clearly water contaminating

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Cramolin Contact Cleaner

Revision date: 27.11.2019

Product code: 102

Page 8 of 8

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information**Relevant H and EUH statements (number and full text)**

H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)