

TB1141D4722-400 ✓ ACTIVE

TE Internal #: TB1141D4722-400

M8/M12 Cable Assemblies, Sensor/Actuator, 4 Position, M8 Plug, M8 Pigtail, Straight Connector Orientation (End A), Length 40 m, Shielded, Single Ended

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies



M8/M12 Application Type: **Sensor/Actuator**

Number of Positions: **4**

Connector Type (End A): **M8 Plug**

Cable Assembly Type: **M8 Pigtail**

Connector Orientation (End A): **Straight**

Features

Product Type Features

LED	Without
Product Type	Cable Assembly
Assembly Type	Pigtail
Connector Type (End A)	M8 Plug
Cable Assembly Type	M8 Pigtail

Configuration Features

Number of Positions	4
---------------------	---

Mechanical Attachment

Screw & Hole Thread Size	M8
Connector Orientation (End A)	Straight

Housing Features

Housing Material	Nylon
------------------	-------

Operation/Application

M8/M12 Application Type	Sensor/Actuator
-------------------------	-----------------



Shielded Yes

Other

Cable Assembly Length 40 m

Cable Assembly Configuration Single Ended

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant with Exemptions

EU ELV Directive 2000/53/EC Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016 Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JAN 2022 (223)
 Candidate List Declared Against: JAN 2022 (223)
 SVHC > Threshold:
 Pb (1.2% in Component Part)
Article Safe Usage Statements:
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[RPC-M8-MS-4CON-P-40SH](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_TB1141D4722-400_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_TB1141D4722-400_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_TB1141D4722-400_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Catalog-Single Pair Ethernet M8 Hybrid Board Receptacle IP67 and Single Pair Ethernet M8 Hybrid Cordset](#)

English

Product Specifications

[Application Specification](#)

English