# Optical Encoder

Series 62A, V,D

Compact, 1/2" Package



#### **FEATURES**

- Low Cost
- Long Life
- Available in 3.3 or 5.0 Vdc Operating Voltages
- High Torque Version to Emphasize Rotational Feel
- Economical Size
- Optically Coupled for More than a Million Cycles
- Optional Integral Pushbutton
- Compatible with CMOS, TTL and HCMOS Logic
- Available in 12,16, 20, 24 and 32
   Detent Positions (Non-detent Also Available)
- Choices of Cable Length and Terminations


#### **APPLICATIONS**

• Global Positioning/Driver Information Systems


Medical Equipment




### **DIMENSIONS** In inches (and millimeters)



#### **DIMENSIONS** In inches (and millimeters)




#### CIRCUITRY, TRUTH TABLE, AND WAVEFORM Standard Quadrature 2-Bit Code




Clockwise Rotation		
Position	Output A	Output B
1		
2	•	
3	•	•
4		•

 Indicates logic high; blank indicates logic low. Code repeats every 4 positions.

#### 3.3 Volt (Style V only)





# Grayhill Optical Encoder (Series 62A, V, D)



#### **SPECIFICATIONS**

#### **Mechanical Ratings**

Rating: 5 Vdc, 10 mA, resistive Contact Resistance: less than 10 ohms

(TTL or CMOS compatible)

Pushbutton Life: 3 million actuations

minimum

Contact Bounce: less than 4 mS at make

and less than 10 mS at break
Actuation Force: 1000 ±300 grams
Pushbutton Travel: .010/.025 inch
Coding: 2-bit quadrature coded output
Operating Voltage: 5.0 ±.25 Vdc,
3.30±.125 Vdc (style V only)
Voltage Breakdown: 250 Vac between

mutually insulated parts

Supply Current: 30 mA maximum

Logic Output Characterisitics: Logic High: 3.8 Vdc (5.0 Vdc); 2.3 (3.3 Vdc)

Logic High: 3.8 Vdc (5.0 Vdc); 2.3 (3.3 minimum

Logic Low: 0.8 Vdc maximum

**Rotational Life:** 1,000,000 cycles minimum (One cycle is a rotation through all positions and a full return)

**Minimum Sink Current**: 2.0 mA for 5 Vdc; 1.0 mA for 3.3 Vdc

Power Consumption: 150 mW maximum

for 5 Vdc; 80 mW for 3.3 Vdc

Optical Rise and Fall Times: less than 30

mS maximum
Operating Torque:

Style A and V: 2.0 ±1.4 in-oz. initially
Style D: 3.5 ±1.4 in-oz initially
Non-detent: less than 1.5 in-oz initially
Shaft Push Out Force: 45 lbs minimum
Mounting Torque: 15 in-lbs maximum
Terminal Strength: 15 lbs cable pull-out force

minimum

Operating Speed: 100 RPM maximum Axial Shaft Play: .010 maximum

#### **Environmental Ratings**

Operating Temperature Range: -40°C to 85°C Storage Temperature Range: -55°C to 100°C Relative Humidity: 90–95% at 40°C for 96 hours

**Vibration Resistance:** Harmonic motion with amplitude of 15G, within a varied 10 to 2000 Hz frequency for 12 hours per MIL-STD-202, Method 204

**Mechanical Shock:** Test 1: 100G for 6 mS, half sine, 12.3 ft/s; Test 2: 100G for 6 mS, sawtooth, 9.7 ft/s

#### **Materials and Finishes**

Code Housing: Reinforced thermoplastic

**Shaft:** Zinc or aluminum **Bushing:** Zinc casting

Shaft Retaining Ring: Stainless steel

Detent Spring: Stainless steel

Printed Circuit Boards: NEMA grade FR-4

gold over nickel or palladium **Terminals:** Brass, tin-plated

Mounting Hardware: One brass, nickel-plated nut and stainless steel lockwasher supplied with each switch. Nut is 0.094 inches thick by

0.562 inches across flats. **Rotor:** Thermoplastic


Code Housing: Thermoplastic
Pushbutton Dome: Stainless steel
Dome Retaining Disk: Thermoplastic
Pushbutton Housing: Thermoplastic
Phototransistor: Planar Silicon NPN
Infrared Emitter: Gallium aluminum arsenide
Pushbutton Contact: Brass, nickel-plated
Plex Cable: 28 AWG, stranded/top coated
wire, PVC coated on .050 or .100" centers
(cabled version)

Header Pins: Phospher bronze, tin-plated

Spacer: ABS

Backplate/Strain Relief: Stainless steel

#### ORDERING INFORMATION



## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Grayhill:

62A11-01-020S 62A11-01-050S 62A11-01-060C 62A11-02-020C 62A11-02-050S 62A11-02-060C 62A15-01-060C 62A15-02-030S 62A15-02-060C 62A22-01-060C 62A22-02-020C 62A22-02-035S 62A22-02-060C 62V22-02-020C 62A15-01-240C 62A11-01-100SH 62A15-02-080SH 62A22-02-030CH 62A01-01-060SH 62D15-01-100S 62A22-02-120C 62V11-01-110C 62A08-02-030S 62D22-02-020C 62A01-01-050S 62D11-01-080SH 62A15-02-070SH 62A11-02-020S 62A18-02-060S 62V01-01-200SH 62A11-02-220CH 62D11-02-050C 62A11-01-060S 62A11-02-085S 62A22-02-045CH 62V30-02-030S 62A11-02-080CH 62D11-02-060C 62V15-02-020CH 62D22-02-080SH 62A22-02-070CH 62A11-02-120CH 62V22-02-030SH 62A22-01-030S 62A22-01-080S 62D11-02-100S 62A11-01-120S 62A11-01-035C 62A11-01-150S 62A22-01-100C 62V11-02-110C 62V15-02-080CH 62A11-01-020C 62A11-01-020C 62A11-01-020SH 62A11-01-020SH 62A11-01-020CH 62A11-01-020C 62A11-01-020CH 62A11-02-020CH 62A11-01-020CH 62A11-02-050CH 62A11-01-020CH 62A11-01-020CH 62A11-02-020S 62A11-01-020SH 62A11-02-020CH 62A11-02-035C 62D22-02-035S 62A22-02-035C 62V03-02-030S 62A01-01-200S 62A15-02-020CH 62A11-02-035C 62A22-01-030S 62A22-02-035CH 62A11-02-035C 62A22-02-035CH 62A11-01-020SH 62A11-02-020S 62A11-02-035C 62A22-02-035CH 62A11-02-035CH 62A22-02-035CH 62A11-02-035CH 62A22-02-035CH 62A22-02-03