

ARTESYN AEE10W-M SERIES

10 Watts



The AEE10W-M series of 10 watt isolated DC-DC converters are designed for demanding instrumentation applications that require supplementary or reinforced insulation to comply with stringent industrial or medical safety standards.

DATA SHEET

Total Power:

10 Watts

Input Voltage:

12 V, 24 V or 48 V

of Outputs:

Single, Dual

SPECIAL FEATURES

- 4200 VAC reinforced insulation
- Insulation rated for 300 Vac working voltage
- Medical safety to UL/CSA/EN/IEC 60601-1 3rd Edition
- 2 MOOP rated
- Wide 2:1 input voltage range
- Fully regulated output voltage
- Low leakage current
- Operating temp. range -40°C to $+85^{\circ}\text{C}$ (with derating)
- Input filter meets EN 55022, class A and FCC, level A
- Overload protection
- 2"x 1" plastic package
- 3 years product warranty

SAFETY

- cUL/UL60950-1, CSA C22.2 No. 60950-1-03
- UL60601-1, CSA C22.2 No.601-1
- IEC/EN 60950-1, IEC/EN 60601-1 3rd Edition, 2 MOOP
- IEC60950-1 CB report, cUL/UL 60950-1 certificate
- UL60601-1 UL certificate
- Medical EMC Standard meets 4th Edition of EMI EN55011 and EMS EN60601-1-2




ELECTRICAL SPECIFICATIONS

| Input | |
|-------------------------|--|
| Input range | 9 - 18 Vdc; 18 - 36 Vdc; 36 - 75 Vdc |
| Efficiency | 82% |
| Output | |
| Voltage tolerance | ±1.0% |
| Line regulation | ±0.5% |
| Load regulation | 1.2% |
| Noise/ripple | 100 mV |
| OCP and S/C protection | Hiccup |
| Over voltage protection | Latched |
| OTP protection | Latched |
| Switching frequency | 150 KHz |
| Temperature coefficient | ±0.02 /°C |
| Isolation | |
| I/O isolation | 4200 Vrms 300 Vrms working voltage according to IEC/EN 60601-1 1000 Vrms working voltage according to IEC/EN 60950-1 |
| Insulation resistance | 10 Gohm |
| Insulation capacitance | 80 pF |

ENVIRONMENTAL SPECIFICATIONS

| | |
|-------------------------------------|----------------------------|
| Operating ambient temperature range | -40 °C to +85 °C |
| Storage temperature | -50 °C to +125 °C |
| Humidity | 5% to 95% (non-condensing) |
| Calculated MTBF | 1 Mhrs |

MECHANICAL DRAWINGS



| Pin Connectors | | |
|----------------|---------------|-------------|
| Pin No. | Single Output | Dual Output |
| 1 | +Vin | +Vin |
| 2 | -Vin | -Vin |
| 3 | +Vout | +Vout |
| 4 | No Pin | Common |
| 5 | -Vout | -Vout |

- T: 11.0 mm (0.43 inch) for 24 V Output Models
- T: 10.2 mm (0.40 inch) for Other Output Models
- All dimensions in mm (inches)
- Tolerance: X.X±0.25 (X.XX±0.01)
X.XX±0.13 (X.XXX±0.005)
- Pin dimension tolerance: ±0.05 (±0.002)

PHYSICAL CHARACTERISTICS

| | |
|--------------------------|---|
| Case Size (24 V Output) | 50.8 x 25.4 x 11 mm (2.0 x 1.0 x 0.43 inches) |
| Case Size (Other Output) | 50.8 x 25.4 x 10.2 mm (2.0 x 1.0 x 0.40 inches) |
| Case Material | Aluminium Alloy, Black Anodized Coating |
| Base Material | FR4 PCB (flammability to UL 94V-0 rated) |
| Pin Material | Copper Alloy with Gold Plate Over Nickel Subplate |
| Weight | 30 g |

ORDERING INFORMATION

| Artesyn Part number | Input Voltage | Output 1 Voltage | Output 2 Voltage | Maximum Power |
|---------------------|---------------|------------------|------------------|---------------|
| AEE01A12-M | 9 - 18 V | 5 V @ 1.6 A | | 8 W |
| AEE00B12-M | 9 - 18 V | 12 V @ 0.835 A | | 10 W |
| AEE00BB12-M | 9 - 18 V | 12 V @ 0.417 A | -12 V @ 0.417 A | 10 W |
| AEE00CC12-M | 9 - 18 V | 15 V @ 0.333 A | -15 V @ 0.333 A | 10 W |
| AEE02A24-M | 18 - 36 V | 5 V @ 2 A | | 10 W |
| AEE00B24-M | 18 - 36 V | 12 V @ 0.835 A | | 10 W |
| AEE00BB24-M | 18 - 36 V | 12 V @ 0.417 A | -12 V @ 0.417 A | 10 W |
| AEE00CC24-M | 18 - 36 V | 15 V @ 0.333 A | -15 V @ 0.333 A | 10 W |
| AEE02A48-M | 36 - 75 V | 5 V @ 2 A | | 10 W |
| AEE00B48-M | 36 - 75 V | 12 V @ 0.835 A | | 10 W |
| AEE00BB48-M | 36 - 75 V | 12 V @ 0.417 A | -12 V @ 0.417 A | 10 W |
| AEE00CC48-M | 36 - 75V | 15 V @ 0.333 A | -15 V @ 0.333 A | 10 W |



For international contact information,
visit advancedenergy.com.

powersales@aei.com (Sales Support)
productsupport.ep@aei.com (Technical Support)
+1 888 412 7832

ABOUT ADVANCED ENERGY

Advanced Energy (AE) has devoted more than three decades to perfecting power for its global customers. AE designs and manufactures highly engineered, precision power conversion, measurement and control solutions for mission-critical applications and processes.

Our products enable customer innovation in complex applications for a wide range of industries including semiconductor equipment, industrial, manufacturing, telecommunications, data center computing, and medical. With deep applications know-how and responsive service and support across the globe, we build collaborative partnerships to meet rapid technological developments, propel growth for our customers, and innovate the future of power.

PRECISION | POWER | PERFORMANCE

Specifications are subject to change without notice. Not responsible for errors or omissions. ©2020 Advanced Energy Industries, Inc. All rights reserved. Advanced Energy®, AE® and Artesyn™ are U.S. trademarks of Advanced Energy Industries, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Artesyn Embedded Technologies:](#)

[AEE00BB48-M](#) [AEE00BB24-M](#) [AEE00CC48-M](#) [AEE00BB12-M](#) [AEE00CC24-M](#) [AEE00CC12-M](#)