6000A Series

Surface Mount Power Inductors

	Inductance, L	lsat⁴	DC Current ²	SRF	DC Resistanc
Order Code	0.1V@100KHz (±10%)	Max.	Max.	Тур.	Max.
	μH	А	A	MHz	mΩ
60A582C	5.8	22	14.5	31	5
60A782C	7.8	19	13.5	26	6
60A103C	10.2	17	12.0	21	7
60A163C	16.0	13	9.6	17	9
60A193C	19.4	12	8.5	15	11
60A233C	23.0	11	8.4	13	12
60A273C	27.0	10	7.5	13	15
60A313C	31.4	9.5	6.8	12	18
60A363C	36.0	8.8	6.4	11	20
60A413C	41.0	8.4	5.6	10	26
60A583C	57.8	6.2	4.9	8	36

Storage temperature range	-40°C to 150°C
operating nee an temperature range	-40 0 10 85 0

SULDERING INFORMATION [®]	
Peak reflow solder temperature	245°C
Pin finish	Pure tin
Moisture sensitivity level ³	1



muRata I

FEATURES RoHS compliant¹

5.8µH to 57.8µH

J-STD-020D.1 reflow

Up to 22A saturation current

High energy storage, low resistance
UL 94V-0 packaging materials

Custom inductance values available


Murata Power Solutions

The 6000A series is a range of high-current, surface-mount power inductors. They are designed for use in power applications such as DC-DC converters, energy storage and input or output filtering. The products are supplied in tape and reel for high-volume, automated surface-mount assembly.



www.murata-ps.com/support

PACKAGE SPECIFICATIONS




Specifications typical at $T_A = 25^{\circ}C$

- For further information, please visit www.murata-ps.com/rohs
- 2 The maximum DC current is the value at which the inductance falls to 75% of its nominal value or when its temperature rise reaches 40°C, whichever is sooner.
- 3 Representative samples of the product were subjected to the conditioning described in IPC/JEDEC J-STD-020D and passed electrical testing, package coplanarity and visual inspection which revealed no external cracks or changes in package body flatness.
- 4 The instantaneous value when inductance drops to 80% of its normal value.
- 5 Terminal 3 is open-circuit and for mounting stability only.

muRata Ps Murata Power Solutions

6000A Series


Surface Mount Power Inductors



muRata Ps Murata Power Solutions

6000A Series

Surface Mount Power Inductors



Murata Power Solutions, Inc. 11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A. ISO 9001 and 14001 REGISTERED

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice. *© 2013 Murata Power Solutions, Inc.*

www.murata-ps.com/support

KMP_6000A_A04 Page 3 of 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

60A582C 60A782C 60A103C 60A163C 60A193C 60A233C 60A273C 60A313C 60A363C 60A413C 60A583C