

## BOS-Streamline

BS 200 F, IP 40 (IP 54), with loop for attaching lanyard



BS 200 F-7024

Order no.: 82200124

\* = Available on request.

### Characteristics

Colour of enclosure group

Graphite grey, similar to RAL 7024

Colour of enclosure group

Graphite grey

Protection class

IP 40, 54

Enclosure Material

ABS, decor seal made of TPE; for details see Technical Information

Scope of delivery

Lid and base, 1 screw

### Note


Upgradable to IP 54 by fitting DI-D.

### Dimensions

Dimensions

79.4 x 44.1 x 22.2 mm

Product drawing



### Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

## Technical documentation / Downloads

---

### Technical drawings

3D product data in STEP format: Registration necessary  
Product drawing in PDF format: 82200124 BS-200-F-7024.pdf (183.6 KB)  
Product drawing in DXF format: 82200124 BS-200-F-7024.dxf (2.5 MB)  
Drawing for mechanical processing: 82200124 BS-200-F-7024-G.dxf (1.2 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Drawing for max. PCB dimensions in PDF format: 82200124 BS-200-F-7024-pcb.pdf (136.0 KB)

Drawing for max. PCB dimensions in DXF format: 82200124 BS-200-F-7024-pcb.dxf (637.7 KB)

### Product information

BOS-Streamline GB.pdf (2.9 MB)

## Matching accessories

---



### Decor seals

82821003	BS 200 DI-D-1003	For BS 200	Signal yellow
82823001	BS 200 DI-D-3001	For BS 200	Signal red
82825005	BS 200 DI-D-5005	For BS 200	Signal blue
82826032	BS 200 DI-D-6032	For BS 200	Signal green
82827024	BS 200 DI-D-7024	For BS 200	Graphite grey



### Screw covers for enclosure screws

82800011	BS SA-7024	Graphite grey
----------	------------	---------------



### Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59006190	SHR Z KA25x6	SD = 2.5 / ND = 2.0 / KD = 4.4
----------	--------------	--------------------------------