



Click [here](#) for the 3D model.

Dimensions

D	29.5mm MAX
T	20.5mm MAX
H	29.5mm MAX
LL	5mm +/-2mm
S	10mm NOM
S1	15mm NOM
Wire Size	0.9mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	150
Component Weight	29 g

General Information

Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 83 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	6 mH (10 kHz)
Current	6 A
Temperature Range	-25/+120°C
DC Resistance	46 mOhms