


# Conductive Sensors Level Probes Types VN, VNY, VPC, VPP

CARLO GAVAZZI



- 1 to 4 electrodes
- Isolated or unisolated electrodes
- Cable or screw connection
- 1/2", 1" or 1 1/2" without pipe thread according to ISO 228/1-Gxxx"



## Product Description

Level sensor for measuring the level of conductive liquids, i.e. max./min. control of charging or discharging. The function is determined

by the amplifier relay used. The sensors are delivered with standard length electrodes - these are cut off to suit the application.

## Ordering Key

**VPC 110**

Type \_\_\_\_\_  
Housing material \_\_\_\_\_  
Number of electrodes \_\_\_\_\_  
Thread \_\_\_\_\_

## Type Selection

| Pipe thread | Electrode isolation | Housing Material | Ordering no. 1 electrode | Ordering no. 2 electrodes | Ordering no. 3 electrodes | Ordering no. 4 electrodes |
|-------------|---------------------|------------------|--------------------------|---------------------------|---------------------------|---------------------------|
| 1 1/2"      | No                  | Nylon 6          | <b>VN 1</b>              | <b>VN 2</b>               | <b>VN 3</b>               | <b>VN 4</b>               |
| 1 1/2"      | No                  | Nylon 6          | <b>VNY 1</b>             | <b>VNY 2</b>              | <b>VNY 3</b>              | <b>VNY 4</b>              |
| 1 1/2"      | Polyethylene        | Nylon 6          | <b>VNI 1</b>             | <b>VNI 2</b>              | <b>VNI 3</b>              | <b>VNI 4</b>              |
| 1 1/2"      | Polyethylene        | Nylon 6          | <b>VNYI 1</b>            | <b>VNYI 2</b>             | <b>VNYI 3</b>             | <b>VNYI 4</b>             |
| 1/2"        | Polyethylene        | PVC              | <b>VPC 105</b>           | <b>VPC 205</b>            |                           |                           |
| 1"          | Polyethylene        | PVC              | <b>VPC 110</b>           | <b>VPC 210</b>            | <b>VPC 310</b>            |                           |
| 1/2"        | Kynar (PVDF)        | Polypropylene    | <b>VPP 105</b>           | <b>VPP 205</b>            |                           |                           |
| 1"          | Kynar (PVDF)        | Polypropylene    | <b>VPP 110</b>           | <b>VPP 210</b>            | <b>VPP 310</b>            |                           |

## Specifications

|  |   |   |  |
|--|---|---|--|
| <b>Electrodes</b><br>Material<br>Standard length<br>VN, VNY<br>VPC, VPP<br>Diameter<br>VN, VNY<br>VPC, VPP | Stainless steel<br>AISI316/DIN1.4401<br>100 cm<br>50 cm<br>Ø 5 mm<br>Ø 4 mm | <b>Environment</b><br>Degree of protection<br>Operating temperature<br>VN, VNY<br>VPC<br>VPP<br>Storage temperature<br>VN, VNY<br>VPC, VPP<br>Pressure<br>VN, VNY, VPP<br>VPC | IP 67<br>0 to 90°C (32° to 194 °F)<br>0 to 60°C (32° to 140 °F)<br>0 to 100°C (32° to 212 °F)<br>-25° to 100°C (-13° to 212°F)<br>-20° to 110°C (-40° to 230°F)<br>10 bar at 60°C<br>2 bar at 60°C |
| <b>Housing</b><br>Connection<br>VN<br>VNY, VPC, VPP  | Cable (PVC), 2 m<br>Screw terminals   | <b>CE marking</b>   | IEC 529  |

## Mode of Operation

The length of the electrodes determines the levels which will be detected and the amplifier chosen determines the function (see SV...,





S195/196, S1961, ELA, ELC or ELD). If the container is made of a conductive material this can be used as common electrode.

## Accessories


Extension joint for Ø5 mm electrodes (VN/VNI):

**VD1**

## Dimensions



## Wiring Diagrams



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[VPP105](#) [VPP205](#) [VN3](#) [VPC205](#) [VPC210](#) [VNY2](#) [VNY3](#) [VNYI4](#) [VN2](#) [VNYI2](#) [VNYI3](#) [VPC110](#) [VNY4](#) [VPP310](#)  
[VPC310](#)