OVR T1-T2 3N 12.5-275s P TS QS 2CTB815710R0700

EAN: 3660308524928 FR : B752492

Type

T1-T2

Imax: 80 kA

limp: 12,5 kA

Type 1 + 2 SPD's have characteristics of type 1 but also type 2, they are capable of discharging a very high lightning current (T1 10/350µs) and they have as well a low residual voltage (Up).

They are installed in the main distribution switchboard but also in subdistribution board.

Because of their power, Type 1 + 2 SPD's can let pass through a too high residual voltage, if the announced Up is not compatible with the withstand voltage of the equipment to protect or if the cable length to the equipment is longer than 10m, another level of coordination with OVR T2-T3, OVR T3 will be needed.

Thanks to the patented Safety Reserve system, you can extend the lifespan of the installation plan maintenance to reduce downtime risk.

Up: 1,1 kV System

TT/TN-S: 230/400 V



- Safety Reserve system
- Din rail mounting
- Pluggable
- Improved safety
- Back up protection up to 160 A Fuse or 125 A Mcb

IEC 61643-11
EN 61643-11
Key characteristic
Key characteristic Protection mode
Protection mode

Key characteristics			
Protection mode			L-N/L-PE/N-PE
Number of protected lines	<u> </u>		4
Test class			-
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			Yes
Electrical characteristics			
Nominal discharge current	In (8/20)	kA	20
Maximal discharge current	I _{max} (8/20)	kA	80
Impulse current	/ _{imp} (10/350)	kA	12,5
Maximal continuous operating voltage	Uc	V	275
Maximal continuous operating voltage d.c	U c d.c	V	-
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	U _P (L-PE)	kV	1,35
Voltage protection level at In	U _P (L-N)	kV	1,2
Voltage protection level at In	U _P (N-PE)	kV	1,1
Short circuit withstand	/sccr	kA	100
Total current	/TOTAL	kA	50
Follow current interrupted	/ fi	kA	- / 0,1
Ground residual current	/PE	μΑ	<10
TOV withstand (L-N: 5s / N-PE: 200 ms)	<i>U</i> _T	V	337 / 1200
Voltage Combination Wave	<i>U</i> oc	kV	-
Required thermal/back up protection			
Curve B or C Circuit breaker		Α	≤ 125
gG - gL fuse		Α	≤ 160
Comments			
Mechanical characteristics			
Dimensions	HxWxD	mm	95x71.2x69.4
Wire range : Solid wire		mm²	2.5 35
Wire range : Stranded wire		mm²	2.5 25
Stripping length		mm	12.5
Packing quantities		piece	Per 1
Miscellaneous characteristics			
Maximal altitude		m	2 000
Weight		g	600
Response time		ns	<25
Fire resistance according to UL 94			V-0
Replacement cartridges			
Phase / Product ID	OVR T1-T2 12.5-275s C QS		2CTB815710R2600
Neutral / Product ID	OVR T1-T2 N 50-275s C QS		2CTB815710R2700

















