

## FEATURES

### 1. Controls low-level analog signals

PhotoMOS relays feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.

### 2. Controlled with low-level input signals

### 3. Controls various types of loads such as relays, motors, lamps and solenoids.

### 4. Optical coupling for extremely high isolation

Unlike mechanical relays, the PhotoMOS relay combines LED and optoelectronic device to transfer signals using light for extremely high isolation.

### 5. Eliminates the need for a counter electromotive force protection diode in the drive circuits on the input side

### 6. Stable on resistance

### 7. Low-level off state leakage current

### 8. Eliminates the need for a power supply to drive the power MOSFET

A power supply used to drive the power MOSFET is unnecessary because of the built-in optoelectronic device. This results in easy circuit design and small PC board area.

### 9. Low thermal electromotive force (Approx. 1 $\mu$ V)

## TYPICAL APPLICATIONS

- High-speed inspection machines
- Telephone equipment
- Data communication equipment
- Computer

## TYPES

### 1. DC type (AQV10 types)

Output rating*		Part No.				Packing quantity	
		Through hole terminal	Surface-mount terminal		Tape and reel packing style		
Load voltage	Load current		Tube packing style		Picked from the 1/2/3-pin side	Picked from the 4/5/6-pin side	Tube
40 V	700 mA	AQV101	AQV101A	AQV101AX	AQV101AZ	1 tube contains 50 pcs. 1 batch contains 500 pcs.	1,000 pcs
60 V	600 mA	AQV102	AQV102A	AQV102AX	AQV102AZ		
250 V	300 mA	AQV103	AQV103A	AQV103AX	AQV103AZ		
400 V	180 mA	AQV104	AQV104A	AQV104AX	AQV104AZ		

\*Indicate the peak AC and DC values.

Note: For space reasons, the package style indicator "X" or "Z" are not marked on the relay.

### 2. AC/DC type (AQV20 types)

Output rating*		Part No.				Packing quantity	
		Through hole terminal	Surface-mount terminal		Tape and reel packing style		
Load voltage	Load current		Tube packing style		Picked from the 1/2/3-pin side	Picked from the 4/5/6-pin side	Tube
40 V	500 mA	AQV201	AQV201A	AQV201AX	AQV201AZ	1 tube contains 50 pcs. 1 batch contains 500 pcs.	1,000 pcs
60 V	400 mA	AQV202	AQV202A	AQV202AX	AQV202AZ		
250 V	200 mA	AQV203	AQV203A	AQV203AX	AQV203AZ		
400 V	150 mA	AQV204	AQV204A	AQV204AX	AQV204AZ		

\*Indicate the peak AC and DC values.

Note: For space reasons, the SMD terminal shape indicator "A" and the package style indicator "X" or "Z" are not marked on the relay.

# HF PhotoMOS (AQV10○, 20○)

## RATING

### 1. DC type (AQV10 types)

1) Absolute maximum ratings (Ambient temperature: 25°C 77°F)

Item		Symbol	AQV101(A)	AQV102(A)	AQV103(A)	AQV104(A)	Remarks
Input	LED forward current	$I_F$	50 mA				
	LED reverse voltage	$V_R$	10 V				
	Peak forward current	$I_{FP}$	1 A				f = 100 Hz, Duty factor = 0.1%
	Power dissipation	$P_{in}$	150 mW				
Output	Load voltage (DC)	$V_L$	40 V	60 V	250 V	400 V	
	Continuous load current (DC)	$I_L$	0.7 A	0.6 A	0.3 A	0.18 A	
	Peak load current	$I_{peak}$	1.8 A	1.5 A	0.6 A	0.5 A	100 ms (1 shot)
	Power dissipation	$P_{out}$	360 mW				
Total power dissipation		$P_T$	410 mW				
I/O isolation voltage		$V_{iso}$	1,500 V (AC)				
Temperature limits	Operating	$T_{opr}$	-40°C to +85°C -40°F to +185°F				Non-condensing at low temperatures
	Storage	$T_{stg}$	-40°C to +100°C -40°F to +212°F				


2) Electrical characteristics (Ambient temperature: 25°C 77°F)

Item			Symbol	AQV101(A)	AQV102(A)	AQV103(A)	AQV104(A)	Condition	
Input	LED operate current	Typical	$I_{Fon}$	2.3 mA				$I_L = \text{Max.}$	
		Maximum		5 mA					
	LED turn off current	Minimum	$I_{Foff}$	0.8 mA				$I_L = \text{Max.}$	
		Typical		2.2 mA					
LED dropout voltage	Typical	$V_F$	2.3 V				$I_F = 10 \text{ mA}$		
	Maximum		3 V						
Output	On resistance	Typical	$R_{on}$	0.3 Ω	0.37 Ω	2.7 Ω	6.3 Ω	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time	
		Maximum		0.5 Ω	0.7 Ω	4 Ω	8 Ω		
Off state leakage current		Maximum	—	1 μA				$I_F = 0 \text{ mA}$ , $V_L = \text{Max.}$	
Transfer characteristics	Switching speed	Turn on time*	Typical	0.23 ms	0.22 ms	0.13 ms	0.09 ms	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$	
			Maximum	1 ms					
	Turn off time*	Typical	$T_{off}$	0.07 ms			0.08 ms	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$	
		Maximum		1 ms					
	I/O capacitance		Typical	$C_{iso}$	1.3 pF				f = 1 MHz $V_B = 0 \text{ V}$
			Maximum		3 pF				
Initial I/O isolation resistance		Minimum	$R_{iso}$	1,000 MΩ				500 V DC	

Note: Recommendable LED forward current  $I_F = 10 \text{ mA}$ .

For type of connection.

\*Turn on/Turn off time



# HF PhotoMOS (AQV100, 200)

## 2. AC/DC type (AQV20 types)

1) Absolute maximum ratings (Ambient temperature: 25°C 77°F)

Item		Symbol	Type of connection	AQV201(A)	AQV202(A)	AQV203(A)	AQV204(A)	Remarks	
Input	LED forward current	$I_F$		50 mA				f = 100 Hz, Duty factor = 0.1%	
	LED reverse voltage	$V_R$		10 V					
	Peak forward current	$I_{FP}$		1 A					
	Power dissipation	$P_{in}$		150 mW					
Output	Load voltage (peak AC)	$V_L$		40 V	60 V	250 V	400 V	A connection: Peak AC, DC B, C connection: DC	
	Continuous load current	$I_L$		A	0.5 A	0.4 A	0.2 A		0.15 A
				B	0.7 A	0.6 A	0.3 A		0.18 A
				C	1.0 A	0.8 A	0.4 A		0.25 A
	Peak load current	$I_{peak}$			1.8 A	1.5 A	0.6 A		0.5 A
Power dissipation	$P_{out}$		360 mW						
Total power dissipation		$P_T$		410 mW					
I/O isolation voltage		$V_{iso}$		1,500 V AC					
Temperature limits	Operating	$T_{opr}$		-40°C to +85°C -40°F to +185°F				Non-condensing at low temperature	
	Storage	$T_{stg}$		-40°C to +100°C -40°F to +212°F					


2) Electrical characteristics (Ambient temperature: 25°C 77°F)

Item		Symbol	Type of connection	AQV201(A)	AQV202(A)	AQV203(A)	AQV204(A)	Remarks		
Input	LED operate current	Typical	$I_{Fon}$	—	2.4 mA				$I_L = \text{Max.}$	
		Maximum			5 mA					
	LED turn off current	Minimum	$I_{Foff}$	—	0.8 mA				$I_L = \text{Max.}$	
		Typical			2.2 mA					
LED dropout voltage	Typical	$V_F$	—	2.3 V				$I_F = 10 \text{ mA}$		
	Maximum			3 V						
Output	On resistance	Typical	$R_{on}$	A	0.6 Ω	0.74 Ω	5.5 Ω	12.4 Ω	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time	
		Maximum			1 Ω	1.4 Ω	8 Ω	16 Ω		
		Typical	$R_{on}$	B	0.3 Ω	0.37 Ω	2.7 Ω	6.2 Ω	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time	
		Maximum			0.5 Ω	0.7 Ω	4 Ω	8 Ω		
		Typical	$R_{on}$	C	0.15 Ω	0.18 Ω	1.4 Ω	3.1 Ω	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$ Within 1 s on time	
		Maximum			0.25 Ω	0.35 Ω	2 Ω	4 Ω		
Off state leakage current		Maximum	—	—	1 μA				$I_F = 0 \text{ mA}$ , $V_L = \text{Max.}$	
Transfer characteristics	Switching speed	Turn on time*	Typical	$T_{on}$	—	0.38 ms	0.41 ms	0.21 ms	0.18 ms	$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$
			Maximum			1 ms				
		Turn off time*	Typical	$T_{off}$	—	0.08 ms		0.07 ms		$I_F = 10 \text{ mA}$ $I_L = \text{Max.}$
			Maximum			1 ms				
	I/O capacitance		Typical	$C_{iso}$	—	1.3 pF				f = 1 MHz $V_B = 0 \text{ V}$
		Maximum	3 pF							
Initial I/O isolation resistance		Minimum	$R_{iso}$	—	1,000 MΩ				500 V DC	

Note: Recommendable LED forward current  $I_F = 10 \text{ mA}$ .

For type of connection.

\*Turn on/Turn off time



- For Dimensions.
- For Schematic and Wiring Diagrams.
- For Cautions for Use.