




Product group data DILEM4

General

Standards and specifications			IEC/EN 60947, VDE 0660, CSA, UL
Maximum operating frequency			
Mechanical	Ops./h	9000	
Climatic proofing			Damp heat, constant, to IEC 60 068-2-3, Damp heat, cyclical, to IEC 60 068-2-30
Ambient temperature			
Open	°C	-25/50	
enclosed	°C	-25/40	
Mounting position			As required, except vertical with terminals A1/A2 at the bottom
Mechanical shock resistance (IEC/EN 60068-2-27)			
Half-sinusoidal shock, 10 ms			
Basic unit without auxiliary contact module			
Main contacts, make contacts	g	10	
Main contacts Make/break contacts	g	10/8	
Basic unit with auxiliary contact module			
Auxiliary contacts Make/break contacts	g	10/8	
Degree of protection			IP20
Protection against direct contact from the front when actuated by a perpendicular test finger (IEC 536)			Finger and back-ofhand proof
Weight	kg	0,2	
Terminal capacity of auxiliary and main contacts			
Solid	mm ²	1 × (0,75 – 2,5) 2 × (0,75 – 2,5)	
Flexible with ferrule	mm ²	1 × (0,75 – 1,5) 2 × (0,75 – 1,5)	
Solid or stranded	AWG	18 – 14	
Terminal screw		M3.5	
Pozidriv screwdriver	Size	2	
Standard screwdriver	mm	0,8 × 5,5 1 × 6	
Max. tightening torque	Nm	1,2	
Main conducting paths			
Rated impulse withstand voltage	U_{imp}	V AC	6000
Overvoltage category/pollution degree			III/3
Rated insulation voltage			
AC	U_i	V AC	690
Rated operational voltage			
Rated operational voltage	U_e	V AC	690
Safe isolation to VDE 0106 Part 101 and Part 101/A1			
between coil and contacts		V AC	300
between the contacts		V AC	300
Making capacity ($\cos\phi$ to IEC/EN 60947)		A	110
Breaking capacity			
220/230 V		A	90
380/400 V		A	90
500 V AC		A	64
660/690 V		A	54
Component lifespan			
AC-1 component lifespan			 See Page 7
AC-3 component lifespan			 See Page 8
AC-4 component lifespan			 See Page 9
Short-circuit protection Maximum fuse			
Type "1" coordination	gL/gG	A	20

Type "2" coordination gL/gG A 10

AC

AC-1 duty

conv. therm. current 3-pole 50 – 60 Hz

open

at 40 °C A 22

at 50 °C A 20

at 55 °C A 19

Enclosed A 16

1-pole open A 60

conv. therm. current three/four main contacts in parallel, enclosed A 50

AC-3 duty

Rated operational current AC-3 open, 50 – 60 Hz, 3-pole

220/230 V I_e A 8,8

240 V I_e A 8,8

380/400 V I_e A 8,8

415 V I_e A 8,8

440V I_e A 8,8

500 V I_e A 6,4

660/690 V I_e A 4,8

Rating, AC-3 motor load switch

220/230 V P kW 2,2

240V P kW 2,5

380/400 V P kW 4

415 V P kW 4,3

440 V P kW 4,6

500 V P kW 4

660/690 V P kW 4

AC-4 duty

Rated operational current AC-4 open, 50 – 60 Hz, 3-pole

220/230 V I_e A 6,6

240 V I_e A 6,6

380/400 V I_e A 6,6

415 V I_e A 6,6

440 V I_e A 6,6

500 V I_e A 5

660/690 V I_e A 3,4

AC-4

220/230 V P kW 1,5

240 V P kW 1,8

380/400 V P kW 3

415 V P kW 3,1

440 V P kW 3,3

500 V P kW 3

660/690 V P kW 3

DC

Operations

Switching DC current



DC-3

220 V A 1

DC-5

110 V A 2,5

220 V A 1

Current heat losses (3- or 4-pole)

to I_{th} W 2,7

Magnet systems

Voltage tolerance

AC operation

Single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz	$\times U_c$	0,8 – 1,1
Dual-frequency coil 50/60 Hz	$\times U_c$	0,85 – 1,1

Power consumption

AC operation

Single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz	Pick-up	VA	25
Single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz	Pick-up	W	22
Single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz	Sealing	VA	4,6
Single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz	Sealing	W	1,3
Dual-frequency coil 50/60 Hz at 50 Hz	Pick-up	VA	30
Dual-frequency coil 50/60 Hz at 50 Hz	Pick-up	W	26
Dual-frequency coil 50/60 Hz at 50 Hz	Sealing	VA	5,4
Dual-frequency coil 50/60 Hz at 50 Hz	Sealing	W	1,6
Dual-frequency coil 50/60 Hz at 60 Hz	Pick-up	VA	29
Dual-frequency coil 50/60 Hz at 60 Hz	Pick-up	W	24
Dual-frequency coil 50/60 Hz at 60 Hz	Sealing	VA	3,9
Dual-frequency coil 50/60 Hz at 60 Hz	Sealing	W	1,1

Duty factor % DF 100

Switching times at 100 % U_c (main circuits)

Make contact

Closing delay

Closing delay min.	ms	14
Closing delay max.	ms	21

Opening delay

Opening delay min.	ms	8
Opening delay max.	ms	18

Closing delay with top mounting auxiliary contact

ms	45
----	----

Reversing contactors

Changeover time at 110 % U_c

Changeover time min.	ms	16
Changeover time max.	ms	21
Arcing time at 690 V AC	ms	12

Auxiliary contacts

Interlocked opposing contacts to ZH 1/457, including auxiliary contact module Yes

Rated impulse withstand voltage U_{imp} V AC 6000

Overvoltage category/pollution degree III/3

Rated insulation voltage U_i V AC 690

Rated operational voltage

Rated operational voltage	U_e	V AC	600
---------------------------	-------	------	-----

Safe isolation to VDE 0106 Part 101 and Part 101/A1

between coil and auxiliary contacts	V AC	300
-------------------------------------	------	-----

between the auxiliary contacts	V AC	300
--------------------------------	------	-----

Rated operational current

AC-15

220/240 V	I_e	A	6
-----------	-------	---	---

380/415 V	I_e	A	3
-----------	-------	---	---

500 V	I_e	A	1,5
-------	-------	---	-----

Top mounting auxiliary contacts

220/240 V	I_e	A	4
-----------	-------	---	---

380/415 V	I_e	A	2
-----------	-------	---	---

500V	I_e	A	1,5
------	-------	---	-----


DC-13

Contacts in series:			
1	24 V	A	2,5
2	60 V	A	2,5
3	100 V	A	1,5
3	220 V	A	0,5
Conventional thermal current	I_{th}	A	10
Control circuit reliability at $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA	H_F	Fault probability	$<10^{-8}$, < 1 fault in 100 million Operations
Component lifespan at $U_e = 240$ V			
AC-15	Operations	$\times 10^6$	0,2
DC-13			
L/R = 50ms: 2 contacts in series at $I_e = 0.5$ A	Operations	$\times 10^6$	0,15
Short-circuit rating without welding			
Maximum overcurrent protective device			PKZM0-4
Short-circuit protection Maximum fuse			
500 V	A gG/gL		6
500 V	A fast		10
Current heat loss at I_{th}			
Current heat loss per contact at I_e	W		0,2

Notes

 See Page 10


Dimensions

 See Page 10

Determination of the maximum number of operations per hour in relation to rating and utilization category (approximate values), at 400 V

P_N = Max. motor rating (kW) of the relevant contactor

Ops./h = Maximum number of switching operations per hour




Type	Tripping characteristic AC-1	AC-3	AC-2 AC-4
DILE(E)M	2	1	3
DIL00M(-G)	2	1	3
DIL00AM(-G)	2	1	3
DIL0M(-G)	2	1	3
DIL0AM(-G)	2	1	3
DIL1M(-G)	2	1	3
DIL1AM(-G)	2	1	3
DIL2M(-G)	2	1	3
DIL2AM(-G)	2	1	3

Determination of the maximum number of operations per hour in relation to rating and utilization category (approximate values), at 400 V

P_N = Max. motor rating (kW) of the relevant contactor

Ops./h = Maximum number of switching operations per hour



Type	Tripping characteristic AC-1-1	AC-3	AC-4
DIL3M80	2	1	5
DIL3AM85	2	1	5
DIL4M115	2	3	6
DIL4AM145	2	3	6
DILM185	2	1	8
DILM225	2	1	8
DILM250	2	1	8
DILM300	3	2	9
DILM400	3	2	9
DILM500	3	2	9
DILM580	3	4	7
DILM650	3	4	7
DILM750	3	4	7
DILM820	3	4	7

Switching DC

----- conductor can be installed by the customer as required


DILEEM to DILM820

Without overload relay
 $\leq 60 \text{ V DC}$


$> 60 \text{ V DC}$

With overload relay
 $> 60 \text{ V DC}$

1-pole





2-pole




**DILEM4
DIL00M4
DILP160 to DILP800**

1-pole



2-pole



Switching duty for non-motor loads, 3-pole, 4-pole

Operating characteristics

Non-inductive or slightly inductive loads

Typical applications



Electric heaters

Electrical characteristics

Make: 1 × rated current
 Break: 1 × rated current

Utilization category

100 % AC-1



Normal switching duty

Squirrel-cage motors

Operating characteristics

Starting: from rest

Stopping: after attaining full running speed

Electrical characteristics

Make: up to $6 \times$ rated motor current

Break: $1 \times$ rated motor current

Utilization category

100% AC-3

Typical applications

Compressors

Pumps

Fans

Valves

Drives in general in manufacturing and processing machines

Lifts

Escalators

Conveyor belts



Bucket elevators

Mixers

Agitators

Centrifuges

Air-conditioning systems



Extreme switching duty

Squirrel-cage motors

Operating characteristics

Inching, plugging, reversing

Electrical characteristics

Make: up to $6 \times$ rated motor current

Break: $6 \times$ rated motor current

Utilization category



100 % AC-4

Typical applications

Printing presses

Wire-drawing machines Centrifuges

Special drives for manufacturing and processing machines



The following applies for the short-circuit rating of the main contacts and the fusing of the auxiliary contacts: See the "Fuses" transparent overlay for time/current characteristics (please enquire).

The following values apply with the max. permissible ambient temperature:

AC

AC-1-duty conv. therm. current - enclosed

AC-1 duty 1-pole - open

AC-1-duty three/four main contacts parallel - enclosed

AC-3-duty rated operational current - open

AC-4-duty rated operational current - open

DC

Rated operational current Open

The following applies for the rated operational current as well as the component lifespan of the DC-13 auxiliary contact: On and off switching characteristics to DC-13, L/R constant as defined

