

## GLASS PASSIVATED BRIDGE RECTIFIERS

REVERSE VOLTAGE - 50 to 1000Volts  
FORWARD CURRENT - 3.0 Amperes


### FEATURES

- Glass passivated chip junction
- High case dielectric strength
- High surge current capability  
Ideal for printed circuit board

### MACHANICAL DATA

- Terminal:Plated leads solderable per MIL-STD 202E,  
Method 208C
- Case:UL-94 Class V-0 recognized Flame Retardant Epoxy
- Polarity:Polarity symbol marked on body
- Mounting position:any

### D3K



## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave ,60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	D3KB05	D3KB1	D3KB2	D3KB4	D3KB6	D3KB8	D3KB10	UNIT
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Output Current @ T <sub>c</sub> =140°C (with heatsink) @ T <sub>a</sub> =29°C (without heatsink)	I <sub(av)< sub=""></sub(av)<>	3 1.2							A
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	I <sub>FSM</sub>	90							A
Maximum Forward Voltage at 1.5A DC	V <sub>F</sub>	1.05							V
I <sup>2</sup> t Rating for Fusing (t<8.3ms)	I <sup>2</sup> t	35							A <sup>2</sup> s
Maximum Typical Thermal Resistance without heatsink with heatsink without heatsink	R <sub>θja</sub> R <sub>θjc</sub> R <sub>θjL</sub>	55 1.5 15							°C/W
Maximum DC Reverse Current @ T <sub>a</sub> =25°C at Rated DC Blocking Voltage @ T <sub>a</sub> =125°C	I <sub>R</sub>	10.0 500							μA
Operating Temperature Range	T <sub>J</sub>	-55 to +150							°C
Storage Temperature Range	T <sub>STG</sub>	-55 to +150							°C

NOTES:The typical data above is for reference only(典型值仅供参考).

**RATING AND CHARACTERISTIC CURVES**  
**D3KB05 thru D3KB10**



FIG.1-DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG.2-MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS





FIG.4-TYPICAL REVERSE CHARACTERISTICS



The cruve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!