


REVISIONS		REVISED	DATE	APPR
SYM	DESCRIPTION			



STANDOFF	
PART NO.	DIM. A
8820	.125
8823	.187
2330	.250
8826	.312
2331	.375
8829	.437
2332	.500
8832	.562
8835	.625
8838	.687
2333	.750
8841	.812
8844	.875
8847	.937
2334	1.000

MATERIAL: BRASS ALLOY, 360		FINISH: NICKEL	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		TITLE: 4-40 THD	
XX	XXX	BRASS HEX STANDOFF	
---	---	1/4 HEX THD THRU #4-40	
FRACTIONS	ANGLES	DRAWN: T. LORD DATE: 8/16/05	
---	---	CHECKED: T. LORD DATE: 8/16/05	
SCALE	NONE	APPROVED: T. LORD DATE: 8/16/05	
HEAT TREAT: ---	---	SIZE: B	DRAWING NUMBER: SD: SMP-00445
PLOT SCALE: 1=1	---	ISSUE: B	

**ABBATRON**  
 Electronic Connectors and Hardware  
 632 Arch Street, Meadville, Pa. 16335