

VG M25 - K 68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, M 25, 10 mm, OD min. 13 - OD max. 18 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	1772310000
Type	VG M25 - K 68
GTIN (EAN)	4032248129973
Qty.	25 pc(s).

Creation date November 26, 2020 12:06:13 PM CET

Catalogue status 20.11.2020 / We reserve the right to make technical changes.

VG M25 - K 68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	47 mm	Length (inches)	1.85 inch
Net weight	22.1 g		

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (CSA)	115116
Certificate no. cable gland (GERMLOYD)	E-14046	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260		

General information

AF size 1	33 mm	Cable glands	metric
External thread	M 25	Halogen	Yes
Length of thread	10 mm	Material	Polyamide 6
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	18 mm	Outer cable diameter, min.	13 mm
Pitch of thread	1.5 mm	Protection degree	IP67, IP68 - 5 bar (30 min.)
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Seal insert	CR
Standards	EN/IEC 62444	Tightening torque	3.5 Nm
Torque for cap nut, max.	8.5 Nm	Torque for cap nut, min.	7.5 Nm
Torque for connecting adapter, max.	8.5 Nm	Torque for connecting adapter, min.	7.5 Nm
Torque for lock nut, max.	8.5 Nm	Torque for lock nut, min.	7.5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32	eClass 11.0	27144432

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	STEP
Engineering Data	EPLAN.WSCAD