







SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005JLVG

REVISONS		DCI. NO. SPC-F005	* Effective: 7/8/02	* DCP No: 1398				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVI	DATE
XX	XX	XXXX	XXXX	03-10-08	XXXX	03-10-08	XXXX	03-10-08
XXXX	XXXX		XXXX	03-10-08	XXXX	03-10-08	XXXX	03-10-08



① Plug Right Angle, No. of Positions 4 To 80 Ways	② Gold Plated	③ Blank: Standard Type
---	---------------	------------------------

2206RPA-10G
① ② ③

- **Material and Finish**
 1. Insulator : PBT (UL94V-0)
 2. Contact : Copper Alloy
 3. Plating : Gold Plated
- **Feature**
 1. Design for Home Appliances, Aviation Electronics, Automobile Electronics and Computer(PC) Peripherals.
- **Ordering Information**

- **Specifications**
 1. Current rating : 10A AC/DC
 2. Voltage rating : 50V AC/DC
 3. Contact resistance : 20m ohm, max.
 4. Insulation resistance : 500M ohm, Min. At 100V DC
 5. Withstanding voltage : 500V AC for one minute
 6. Operating temperature Range : -25°C to +125°C



RoHS
Compliant

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
XXXX	03-10-08
CHECKED BY:	DATE:
XXXX	03-10-08
APPROVED BY:	DATE:
XXXX	03-10-08

DRAWING TITLE:

PC Board

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	2206RPA-10G	11N6306	XX
SCALE:	NTS	U.D.M.: INCHES [mm]	SHEET: 1 OF 1