



PCEM Family ERU 51

Power choke e-Mobility for DC/DC converter application

Series/Type:
Ordering code: **B78338*A004**
Date: 2018-10-09
Version: 07

Construction

- MnZn ferrite core
- Helical Winding

Features

- Number of turns: 3
- Maximum limited component temperature 150°C
- RoHS compatible
- Qualified with reference to AEC-Q200

Application

- Output Choke for boardnet converters in hybrid or electrical vehicles

Terminals

- Hole for M4 screw, bare copper

Delivery mode

- Cardboard box with 16 chokes on two levels in a box


Marking

- Product brand, ordering code, date code / production identification code



Assembly

- Additional clamp to be considered by customer

Circuit diagram



Dimensional drawing




Alle Maßangaben in mm !
All dimensions in mm !

Tolerance ISO 8015. Size ISO 14405 (E). ISO 2768-c

- 1) blank
- 2) Bereich für Parallelität
area for parallelism
- 3) Maße im eingebauren Zustand
dimensions in assembled state
- 4) gemessen am unteren Kern
measured at the lower core
- 5) an Ober- und Unterseite kein Überstand zulässig
on top and bottom side no projection permissible

Packaging



Technical data and measuring conditions

Specified @ 25°C if not mentioned otherwise, all values without tolerance are typical values

Rated Inductance L_R	Measured at terminals [1, 2], measuring conditions 100 kHz, 1 V
Inductance tolerance	± 10%
Saturation current I_{sat}	Current that will result in approx. 20% drop in inductance values. Temperature response needs to be verified in specific applications. Test results on request.
DC resistance R_{typ}	Measured at terminals [1, 2]
High voltage: N1 - core	500 V _{dc} , 1 s
Switching frequency	200 kHz
Operating temperature range	- 40 °C ... + 150 °C

Characteristics and ordering codes


L_R	I_{sat} 25°C	I_{sat} 100°C	I_{sat} 125°C	R_{DC} (typ)	R_{DC} (max)	Approx. Weight	Project Number	Ordering code
μH	A	A	A	mΩ	mΩ	g		
1.4	300	270	250	0.25	0.30	225	T8414	B78338P2320A004
2.1	205	185	170	0.25	0.30	225	T6823	B78338P2168A004
2.6	160	150	140	0.25	0.30	225	T8380	B78338P2315A004

Other inductance values are available, only on request


L vs. DC bias current I_{DC}

Typical values, values calculated for 3 turns from measurement with 20 turns


B78338P2320A004 (T8414):



B78338P2168A004 (T6823):



B78338P2315A004 (T8380):



Cautions and warnings

- Additional information is contained in our data books, which are also available on the internet. Particular attention should be paid to the derating curves given there. The soldering conditions given there should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not to the housing.
- If the components are to be washed varnished, it is necessary to check whether any washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation. Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.
- The following points must be observed if the components are potted in customer applications:
 - Many potted materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties and, in extreme cases, can damage the core or plastic housing mechanically;
 - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue;
 - The effect of the potting material can change the high frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.

Even for customer specific products, conclusive validation of the components in the circuit can only be carried out by the customer.

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10