


TS 35X15/LL 1M/ST/ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

| | |
|------------|--|
| Version | Rail, TS 35, TS 35 x 15, with slot, Steel, galvanic zinc plated and passivated |
| Order No. | 0236510000 |
| Type | TS 35X15/LL 1M/ST/ZN |
| GTIN (EAN) | 4008190017699 |
| Qty. | 1 m |

Creation date March 30, 2021 5:38:54 AM CEST

Catalogue status 12.03.2021 / We reserve the right to make technical changes.

TS 35X15/LL 1M/ST/ZN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|----------------|------------|-----------------|------------|
| Depth | 15 mm | Depth (inches) | 0.591 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Net weight | 630 g | Width | 1,000 mm |
| Width (inches) | 39.37 inch | | |

Mounting rail

| | | | |
|---|-------------------------------------|----------|--|
| Drill-hole diameter | 5.2 mm | | |
| Installation advice | Direct mounting | | |
| Length of the terminal rail | min. | 0 mm | |
| | max. | 1,000 mm | |
| | nominal | 1,000 mm | |
| Material | Steel | | |
| Pre-punched mounting rail | Yes | | |
| Short circuit strength corresponds to E-Cu wire | 50 mm ² | | |
| Short-time withstand current according to IEC 60947-7-2 | 6 kA/1s | | |
| Slit gap | 11 mm | | |
| Slit gap | | | |
| Slit length | 25 mm | | |
| Slit length | | | |
| Slit width | 5.2 mm | | |
| Slit width | | | |
| Slotted drill holes | Yes | | |
| Solder eyelet hole diameter (D) | 5.2 mm | | |
| Spacing of holes, centre-to-centre | 36 mm | | |
| Standards | In accordance with DIN EN 60715 | | |
| Surface finish | galvanic zinc plated and passivated | | |
| Thickness | 1.5 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001285 | ETIM 7.0 | EC001285 |
| ECLASS 9.0 | 27-40-06-02 | ECLASS 9.1 | 27-40-06-02 |
| ECLASS 10.0 | 27-40-06-02 | ECLASS 11.0 | 27-40-06-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | STEP |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks |