Features


- 1-channel
- · DC version, positive polarity
- Working voltage 26.5 V at 10 μA
- Series resistance max. 327 Ω
- Fuse rating 50 mA
- · DIN rail mounting

Function

The Zener Barrier prevents the transfer of unacceptably high energy from the safe area into the hazardous area.

The zener diodes in the Zener Barrier are connected in the reverse direction. The breakdown voltage of the diodes is not exceeded in normal operation. If this voltage is exceeded, due to a fault in the safe area, the diodes start to conduct, causing the fuse to blow. The Zener Barrier has a positive polarity, i. e. the anodes of the zener diodes are grounded.


Assembly








Connection





Zone 2 Div. 2

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date 2013-09-24 10:22 Date of issue 2013-09-24 071788_eng.xml

end xm
071788
2013-09-24
dissi to
Π
013-09-24 10
Release date

General specifications		
Туре		DC version, positive polarity
Electrical specifications		
Nominal resistance		300 Ω
Series resistance		max. $327~\Omega$
Fuse rating		50 mA
Hazardous area connection	on	
Connection		terminals 1, 2
Safe area connection		Communication 1, 2
Connection		terminals 7, 8
Working voltage		max. 26.9 V , 26.5 V at 10 μA
Conformity		παλ. 20.3 ν αι το μλ
Protection degree		IEC 60529
Ambient conditions		120 00023
		-20 60 °C (-4 140 °F)
Ambient temperature		-25 70 °C (-13 140 °F)
Storage temperature		· · ·
Relative humidity		max. 75 %, without moisture condensation
Mechanical specifications		ID20
Protection degree		IP20
Connection		self-opening connection terminals, max. core cross-section 2 x 2.5 mm ²
Mass		approx. 150 g
Dimensions		12.5 x 115 x 110 mm (0.5 x 4.5 x 4.3 in)
Construction type		modular terminal housing , see system description
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in cor with Ex-areas	nnection	
EC-Type Examination Certif	icate	BAS 01 ATEX 7005, for additional certificates see www.pepperl-fuchs.com
Group, category, type of protection		$\langle x \rangle$ II (1)GD, I (M1) [Ex ia Ga] IIC, [Ex ia Da] IIIC, [Ex ia Ma] I (-20 °C \leq T _{amb} \leq 60 °C) [circuit(s) in zone 0/1/2]
Voltage	U_o	28 V
Current	Io	93 mA
Power	Po	650 mW
Supply		
Maximum safe voltage	U_{m}	250 V
Series resistance		min. 301 Ω
Statement of conformity		TÜV 99 ATEX 1484 X , observe statement of conformity
Group, category, type of pattern temperature class	protection,	(x) II 3G Ex nA IIC T4 Gc [device in zone 2]
Directive conformity		
Directive 94/9/EC		EN 60079-0:2009, EN 60079-11:2007, EN 61241-11:2006, EN 60079-15:2010
International approvals		.,,,,,,
FM approval		
Control drawing		116-0118
UL approval		
Control drawing		116-0139
CSA approval		
Control drawing		116-0119
IECEx approval		IECEx BAS 09.0142
Approved for		[Ex ia Ga] IIC, [Ex ia Da] IIIC, [Ex ia Ma] I
General information		
Supplementary information		EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com.