

202A111 to 196


Straight boot

Fax-on-Demand: (800) 260-9099
(650) 361-6523


FAX ID	Description
3101	SCD

Before ordering check with factory for most current data.

As supplied (a)



After unrestricted recovery (b)



Applications

Use for mechanical protection and connector/cable strain relief. This family of boots has no lip, so that a boot can be installed directly onto the connector accessory thread.

Materials Available

Material*	Material description	Precoating no.	Adhesive part no.**
-3	Semirigid polyolefin	/42 or /86	S-1017 or S-1048
-4	Flexible polyolefin	/42 or /86	S-1017 or S-1048
-12	Viton		
-25	Fluid-resistant elastomer	/42 or /86 or /225	S-1017 or S-1048
-100	Polyolefin, Zerohal	/86 or /180	S-1030 or S-1048

*For more information, please see the appropriate material page in this section.

**For more information, please see Section 5 of this catalog.

Zerohal is a trademark of Raychem Corporation.

Viton is a trademark of E. I. du Pont de Nemours and Company.

Part number	H			J		
	Min. -3, -4, -25 a	Min. -12, -100 a	Max. b	Min. -3, -4, -25 a	Min. -12, -100 a	Max. b
202A111	16.5 (.65)	16.5 (.65)	7.9 (.31)	16.5 (.65)	11.9 (.47)	3.8 (.15)
202A121	24.6 (.97)	22.6 (.89)	9.9 (.39)	24.6 (.97)	17.8 (.70)	5.3 (.21)
202A132	28.4 (1.12)	26.2 (1.03)	14.2 (.56)	28.4 (1.12)	20.3 (.80)	6.6 (.26)
202A142	31.0 (1.22)	31.0 (1.22)	17.8 (.70)	31.0 (1.22)	25.4 (1.00)	7.4 (.29)
202A153	36.1 (1.42)	36.1 (1.42)	21.9 (.86)	36.1 (1.42)	26.2 (1.03)	8.6 (.34)
202A163	42.7 (1.68)	42.7 (1.68)	27.4 (1.08)	42.7 (1.68)	27.2 (1.07)	9.4 (.37)
202A174	51.8 (2.04)	48.3 (1.90)	35.3 (1.39)	51.8 (2.04)	48.3 (1.90)	16.0 (.63)
202A185	66.0 (2.60)	66.0 (2.60)	43.7 (1.72)	66.0 (2.60)	54.1 (2.13)	19.6 (.77)
202A196	86.4 (3.40)	86.4 (3.40)	57.2 (2.25)	86.4 (3.40)	71.4 (2.81)	26.9 (1.06)

	P	R	JO	W
	±10% b	±10% b	Ref. b	±20% b
202A111	25.4 (1.00)	14.2 (.56)	5.8 (.23)	1.27 (.05)
202A121	38.1 (1.50)	21.8 (.86)	9.1 (.36)	1.52 (.06)
202A132	51.3 (2.02)	27.9 (1.10)	13.0 (.51)	1.78 (.07)
202A142	66.8 (2.63)	35.6 (1.40)	17.8 (.70)	1.78 (.07)
202A153	73.7 (2.90)	41.4 (1.63)	16.0 (.63)	1.78 (.07)
202A163	99.1 (3.90)	62.7 (2.47)	18.0 (.71)	2.03 (.08)
202A174	130.3 (5.13)	64.8 (2.55)	41.9 (1.65)	3.30 (.13)
202A185	161.3 (6.35)	90.2 (3.55)	47.8 (1.88)	3.81 (.15)
202A196	212.6 (8.37)	113.0 (4.45)	62.2 (2.45)	4.06 (.16)