Tyco Electronics Our commitment. Your advantage.




tycoelectronics.com

Tyco Electronics Corporation Harrisburg, PA




Printed Circuit Board Terminals and Disconnects





Printed Circuit Board Terminals and Disconnects

Table of Contents



Printed Circuit Board PCB Pin Receptacles

FASTON Printed Circuit Board Tabs and Receptacles8 - 16

Disclaimer

While Tyco Electronics Corporation and its affiliates referenced herein ("Tyco Electronics") have made every reasonable effort to ensure the accuracy of the information in this catalog, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly dis-claims all implied warranties regarding the information contained herein, including, but not limited to, any implied war-ranties of merchantability or fitness for a particular purpose. Tyco Electronics only obligations are those in the Tyco Electronics Standard Terms and Conditions of Sale, and in no case will Tyco Electronics be responsible for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products. Users should independently evaluate the suitability of, and test each product for, their application

Need more information?

Call Technical Support at the numbers listed below.

- Technical Support is staffed with specialists well versed in all Tyco Electronics products. They can provide you with:
- Technical Support
- Catalogs
- Technical Documents
- Product Samples
- Tyco Electronics Authorized Distributor Locations

The dimensions, specifications, designs construction, materials and processes in this catalog are for reference purposes only and are subject to change without notice. Please consult Tvco Electronics for the most current product information

The export of certain Tyco Electronics products is restricted by the Arms Export Control Act (Title 22, U.S.C. Sec 2751, et seq.) or the Export Administration Act of 1979, as amended (Title 50, U.S.C., App. 2401 et seq.). Orders may be subject to export approval by the U.S. Government. Buyer must comply with all applicable export laws of all applicable jurisdictions. © Copyright 2007, 1997, 1994, 1993, 1989 and 1986 by Tyco Electronics Corporation. All International Rights Reserved.

AMP, ACTION PIN, AMP-BARREL, AMP EDGE, AMP-IN, AMP MONO-SHAPE, AMP-O-LECTRIC, AMPOMATOR, Comp-U-Sertor, FASTON, MAG-MATE, QUADRA-MATE, TE LOGO and TYCO ELECTRONICS are trademarks of Tyco Electronics Corporation.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

See inside back cover for Global Contacts and phone numbers.

Power Taps	. 30
Application Tooling	- 39
Part Number Index.	. 40

Restriction on the use of Hazardous Substances (RoHS)

At Tyco Electronics, we're ready to support your RoHS requirements. We've assessed more than 1.5 million end items/components for RoHS compliance, and issued new part numbers where any change was required to eliminate the restricted materials. Part numbers in this catalog are identified as:

RoHS Compliant — Part numbers in this catalog are RoHS Compliant, unless marked otherwise. These products comply with European Union Directive 2002/95/EC as amended 1 January 2006 that restricts the use of lead, mercury, cadmium, hexavalent chromium, PBB, and PBDE in certain electrical and electronic products sold into the EU as of 1 July 2006.

NOTE: For purposes of this Catalog, included within the definition of RoHS Compliant are products that are clearly "Out of Scope" of the RoHS Directive such as hand tools and other non-electrical accessories.

NOTE: Information regarding RoHS compliance is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information provided by our suppliers. This information is subject to change. For latest compliance status, refer to our website referenced at right.

Getting the Information You Need

Our comprehensive on-line RoHS Customer Support Center provides a forum to answer your questions and support your RoHS needs. A RoHS FAQ (Frequently Asked Questions) is available with links to more detailed information. You can also submit RoHS questions and receive a response within 24 hours during a normal work week. The Support Center also provides:

- Cross-Reference from Non-compliant to Compliant Products
- Ability to browse RoHS Compliant Products in our on-line catalog
- Downloadable Technical Data Customer Information Presentation
- More detailed information regarding the definitions used above
- So whatever your questions when it comes to RoHS we have the answers at www.tycoelectronics.com/leadfree

RoHS Customer



Catalog 82159 Revised 12-07

www.tycoelectronics.com

millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are in inches and Dimensions are shown for reference purposes only Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

2




Printed Circuit Board Terminals and Disconnects

Table of Contents (Continued)



Printed Circuit Board (PCB) Receptacles




AMP-BARREL Terminals






Miniature AMP-IN Terminals



Low Profile Miniature AMP-IN Connectors






Printed Circuit Board Disconnects

Test Probe Receptacles



AMP-IN and AMP EDGE Terminals



Power Taps

3

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise specified. Values in brackets Dimensions are shown for reference purposes only. Specifications subject www.tycoelectronics.com are metric equivalents. to change.

[≇] Tyco Electronics


Printed Circuit Board Terminals and Disconnects

Printed Circuit Board (PCB) Pin Receptacles

Product Facts

- Components with pin contact can be easily inserted into the printed circuit board after the pin receptacles are flow soldered
- The receptacles hold the pins from the components without the necessity of soldering
- Components can be easily removed from the printed circuit board for replacement or repair
- Components with pin contacts may be mated and unmated 10 times
- The receptacle contacts are securely clinched to the printed circuit board prior to soldering
- The receptacles are machine applied by semiautomatic and automatic insertion equipment
- Components may be inserted from either side of the printed circuit board

Technical Documents Product Specification



The Printed Circuit Board

100 1111

Application Specification 114-2127

Pin Receptacle provides a reliable and cost effective means of attaching components with pin contacts to a printed circuit board. Components are held in place without solder allowing for their easy removal from the printed circuit board for replacement or repair. Receptacle contacts are inserted and securely clinched to the printed circuit board by means of semiautomatic or automatic machines.

Catalog 82159
Revised 12-07Dimensions are in inches and
millimeters unless otherwise
specified. Values in brackets
are metric equivalents.Dimensions are shown for
reference purposes only.
Specifications subjectUSA: 1-800-522-6752
Canada: 1-905-470-4425South America: 55-11-2103-6000
Hong Kong: 852-2735-1628
Japan: 81-44-844-8013
UK: 44-8706-080-208

Downloaded from Arrow.com.


4

Printed Circuit Board Terminals and Disconnects

Printed Circuit Board (PCB) Pin Receptacles (Continued)

Material and Finish


Tin plated phosphor bronze



Mating	PCB		Dimensions		Receptacle	Insertion	
Pin Dia.	Thickness	Α	В	С	Part No.	Head ¹	
.088093 2.24-2.36	.063079 1.60-2.01	.236 5.99	.276 7.01	.181 4.60	63566-1	904608-1	
.098 2.49	.063079 1.60-2.01	.236 5.99	.276 7.01	.181 4.60	63572-1	853439-3	

¹For use with either AMP FHIS Bench Machine 464300-1 or AMP Comp-U-Sertor II Machine 122300-1. **Note:** Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Recommended PCB Layout



Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

5

Printed Circuit Board Terminals and Disconnects

Printed Circuit Board (PCB) Receptacles


Product Facts

- Receptacles accept all .250 x .016 [6.35 x 0.41] thick terminal configurations
- Receptacles available for .250 x .032 [6.35 x 0.81] thick FASTON tab terminals
- Receptacles available for prepless termination of 24-22 AWG [0.2 - 0.4 mm²] solid wire using displacement crimp technique
- Available in tin-plated brass
- No tooling needed to insert or remove terminals
- Continuous strip contacts allow high-speed application with single or multiple-head insertion machines
- An economical means of retrofitting and field replacing wire-to-board connections

Technical Documents Product Specification

108-2005 Receptacle, Spade, PCB

Application Specifications 114-2001 Receptacle, PCB 114-2037 Receptacle, PCB, Clinchable



The pc board receptacle is a cost saving design that gives you a wide selection of wire termination alternatives. It is used in new equipment which provides versatility of connection and in old equipment to allow field replacements of units without costly retrofitting. In all cases installation of wire-to-board termination is accomplished without tools. For additional savings, the receptacle is designed to be inserted into your board by high-speed application equipment, then wave soldered giving you the lowest applied cost.

terminated with terminals having tongue widths and thicknesses of .250 x .016 [6.35 x 0.41] and FASTON tab terminals of .250 x .032 [6.35 x 0.81]. These terminated wires are plugged into the receptacle and may be removed and replugged as required. An added feature is the ability of one receptacle to accept a 24-22 AWG [0.2-0.4 mm²] unterminated solid wire as well as a terminated wire.

Receptacle is used in wire-

terminations. Wires may be

to-printed circuit board

The receptacle has applications in all industries requiring wire-to-pc board applications both in new equipment and existing equipment. The purpose

receptacle can be used to give flexibility in selection of wire termination, including tongue, fork, open barrel, and FASTON tabs. This receptacle also has the ability to replace screw and nut arrangements. In existing equipment, the receptacle is just as versatile and can be used for field replacement where the original wire termination remains the same, but the board layout changes. In essence, it allows you to plug the previously terminated wires into the new model without costly changes to wire termination tooling.

of its design is to allow

field replacement without

costly retrofitting. In new

equipment, the pc board

6

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Electronics

Printed Circuit Board Terminals and Disconnects

Printed Circuit Board (PCB) Receptacles (Continued)

Material and Finish Tin plated brass



		Dimer	nsions		Strip	Form	Loose Piece	
Accepts	A Max.	В	С	D Max.	Receptacle	Inserter Applicator ²	Receptacle	
.250 x .016					62745-1	—		
6.25 × 0.41 .2	.290 7.37	.292 7.42	.012 0.30		62111-2	467322-1	62806-1	
	7.07	1.07 7.12 0.00	0.00		62751-1 ³	467322-2		
.250 x .016 6.35 x 0.41 24-22 AWG Solid Wire	.290 7.37	.292 7.42	.012 0.30	.190 4.83	62199-2	467322-1	_	
.250 x .032 6.35 x 0.81 FASTON Tab Terminals	.390 9.91	.318 8.08	.025 0.64	.275 6.99	62172-21	_	_	

7

¹For .123±.002 [3.12±0.05] board hole only. ²For use with AMP "U" Frame Machine 691679-1. ³With clinchable pcb tabs.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise specified. Values in brackets Dimensions are shown for reference purposes only. Specifications subject www.tycoelectronics.com are metric equivalents. to change.

Printed Circuit Board Terminals and Disconnects

FASTON Printed Circuit Board Tabs and Receptacles

Product Facts

- Full line of PCB tabs and receptacles
- Straight and right-angle tabs available in .250, .187 and .110 series
- Receptacles produced in .250/.205 x .032 or .025. Standard or low insertion force receptacles available
- Strip product for automatic insertion
- Compatible with industry insertion equipment or full line of equipment available from Tyco Electronics



Tyco Electronics now offers a complete line of Printed Circuit Board tabs and receptacles. Tyco Electronics PCB product can be found in switches and on control boards around the world. Our product offering includes .250, .187 and .110 series vertical tabs, .250 and .187 right-angle tabs and .250/.205 vertical receptacles. Product is available in loose piece and strip form. In a short time, our product offering has grown from a handful of part numbers to dozens of parts. We continue to add to our product family as design changes, innovation and customers' requirements expand.

Insertion equipment is available for our entire strip

The Tyco Electronics product has been designed

product. The semiautomatic, air-powered Modular Insertion System (MIS) Bench machine is available for customers with moderate insertion requirements. The compact, fully automatic Comp-U-Sertor II machine is available for applications where larger volumes will be inserted and where programmable, microprocessor controlled equipment is desired. Insertion heads for both pieces of equipment are interchangeable, requiring less equipment investment. Tyco Electronics will also custom build a complete "pass through" system for high-end customer applications.

to be compatible with industry insertion equipment. In many cases, this product will work as a "drop in" replacement for existing product. In some cases, slight modifications or minor tooling changes are necessary. Please consult Technical Support or the Global Application Tooling Group for more details.

Tyco Electronics is one of the only companies that offers printed circuit board tabs and receptacles as well as the crimp to wire receptacles and tabs that offer a complete solution for your packaging needs.

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 S Canada: 1-905-470-4425 H Mexico: 01-800-733-8926 Ja C. America: 52-55-1106-0803 U

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Downloaded from Arrow.com.


8

Printed Circuit Board Terminals and Disconnects

FASTON Printed Circuit Board Tabs and Receptacles (Continued)

250 Series Printed Circuit Board Tabs

Stock Thickness — .032 [0.81] **Board Hole Size** — $.055 \pm .002 [1.40 \pm 0.05]$ Dia.




Dimensions			Material	81	A .	Terminal Part No.		
L	К	Е	and Finish	° 71	Q.	Strip ²	Loose Piece ¹	
.502 12.75	.125 3.18	.312 7.92	Tin Plated Brass	Х	Х	63839-1 ³	—	
.547 13.89	.157 3.99	.312 7.92	Tin Plated Brass	Х	Х	63986-1	_	
.552 14.02	.150 3.81	.312 7.92	Tin Plated Brass	_	—	1217566-1	_	
.622	.125	.312	Tip Distant Drass	Х	Х	_	62409-1 ³	
15.80	3.18	7.92	TITI Plated Brass	_	—	_	1217056-1	
.487 .125 .312 12.37 3.18 7.92 Tin Pla		Tin Plated Brass	Х	х	62650-1 ³	_		
.532 13.51	.175 4.45	.312 7.92	Tin Plated Brass	Х	х	63650-1 ³	_	
.622	.125	.452	Tip Distant Drass	Х	Х	_	63900-1	
15.80	3.18	11.48	Tin Plated Brass	_	_	63755-1 ³	_	
	L .502 12.75 .547 13.89 .552 14.02 .622 15.80 .487 12.37 .532 13.51 .622	L K .502 .125 12.75 3.18 .547 .157 13.89 3.99 .552 .150 14.02 3.81 .622 .125 15.80 3.18 .487 .125 12.37 3.18 .532 .175 13.51 4.45 .622 .125	L K E .502 .125 .312 12.75 3.18 7.92 .547 .157 .312 13.89 3.99 7.92 .552 .150 .312 14.02 3.81 7.92 .622 .125 .312 12.37 3.18 7.92 .552 .150 .312 15.80 3.18 7.92 .622 .125 .312 13.51 4.45 7.92 .622 .125 .312 13.51 4.45 7.92 .622 .125 .452	L K E and Finish .502 .125 .312 Tin Plated Brass 12.75 3.18 7.92 Tin Plated Brass .547 .157 .312 Tin Plated Brass .552 .150 .312 Tin Plated Brass .402 3.81 7.92 Tin Plated Brass .552 .150 .312 Tin Plated Brass .622 .125 .312 Tin Plated Brass .622 .125 .312 Tin Plated Brass .532 .175 .312 Tin Plated Brass .622 .125 .452 Tin Plated Brass	L K E and Finish And .502 .125 .312 Tin Plated Brass X .547 .157 .312 Tin Plated Brass X .547 .157 .312 Tin Plated Brass X .552 .150 .312 Tin Plated Brass .622 .125 .312 Tin Plated Brass .622 .125 .312 Tin Plated Brass .487 .125 .312 Tin Plated Brass X .532 .175 .312 Tin Plated Brass X .5622 .125 .452 Tin Plated Brass X	L K E and Finish M Image: Second s	L K E and Finish M </td	

Board Hole Size:.060/.053 [1.52/1.35] Dia.
 Insertion equipment available.
 Dimple.

Stock Thickness — .032 [0.81] **Board Hole Size** — .100 ± .002 [2.54 ± 0.05] Dia.

Downloaded from Arrow.com.



Material	81	€ ₽°	Termi	nal Part No.
and Finish	° 7	ୢୄୄୄ	Strip ¹	Loose Piece
Tin Plated Brass	Х	Х	63066-1	63067-1

¹ Insertion equipment available.

Note: Part Numbers are RoHS compliant except: \blacklozenge Indicates non-RoHS compliant.


						9
С	atalog 82159	Dimensions are in inches and	Dimensions are shown for	USA: 1-800-522-6752	South America: 55-11-2103-6000	
R	Revised 12-07	millimeters unless otherwise	reference purposes only.	Canada: 1-905-470-4425	Hong Kong: 852-2735-1628	
		specified. Values in brackets	Specifications subject	Mexico: 01-800-733-8926	Japan: 81-44-844-8013	
W	/ww.tycoelectronics.com	are metric equivalents.	to change.	C. America: 52-55-1106-0803	UK: 44-8706-080-208	

Printed Circuit Board Terminals and Disconnects

FASTON Printed Circuit Board Tabs and Receptacles (Continued)

250 Series Printed Circuit Board Tabs (Continued)

Stock Thickness — .032 [0.81] **Board Hole Size** — $.055 \pm .002 [1.40 \pm 0.05]$ Dia.




Dimensions		6	Material	.91	\$₽ °	Terminal Part No.		
L	К	E	and Finish	•74	e.	Strip ¹	Loose Piece	
.552	.150	.312	Tin Plated Brass	Х	Х	63862-1 ²	1742188-12	
14.02	3.81	7.92	The Plated Brass	Х	Х	63824-1	63849-1	
.582	.180	.312	Tin Plated Brass	Х	Х	1217136-1	_	
14.78	4.57	7.92	Thirt lated Diass	Х	Х	_	1217421-1	
.650 16.51	.150 3.81	.410 10.41	Tin Plated Brass	х	х	1217126-1 ²	_	
.710 18.03	.150 3.81	.470 11.94	Tin Plated Brass	х	х	1217125-1	1217169-1	
.780	.150	.540	Tin Plated Brass	Х	Х	1217127-1	_	
26.18	3.81	13.72	Thir Flatou Diabo	Х	Х	_	1217167-1	

¹ Insertion equipment available.

² Dimple.

.055 \pm .002 [1.40 \pm 0.05] Dia.




Dimension L	Material and Finish	.R .	∰ ∘	Terminal Part No.
1.062 26.97	Tin Plated Brass	Х	Х	63949-1
1.207 30.66	Tin Plated Brass	Х	Х	63950-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

10					
	Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise	Dimensions are shown for reference purposes only.	USA: 1-800-522-6752 Canada: 1-905-470-4425	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628
	www.tycoelectronics.com	specified. Values in brackets are metric equivalents.	Specifications subject to change.	Mexico: 01-800-733-8926 C. America: 52-55-1106-0803	Japan: 81-44-844-8013 UK: 44-8706-080-208


₹_{Tyco} Électronics

Printed Circuit Board Terminals and Disconnects



205 Series **Printed Circuit Board Only**

Stock Thickness — .020 [0.51] **Board Hole Size** — .100 – .095 [2.54 – 2.41] Dia.



Dimensions		Material	81	A .	Terminal	
L	W	and Finish	.R.	()	Part No. 62411-11	
.525 13.34	.070 1.78	Tin Plated Brass	х	х		
.545 13.84	.160 4.06	Tin Plated Brass	Х	х	60284-2	

.250/.205 Printed Circuit

- L -

.250 🗻



Board Receptacles


Board Receptacles Stock Thickness — .016 [0.	.330 [8.38]	200 	 ₹		295 [7.49]	.062 [1.57		.100 [2.54]	.295 [7.49]		
			A	Fits Dimensions		Material	B		Par	C rt No.	
		Style	Tab	A	L	and Finish	.F 1	S₽•	Strip	Loose Piece	
			.032 0.81 (LIF)	.075 1.91	.480 12.19	Tin Plated Brass	_	_	63968-1	_	
			.032 0.81	.075 1.91	.480 12.19	Tin Plated Brass	—	—	63969-1	1217080-1	
		А	.025 0.64 (LIF)	.075 1.91	.480 12.19	Tin Plated Brass	—	—	63994-1	_	
			.025	.075	.510 12.95	Tin Plated Brass	—	—	1217137-1 ²	_	
			0.64	1.91	.480 12.19	Tin Plated Brass	_	_	1217180-1	_	
		В	.020 0.51	—	—	Tin Plated Phos Bronze	—	—	1217107-1 ¹	_	
Note: Part Numbers are Ro	HS	С	.250 x .016 6.35 x 0.41 Spade	_	_	Tin Plated Brass	_	_	62751-1	62806-1	
compliant except: ♦ I non-RoHS compliant		¹ Horizonta ² .180 [4.5	al mount. 7] length — sold	ler legs.							. 11
Catalog 82159 Revised 12-07	millimete	ns are in inch rs unless othe Values in bra	rwise refer		e shown fe oses only. subiect		5-470-44		South America Hong Kong: 85 Japan: 81-44-8		
www.tycoelectronics.com		c equivalents.		ange.	545,501	C. America: 5			UK: 44-8706-0		


Downloaded from Arrow.com.


FASTON Printed Circuit Board Tabs and Receptacles (Continued)

187 Series Printed Circuit Board Tabs

Stock Thickness — .020 [0.51]








Туре	Board					Material	.91	€ ₽°	Terminal	
Type	Thickness	Т	L	Е	Н	and Finish	° 7 4	<u>ا</u> ب	Part No.	
А	.055 1.38	.250 6.35	.332 8.43	.250 6.35	.283 7.19	Pre-Tin Brass	Х	Х	61543-1 ²	
A	.062 1.57	.250 6.35	.332 8.43	.250 6.35	.283 7.19	Pre-Tin Brass	Х	Х	62403-1 ²	
В	.062 1.57	_	.545 13.84	.250 6.35	_	Tin Plated Brass	Х	Х	61907-1 ¹	
С	.062 1.57	.250 6.35	.332 8.43	.250 6.35	.303 7.70	Pre-Tin Brass	Х	Х	62221-1 ²	

Loose piece only.
 Insertion equipment available.




Tab	Board	Dimer	nsions	Material	-	A	Terminal Part No.		
Thickness	Hole Size	L	н	and Finish	. 71	€ ₽•	Strip ²	Loose Piece	
.032 0.81	.053057 1.35-1.45	.487 12.37	.280 7.11	Tin Plated Brass	х	х	63525-1 ¹	1217057-11	
.020	.050054	.487 12.37	.285 7.24	Tin Plated Brass	Х	х	63603-1	1217131-1	
0.51	1.27-1.37	.440 11.18	.312 7.92	Tin Plated Brass	Х	Х	63838-1	_	

¹ Dimple. ² Insertion equipment available.

Note: Part Numbers are RoHS compliant except: \blacklozenge Indicates non-RoHS compliant.


12				·	
	Catalog 82159	Dimensions are in inches and	Dimensions are shown for	USA: 1-800-522-6752	South America: 55-11-2103-6000
	Revised 12-07	millimeters unless otherwise	reference purposes only.	Canada: 1-905-470-4425	Hong Kong: 852-2735-1628
	www.tycoelectronics.com	specified. Values in brackets are metric equivalents.	Specifications subject to change.	Mexico: 01-800-733-8926 C. America: 52-55-1106-0803	Japan: 81-44-844-8013 UK: 44-8706-080-208



Dimple.
 No hole or dimple.
 Insertion equipment available.

Right-Angle Printed Circuit Board Tabs


(Continued)



Stock Thickness	Board Hole Size	Material and Finish	. ¶ 1	€ ₽°	Terminal Part No.
.032	.053057	Tin Plated Brass	Х	Х	1217061-1
0.81	1.35-1.45	Thir Flated Diass	_	—	1217756-1 ¹
.020	.050054	Tin Plated Brass	Х	Х	1217062-1
0.51	1.27-1.37	Thi Flated Blass	_	—	1217156-1 ¹

¹ Loose piece.

Tab Caps 187 and 250 Series



Tab Size	Material	UL 941	Color	Dimer	nsions	Insulator
Tab Size	wateria	UL 941	Color	т	W	Part No.
"187" Series .020 [0.51] Thick	Nylon	V2	Natural	.320 8.13	.260 6.60	360041-1
"250" Series .032 [0.81] Thick	Nylon	V2	Natural	.380 9.65	.320 8.13	360042-1

¹ Flammability rating.


Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


13

Dimensions are in inches and	Dimensions are shown for	USA: 1-800-522-6752	South America: 55-11-2103-6000
millimeters unless otherwise	reference purposes only.	Canada: 1-905-470-4425	Hong Kong: 852-2735-1628
specified. Values in brackets	Specifications subject	Mexico: 01-800-733-8926	Japan: 81-44-844-8013
are metric equivalents.	to change.	C. America: 52-55-1106-0803	UK: 44-8706-080-208

FASTON Printed Circuit Board Tabs and Receptacles (Continued)

.110 Series Printed Circuit Board Tabs **Stock Thickness** — .020 [0.51]






Style	Mating Hole Diameter	Dim. L	Material and Finish	<i>.</i> 72	()	Terminal Part No.
А	.060055 1.52-1.40	.490 12.45	Tin Plated Brass	х	х	61134-3 ¹
В	.067063	.485	Tin Plated Brass	Х	Х	61968-1 ²
D	1.70-1.60	12.32	TITI FIALEU DIASS	Х	Х	62437-1 ¹
		.490 12.45	Tin Plated Brass	х	х	62395-1 ²
	.044048	.622 15.80	Tin Plated Brass	х	х	63756-1 ^{2,3}
С	1.12-1.22	.910 23.11	Tin Plated Brass	_	_	63794-14
		.622 15.80	Tin Plated Brass	—	—	1217514-1
	.067073 1.70-1.85	.490 12.45	Pre-tin/ Pre-copper	х	х	62669-1 ²
D	.062068 1.57-1.73	.545 13.84	Tin Plated Brass	_	_	1217577-1 ²

1 Loose piece only. ² Insertion machine available. ³ .032 [0.81] Stock. ⁴ .060 [1.52] Tab width.





Tab Thickness	PCB Hole Dia. +0/01 [+0/03]	Material and Finish	.81	()	Terminal Part No.
.032 0.81	.055 1.40	Tin Plated Brass	_	_	725963-2
.020 0.51	.051 1.30	Tin Plated Brass	_	_	725996-2

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

14					
	Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise specified. Values in brackets	Dimensions are shown for reference purposes only. Specifications subject	USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013
	www.tycoelectronics.com	are metric equivalents.	to change.	C. America: 52-55-1106-0803	UK: 44-8706-080-208

Electronics


Printed Circuit Board Terminals and Disconnects

FASTON Printed Circuit Board Tabs and Receptacles (Continued)

FASTON RAST 5 Tab Header Assembly, 250 Series

Product Facts

- .250 x .032 [6.3 x 0.8]
 FASTON Tabs built on 5 mm centerlines
- Shrouded Header Assembly that conforms to the European RAST 5 Standard
- Mating Tyco Electronics Connector Families include Positive Lock RAST 5 Connector System, AMP Standard Timer RAST 5, AMP multifitting, AMP multifitting MKII, AMP MONO-SHAPE TAB MKI, and AMP MONO-SHAPE MKII
- Vertical and Right-Angle Versions available in 2 through 8 positions
- Tin Plated Brass Tabs are Standard, Silver Plated Tab Versions are available upon Request
- Lead Free Design is RoHS and ELV Compliant
- UL 94 V-0 Housing meets Glow Wire IEC 60695-1 Section 30.2.3 – 750° NO FLAME
- Component Recognition



The FASTON RAST 5 Tab Header Assembly system is designed to provide a RAST 5 interface to a Printed Circuit Board. The RAST 5 Standard defines and standardizes the connector mating interface. 250 Series Tabs are placed on 5mm center lines with a plastic shroud that has keying, polarization, and locking features that help designed to accept any RAST 5 compliant female receptacle system or individual quick connects.

The most common application for this product is for household appliance controls where OEMs want to minimize the possibility of crossed wires. It is also suited for other applications such as gaming, vending, and exercise equipment controls as well as residential, commercial and industrial HVAC and light industrial equipment. The

system comes fully assembled and is easily press fit into the board for the soldering operation. Preassembly of the tabs into the Header ensures tab perpendicularity to the board. The solder leg PCB layout is based on the Industry Standard for similar systems available on the market. To further enhance correct place onto the board, the vertical system includes a plastic post which allows Header placement to be polarized.

USR and CSR under File No. E28476

 VDE tested according to DIN EN61984 (VDE0627): 2002-09; EN61984: 2001 VDE Reg. No. B718 prevent mismating of the corresponding RAST 5 female receptacle housing. The header assembly is

Material


UL 94 V-0, 6/6 Nylon

See Tyco Electronics Catalogs 296599, 889803, 1308197, 1308209 for the complete line of RAST products.

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 Catalog 82159 Revised 12-07 Dimensions are in inches and USA: 1-800-522-6752 Dimensions are shown for reference purposes only. Canada: 1-905-470-4425 millimeters unless otherwise specified. Values in brackets Specifications subject Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 www.tycoelectronics.com UK: 44-8706-080-208 are metric equivalents. to change.

15

Printed Circuit Board Terminals and Disconnects



02-I

02-P

	03-A	.681 [17.30]	521382-3	521384-3
3	03-B	.681 [17.30]	1-521382-3	1-521384-3
3	03-D	.681 [17.30]	2-521382-3	2-521384-3
	_	.681 [17.30]	3-521382-3	3-521384-3
	04-A	.878 [22.30]	521382-4	521384-4
	04-B	.878 [22.30]	1-521382-4	1-521384-4
4	04-C	.878 [22.30]	2-521382-4	2-521384-4
4	04-F	.878 [22.30]	3-521382-4	3-521384-4
	04-G	.878 [22.30]	4-521382-4	4-521384-4
	_	.878 [22.30]	5-521382-4	5-521384-4
	05-B	1.075 [27.30]	521382-5	521384-5
F		1.075 [27.30]	1-521382-5	1-521384-5
5	_	1.075 [27.30]	2-521382-5	2-521384-5
	_	1.075 [27.30]	3-521382-5	3-521384-5
6	06-A	1.272 [32.30]	521382-6	521384-6
0	06-D	1.272 [32.30]	1-521382-6	1-521384-6
	07-C	1.469 [37.30]	521382-7	521384-7
7	_	1.469 [37.30]	1-521382-7	1-521384-7
1	_	1.469 [37.30]	2-521382-7	2-521384-7
	_	1.469 [37.30]	3-521382-7	3-521384-7
	08-D	1.665 [42.30]	521382-8	521384-8
8	_	1.665 [42.30]	1-521382-8	1-521384-8
	08-C	1.665 [42.30]	2-521382-8	2-521384-8

.484 [12.30]

5-521382-2

6-521382-2

6-521384-2

Refer to the Tyco Electronics Customer Drawing for additional details. For more information related to the RAST 5 Standard, see Tyco Electronics Literature Distribution no. 1308243.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

16

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Electronics


Printed Circuit Board Terminals and Disconnects

AMP-BARREL Terminals

Product Facts

- Unique insulation displacement technology
- Eliminates wire preparation—no stripping or soldering
- Capable of being wavesoldered to pc board with other components, enabling wires to be terminated at a more conducive time and location
- Anti-solder wicking design
- Accepts a wide range of wire sizes, solid or stranded
- Available in single and two-wire version
- Reusable terminal
- Available in loose-piece or strip version
- Semiautomatic insertion machine for strip version
- Simple, rugged low cost wire insertion tool
- Recognized Under Component Recognition Program of Underwriters Laboratories. Inc.
 File No. E28456

Technical Documents Product Specification



AMP-BARREL Terminals solve the problem of interconnecting discrete wires to printed circuit boards without permanently soldering them in place, and provide cost savings by eliminating the need for two-piece terminal systems, terminal strips or expensive space-consuming modular connectors. the use of a simple, lowcost screwdriver type tool or low cost plastic stuffer cap. These caps use a standard Phillips type screwdriver to terminate the wire. When left in place on the terminal they provide strain relief and insulation. They may be removed and reused for field changes and/or repairs. The high compliancy of the terminal This product also offers a wire cutoff version which allows the wire to be placed across the top of the terminal where the hand tool terminates and trims the wire in one action.

Similarly constructed, but of smaller size, are the .070 [1.78] and .090 [2.29] diameter AMP-BARREL Terminals. These terminals accept, respectively sizes of 28-26 AWG [0.08-0.15 mm²] with a maximum insulation diameter of .036 [0.91] and 28-22 AWG [0.08-0.4 mm²] with a maximum insulation diameter of .053 [1.35]. They also will accept two wires of the same gauge and type. The .156 [3.96] diameter AMP-BARREL Terminal accepts a wire range of 24-18 AWG [0.2-0.8 mm²] with a maximum insulation diameter of .115 [2.92]. It is made of tin-lead plated brass and will accept one wire per terminal.

108-6043 .070 [1.78] Diameter Terminal 108-6044 .090 [2.29] Diameter Terminal 108-6025 .125 [3.18] Diameter Terminal 108-6026 .156 [3.96] Diameter Terminal

Application Specification

114-6000 AMP-BARREL Terminals

Instruction Sheets

408-3187 408-6505 408-6553 These unique insulation displacement terminals are suitable for most printed circuit boards from .047 [1.19] to .125 [3.18] thick and are mounted in a space-saving, free-standing manner wherever required.

AMP-BARREL Terminals may be obtained in loose piece or strip form for semiautomatic machine insertion. Upon insertion, they are hand or wavesoldered with other components without fear of solder wicking into the wire termination area.

Termination is achieved by placing the end of a pre-cut unstripped wire horizontally to the board at the top of the AMP-BARREL Terminal. Insertion to the proper depth is accomplished by assures a highly reliable, stable interconnection and withstands extreme temperature, vibration and shock.

AMP-BARREL Terminals offer the added benefit of accepting a wide wire range, solid or stranded, within the same terminal. The .125 [3.18] diameter AMP-BARREL Terminal accepts a wire range of 28-18 AWG [0.08-0.8 mm²] with a maximum insulation diameter of .086 [2.18]. It is made of high strength, high ductility, pre-tinned phosphor bronze and accepts one or two wires of the same type that may vary in size by one wire gauge. The C-shaped cross-slot assures a reliable two-wire termination.

All AMP-BARREL Terminals are reusable. This feature is extremely important when correcting wiring errors, making field repairs or modifications.

17

Catalog 82159 Revised 12-07


www.tycoelectronics.com

millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are in inches and

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Printed Circuit Board Terminals and Disconnects



Conductor (solid or stranded)

Terminal					PC	Board		Termir	nal Dime	ensions		Part	Nos.
Size	AWG	ize Range mm ²	Max. Ins. O.D.	Wire per Terminal	Thk. Range	Mtg. Hole Dia.	Α	В	С	D	Е	Loose Pc.	Strip
.070 1.78	28-26	0.08-0.15	.036 0.91	1 or 2	.047062 1.19-1.57	.035040 0.89-1.02	.280 7.11	.090 2.29	.175 4.45	.070 1.78	.042 1.07	1742255-1	1742255-2
.090 2.29	28-22	0.08-0.4	.053 1.35	1 or 2	.047094 1.19-2.39	.050054 1.27-1.37	.340 8.64	.120 3.05	.210 5.33	.090 2.24	.056 1.42	1742254-1	1742254-2
				.086	.062094 1.57-2.39	.061065 1.55-1.65	.458 11.63	.118 3.00	.325 8.26	.125 3.18	.067 1.70	552699-1*	_
.125	00.10	0.08-0.8	.086		.062125 1.57-3.18	.061065 1.55-1.65	**	.118 3.00	.325 8.26	.125 3.18	.067 1.70	_	552699-2*
3.18 Standard	28-18	0.08-0.8	2.18	1 or 2	.062094 1.57-2.39	.061065 1.55-1.65	.458 11.63	.118 3.00	.325 8.26	.125 3.18	.067 1.70	552699-4	_
					.062125 1.57-3.18	.061065 1.55-1.65	**	.118 3.00	.325 8.26	.125 3.18	.067 1.70	_	552699-5
.125 3.18 With wire cut-off features	28-18	0.08-0.8	.086 2.18	1 or 2	.062094 1.57-2.39	.061065 1.55-1.65	**	.118 3.00	.325 8.26	.125 3.18	.067 1.70	_	554935-2*
.156 3.96	24-18	0.2-0.8	.115 2.92	1	.062094 1.57-2.39	.078082 1.98-2.08	.390 9.91	.125 3.18	.250 6.35	.156 3.96	.084 2.13	1742253-1	1742253-2

*Has tough insulation cutting feature in wire slot (see Detail A in illustration). These barrels are not recommended for smaller standard wires. **Cutoff is adjustable depending on board thickness.

Notes:

.070 [1.78] and .090 [2.29] terminals accept two wires of the same gauge and type.
 The .125 [3.18] terminal accepts two wires of the same type that may vary in size by one wire gauge.
 .070 [1.78] and .090 [2.29] terminals have a solder resist material on the inside of barrel which prevents solder wicking.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.


18				
Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise	Dimensions are shown for reference purposes only.	USA: 1-800-522-6752 Canada: 1-905-470-4425	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628
	specified. Values in brackets	Specifications subject	Mexico: 01-800-733-8926	Japan: 81-44-844-8013
www.tycoelectronics.co		to change.	C. America: 52-55-1106-0803	UK: 44-8706-080-208

Printed Circuit Board Terminals and Disconnects

AMP-BARREL Terminals (Continued)

Recommended Printed Circuit Board Dimensions

(for use in .047 [1.19] to .125 [3.18] pc boards)




Terminal Size		Minimum Hole Spacing	
Terminal Size	Α	В	С
.070	.100	.050	.105
1.78	2.54	1.27	2.67
.090	.150	.075	.135
2.29	3.81	1.91	3.43
.125	.200	.100	.175
3.18	5.08	2.54	4.45
.156	.220	.110	.190
3.96	5.59	2.79	4.83

Wire Stuffer Caps **Product Facts**

Insulates
Provides strain relief
Acts as field service repair tool

Material

Thermoplastic



Wire S	ize Range	Color	For Use With	Wire Stuffer Cap		
AWG	mm ²	Color	Terminal Part No.	Part No.		
28-26	0.08-0.15	Natural	1742255	553593-1		
28-22	0.08-0.4	Natural	1742254	553594-1		
22-18	0.4-0.8	Yellow	552699	230707-1		
28-24	0.08-0.2	Natural	552699	230707-3		
24-18	0.2-0.8	Natural	1742253	553595-1		

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise Dimensions are shown for reference purposes only. Specifications subject specified. Values in brackets www.tycoelectronics.com are metric equivalents. to change.

19

Electronics

Printed Circuit Board Terminals and Disconnects

AMP-BARREL Terminals (Continued)

Application Tooling

Wire Insertion Tool


Precut, unstripped wires are easily terminated in the AMP-BARREL Terminal with a simple screwdriver type tool. It properly positions the wire to the correct depth in the terminal. For two wire applications, the second wire pushes the first wire into the lower section of the terminal.

For improved comfort, a slip-on cushion grip is available.

The Wire Insertion Tool should be used for wire termination only; it should not be used to seat terminals onto the pc board


Cushion Grip

Material and Finish Elastomer Part No. 231279-1



	Wire Size Range AWG mm ²		Color Code on Tool Shaft	For use with Terminal Part No.	Wire Insertion Tool Part Nos.	
	22-18	0.4-0.8	Yellow	552699-1, 552699-2 552699-4, 552699-5	552714-1	
	24-18	0.2-0.8	Red	1742253-1 and 552714-2 1742253-2 552714-2		
ırd.	28-24	0.08-0.2	White	552699-1, 552699-2 552699-4, 552699-5	552714-3	
	28-22	0.08-0.4	Blue	1742254-1 and 1742254-2	552714-4	
	28-26 0.08-0.15 0		Green	1742255-1 and 1742255-2	552714-5	
	22-26 0.4-0.15 No		None	554935-2	231890-1	





of a ram and pedestal assembly for use in a standard drill press. The ram assembly holds the terminal and provides a firm seat during insertion. It fits into the drill chuck. The pedestal assembly sits on the drill table and supports the pc board during insertion.

Kit No. 230549-3 for .070 [1.78] AMP-BARREL Terminal Part No. 1742255-1

Kit No. 230549-4 for .090 [2.29] AMP-BARREL Terminal Part No. 1742254-1

Kit No. 230549-1 for .125 [3.18] AMP-BARREL Terminals Part Nos. 552699-1 and 552699-4 Kit No. 230549-2 for .156 [3.96] AMP-BARREL Terminal

Part No. 1742253-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

20		
	Catalog 82159	Dimer
	Revised 12-07	millim
		specif
	www.tvcoelectronics.com	are m

ensions are in inches and Di neters unless otherwise re ified. Values in brackets Sp netric equivalents. to

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Electronics

Printed Circuit Board Terminals and Disconnects

QUADRA-MATE Wire-to-Printed Circuit Board Terminal

Product Facts

- Redundant wire insulation displacement termination
- Built-in strain relief
- Accepts 28-24 AWG [0.09-0.2 mm²]
- Feed-thru connections allow wiring flexibility
- Free-standing
- Low board profile (less than ¼" [6.35 mm] high)
- Available in loose piece or strip form
- Mass termination adaptability
- Capable of being reused
- Low applied costs

Applications

- Electronic games
- Computer
- Telephone equipment
- Business machines
- Electronic control equipment

Technical Documents Application Specification 114-2051

Product Specification

The QUADRA-MATE Wireto-Printed Circuit Board Terminal is an extension of the MAG-MATE connector program, and is designed to terminate discrete wires to a pc board via insulation displacement slot technology. It is capable of accepting solid or stranded wire and permits wire end or feed-thru terminations. The terminal features four slots for redundant wire terminations and strain relief. The terminals are installed in random positions or in rows on the edge of a pc board either by hand tool, semiautomatic or fully-automatic machines.


Thermal Shock Data for

Wire-to-Board Terminal

The terminal is compact in design and readily adaptable to a wide variety of materials and plating selections, as well as terminating techniques such as daisy chaining, single ending and on-board jumping and programming.

The .100 [2.54] wide terminal has an overall height of approximately .210 [5.33] and occupies less than .120 x .130 [3.05 x 3.3] of board area and accommodates wire sizes 28-24 AWG [0.09-0.2 mm²] (see table). The terminals are supplied in both loose piece and strip form and are easily assembled to the pc board in conjunction with on-board components prior to wave soldering. With the terminal being an integral part of the board, insertion of the unstripped wire into the four insulation displacement slots is accomplished by use of a simple hand tool (see table).

21




Catalog 82159	Dimensions are in inches and	Dimensions are shown for	USA: 1-800-522-6752	South America: 55-11-2103-6000
Revised 12-07	millimeters unless otherwise	reference purposes only.	Canada: 1-905-470-4425	Hong Kong: 852-2735-1628
	specified. Values in brackets	Specifications subject	Mexico: 01-800-733-8926	Japan: 81-44-844-8013
www.tycoelectronics.com	are metric equivalents.	to change.	C. America: 52-55-1106-0803	UK: 44-8706-080-208

Printed Circuit Board Terminals and Disconnects

QUADRA-MATE Wire-to-Printed Circuit Board Terminal (Continued)

Typical Assembly Material and Finish

Terminal – Brass, tin plated over copper underplate Other plating and terminal materials available. Contact Tyco Electronics. **Max. Ins. Dia.** — .060 [1.52]




Wire	Size (AWG) over m	m ²		;	
7-Strand	Solid	Fused	Loose Piece	Strip	Wire to Term. Hand Tool
24 0.2	24-26 0.2-0.13	26 0.13	62977-1	63007-1	
26 0.14	26-28 0.13-0.08	28 0.09	63024-1*	63003-1*	274377-1 (Heavy Duty)
28 0.09	28 0.08	28 0.09	63025-1*	63004-1*	

Semiautomatic insertion of strip parts to pc board is accomplished using mini-insertion head, Part No. 803371-1 in "U" frame applicator, Part No. 691679-1. For more sophisticated application equipment including cable makers and C.N.C. machines, contact Tyco Electronics.

* Available upon request, contact Tyco Electronics.

Recommended PC Board Applications

Note: Wire slots are designed to terminate wire sizes and types with polyvinyl chloride (PVC) insulation, Class 12B. For other wire sizes and insulation types, contact Tyco Electronics for application approval.



Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

22					
	Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise	Dimensions are shown for reference purposes only.	USA: 1-800-522-6752 Canada: 1-905-470-4425	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628
	www.tycoelectronics.com	specified. Values in brackets are metric equivalents.	Specifications subject to change.	Mexico: 01-800-733-8926 C. America: 52-55-1106-0803	Japan: 81-44-844-8013 UK: 44-8706-080-208

Electronics

Printed Circuit Board Terminals and Disconnects

Printed Circuit Board Disconnects

Product Facts


- Quick connect or disconnect
- Automatic or semiautomatic application of strip form receptacles to wire
- Receptacles for wire size range 28 AWG [0.08] thru 17 AWG [1.0] and tinsel wire
- Automatic or semiautomatic insertion of strip form pins to printed circuit boards
- Solid or formed pins, singleor double-sided printed circuit board capability
- Choice of materials and platings

Technical Documents Product Specification 108-1025 108-1059

Application Specification 114-1008

Instruction Sheets

408-7850 408-7951 408-7963 408-7698 408-7850 408-7377 408-7345



Tyco Electronics printed circuit disconnect embodies the dual features of automation and the ability to make quick wiring changes. The special formed pins, available in .058 [1.47] and .093 [2.36] diameters, can be inserted in a printed circuit board quickly and reliably by fully automatic or semiautomatic machinery.

All receptacles feature a precision wire crimp with an insulation crimp for high mechanical strength. A variety of wire and insulation ranges are available as listed. The combination of the pin and receptacle enables users to bring a variety of wires to a printed circuit board and offers the capability of a quick connect or disconnect. The product is ideal for use in prototype and production applications, particularly where wiring changes or rapid pc board interconnections are required. Specific users include radio, television, test equipment, computer and business machine industries.

The solid pin family, in .058 [1.47] diameter, is attached manually; its knurled edge retains it mechanically in the board until soldering is complete. All pins must be soldered to insure mechanical and electrical reliability. Pins may be used for either single or doublesided pc boards. The receptacles are applied quickly and efficiently to wire using semiautomatic AMP-O-LECTRIC or fully automatic AMPOMATOR machines.


Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

23



.058 [1.47] Diameter Solid Pins


Туре	Hole	Pc Board	Dimensions			Material	Part Nos.
	Diameter	Thickness	Α	В	С	and Finish	Loose Piece
А	.062059 1.57-1.50	.125 3.18	.195 4.95	.385 9.78	.110 2.79	Brass, Tin	3-60753-2
А	.062059 1.57-1.50	.0312 0.79	.195 4.95	.260 6.60	.110 2.79	Brass, Tin	3-60839-1

.058 [1.47] Diameter Formed Pins

T	Hole	Pc Board		Dimensio	ns	Material	Part	Nos.	Insertion
Туре	Diameter	Thickness	Α	В	С	and Finish	Strip Form	Loose Piece ¹	Head
в	.050046	.063 or .094	.210	.360	.095	Phos. Brz., Pre-Tin	60802-2	60803-2	904554-1
В	1.27-1.17	1.60 or 2.39	5.33	3 9.14 2.41 Ph	Phos. Brz., Gold ²	3-60802-1	3-60803-1	904554-1	
						Phos. Brz., Pre-Tin	60809-1	60874-1	904554-1
В	.062058 1.57-1.47	.063 or .094 1.60 or 2.39	.210 5.33	.360 9.14	.095 2.41	Phos. Brz., Gold ²	3-60809-2	3-60874-2	904554-1
	1.57-1.47	1.00 01 2.03	5.55	5.14	2.41	Phos. Brz., Tin	60809-4	_	904554-1
В	.070066 1.78-1.68	.063 or .094 1.60 or 2.39	.210 5.33	.360 9.14	.095 2.41	Phos. Brz., Pre-Tin	60813-1	61018-1	904554-1
С	.050046 1.27-1.17	.063 or .094 1.60 or 2.39	.210 5.33	.360 9.14	.095 2.41	Phos. Brz., Gold ³	61038-1	61067-1	904554-1
D	.073067	.063	.210	.310	.095	Phos. Brz., Pre-Tin	60824-1	61097-1	904554-2
D	1.85-1.70	1.60	5.33	7.87	2.41	Phos. Brz., Gold ²	3-60824-2	3-61097-2	904554-2
E	.050046 1.27-1.17	.063 1.60	.210 5.33	.310 7.87	.095 2.41	Phos. Brz., Gold ³	640967-2	_	904554-2
E	.061055 1.55-1.40	.047 1.19	.210 5.33	.310 7.87	.095 2.41	Phos. Brz., Pre-Tin	641944-1	_	_
-	.061055	.063	.210	.310	.095	Phos. Brz., Pre-Tin	60973-1	640394-1	904554-2
Е	1.55-1.40	1.60	5.33	7.87	2.41	Phos. Brz., Gold ²	3-60973-2	_	904554-2

1Use Insertion Tool Part No. 689141-1 for Loose Piece Pins 2.000030 [0.00076] gold plated 3.000030 [0.00076] gold plated in disconnect area **Note:** All above formed pins are made from .010 [0.25] thick material


.093 [2.36] Diameter Formed Pins



Hole	Pc Board	Dimensions		ons	Material	Part	Insertion	
Diameter	Thickness	Α	В	С	and Finish	Strip Form	Loose Piece	Machine
.073067 1.85-1.70	.063 1.60	.305 7.75	.410 10.41		Phos. Brz., Pre-Tin	61137-1	350491-1	904558-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

24 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise Dimensions are shown for reference purposes only. Specifications subject USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 specified. Values in brackets www.tycoelectronics.com to change. are metric equivalents.



.058 [1.47] Diameter

	Wire S	ize Range	Insulation	Dime	nsions			Part N	los.	
Туре	AWG	mm ²	Diameter	A	В	Material and Finish	Strip Form ³	Loose Piece	Hand Tool	Insertion ^s Head
А	28-26	0.08-0.15	.035045 0.89-1.14	.155 3.94	.380 9.65	Phos. Brz., Pre-Tin	60354-7	—	—	
						Phos. Brz., Gold1	60888-2	60983-1		450000 4
А	26-22	0.15-0.4	.035065	.155		Phos. Brz., Pre-Tin	60888-1	60983-2	90131-4	452383-1
~	20 22	0.10 0.4	0.89-1.65	3.94 9.65	Be. Cu., Tin	60888-3	60983-4	90131-4		
						Be. Cu., Gold1	60888-4	60983-3		
А	26-20	0.15-0.6	.040110 1.02-2.79	.155 3.94	.395 10.03	Be. Cu., Tin	350196-14	_	_	_
						Phos. Brz., Pre-Tin	60598-3	60789-1		
•	04.00	0.2-0.6	.045070	.155	.380	Be. Cu., Tin	60598-4	60789-2	01507.1	450000
A	24-20	0.2-0.6	1.14-1.78	3.94	9.65	Phos. Brz., Gold	60598-7	60789-3	91507-1	452383-1
						Be. Cu., Gold ²	60598-9	60789-8		
А	24-20	0.2-0.6	.060090	.155	.395	Phos. Brz., Pre-Tin	60940-1	60986-1	90221-2	
~	24 20	0.2 0.0	1.52-2.29	3.94	10.03	Be. Cu., Tin	60940-2	_	90221-2	_
В	22-17	0.4-1.0	_	.155 3.94	.300 7.62	Be. Cu., Tin	640259-1	640024-1	90314-1	453850-1
С	26-22	0.15-0.4	.035065	.160	.330	Be. Cu., Gold ²	61513-1	350189-2		
č		0.10 0.4	0.89-1.65	4.06	8.38	Phos. Brz., Pre-Tin	61513-2	350189-1	90131-4	
						Be. Cu., Gold ²	61119-1	61276-1		
С	24-20	0.2-0.6	.045070 1.14-1.78	.160	.330 8 38	Phos. Brz., Pre-Tin	61119-2	61276-2	91507-1	453850-1
			1.14-1.70	4.06 8.38 —	Be. Cu., Tin	61119-3	61276-3			
D	Tinse	l Wire	.030040 0.76-1.02	.155 3.94	.380 9.65	Phos. Brz., Pre-Tin	350393-1	_	_	

.093 [2.36] Diameter

	Wire S	ize Range	Insulation	Dimensions				Part Nos.			
Туре	AWG	mm ²	Diameter	A	B	Material and Finish	Strip Form ³	Loose Piece	Hand Tool	Insertion Head	
A	28-26	0.08-0.15	.032057 0.81-1.45	.255 6.48	.545 13.84	Phos. Brz., Tin	35022-1	_	_	452383-1	
А	22-18	0.4-0.8	.060110 1.52-2.79	.255 6.48	.550 13.97	Phos. Brz., Tin	61291-1	61260-1	90135-2	452383-3	
В	22-18	0.3-0.9	—	.255 6.48	.435 11.05	Phos. Brz., Tin	350015-2	—	—	435850-1	

1.000030 [0.00076] gold plated 2.000015 [0.00038] gold plated

².00015 [0.00038] gold plated
 ³Machine applied; applicator required. For machine and applicator part numbers, call the Tooling Assistance Center at 1-800-722-1111.
 ⁴These receptacles have an overlap insulation crimp.
 ⁵Use the listed insertion head with either the Comp-U-Sert or II Insertion Machine No. 122300-1 or MIS Bench Machine No. 66280-4.
 Note: Part Nos. 350221-1, 61291-1 and 61260-1 are made from .012 [0.30] thick material. All other receptacles are made from .010 [0.25] thick material.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise Dimensions are shown for reference purposes only. Specifications subject USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 specified. Values in brackets www.tycoelectronics.com are metric equivalents. to change.

25


Printed Circuit Board Terminals and Disconnects

AMP EDGE Single Lead Printed Circuit Terminals

Product Facts

- Friction fitting, quick connect/disconnects no insertion nor extraction tools required
- Excellent vibration and shock resistance
- Accepts wire size range 32-16 AWG [0.03-1.4 mm²]
- Wide choice of materials and finishes
- High-speed machine terminated for volume production at lowest installed cost

Technical Documents Product Specification 108-1011 AMP EDGE Terminals




AMP EDGE Terminals are quick connect/disconnect devices that adjust securely, through friction fitting, to machine slots in the type of board for which they are designed. Friction fitting not only precleans the contact areas, but also provides excellent vibration and shock resistance even under heavy stresses. Firm wire insulation support is a companion factor for positive retention in the board. These terminals, wholly aerated to eliminate moisture traps, may be applied anywhere on the perimeter of the board. They eliminate the need for eyelets and plated-through holes on two-sided boards and can be used back-to-back for commoning circuits.

26					
	Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise specified. Values in brackets	Dimensions are shown for reference purposes only. Specifications subject	USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013
	www.tycoelectronics.com	are metric equivalents.	to change.	C. America: 52-55-1106-0803	UK: 44-8706-080-208

AMP EDGE Single Lead Printed Circuit Terminals (Continued)

Related Product Data Application Tooling — pages 36-38



T	Wire Siz	ze Range	Matarial	Finish	Stock	lus Dis	Board		Dimensions	6	Strip
Туре	AWG	mm ²	Material	Finish	Thk.	Ins. Dia.	Thk.	Α	В	С	Form Part Nos. ⁷
А	32-24	0.03-0.2	Phos. Brz.	Tin	.010 0.25	.020050 0.51-1.27	.062 1.57	.045 1.14	.080 2.03	.153 3.89	61389-21
А	30-22	0.05-0.4	Phos. Brz.	Tin	.010 0.25	.075 1.91	.062 1.57	.046 1.17	.080 2.03	.153 3.89	61455-2 ¹
А	22-20	0.4-0.6	Phos. Brz.	Tin	.010 0.25	.075 1.91	.062 1.57	.050 1.27	.080 2.03	.153 3.89	42263-71
В	22-18	0.4-0.8	Phos. Brz.	Tin	.010 0.25	.080100 2.03-2.54	.062 1.57	.050 1.27	.080 2.03	.153 3.89	61561-2 ²
В	22-18	0.4-0.8	Brass	Tin	.016 0.41	.080100 2.03-2.54	.062 1.57	.052 1.32	.088 2.24	.160 4.06	60156-2 ³
В	22-18	0.4-0.8	Brass	Tin	.016 0.41	.080100 2.03-2.54	.062 1.57	.056 1.42	.088 2.24	.160 4.06	60704-14
С	22-16	0.4-1.4	Brass	Tin	.012 0.30	_	.062 1.57	.046 1.17	.070 1.78	.200 5.08	61782-15
С	22-16	0.4-1.4	Brass	Tin	.012 0.30	_	.062 1.57	.046 1.17	.070 1.78	.200 5.08	61782-26

1(2) dimples outside (.010 high) [0.25]
²(2) dimples inside (.020 high) [0.51]
³(2) dimples inside (.014 high) [0.36]
⁴(2) dimples inside (.005 high) [0.13]
⁵(2) dimples inside (.023 high) [0.58]
⁶(2) dimples inside (.023 high) [0.58], reverse reeled
⁷Machine applicator required. For machine and applicator part numbers, call the Tooling Assistance Center at 1-800-722-1111.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

27

Catalog 82159 Revised 12-07 www.tycoelectronics.com	Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.	Dimensions are shown for reference purposes only. Specifications subject to change.	USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208
---	--	--	---	--


₹_{Тусо} **Electronics**

Printed Circuit Board Terminals and Disconnects

Miniature AMP-IN Terminals

Product Facts

- Eliminates manual preparation of wires prior to soldering into pc boards
- Low applied cost
- Total height above pc board is less than most other components
- Available for 26-10 AWG, [0.15-5.5 mm²]
- Terminal locking lance holds wire in pc board for flow soldering
- Design allows both wire and terminal to be soldered and assures proper solder flow
- Insulation support provides strain relief for wire and protection of solder joint
- Type A terminals will provide both a positive board stop and positive insulation stop
- Type E terminal offers minimum below pc board length



The miniature AMP-IN Terminal is designed not as an electrical terminal but as a mechanical holding device to enhance soldering of hookup wires to printed circuit boards. The combination of terminal and application tooling eliminates costly manual preparation of wires prior to soldering, and positions the wire to achieve reliable solder joints. Movement of the wire during soldering is restricted, providing for proper solder flow.

Technical Documents Product Specification 108-1081

Application Specification 114-1016


Material and Finish

008 phosphor bronze, Pre-tin plated Pc Board Thickness — .062 [1.57]

Catalog 82159 Revised 12-07 Dimensions are shown for reference purposes only. South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 USA: 1-800-522-6752 Canada: 1-905-470-4425 Dimensions are in inches and millimeters unless otherwise specified. Values in brackets Specifications subject Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 www.tycoelectronics.com UK: 44-8706-080-208 are metric equivalents. to change.

28

Miniature AMP-IN Terminals (Continued)





	AWG	mm ²	Diameter	Diameter	Board (Ref.)	Part Nos.3
А	22-18	0.3-0.9	.060110 1.52-2.79	.072±.003 1.83 ^{±.0.08}	.100 2.54	3-794121-1
A	26-22	0.12-0.4	.040110 1.02-2.79	.055±.004 1.40±0.10	.100 2.54	3-794122-1
	18-14	0.8-2.0	.090150 2.29-3.81	.125±.003 3.18±0.08	.125 3.18	3-770060-1
В	12	3.0	.090150 2.29-3.81	.125±.003 3.18 ^{±0.08}	.125 3.18	3-794013-1
	10	5.5	.200 5.08	.150 3.81 Ref.	.125 3.18	3-794037-1
0	22-18	0.4-0.8	.060110 1.52-2.79	.073±.004 1.85±.0.10	.100 2.54	3-640311-1
С	26-22	0.15-0.4	.040100 1.02-2.54	.055±.004 1.40 ^{±0.10}	.100 2.54	3-640401-1
	22-18	0.4-0.8	.060110 1.52-2.79	.073±.004 1.85±.0.10	.125 3.18	3-350566-1
D	26-22	0.15-0.4	.060100 1.52-2.54	.055±.004 1.40±0.10	.135 3.43	3-640108-1
	26-22	0.15-0.4	.040070 1.02-1.78	.125± .003 3.18 ^{±0.08}	.125 3.18	3-640663-1
E	22-18	0.8-0.4	.060110 1.52-2.79	.072±.004 1.83±.0.10	.090 2.29	3-770565-2

Notes: 1. Higher tensile available with nose crimp type C.
 2. Not available in loose piece.
 3. No hand tools available.
 4. Machine applied applicator required. For machine and applicator part numbers, call the Tooling Assistance Center at 1-800-722-1111.

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise Dimensions are shown for reference purposes only. Specifications subject specified. Values in brackets www.tycoelectronics.com are metric equivalents. to change.

29

Printed Circuit Board Terminals and Disconnects

Low Profile Miniature AMP-IN Connectors

Product Facts

- Connector housing provides gang insertion into pc board
- Housing insulates and provides short-circuit protection between contacts
- Housings are available in 2 to 15 positions for .079 [2.01] and 2 to 20 for .098 [2.49] centerline spacing
- Low profile design— .200 [5.08]
- Contacts available for 30-26 AWG [0.05-0.15 mm²] and 26-22 AWG [0.15-0.4 mm²]


Technical Documents

Product Specification— 108-5163

Application Specification-114-5062

Material and Finish

Housing-Nylon, 94V-0 rated Contact—See chart Pc Board Thickness Range— .047-.062 [1.19-1.57]



Low Profile Miniature AMP-IN Connectors provide an easy means of gang inserting leads into printed circuit boards. The design of the crimp snap-in contact aids in locating the pc board hole and inserting the contact into that hole.

The low profile housing allows compactness of leads while providing insulation between them to prevent short-circuits. Housings are available in 2 to 15 positions for .079 [2.01] centerline spacing and 2 to 20 positions for .098 [2.49] centerline spacing.

Contacts come in 26-22 AWG [0.15-0.4 mm²] and 30-26 AWG [0.05-0.15 mm²] with insulation support crimp to provide strain relief. They accommodate a board thickness of .047 [1.19] to .062 [1.57].

Wire S	ize Range	Insulation	Hole	Material	Contact	Part No.	Hand Tool	
AWG	mm ²	Diameter	Diameter	and Finish	Strip Form ³	Loose Piece	Part Nos.	
30-26	0.05-0.15	.043055	.031 0.79	Brass, Pre-Tin	172781-1	172797-1		
30-20	0.05-0.15	1.09-1.40	.039 0.99	Brass, Tin	172781-4	172797-4	755405-1	
26-22 0.	0 15-0 4	.055059	.031 0.79	Brass, Tin	172782-5	_		
		1.40-1.50	.039 0.99	Brass, Tin	172782-7	_	755405-1	

Notes: 1. Refer to pages 36-38 for application tooling.

Use Extraction Tool Part No. 753760-1.
 Machine applied applicator required. For machine and applicator part numbers, call the Tooling Assistance

Center at 1-800-722-1111.

	No. of	.079 [2.01] Centerline		.098 [2.49] Centerline	
	Positions	Α	Part Nos.	Α	Part Nos.
	2	.189 4.80	172890-2	.236 5.99	172520-2
	3	.268 6.81	172890-3	.335 8.51	172520-3
	4	.346 8.79	172890-4	.433 11.00	172520-4
	5	.425 10.80	172890-5	.532 13.51	172520-5
	6	.504 12.80	172890-6	.630 16.00	172520-6
	7	.583 14.81	172890-7	.729 18.52	172520-7
	8	.661 16.79	172890-8	.827 21.01	172520-8
	9	.741 18.82	172890-9	.926 23.52	172520-9
A [3.51]	10	.820 20.83	1-172890-0	1.024 26.01	1-172520-0
	11	_	—	1.123 28.52	1-172520-1
.079 [5.00]	12	.977 24.82	1-172890-2	1.221 31.01	1-172520-2
[2.01]	13	—	—	1.320 33.53	1-172520-3
	14	_	_	1.418 36.02	1-172520-4
	15	1.214 30.84	1-172890-5	1.517 38.53	1-172520-5
Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.	20	_	_	2.010 51.05	2-172520-0

30

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Printed Circuit Board Terminals and Disconnects

Test Probe Receptacles

Product Facts

- Leg mounts are "V" shaped to promote solder wicking and consistent fillets
- Receptacle is recessed in housing to prevent shorting or flashover
- Probe may be inserted in either end of test probe receptacle except Type C
- Housing color is molded, not dyed
- Accepts .080±.001 [2.03^{±0.025}] probes

Material and Finish

Housing—Nylon type 6/6 Contact—Beryllium copper Receptacle and Legs—Brass, ASTM B36, Alloy 6 Contact Plating—See table below

Technical Documents Product Specification—

108-1082 Receptacle, Test Probe

Performance Characteristics Insulation Resistance— 10,000 megohms

Retention Value—

Color Suffix Table Suffix Dash Number -0 -1 -2 -3 -4 -5 -6 -7 -8 -9

16oz. [4.45 N]



The Tyco Electronics line of Test Probe Receptacles is designed to pro-vide low-cost test probe capability of circuits on pc boards, with-out interruption of operating currents, with precise reliability.

Receptacles are available with either two or three mounting

.561 [14.25]

.160 [4.06]

Туре А

Туре С

B Max

.090 [2.29]


are not part of the live testing circuit. Receptacles are also available either in the standard height, or in a taller height (to permit probing at any position on the board where clearance to probe is necessary). The three-leg mount gives maximum stability. The two-leg mount yields maximum density.


The present line of test probe receptacles fits a range of board thicknesses from 1/32 to 1/8 depending on the length of the receptacle legs. The legs mount in .052 [1.32] diameter holes.

.156

B Max

Α







Operating Temperature— 55°C to 85°C [131°F to 185°F]

*Mounting hole location for .050-.054 [1.27-1.37] dia. holes

.300* [7.62]

156

	Turne	Contact		Dimensions		Housing	Part Nos.*	
	Туре	Finish	Α	В	С	Colors	Part Nos."	
		Bright Tin	.130 3.30	.230 5.84	.138 3.51	See Table	1-521799-x	
		Silver	.130 3.30	.230 5.84	.138 3.51	See Table	2-582118-x	
		Gold	.130 3.30	.230 5.84	.138 3.51	See Table	3-582118-x	
	A	Gold	.130 3.30	.230 5.84	.138 3.51	Natural	6-582118-9	
Housing		Bright Tin	.130 3.30	.467 11.86	.375 9.53	See Table	1-521800-x	
Color		Gold	.130	.467	.375	See Table	3-582340-x	
Black		Ciola	3.30	11.86	9.53	Oce Table	0 302040	
Brown Red		Gold	.130 3.30	.230 5.84	.138 3.51	See Table	3-582119-x	
Orange Yellow	В	Gold	.130 3.30	.467 11.86	.375 9.53	See Table	3-582120-x	
Green Blue	С	Gold	.130 3.30	.230 5.84	.138 3.51	See Table	350180-x	
Violet Gray		Gold	.180 4.57	.230 5.84	.138 3.51	See Table	1-380736-x	
White	D	Bright Tin	.180 4.57	.230 5.84	.138 3.51	Green	3-521801-5	

.100 [2.54]

.200* [5.08]

*Part numbers with a numerical suffix are only for the specific color listed in the chart.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 Catalog 82159 Revised 12-07 Dimensions are shown for Dimensions are in inches and USA: 1-800-522-6752 reference purposes only. Canada: 1-905-470-4425 millimeters unless otherwise specified. Values in brackets Specifications subject Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 www.tycoelectronics.com are metric equivalents. to change.

31

Printed Circuit Board Terminals and Disconnects

Power Taps

Product Facts

- ACTION PIN contacts eliminate soldering
- Provides high current, separable connection to pc board traces
- Wire-to-board connection using common terminals
- All metal-to-metal assembly for long-term integrity
- Standard DIP outlines (.300 x .100 [7.62 x 2.54]), 10 positions, and .250 x .125 [6.35 x 3.18], 6 and 10 positions, plus high current versions on .400 x .200 [10.16 x 5.08] footprint in 4 and 6 positions, .300 x .100 [7.62 x 2.54] in 8 positions, and both 2 and 3 position in-line .100 [2.54] tab taps
- Low resistance interface
- Internally threaded tap to secure screw to terminal
- Anti-rotational embossments hold wire and terminal in place
- Standard Power Taps rated at 2.5 amps per pin-6 position 15 amps, 10 position 25 amps current carrying capability

Taps are designed for the growing need for power to printed circuit board applications required in today's electronic industry. The taps provide a high current, separable connection to a pc board. Pin configuration is of the standard DIP outline with


Tyco Electronics Power

ACTION PIN contacts provide a low resistance interface with tin platedthrough holes in the pc board, thereby eliminating the need for soldering

The variety of available power taps allow for various installation schemes. The Uninsulated Tap and Low Profile Tap can be used in bus bar pattern. The High Profile and Low Profile Taps offer insulation protection from other components. The High Current versions provide a greater power

density option with current ratings from 10 amps on the 2 position in-line .250 [6.35] tab tap up to 40 amps on the 8 position dual .250 [6.35] tab tap.

All Tyco Electronics Power Tap configurations are easily inserted into the pc board with a simple



- High Current Power Taps rated at up to 5 amps per pin-2 position 10 amps, 3 position 15 amps,
 - 4 and 6 position 20 amps and 8 position 40 amps

.300 x .100 [7.62 x 2.54] or .250 x .125 [6.35 x 3.18] for the Standard versions, plus .400 x .200 [10.16 x 5.08], .300 x .100 7.62 x 2.54. and in-line spacing for the High Current versions.

Tyco Electronics o customer supplied tool.

32

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

₹_{Тусо} Électronics

Printed Circuit Board Terminals and Disconnects

Standard Power Taps

Standard Insulated Power Tap **Material and Finish**

Connector Body and Lid—Nylon, 105°C 94V-0 rated **Contact**—Copper alloy, bright tin-lead plated and matte tin plated Screw—Plated steel

Electrical and Mechanical Characteristics


Resistance-2 milliohms, max. (stud hole to ACTION PIN contact) Insertion Force—40 lbs. [177.9 N], max. per pin Retention Force-7 lbs. [31.1 N], min. per pin


Technical Documents Product Specification

108-11030 Tap, Power Distribution

Application Specification 114-11000 Tap, Power Distribution

Handbook 5697 Guide to Application of ACTION PIN Connectors





Тар	Pcb	Description	Screw	Part Nos.		
Version	Thickness	Description	Hole Size	Tin-Lead	Tin	
High Profile	.062125 1.57-3.18	Housing and contact assembled without screw ¹	6-32	55557-3♦	5055557-3	
High Profile	.062125 1.57-3.18	Housing and contact assembled with screw ^{1,2}	6-32	55557-4♦	5055557-4	
Low Profile	.062125 1.57-3.18	Housing and contact assembled with screw ²	6-32	55556-4♦	5055556-4	
Low Profile	.062125 1.57-3.18	Housing and contact assembled with screw ^{2,3}	6-32	55673-2 ♦	5055673-2	
Low Profile	.062125 1.57-3.18	Housing and contact assembled without screw	6-32	55556-3♦	5055556-3	
Low Profile	.062125 1.57-3.18	Housing and contact assembled without screw	M4	55556-9♦	5055556-9	

¹Cover not assembled ²Screw not assembled ³No anti-rotational embossments

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 Catalog 82159 Revised 12-07 Dimensions are in inches and millimeters unless otherwise Dimensions are shown for reference purposes only. Specifications subject USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 specified. Values in brackets www.tycoelectronics.com are metric equivalents. to change.

33

Electronics

Printed Circuit Board Terminals and Disconnects


Standard Power Taps (Continued)

Standard Uninsulated Power Taps

Material and Finish Contact—Copper alloy, post plated bright tin-lead and matte tin plated Screw—Stainless steel, passivated

Electrical and Mechanical Characteristics

Resistance—2 milliohms, max. (stud hole to ACTION PIN contact) Insertion Force—40 lbs. [177.9 N] max. per pin Retention Force—7 lbs. [31.1 N] min. per pin





Size	Pcb		Dimer	sions		Description	Screw	Part N	umber
5120	Thickness	Α	В	С	D	Description	Size	Tin Lead	Tin
.300 x .100	000 405	440	005	100		Without Screw	6-32	55558-3 🔶	5055558-3
7.62 x 2.54	.062125 1.57-3.18	.440 11.18	.325 8.26		.100 .300 2.54 7.62	With Screw	6-32	55558-4 ♦	5055558-4
10 Position	1.57 0.10	11.10	0.20	2.04		Without Screw	6-32	55558-7 🔶 1	5055558-7
.250 x .125 6.35 x 3.18	.062125	.320	.275	.125	.250	Without Screw	6-32	55323-5 ♦	5055323-5
6 Position	1.57-3.18	8.13	6.99	3.18	6.35	With Screw	6-32	55323-9 ♦	5055323-9
.250 x .125 6.35 x 3.18	.062125	.570	.275	.125	.250	Without Screw	6-32	55323-6 ♦	5055323-6
10 Position	1.57-3.18	14.48	6.99	3.18	3.18 6.35	With Screw	6-32	1-55323-0 ♦	1-5055323-0

¹No Anti-rotation Embossments

High Current* Power Taps *Up to 20 amps Material and Finish

Contact—Phosphor bronze, tin-lead and matte tin plated **Screw**—Stainless steel, passivated








Electrical and Mechanical Characteristics

Current Rating—20 amperes max. Insertion Force—40 lbs. [180 N] max. per pin

Retention Force—7 lbs. [30 N] min. per pin



Size	Pcb		Dimer	nsions		Description	Part Number		
Size	Thickness	Α	В	С	D	Description	Tin Lead	Tin	
4 Position	.062125	.358	.431	.200	.400	With Screw	213815-1 ♦	5-213815-1	
4 FOSILION	1.57-3.18	9.09	10.95	5.08	10.16	Without Screw	216906-1 ♦	—	
6 Position	.062125	.358	.431	.431 .100 10.95 2.54	.400	With Screw	213816-1 ♦	5-213816-1	
6 Position	1.57-3.18	9.09	10.95		10.16	Without Screw	216907-1 ♦	_	

¹No Anti-rotation Embossments featured on High Current Taps. Therefore, if application requires, use of Bellville lockwashers with a high surface contact area are strongly recommended.

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

34					
	Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise	Dimensions are shown for reference purposes only.	USA: 1-800-522-6752 Canada: 1-905-470-4425	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628
	www.tycoelectronics.com	specified. Values in brackets are metric equivalents.	Specifications subject to change.	Mexico: 01-800-733-8926 C. America: 52-55-1106-0803	Japan: 81-44-844-8013 UK: 44-8706-080-208

Printed Circuit Board Terminals and Disconnects

High Current* Power Taps

Designed to mate with FASTON and Positive-Lock Receptacles


*Up to 5 amps per pin

Material and Finish

Contact—Phosphor bronze, post plated tin-lead, except as noted in chart Screw—Stainless steel, passivated Washer—Stainless steel

Electrical and Mechanical Characteristics

Current Rating—5 amps max. per pin Insertion Force—40 lbs. [180 N] max. per pin



Style	Pcb		Dimer	nsions		Configuration	Description	Part	Receptacle
Style	Thickness	A B C		С	D	Configuration	Description	Number	Mating
Ι	.062 x .125 1.57 x 3.18	.200 5.08	.531 13.49	_	_	.250 x .032 6.35 x 0.81 Tab	With Hole	216926-1 ♦	Positive Lock
П	.062 x .125 1.57 x 3.18	.100 2.54	.531 13.49	_	_	.250 x .032 6.35 x 0.81 Tab	With Hole	216843-1 ♦	Positive Lock
Ш	.062 x .125 1.57 x 3.18	.400 10.16	.200 5.08	.531 13.49	.431 10.95	1- .250 x .032 6.35 x 0.81 Tab 2- .110 x .032 2.79 x 0.81 Tab	With Hole Without Washer Without Screw	216905-1♦ ¹	Positive Lock
IV	.125	.300	.100	.485	.500	2- .250 x .032 6.35 x 0.81 Tab	With Dimple	5167892-3 ²	FASTON Receptacle
IV	3.18	7.62	2.54	12.32	12.7	6.35 x 0.81 ^{Tab}	With Hole	167892-6 ²	Positive Lock

¹No Anti-rotation Embossments featured on High Current Taps. Therefore, if application requires product supplied without washer and screw, use of lockwashers with a high surface contact area are strongly recommended.

²Phosphor bronze, post plated matte tin.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


Catalog 82159Dimensions are in inches and
millimeters unless otherwiseDimensions are shown for
reference purposes only.USA: 1-800-522-6752
Canada: 1-905-470-4425South America: 55-11-2103-6000
Hong Kong: 852-2735-1628www.tycoelectronics.comare metric equivalents.Dimensions are shown for
reference purposes only.USA: 1-800-522-6752
Canada: 1-905-470-4425South America: 55-11-2103-6000
Hong Kong: 852-2735-1628www.tycoelectronics.comare metric equivalents.Specifications subject
to change.Mexico: 01-800-733-8926
C. America: 52-55-1106-0803Japan: 81-44-844-8013
UK: 44-8706-080-208

35

₹_{Tyco} **Électronics**

Printed Circuit Board Terminals and Disconnects

Application Tooling/PCB Layout



	-	C				Tuno		Dimensions	
				H	в.	Туре	Α	В	С
Recommended Pc Board Layout	 ⊕	Ð	Đ	Ð	 	4 Position	.400 10.16	.200 5.08	.200 5.08
Drilled Hole Diameter—	Ť	Ŭ	Ũ	Ũ	Å	6 Position	.400 10.16	.100 2.54	.200 5.08
.063±.001 [1.60±0.03] Cu Thickness—	Ð	Ð	Ð	Ð	⊕ <u></u> †	I	—	.200 5.08	.200 5.08
.001003 [0.03-0.08]						II	_	.100 2.54	.200 5.08
Sn Thickness— .0002 min.[0.004 min.]							.400 10.16	.200 5.08	.200 5.08
Finished Hole— .055061 [1.39-1.54]						IV	.300 7.62	.100 2.54	.300 7.62
After Reflow—									

Installation Tooling

.054-.061 [1.36-1.54]

Use with Hand Press Part No. 677430-1

High Current Power Tap

Turne	Part Number	Tooling Part Number		
Туре	Fait Nulliber	Upper Tool	Lower Tool	
4 Position	216906-1	432848-1	433600-2 or	
6 Position	216907-1	432040-1	432130-2	
Style I	216926-1	432845-1	433600-2 or	
Style II	216843-1	432045-1	432130-2	
Style III	216905-1	432847-1	433600-2 or 432130-2	
Style IV	5-167892-3 167892-6	432849-1	433600-2 or 432130-2	

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

36					
	Catalog 82159 Revised 12-07	Dimensions are in inches and millimeters unless otherwise	Dimensions are shown for reference purposes only.	USA: 1-800-522-6752 Canada: 1-905-470-4425	South America: 55-11-2103-6000 Hong Kong: 852-2735-1628
	www.tycoelectronics.com	specified. Values in brackets are metric equivalents.	Specifications subject to change.	Mexico: 01-800-733-8926 C. America: 52-55-1106-0803	Japan: 81-44-844-8013 UK: 44-8706-080-208



Printed Circuit Board Terminals and Disconnects

Application Tooling

Fully-automatic machines

AMPOMATOR CLS IV+ Lead-Making Machines, Part Nos. 356500-1, -2



AMP-O-LECTRIC Model "G" Terminating Machines, Part Nos. 354500-1, -9, -11



that measure, cut, strip and terminate single leads. Microprocessor-controlled, and programmed and operated using an easy-to-follow, menu-driven touch-screen. Features include directdrive terminating units with precision crimp height adjustment, fully programmable setups, wire runout and splice detection, and motorized pre-feed with wire straightener. Crimp quality monitoring is also available. For more information, request Catalog 124324.

Part Nos. 1320895-1, -2

AMP-O-MATIC Stripper-

Crimper Machines,



AMP 3K/40 and AMP 5K/40 Terminating Machines



Semiautomatic bench crimping machines that also strip the wire, and are therefore used for terminating jacketed cable. Feature manual precision adjustment of crimp height, keyed strip blades for faster, more accurate setups, and an efficient scrap removal system. All adjustments can be made from the front of the machines without special tools. Available with crimp quality monitoring.

For more information, request Catalog **65004**.

As a value oriented terminator, the AMP 3K/40 and AMP 5K/40 terminators are designed for customers that require the increased output and quality of a semiautomatic machine at a competitive price. By incorporating the most commonly requested features as stan-dard and offering a long list of optional equipment, these terminators offer flexibility to meet the specific needs of various applications at the lowest possible cost. For more information, request Catalog **1654856**

For more information, request Catalog **65828**.

Semiautomatic bench

machines for crimping

reeled terminals and con-

tacts, featuring a quiet and reliable direct motor drive,

microprocessor controls for

lighting designed for operator convenience. All models

ease of setup and operation, and guarding and

are equipped with either

sion adjustment of crimp height. Machine-mounted

sensors are available for

crimp quality monitoring

using conventional minia-

manual or automatic preci-

Optional Stripping Module for the AMP 3K/40, AMP 5K/40 and AMP-O-LECTRIC Model "G" Terminating Machines



The combination of the Stripping Module with the AMP-O-LECTRIC Model "G" Terminator or the AMP 3K/40, and AMP 5K/40 terminating machines provides an economical, proficient method of stripping wire and crimping terminals on the same machine. Wires are stripped moments before crimping, meaning there is virtually no chance of damaging wire conductors during handling or storage. Once the wire is fed into the start sensor, the Stripping Module does the rest, improving placement accuracy.

For more information, request Catalog **1309085**.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 37

Electronics

Printed Circuit Board Terminals and Disconnects

Application Tooling (Continued)




CERTI-CRIMP Straight

Premium grade hand tools

Action Hand Tools (SAHT)



featuring ratchet control to provide complete crimp cycle. Die sets close in a straight line. Include a contact locator and wire stop, plus an insulation crimp adjustment lever, when applicable. Approximate weight 1.3 lb [0.59 kg] For more information, request Catalog **65780**.



Printed Circuit Board Terminals and Disconnects

Application Tooling (Continued)

AMP-O-MATIC "U" Frame Machine Part No. 691679-1 (Installs Board Mount Receptacles)

Product Specifications

Weight - 50 lbs. **Width** — 18 Height — 23 **Depth** — 19 Air Supply — 80 psi Electrical Power — 115 VAC, 60 Hz

These insertion machines install contacts into printed circuit boards at rates to 2000 per hour. A spotlight highlights the insertion area and a lower tooling assures precise board location. The machines are actuated by a foot pedal and are bench mounted.





Microprocessor-controlled X-Y positioning table inserts a variety of products into pc boards, including .0252 stamped or bandoliered posts, mini-spring sockets, and FASTON tabs. Insertion heads for various products are interchangeable, and can be used with bench machines. Controlled, programmed and operated using an interactive touchscreen. Options include double-action clinch tooling, powered dereeler, splice run-out detector, take-up winder for paper tape, and scrap chopper. For more information, request Catalog 296059.

Modular Insertion System (MIS) Bench Machines, 217600 Series, 662820 Series (shown)

Strip Form Part Number	Insertion Head Part Number
60802-1	904554-1
60802-2	904554-1
60809-1	904554-1
60809-2	904554-1
60809-4	904554-1
60813-1	904554-1
61038-1	904554-1
60824-1	904554-2
60824-2	904554-2
640967-2	904554-2
641944-1	904554-2
60973-1	904554-2
60973-2	904554-2
61137-1	904558-1



Bench machines for inserting a variety of products into pc boards. Uses the same interchangeable insertion heads as the Comp-U-Sertor II Machines. Series 217600 features a manually-operated X-Y positioning fixture and locator spotlight. The machine cycles when the board hole is placed on the anvil and both triggers on the dual handles attached to the X-Y fixture are depressed. Series 662820, without board fixturing, cycle automatically when the hole is properly located. A stabilizing disk over the anvil helps keep the board level. For more information, request Catalog **296059**.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 82159 Revised 12-07

www.tycoelectronics.com

millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are in inches and Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

39

Printed Circuit Board Terminals and Disconnects

Part Number Index

Note: This index lists all cataloged parts by base no. only. Complete part nos. (with prefixes and/or suffixes) are shown on the page(s) indicated.

Part No.	Page	Part No.	Page	Part No.	Page
35022	25	63024	22	360041	13
42263	27	63025	22	360042	13
55323	34	63066	9	380736	31
55556	33	63067	9	432130	36
55557	33	63525	12	432845	36
55558	34	63566	5	432847	36
55673	33	63572	5	432848	36
60156	27	63603	12	432849	36
60284	11	63650	9	433600	36
60354	25	63755	9	435850	25
60598	25	63756	14	452383	25
60704	27	63794	14	453850	25
60753	24	63824	10	467322	7
60789	25	63838	12	521382	
60802	24, 39	63839	9	521384	16
60803	24, 85	63849	10	521799	31
60809	24, 39	63860	13	521800	31
60813	24, 39		10		31
		63862		521801	
60824	24, 39	63900	9	552699	18, 19, 20
60839	24	63949	10	552714	20
60874	24	63950	10	553593	19
60888	25	63951	11	553594	19
60940	25	63952	11	553595	19
60973	24, 39	63968	11	554935	18, 20
60983	25	63969	11	582118	31
60986	25	63982	13	582119	31
61018	24	63986	9	582120	31
61038	24, 39	63994	11	582340	31
61067	24	90131	25	640024	25
61097	24	90135	25	640108	29
61119	25	90221	25	640259	25
61134	14	90314	25	640311	29
61137	24, 39	91507	25	640394	24
61260	25	122300	39	640401	29
61276	25	167892	35, 36	640663	29
61291	25	172520	30	640967	24, 39
61389	27	172781	30	641944	24, 39
61455	27	172782	30	662820	39
61513	25	172797	30	691679	39
61543	12	172890	30	725963	14
61561	27	213815	34	725996	14
61782	27	213816	34	755405	30
61907	12	216843	35, 36	770060	29
61968	12	216905	35, 36	770565	2
62111	7	216905	34, 36	794013	
62172	7	216908		794013	28
			34, 36		
62199	7	216926	35, 36	794121	29
62221	12	217600	39	794122	29
62395	14	230549	20	853439	5
62403	12	230707	19	904554	24, 39
62409	9	231279	20	904558	24, 39
62411	11	231890	20	904608	5
62437	14	274377	22	928814	11
62650	9	350015	25	1217056	ç
62669	14	350180	31	1217057	12
62745	7	350189	25	1217061	13
62751	7, 11	350196	25	1217062	13
62806	7, 11	350393	25	1217080	11
62977	22	350491	24	1217107	11
63003	22	350566	29	1217124	13
63004	22	354500	37	1217125	10
63007	22	356500	37	1217126	10

40

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for
reference purposes only.USA: 1-800-522-6752
Canada: 1-905-470-4425
Mexico: 01-800-733-8926
C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Printed Circuit Board Terminals and Disconnects

Part Number Index (Continued)

Part No.	Page	Part No.	Page	Part No.	Page
1217127	10	1217421	10	1742254	18, 19, 20
1217131	12	1217514	14	1742255	18, 19, 20
1217136	10	1217566	9	1742361	13
1217137	11	1217577	14	1742362	13
1217156	13	1217754	11	5055323	34
1217167	10	1217756	13	5055556	33
1217169	10	1320895	37	5055557	33
1217180	11	1742188	10	5055558	34
1217332	13	1742253	18, 19, 20	5055673	33

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise respectified. Values in brackets are metric equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

41



Engineering Notes



42

Catalog 82159 Revised 12-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for
reference purposes only.U
C
C
C
N
to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208



Americas

Argentina - Buenos Aires +54-11-4733-2200 +54-11-4733-2211 Phone: Fax:

Brasil – São Paulo Phone: +55-11-3611-1311 Fax: +55-11-3611-0397

(Technical Support) Phone: +905-470-4425 Fax:

> Colombia - Bogota Phone: +57-1-231-9398 Fax: +57-1-660-0206

Canada – Toronto Phone: +905-475-6222 Fax: +905-474-5520

Product Information Center:

+905-474-5525

Mexico – Mexico City Phone: +52-55-1106-0800 +01-800-733-8926 Fax: +52-55-1106-0901

United States - Harrisburg, PA Phone: +717-564-0100 Fax: +717-986-7575 Product Information Center:

(Technical Support) Phone: +800-522-6752 Fax: +717-986-7575

Global Contacts

For Latin/South American
 Countries not shown

 Phone:
 +54-11-4733-2015

 Fax:
 +54-11-4733-2083

Asia/Pacific

Australia – Sydney Phone: +61-2-9554-2600 Fax: +61-2-9502-2556 Product Information Center: (Technical Support)

+61-2-9840-8200 +61-2-9634-6188 Phone: Fax:

India – Bangalore Phone: +91-80-285-40800 Fax: +91-80-285-40820

Indonesia - Jakarta +65-6482-0311 Phone: Fax: +65-6482-1012 Japan – Toyko Phone: +81-44-844-8111 Fax: +81-44-812-3207 Product Information Center: (Technical Support) +81-44-844-8013 +81-44-812-3200 Phone: Fax:

Korea – Seoul Phone: +82-2-3415-4500 +82-2-3486-3810 Fax:

Fax:

Malaysia – Kuala Lumpur Phone: +60-3-78053055 +60-3-78053066 New Zealand - Auckland Phone: +64-9-634-4580 Fax: +64-9-634-4586

Philippines – Makati City Phone: Fax: +632-848-0171 +632-867-8661

People's Republic of China Hong Kong Phone: +852-2735-1628

Fax: +852-2735-0243 Shanghai

+86-21-2407-1588

Phone:

+86-21-2407-1599 Fax: Taiwan – Taipei Phone: +886-2-8768-2788 Fax: +886-2-8768-2268

 Singapore
 – Singapore

 Phone:
 +65-6482-0311

 Fax:
 +65-6482-1012

Thailand - Bangkok Phone: Fax: +66-2-955-0500 +66-2-955-0505

 Vietnam and Indochina –

 Ho Chi Minh City

 Phone:
 +84-8 930-5546

 Fax:
 +84-8 930-3443

Europe/Middle East/Africa

Austria – Vienna Phone: +43-1 90 5 60-0 Fax: +43-1 90 5 60-1333 Fax:

Belgium – Kessel-Lo Phone: +32-16-35-23-00 Fax: +32-16-35-23-52 Fax:

Germany – Bensheim Phone: +49-6251-133-0 Fax: +49-6251-133-1600 **Product Information Center:** (Technical Support) Phone: +49-6251-133-1999 +49-6251-133-1988 Fax:

Lithuania – Vilnius Phone: +370-5-2131-402 Fax: +370-5-2131-403

Netherlands – 's-Hertogenbosch Phone: +31-73-624-62-46 Fax: +31-73-621-23-65 Product Information Center: (Technical Support)

Spain - Barcelona Phone: +34-93-291-0330 Fax: +34-93-201-7879 Product Information Center: (Technical Support): Phone: +34-93-291-0330 Fax: +34-93-200-3779

Sweden – Upplands Väsby Phone: +46-8-50-72-50-00

Phone: +359-2-971-2152 Fax: +359-2-971-2153

Czech Republic – Kurim Phone: +420-5-41-162-111 Fax: +420-5-41-162-223

Denmark - Glostrup Phone: +45-43-480-452 Fax: +45-43-441-414

Egypt – Cairo

Phone: +20-2-29 04 281 Fax: +20-2-41 92 334

Estonia – Tartu

Phone: +372-5138-274 Fax: +372-7400-779

Finland – Helsinki Phone

+358-95-12-34-20 +358-95-12-34-250 Fax:

 France
 Cergy-Pontoise

 Phone:
 +33-1-3420-8888

 Fax:
 +33-1-3420-8600
 Product Information Center: (Technical Support) Phone: +33-1-3420-8943 Fax: +33-1-3420-8623 Fax:

Germany – Langen Phone: +49-6103-709-0 +49-6103-709-1223 Fax:

Germany – Speyer Phone: +49-6232-30-0 Fax: +49-6232-30-2243

Germany - HTS Division - Neunkirchen +49-2247-305-0 +49-2247-305-122 Phone: Fax:

Greece - Athens +30-210-9370-396/397 +30-210-9370-655 Phone: Fax:

Hungary - Budapest +36-1-289-1000 +36-1-289-1010 Phone: Fax:

Ireland - Dublin Phone: +353-1-820-3000 Fax: +353-1-820-9790

Israel – Yokneam Phone: +972-4-959-0508 Fax: +972-4-959-0506

Italy – Collegno (Torino) Phone: +39-011-4012-111 Fax: +39-011-4031116

Phone: +31-73-6246-999 Fax: +31-73-6246-998

Norway - Nesbru Phone: +47-66-77-8886 Fax: +47-66-77-8855

 Poland – Warsaw

 Phone:
 +48-22-45-76-700

 Fax:
 +48-22-45-76-720

 Romania
 – Bucharest

 Phone:
 +40-21-311-3479/3596

 Fax:
 +40-21-312-0574

Russia – Moscow +7-495-926-5506/07/08/09 +7-495-926-5505 Phone: Fax:

Russia – St. PetersburgPhone:+7-812-718-8192Fax:+7-812-718-8193

Slovenia – Ljubljana Phone: +386-1561-3270 Fax: +386-1561-3240

South Africa - Port Elizabeth Phone: +2741-503-4500 Fax: +2741-581-0440

Fax: +46-8-50-72-50-01

Switzerland – Steinach Phone: +41-71-447-0447 Fax: +41-71-447-0444

Turkey - Istanbul

+90-212-281-8181/2/3 +90-212-281-8184 Phone: Fax:

Ukraine - Kiev Phone: +380-044-206-2265 Fax: +380-044-206-2264

United Kingdom - Swindon Phone: +44-8706-080-208 Fax: +44-1793-572-516 **Product Information Center:**
 Freephone
 GB: 0800-267-666

 Phone:
 +44-8706-080-208

 Fax:
 +44-208-420-8081

For Middle East/African Countries
 Not Shown

 Phone:
 +33-1-3420-8866

 Fax:
 +33-1-3420-8300

82159-PDF-LUG-12-07 Printed in the U.S.A.

Tyco Electronics Corporation www.tycoelectronics.com

Tyco Electronics Our commitment. Your advantage.



tycoelectronics.com

Tyco Electronics Corporation Harrisburg, PA



Printed Circuit Board Terminals and Disconnects

