A RESTRICTED BASIS AND IS NOT TO BE U	
High Conductivity Seamless Copper Tube	
Electro-Tin	
2 AWG	31 R Ref
Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	
15/16 in.	
#10	
Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.23±.04 .20±.02 DIA
90°C	
Yes	
BROWN	Wire inspection window
P33	
(10)	
	.12±.02 —
	Electro-Tin 2 AWG Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric 15/16 in. #10 Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. 90 ° C Yes BROWN P33

REVISED WIRE SIZE TO 2 AWG

DESCRIPTION

9/10


DATE

02

REV

JHNUJHNU

BY CHK



ECN

DRAWING NO / CAD FILE

LCAN2-10-CUST