


FLOJET

a xylem brand

D3135H7011AR

*Self-Priming DUPLEX II
Diaphragm Pump 12v dc*

- ◆ Pressure-switch control to run the pump only as needed
- ◆ Intermittent duty
- ◆ Handles Water-like and Viscous Liquids Up to 250 cP
Chemical-resistant
- ◆ Polypropylene pump head for long life
- ◆ Internal bypass for excellent performance range
- ◆ Built in back-flow preventer
- ◆ Heavy duty ball bearing drive system.
- ◆ Can run dry without damage and handle liquids up to 140°F (60C).
- ◆ Self-priming from dry capability up to 1.5m. Pump may be located above the liquid level.



CONNECTIONS: 9.5mm (3/8") NPT.

PRESSURE SWITCH SETTINGS:

Cuts in at 5.8 bar (85 psi)

Cuts out at 6.8 bar (100 psi)

MATERIALS OF CONSTRUCTION:


Pump head: Glass-filled Polypropylene

Diaphragm: Santoprene®

Valves: EPDM

OUTPUT:

Up to 8 litres/minute (1.8 gallons/minute).



FUSE SIZE: 10 amp

WEIGHT: 2.3 Kg

